



Product: [9223](#)

Audio Coax, Low Noise, 22 AWG Str TC, Foil + 95% TC Brd, PVC Jkt

Product Description

Audio Coax, Low Noise, 22 AWG (7x30) Tinned Copper Conductor, Inner PE Conductive Layer, PE Insulation, Duobond® II + 95% Tinned Copper Braid Shield, PVC Jacket

Technical Specifications

Product Overview

Suitable Applications:	Low noise microphone, Analog audio, Instrumentation
------------------------	---

Construction Details

Conductor

Size	Stranding	Nom. Diameter	Material
22 AWG	7x30	0.029 in	TC - Tinned Copper

Insulation

Material	Nom. Insulation Diameter
PE - Polyethylene (Conductive)	0.036 in (0.91 mm)
PE - Polyethylene	0.112 in (2.84 mm)

Outer Shield

Layer	Outer Shield Type	Material	Material Trade Name	Coverage
1	Tape	Tri-Laminate (Alum+Poly+Alum)	Duobond® II	100%
2	Braid	Tinned Copper (TC)		95%

Outer Jacket

Material	Nom. Diameter
PVC - Polyvinyl Chloride	0.195 in (4.95 mm)

Overall Cable Diameter (Nominal):	0.195 in (4.95 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Nom. Conductor DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield
15.1 Ohm/1000ft (49.5 Ohm/km)	3.8 Ohm/1000ft (12 Ohm/km)	37 pF/ft (120 pF/m)

Electrical Characteristics Notes:	NBS Low Noise Test (Modified), MIL-C-17 Paragraph 4.8.14, 8 mV Peak to Peak Max
-----------------------------------	---

Mechanical Characteristics

Temperature

Operating
-35°C to +75°C

Bend Radius

Installation Min.
2 in

Max. Pull Tension:	8.85 lbs (4.01 kg)
Bulk Cable Weight:	24 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor (Not Riser or Plenum), Indoor
Sustainability:	CA Prop 65
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Product Notes

Notes:	Not recommended for RF use
--------	----------------------------

History

Update and Revision:	Revision Number: 0.276 Revision Date: 12-15-2021
----------------------	--

Variants

Item #	Color	Putup Type	Length	UPC
9223 010100	Black	Reel	100 ft	612825358831
9223 010500	Black	Reel	500 ft	612825357742
9223 0101000	Black	Reel	1,000 ft	612825357759

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[9223 010500](#) [9223 0101000](#) [9223 010100](#)