
Vishay Semiconductors



Silicon PIN Photodiode



DESCRIPTION

VEMD5080X01 is a high speed and high sensitive PIN photodiode with enhanced sensitivity for visible light. It is a low profile surface-mount device (SMD) including the chip with a 7.5 mm² sensitive area detecting visible and near infrared radiation.

FEATURES

- Package type: surface-mount
- Package form: top view
- Dimensions (L x W x H in mm): 5 x 4 x 0.9
- Radiant sensitive area (in mm²): 7.5
- AEC-Q101 qualified
- Enhanced sensitivity for visible light
- Suitable for visible and near infrared radiation
- Fast response times
- Angle of half sensitivity: $\varphi = \pm 65^{\circ}$
- Floor life: 72 h, MSL 4, according to J-STD-020
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

APPLICATIONS

• High speed photo detector

PRODUCT SUMMARY				
COMPONENT	I _{ra} (μΑ)	φ (°)	λ _{0.1} (nm)	
VEMD5080X01	45	± 65	350 to 1100	

Note

• Test conditions see table "Basic Characteristics"

ORDERING INFORMATION				
ORDERING CODE	PACKAGING	REMARKS	PACKAGE FORM	
VEMD5080X01	Tape and reel	MOQ: 1000 pcs, 1000 pcs/reel	Top view	
VEMD5080X01-GS15	Tape and reel	MOQ: 5000 pcs, 5000 pcs/reel	Top view	

Note

• MOQ: minimum order quantity

ABSOLUTE MAXIMUM RATINGS (T _{amb} = 25 °C, unless otherwise specified)				
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT
Reverse voltage		V _R	20	V
Power dissipation	T _{amb} ≤ 25 °C	Pv	215	mW
Junction temperature		Тj	110	°C
Operating temperature range		T _{amb}	-40 to +110	°C
Storage temperature range		T _{stg}	-40 to +110	°C
Soldering temperature	According to reflow solder profile Fig. 8	T _{sd}	260	°C
Thermal resistance junction to ambient		R _{thJA}	350	K/W
ESD safety HBM	\pm 2000 V, 1.5 k $\Omega,$ 100 pF, 3 pulses	ESD _{HBM}	≥2	kV

(e4)

RoHS COMPLIANT HALOGEN FREE





www.vishay.com

Vishay Semiconductors

BASIC CHARACTERISTICS (T _{amb} = 25 °C, unless otherwise specified)						
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
Forward voltage	I _F = 50 mA	V _F	-	0.9	1.3	V
Breakdown voltage	I _R = 100 μA, E = 0	V _(BR)	20	-	-	V
Reverse dark current	V _R = 10 V, E = 0	I _{ro}	-	0.2	10	nA
Diode capacitance	V _R = 0 V, f = 1 MHz, E = 0	CD	-	80	-	pF
	V _R = 3 V, f = 1 MHz, E = 0	CD	-	30	40	pF
Open circuit voltage	$E_e = 1 \text{ mW/cm}^2$, $\lambda = 950 \text{ nm}$	Vo	-	320	-	mV
Temperature coefficient of V_o	$E_e = 1 \text{ mW/cm}^2$, $\lambda = 950 \text{ nm}$	TK _{Vo}	-	-3.0	-	mV/K
Short circuit current	$E_e = 1 \text{ mW/cm}^2$, $\lambda = 950 \text{ nm}$	I _k	-	45	-	μA
Temperature coefficient of ${\rm I}_{\rm k}$	$E_e = 1 \text{ mW/cm}^2$, $\lambda = 950 \text{ nm}$	TK _{lk}	-	0.1	-	%/K
Reverse light current	$E_e = 1 \text{ mW/cm}^2$, $\lambda = 950 \text{ nm}$, $V_R = 5 \text{ V}$	I _{ra,IR}	33	45	53	μA
	$E_e = 0.2 \text{ mW/cm}^2$, $\lambda = 525 \text{ nm}$, $V_R = 5 \text{ V}$	I _{ra,G}	3.1	5.0	6.6	μA
	$E_{e} = 1 \text{ mW/cm}^{2}, \lambda = 460 \text{ nm}, V_{R} = 5 \text{ V}$	I _{ra,B}	13.5	18	25	μA
Angle of half sensitivity		φ	-	± 65	-	0
Wavelength of peak sensitivity		λ _p	-	950	-	nm
Range of spectral bandwidth		λ _{0.1}	-	350 to 1100	-	nm
Rise time	V_R = 10 V, R_L = 1 k Ω , λ = 830 nm	t _r	-	70	-	ns
Fall time	V_R = 10 V, R_L = 1 k Ω , λ = 830 nm	t _f	-	70	-	ns

BASIC CHARACTERISTICS (Tamb = 25 °C, unless otherwise specified)

Basic characteristics graphs to be extended to 110 °C ambient temperatures where applicable.




Fig. 1 - Reverse Dark Current vs. Ambient Temperature





Fig. 2 - Relative Reverse Light Current vs. Ambient Temperature

For technical questions, contact: <u>detectortechsupport@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>



Vishay Semiconductors



www.vishay.com

SHA

Fig. 3 - Reverse Light Current vs. Irradiance




Fig. 4 - Reverse Light Current vs. Reverse Voltage




Fig. 5 - Diode Capacitance vs. Reverse Voltage




Fig. 6 - Relative Spectral Sensitivity vs. Wavelength




Fig. 7 - Relative Sensitivity vs. Angular Displacement


3

For technical questions, contact: <u>detectortechsupport@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>



Vishay Semiconductors


PACKAGE DIMENSIONS in millimeters





Vishay Semiconductors


TAPE AND REEL DIMENSIONS in millimeters




For technical questions, contact: <u>detectortechsupport@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>

Vishay Semiconductors

SOLDER PROFILE



www.vishay.com



DRYPACK

Devices are packed in moisture barrier bags (MBB) to prevent the products from moisture absorption during transportation and storage. Each bag contains a desiccant.

FLOOR LIFE

Time between soldering and removing from MBB must not exceed the time indicated in J-STD-020:

Moisture sensitivity: level 4

Floor life: 72 h

Conditions: $T_{amb} < 30\ ^\circ C,\ RH < 60\ \%$

DRYING

In case of moisture absorption devices should be baked before soldering. Conditions see J-STD-020 or recommended conditions:

192 h at 40 °C (+ 5 °C), RH < 5 % or 96 h at 60 °C (+ 5 °C), RH < 5 %



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.