

# Cable-sensor


## for air measurements

# Type K5S<sub>RS</sub>

Issue of 11/19

### Sensor

1 x Pt100 F0,3 (old cl. B) DIN EN 60751  
4-wire-circuit -exposed-  
temperature range -50...200°C



### Protective tube material

1.4571

### Protective tube diameter

ø 4,5 mm slashed

### Installment length L1/ Length of protective tube

40 mm / 60 mm  
100 mm / 120 mm

### Thread

G1/4A  
1/4NPT

### Cable


TeTe 4x0,14 (200°C)

### Cable length

2500 mm

### Order Example

K5S-4L-200-1/4NPT-100



Subject to change without notice

**D- 99331 Geratal OT Geraberg, Gewerbepark 6**

**Tel: +49 (0) 3677 / 7956-0 // Fax: +49 (0) 3677 / 795 625**

**E-Mail: info@electrotherm.de**

**Internet: www.electrotherm.de**