


CM8V-T1A

Tuning Fork Crystal 32.768 kHz



DIMENSIONS



APPLICATIONS

IoT
 Metering
 Industrial
 Automotive
 Health Care
 Wearables, Portables

DESCRIPTION

The CM8V-T1A is a low frequency SMT Quartz Crystal Unit that incorporates a tuning fork Quartz Crystal Resonator. It operates under vacuum in a hermetically sealed ceramic package with metal lid.

FEATURES

Ultra small size, low profile, lightweight (4.6 mg).
 Outstanding hermetic sealing with gold-tin preform.
 High stability and low aging guaranteed by hermetic sealing.
 Available for extended operating temperature range.
 High shock and vibration resistant.
 100% Pb-free, RoHS-compliant.
 Automotive qualification according to AEC-Q200 available.

ELECTRICAL CHARACTERISTICS AT 25°C

Standard Frequencies 32.768 kHz / 100.000 kHz ¹⁾	F _L	32.768	kHz
Load capacitance ²⁾	C _L	4.0 / 6.0 / 7.0 / 9.0 / 12.5	pF
Frequency tolerance ³⁾	ΔF/F	±20	ppm
	ΔF/F	±100	ppm
Series resistance typ./max.	R _S	55 / 70	kΩ
Motional capacitance typ.	C ₁	4.7	fF
Static capacitance typ.	C ₀	1.2	pF
Drive level max.	P	0.5	μW
Insulation resistance min.	R _i	500	MΩ
Aging first year max.	ΔF/F	±3	ppm
Turnover temperature	T ₀	25 ±5	°C
Frequency vs. temperature	ΔF/F ₀	-0.035 ppm/°C ² (T - T ₀) ² ±10%	

1) Other frequencies on request.
 2) Other load capacitances on request.
 3) Tighter frequency tolerances on request.

STANDARD FREQUENCIES

Frequencies
32.768 kHz / 100.000 kHz
Other frequencies on request

ENVIRONMENTAL CHARACTERISTICS

		Conditions	Max. Dev.
Storage temp. range		-55 to +125°C	
TA Operating temperature range		-40 to +85°C	
TB Extended oper. temp. range		-40 to +125°C	
TC Extended oper. temp. range		-55 to +125°C	
Shock resistance	ΔF/F	5000 g, 0.3 ms, ½ sine	±5 ppm
Vibration resistance	ΔF/F	20 g / 10–2000 Hz	±5 ppm

TERMINATIONS AND PROCESSING

Type	Termination	Processing
CM8V-T1A	Au flashed pads	IPC/JEDEC J-STD-020C 260°C / 20 - 40 s

ORDERING INFORMATION

C M 8 V - T 1 A 32.768 kHz 12.5 pF ±20 ppm TA QC	
Ceramic package	Frequency F_L
Metal lid	Load capacitance C_L 4.0 pF, 6.0 pF 7.0 pF 9.0 pF 12.5 pF Other C_L on request
Package size 8 = 2.0 x 1.2 x 0.60 mm	Frequency tolerance ±20 ppm ±100 ppm Tighter freq. tolerances on request
Tuning fork	Temperature range TA = -40 to +85°C (Standard) TB = -40 to +125°C TC = -55 to +125°C
SMT Package	Qualification QC = Commercial Grade (Standard) QA = Automotive Grade AEC-Q200
Au flashed pads	
Pads on both ends	

A unique part number will be generated for each product specification, i.e:	
20xxxx-MC01	1'000 pcs (in 8 mm tape on 7" reel)
20xxxx-MC03	3'000 pcs (in 8 mm tape on 7" reel)

All specifications subject to change without notice.



A COMPANY OF THE SWATCH GROUP

Micro Crystal AG
Muehlestrasse 14
CH-2540 Grenchen
Switzerland

Phone +41 32 655 82 82
Fax +41 32 655 82 83
sales@microcrystal.com
www.microcrystal.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Micro Crystal:

[CM8V-T1A-32.768k-12.5pF-20PPM-TA-QA](#) [CM8V-T1A-32.768kHz-12.5pF-20PPM-TB-QC](#) [CM8V-T1A-32.768kHz-12.5pF-20PPM-TA-QC](#) [CM8V-T1A-32.768kHz-9pF-20PPM-TA-QC](#) [CM8V-T1A-32.768kHz-12.5pF-20PPM-TC-QC](#) [CM8V-T1A-32.768kHz-4pF-20PPM-TA-QC](#) [CM8V-T1A-100.000kHz-9pF-100PPM-TA-QC](#) [CM8V-T1A-32.768kHz-9pF-100PPM-TA-QC](#) [CM8V-T1A-32.768k-9pF-20PPM-TB-QA](#) [CM8V-T1A-32.768k-12.5pF-20PPM-TB-QA](#) [CM8V-T1A-32.768kHz-7pF-100PPM-TA-QC](#) [CM8V-T1A-32.768kHz-9pF-20PPM-TB-QC](#) [CM8V-T1A-32.768kHz-6pF-20PPM-TA-QC](#) [CM8V-T1A-32.768kHz-7pF-20PPM-TB-QC](#) [CM8V-T1A-32.768kHz-7pF-20PPM-TA-QC](#) [CM9V-T1A-32.768kHz-7pF-100PPM-TA-QC](#) [CM9V-T1A-32.768kHz-12.5pF-20PPM-TA-QC](#) [CM9V-T1A-32.768kHz-9pF-20PPM-TA-QC](#) [CM9V-T1A-32.768kHz-7pF-20PPM-TA-QC](#) [CM8V-T1A 32.768kHz 4.0pF 20ppm TA QC](#) [201615-MC03](#) [CM8V-T1A-32.768kHz-4pF-20PPM-TA-QC T1](#) [CM8V-T1A-32.768kHz-4pF-20PPM-TA-QC T3](#) [CM8V-T1A-0.3-32.768kHz-12.5pF-20PPM-TAQC](#) [CM8V-T1A-0.3-32.768kHz-6pF-20PPM-TA-QC](#) [CM8V-T1A-0.3-32.768kHz-7pF-20PPM-TA-QC](#) [CM8V-T1A-0.3-32.768kHz-9pF-20PPM-TA-QC](#) [CM8V-T1A-32.768kHz-12.5pF-20PPM-TC-QA](#)