

# **Film Capacitors**

## Metallized Polyester Film Capacitors (MKT)

 Series/Type:
 B32520 ... B32529

 Date:
 September 2019

© TDK Electronics AG 2020. Reproduction, publication and dissemination of this publication, enclosures hereto and the information contained therein without TDK Electronics' prior express consent is prohibited.



#### Metallized polyester film capacitors (MKT)

#### General purpose (stacked/wound)

#### B32520 ... B32529

#### **Typical applications**

- Blocking
- Coupling, decoupling
- Bypassing
- RFI for automotive

#### Climatic

- Max. operating temperature: 125 °C
- Climatic category (IEC 60068-1:2013): 55/125/56

#### Construction

- Dielectric: polyethylene terephthalate (polyester, PET)
- Stacked-film technology for lead spacing 5 to 15 mm (= code C, D or E in digit 7 of ordering code)
- Wound capacitor technology for lead spacing 10 to 37.5 mm (= code N, Q or R in digit 7 of ordering code)
- Plastic case (UL 94 V-0)
- Epoxy resin sealing (UL 94 V-0)

#### Features

- High pulse strength
- High contact reliability
- RoHS-compatible
- Halogen-free capacitors available on request
- AEC-Q200D compliant

#### Terminals

- Parallel wire leads, lead-free tinned
- Special lead lengths available on request

#### Marking

Manufacturer's logo, rated capacitance (coded), cap. tolerance (code letter), rated DC voltage, date of manufacture (coded), coded type ("1") for lead spacing 5 mm, series and lot number for lead spacing ≥10 mm


#### **Delivery mode**

Downloaded from

Bulk (untaped) Taped (Ammo pack or reel) For notes on taping, refer to chapter "Taping and packing".

Please read *Cautions and warnings* and *Important notes* at the end of this document. m Arrow.com.

#### Dimensional drawing



Dimensions in mm

Lead spacing	Lead diameter	Туре
<i>e</i> ±0.4	d <sub>1</sub> ±0.05	
5.0	0.5	B32529
7.5	0.5	B32520
10.0	0.6 <sup>1)</sup>	B32521
15.0	0.8	B32522
22.5	0.8	B32523
27.5	0.8	B32524
37.5	1.0	B32526

1) 0.5 mm for capacitor width w = 4 mm. Exception for B32521D series.



MKT

B32520 ... B32529

## General purpose (stacked/wound)

## Overview of available types

Lead spacing 5.0 mm							7.5 r	nm			10.0 mm				
Туре	B32						B325				B32				
Page	6						9				10				
Technology	s	s	S	s	s	s	s	s	s	s	s	s	s	s	S
V <sub>R</sub> (V DC)	50	63	100	250	400	630	63	100	250	400	63	100	250	400	630
V <sub>RMS</sub> (V AC)	32	40	63	160	200	400	40	63	160	200	40	63	160	200	350
C <sub>R</sub> (μF)															
0.0010															
0.0015															
0.0022															
0.0033															
0.0047															
0.0068															
0.010															
0.015															
0.022															
0.033															
0.047															
0.056															
0.068															
0.082															
0.10															
0.12															
0.15															
0.18															
0.22															
0.33															
0.47															
0.68															
1.0															
1.5															
2.2															
3.3															
4.7															

Technology: s = Stacked-film technology / w = Wound capacitor technology



мкт

B32520 ... B32529

General purpose (stacked/wound)

## Overview of available types

Lead spacing	15.0	mm					22.5	mm				27.5 mm				
Туре	B32	522					B32	523				B32524				
Page	12						14				15					
Technology	s	s/w	s/w	S	w	S	w	w	w	w	W	w	w	W	w	W
V <sub>R</sub> (V DC)	63	100	250	400	450	630	63	100	250	400	630	63	100	250	400	630
V <sub>RMS</sub> (V AC)	40	63	160	200	200	350	40	63	160	200	200	40	63	160	200	220
C <sub>R</sub> (μF)																
0.047																
0.068																
0.10																
0.15																
0.22																
0.33																
0.39																
0.47																
0.56																
0.68																
1.0																
1.5																
2.2																
3.3																
4.7																
6.8																
10																
15																
22																
33																
47																
68																
100																

Technology: s = Stacked-film technology / w = Wound capacitor technology



MKT

B32520 ... B32529

General purpose (stacked/wound)

## Overview of available types

Lead spacing	37.5 mm			
Туре	B32526			
Page	17			
Technology	W	w	w	w
V <sub>R</sub> (V DC)	63	100	250	400
V <sub>RMS</sub> (V AC)	40	63	160	200
C <sub>R</sub> (μF)				
3.3				
4.7				
5.6				
6.8				
8.2				
10				
15				
22				
33				
47				
56				
68				
82				
100				
150				
220				

Technology: s = Stacked-film technology / w = Wound capacitor technology





B32529

General purpose (stacked)

#### Ordering codes and packing units (lead spacing 5 mm)

V <sub>R</sub>	V <sub>RMS</sub>	C <sub>R</sub>	Max. dimensions	Ordering code	Ammo	Reel	Untaped
	f ≤60 Hz		$w \times h \times I$	(composition see	pack		
V DC	V AC	μF	mm	below)	pcs./MOQ	pcs./MOQ	pcs./MOQ
50	32	3.3	$7.8\times13.0\times7.8$	B32529D5335+***	4000	3200	4000
		4.7	$7.8\times13.0\times7.8$	B32529D5475M***	4000	3200	4000
63	40	0.0010	$2.5\times6.5\times7.3$	B32529C0102+***	12800	11200	8000
		0.0015	$2.5\times6.5\times7.3$	B32529C0152+***	12800	11200	8000
		0.0022	$2.5\times6.5\times7.3$	B32529C0222+***	12800	11200	8000
		0.0033	$2.5\times6.5\times7.3$	B32529C0332+***	12800	11200	8000
		0.0047	$2.5\times6.5\times7.3$	B32529C0472+***	12800	11200	8000
		0.0068	$2.5\times6.5\times7.3$	B32529C0682+***	12800	11200	8000
		0.010	$2.5\times6.5\times7.3$	B32529C0103+***	12800	11200	8000
		0.015	$2.5\times6.5\times7.3$	B32529C0153+***	12800	11200	8000
		0.022	$2.5\times6.5\times7.3$	B32529C0223+***	12800	11200	8000
		0.033	$2.5\times6.5\times7.3$	B32529C0333+***	12800	11200	8000
		0.047	$2.5\times6.5\times7.3$	B32529C0473+***	12800	11200	8000
		0.068	$2.5\times6.5\times7.3$	B32529C0683+***	12800	11200	8000
		0.10	$2.5\times6.5\times7.3$	B32529C0104+***	12800	11200	8000
		0.15	$2.5\times6.5\times7.3$	B32529C0154+***	12800	11200	8000
		0.22	$2.5\times6.5\times7.3$	B32529C0224+***	12800	11200	8000
		0.33	$3.0 \times 6.5 \times 7.3$	B32529C0334+***	10800	9600	8000
		0.47	$3.5 \times 8.0 \times 7.3$	B32529C0474+***	9200	8000	8000
		0.68	$4.5\times 9.5\times 7.3$	B32529C0684+***	7200	6000	6000
		1.0	$4.5\times 9.5\times 7.3$	B32529C0105+***	7200	6000	6000
		1.5	$6.0\times10.5\times7.5$	B32529C0155+***	5200	4400	4000
		2.2	$7.8\times13.0\times7.8$	B32529D0225+***	4000	3200	4000
100	63	0.0010	$2.5\times6.5\times7.3$	B32529C1102+***	12800	11200	8000
		0.0015	$2.5\times6.5\times7.3$	B32529C1152+***	12800	11200	8000
		0.0022	$2.5\times6.5\times7.3$	B32529C1222+***	12800	11200	8000
		0.0033	$2.5\times6.5\times7.3$	B32529C1332+***	12800	11200	8000
		0.0047	$2.5\times6.5\times7.3$	B32529C1472+***	12800	11200	8000
		0.0068	$2.5 \times 6.5 \times 7.3$	B32529C1682+***	12800	11200	8000
		0.010	$2.5 \times 6.5 \times 7.3$	B32529C1103+***	12800	11200	8000
		0.015	$2.5\times6.5\times7.3$	B32529C1153+***	12800	11200	8000

MOQ = Minimum Order Quantity, consisting of 4 packing units. Further E series and intermediate capacitance values on request.

#### Composition of ordering code

+ = Capacitance tolerance code:

M =±20%

 $K = \pm 10\%$ 

 $J = \pm 5\%$ 

\*\*\* = Packaging code:

289 = Ammo pack

189 = Reel

000 = Untaped (standard lead length 6 -1 mm)



B32529 General purpose (stacked)

# MKT → 5 ◄

## Ordering codes and packing units (lead spacing 5 mm)

$V_{R}$	$V_{\text{RMS}}$	C <sub>R</sub>	Max. dimensions	Ordering code	Ammo	Reel	Untaped
	f ≤60 Hz		$w \times h \times I$	(composition see	pack		
V DC	V AC	μF	mm	below)	pcs./MOQ	pcs./MOQ	pcs./MOQ
100	63	0.022	$2.5\times6.5\times7.3$	B32529C1223+***	12800	11200	8000
		0.033	$2.5\times6.5\times7.3$	B32529C1333+***	12800	11200	8000
		0.047	$2.5\times6.5\times7.3$	B32529C1473+***	12800	11200	8000
		0.068	$2.5\times6.5\times7.3$	B32529C1683+***	12800	11200	8000
		0.10	$2.5\times6.5\times7.3$	B32529C1104+***	12800	11200	8000
		0.15	$3.0\times~6.5\times7.3$	B32529C1154+***	10800	9600	8000
		0.22	$3.5\times8.0\times7.3$	B32529C1224+***	9200	8000	8000
		0.33	$3.5 \times 8.0 \times 7.3$	B32529C1334+***	9200	8000	8000
		0.47	$4.5\times 9.5\times7.3$	B32529C1474+***	7200	6000	6000
		0.68	$6.0\times10.5\times7.5$	B32529C1684+***	5200	4400	4000
		1.0	$7.8 \times 13.0 \times 7.8$	B32529D1105+***	4000	3200	4000
250	160	0.0010	$2.5\times6.5\times7.3$	B32529C3102+***	12800	11200	8000
		0.0015	$2.5\times6.5\times7.3$	B32529C3152+***	12800	11200	8000
		0.0022	$2.5\times6.5\times7.3$	B32529C3222+***	12800	11200	8000
		0.0033	$2.5\times~6.5\times7.3$	B32529C3332+***	12800	11200	8000
		0.0047	$2.5\times6.5\times7.3$	B32529C3472+***	12800	11200	8000
		0.0068	$2.5\times6.5\times7.3$	B32529C3682+***	12800	11200	8000
		0.010	$2.5\times6.5\times7.3$	B32529C3103+***	12800	11200	8000
		0.015	$2.5\times6.5\times7.3$	B32529C3153+***	12800	11200	8000
		0.022	$2.5\times6.5\times7.3$	B32529C3223+***	12800	11200	8000
		0.033	$3.0\times~6.5\times7.3$	B32529C3333+***	10800	9600	8000
		0.047	$3.5\times8.0\times7.3$	B32529C3473+***	9200	8000	8000
		0.068	$4.5\times 9.5\times7.3$	B32529C3683+***	7200	6000	6000
		0.10	$4.5\times 9.5\times7.3$	B32529C3104+***	7200	6000	6000
		0.15	$5.0\times10.0\times7.5$	B32529C3154+***	6400	5600	6000
		0.22	$7.8\times13.0\times7.8$	B32529D3224+***	4000	3200	4000
		0.33	$7.8\times13.0\times7.8$	B32529C3334+***	4000	3200	4000
		0.47	$7.8 \times 13.0 \times 7.8$	B32529C3474+***	4000	3200	4000

MOQ = Minimum Order Quantity, consisting of 4 packing units. Further E series and intermediate capacitance values on request.

#### Composition of ordering code

+ = Capacitance tolerance code:

 $M = \pm 20\%$ 

- $K = \pm 10\%$
- $J = \pm 5\%$

- \*\*\* = Packaging code:
  - 289 = Ammo pack
  - 189 = Reel
  - 000 = Untaped (standard lead length 6 -1 mm)





B32529

General purpose (stacked)

#### Ordering codes and packing units (lead spacing 5 mm)

V <sub>R</sub>	V <sub>RMS</sub>	C <sub>R</sub>	Max. dimensions	Ordering code	Ammo	Reel	Untaped
	f ≤60 Hz		$w \times h \times I$	(composition see	pack		
V DC	V AC	μF	mm	below)	pcs./MOQ	pcs./MOQ	pcs./MOQ
400	200	0.0010	$2.5\times6.5\times7.3$	B32529C6102+***	12800	11200	8000
		0.0015	$2.5\times6.5\times7.3$	B32529C6152+***	12800	11200	8000
		0.0022	$2.5\times6.5\times7.3$	B32529C6222+***	12800	11200	8000
		0.0033	$2.5\times6.5\times7.3$	B32529C6332+***	12800	11200	8000
		0.0047	$2.5\times6.5\times7.3$	B32529C6472+***	12800	11200	8000
		0.0068	$2.5\times6.5\times7.3$	B32529C6682+***	12800	11200	8000
		0.010	$3.0\times~6.5\times7.3$	B32529E6103+***	10800	9600	8000
		0.015	$3.0\times~6.5\times7.3$	B32529E6153+***	10800	9600	8000
		0.022	$3.5 \times 8.0 \times 7.3$	B32529E6223+***	9200	8000	8000
		0.033	$4.5\times 9.5\times7.3$	B32529E6333+***	7200	6000	6000
		0.047	$4.5\times 9.5\times7.3$	B32529E6473+***	7200	6000	6000
		0.068	$6.0\times10.5\times7.5$	B32529E6683+***	5200	4400	4000
		0.10	$7.8\times13.0\times7.8$	B32529E6104+***	4000	3200	4000
		0.15	$7.8 \times 13.0 \times 7.8$	B32529E6154+***	4000	3200	4000
630	400	0.0010	$2.5\times6.5\times7.3$	B32529C8102+***	12800	11200	8000
		0.0015	$2.5\times6.5\times7.3$	B32529C8152+***	12800	11200	8000
		0.0022	$2.5\times6.5\times7.3$	B32529C8222+***	12800	11200	8000
		0.0033	$3.5\times8.0\times7.3$	B32529C8332+***	9200	8000	8000
		0.0047	$3.5\times8.0\times7.3$	B32529C8472+***	9200	8000	8000
		0.0068	$3.5\times8.0\times7.3$	B32529C8682+***	9200	8000	8000
		0.010	$5.0\times10.0\times7.5$	B32529C8103+***	6400	5600	6000
		0.015	$5.0\times10.0\times7.5$	B32529C8153+***	6400	5600	6000
		0.022	$7.8\times13.0\times7.8$	B32529C8223+***	5200	4400	4000
		0.033	$7.8 \times 13.0 \times 7.8$	B32529C8333+***	4000	3200	4000

MOQ = Minimum Order Quantity, consisting of 4 packing units. Further E series and intermediate capacitance values on request.

#### Composition of ordering code

+ = Capacitance tolerance code:

- M =±20%
- $K = \pm 10\%$
- $J = \pm 5\%$

- \*\*\* = Packaging code:
  - 289 = Ammo pack
  - 189 = Reel
  - 000 = Untaped (standard lead length 6 -1 mm)



B32520 General purpose (stacked)



## Ordering codes and packing units (lead spacing 7.5 mm)

V <sub>R</sub>	V <sub>RMS</sub>	C <sub>R</sub>	Max. dimensions	Ordering code	Ammo	Reel	Untaped
	f ≤60 Hz		$w \times h \times l$	(composition see	pack		-
V DC	V AC	μF	mm	below)	pcs./MOQ	pcs./MOQ	pcs./MOQ
63	40	0.47	$3.0 \times 8.0 \times 10.0$	B32520C0474+***	10400	9600	8000
		0.68	$4.0 \times 8.5 \times 10.0$	B32520C0684+***	8000	7200	6000
		1.0	5.0 imes10.5 imes10.0	B32520C0105+***	6400	5600	4000
		1.5	5.0 imes10.5 imes10.0	B32520C0155+***	6400	5600	4000
		2.2	$6.0 \times 12.0 \times 10.3$	B32520C0225+***	5200	4400	3000
100	63	0.15	$3.0 \times 8.0 \times 10.0$	B32520C1154+***	10400	9600	8000
		0.22	$3.0 \times 8.0 \times 10.0$	B32520C1224+***	10400	9600	8000
		0.33	$4.0\times \ 8.5\times 10.0$	B32520C1334+***	8000	7200	6000
		0.47	5.0 imes10.5 imes10.0	B32520C1474+***	6400	5600	4000
		0.68	$6.0\times12.0\times10.3$	B32520C1684+***	5200	4400	3000
		1.0	$6.0\times12.0\times10.3$	B32520C1105+***	5200	4400	3000
250	160	0.068	$3.0 \times 8.0 \times 10.0$	B32520C3683+***	10400	9600	8000
		0.10	$4.0\times \ 8.5\times 10.0$	B32520C3104+***	8000	7200	6000
		0.15	5.0  imes 10.5  imes 10.0	B32520C3154+***	6400	5600	4000
		0.22	$6.0\times12.0\times10.3$	B32520C3224+***	5200	4400	3000
400	200	0.015	$3.0 \times 8.0 \times 10.0$	B32520E6153+***	10400	9600	8000
		0.022	$3.0 \times 8.0 \times 10.0$	B32520E6223+***	10400	9600	8000
		0.033	$4.0\times \ 8.5\times 10.0$	B32520E6333+***	8000	7200	6000
		0.047	$4.0\times \ 8.5\times 10.0$	B32520E6473+***	8000	7200	6000
		0.068	5.0  imes 10.5  imes 10.0	B32520E6683+***	6400	5600	4000
		0.10	5.0 imes10.5 imes10.0	B32520E6104+***	6400	5600	4000
		0.15	$6.0\times12.0\times10.3$	B32520E6154+***	5200	4400	3000

MOQ = Minimum Order Quantity, consisting of 4 packing units.

Further E series and intermediate capacitance values on request.

## Composition of ordering code

- + = Capacitance tolerance code:
  - $M = \pm 20\%$
  - K = ±10%
  - $J = \pm 5\%$

\*\*\* = Packaging code:

289 = Ammo pack

- 189 = Reel
- 000 = Untaped (standard lead length 6 -1 mm)





B32521

General purpose (stacked/wound)

#### Ordering codes and packing units (lead spacing 10 mm)

V <sub>R</sub>	V <sub>RMS</sub>	C <sub>R</sub>	Max. dimensions	Ordering code	Ammo	Reel	Untaped
	f ≤60 Hz		$w \times h \times l$	(composition see	pack		
V DC	V AC	μF	mm	below)	pcs./MOQ	pcs./MOQ	pcs./MOQ
63	40	0.47	4.0 × 7.0 × 13.0	B32521C0474+***	4000	6800	4000
		0.68	$4.0 \times 7.0 \times 13.0$	B32521C0684+***	4000	6800	4000
		1.0	$4.0\times 9.0\times 13.0$	B32521C0105+***	4000	6800	4000
		1.5	5.0  imes 11.0  imes 13.0	B32521C0155+***	3320	5200	4000
		2.2	5.0  imes 11.0  imes 13.0	B32521C0225+***	3320	5200	4000
		3.3	$6.0\times12.0\times13.0$	B32521C0335+***	2720	4400	4000
100	63	0.047	$4.0\times~7.0\times13.0$	B32521C1473+***	4000	6800	4000
		0.068	$4.0\times~7.0\times13.0$	B32521C1683+***	4000	6800	4000
		0.10	$4.0\times~7.0\times13.0$	B32521C1104+***	4000	6800	4000
		0.15	$4.0\times~7.0\times13.0$	B32521C1154+***	4000	6800	4000
		0.22	$4.0\times~7.0\times13.0$	B32521C1224+***	4000	6800	4000
		0.33	$4.0\times~7.0\times13.0$	B32521C1334+***	4000	6800	4000
		0.47	$4.0\times 9.0\times 13.0$	B32521C1474+***	4000	6800	4000
		0.68	5.0  imes 11.0  imes 13.0	B32521C1684+***	3320	5200	4000
		1.0	$6.0\times12.0\times13.0$	B32521C1105+***	2720	4400	4000
250	160	0.010	$4.0\times 7.0\times 13.0$	B32521C3103+***	4000	6800	4000
		0.015	$4.0 \times 7.0 \times 13.0$	B32521C3153+***	4000	6800	4000
		0.022	$4.0 \times 7.0 \times 13.0$	B32521C3223+***	4000	6800	4000
		0.033	$4.0\times 7.0\times 13.0$	B32521C3333+***	4000	6800	4000
		0.047	$4.0\times 7.0\times 13.0$	B32521C3473+***	4000	6800	4000
		0.056	$4.0\times 7.0\times 13.0$	B32521C3563+***	4000	6800	4000
		0.068	$4.0 \times 7.0 \times 13.0$	B32521C3683+***	4000	6800	4000
		0.082	$4.0 \times 7.0 \times 13.0$	B32521C3823+***	4000	6800	4000
		0.10	$4.0\times 7.0\times 13.0$	B32521C3104+***	4000	6800	4000
		0.12	$4.0\times 9.0\times 13.0$	B32521C3124+***	4000	6800	4000
		0.15	$4.0\times 9.0\times 13.0$	B32521C3154+***	4000	6800	4000
		0.18	5.0  imes 11.0  imes 13.0	B32521C3184+***	3320	5200	4000
		0.22	5.0  imes 11.0  imes 13.0	B32521C3224+***	3320	5200	4000
		0.33	$5.0\times11.0\times13.0$	B32521C3334+***	3320	5200	4000
		0.47	$6.0\times12.0\times13.0$	B32521C3474+***	2720	4400	4000

MOQ = Minimum Order Quantity, consisting of 4 packing units. Further E series and intermediate capacitance values on request.

#### Composition of ordering code

+ = Capacitance tolerance code:

M =±20%

- K = ±10%
- $J = \pm 5\%$

\*\*\* = Packaging code:

289 = Ammo pack

```
189 = Reel
```

000 = Untaped (standard lead length 6 -1 mm)



B32521 General purpose (stacked/wound)



## Ordering codes and packing units (lead spacing 10 mm)

V <sub>R</sub>	V <sub>RMS</sub>	C <sub>R</sub>	Max. dimensions	Ordering code	Ammo	Reel	Untaped
	f ≤60 Hz		$w \times h \times l$	(composition see	pack		
V DC	V AC	μF	mm	below)	pcs./MOQ	pcs./MOQ	pcs./MOQ
400	200	0.010	$4.0\times 7.0\times 13.0$	B32521E6103+***	4000	6800	4000
		0.015	$4.0\times~7.0\times13.0$	B32521E6153+***	4000	6800	4000
		0.022	$4.0\times~7.0\times13.0$	B32521E6223+***	4000	6800	4000
		0.033	$4.0\times~7.0\times13.0$	B32521E6333+***	4000	6800	4000
		0.047	$4.0\times 9.0\times 13.0$	B32521E6473+***	4000	6800	4000
		0.068	$4.0\times 9.0\times 13.0$	B32521E6683+***	4000	6800	4000
		0.10	5.0  imes 11.0  imes 13.0	B32521E6104+***	3320	5200	4000
		0.15	$6.0\times12.0\times13.0$	B32521E6154+***	2720	4400	4000
630	350	0.010	$4.0\times~7.0\times13.0$	B32521D8103+***	_	6800	4000
		0.015	$4.0\times 9.0\times 13.0$	B32521D8153+***	-	6800	4000
		0.022	5.0  imes 11.0  imes 13.0	B32521D8223+***	-	5200	4000
		0.033	5.0  imes 11.0  imes 13.0	B32521D8333+***	-	5200	4000
		0.047	$6.0\times12.0\times13.0$	B32521D8473+***		4400	4000

MOQ = Minimum Order Quantity, consisting of 4 packing units.

Further E series and intermediate capacitance values on request.

#### Composition of ordering code

+ = Capacitance tolerance code:

- $\begin{array}{l} \mathsf{M}=\pm 20\%\\ \mathsf{K}=\pm 10\% \end{array}$
- $J = \pm 5\%$

\*\*\* = Packaging code:

289 = Ammo pack

189 = Reel

000 = Untaped (standard lead length 6 -1 mm)





B32522

General purpose (stacked/wound)

#### Ordering codes and packing units (lead spacing 15 mm)

V <sub>R</sub>	V <sub>RMS</sub>	C <sub>R</sub>		Max. dimensions	Ordering code	Ammo	Reel	Untaped
	f ≤60 Hz			$w \times h \times I$	(composition see	pack	pcs./	pcs./
V DC	V AC	μF		mm	below)	pcs./MOQ	MOQ	MOQ
63	40	0.68		5.0  imes 10.5  imes 18.0	B32522C0684+***	4680	5200	4000
		1.0		$5.0\times10.5\times18.0$	B32522C0105+***	4680	5200	4000
		1.5		$5.0\times10.5\times18.0$	B32522C0155+***	4680	5200	4000
		2.2		$5.0\times10.5\times18.0$	B32522C0225+***	4680	5200	4000
		3.3		$6.0\times11.0\times18.0$	B32522C0335+***	3840	4400	4000
		4.7		$7.0\times12.5\times18.0$	B32522C0475+***	3320	3600	4000
		6.8		$8.5 \times 14.5 \times 18.0$	B32522C0685+***	2720	2800	2000
		10		$9.0\times17.5\times18.0$	B32522C0106+***	2560	2800	2000
100	63	0.33		$5.0\times10.5\times18.0$	B32522C1334+***	4680	5200	4000
		0.47		$5.0\times10.5\times18.0$		4680	5200	4000
		0.68		$5.0\times10.5\times18.0$		4680	5200	4000
		1.0		$5.0\times10.5\times18.0$	B32522C1105+***	4680	5200	4000
		1.0	$\nabla$	$6.0\times11.0\times18.0$	B32522Q1105+***	3840	4400	4000
		1.5		$6.0\times11.0\times18.0$	B32522C1155+***	3840	4400	4000
		1.5	$\nabla$	$7.0\times12.5\times18.0$	B32522Q1155+***	3320	3600	4000
		2.2		$7.0\times12.5\times18.0$	B32522C1225+***	3320	3600	4000
		2.2	$\nabla$	$8.5 \times 14.5 \times 18.0$	B32522Q1225+***	2720	2800	2000
		3.3		$8.5 \times 14.5 \times 18.0$	B32522C1335+***	2720	2800	2000
		3.3	$\nabla$	$9.0\times17.5\times18.0$	B32522Q1335+***	2560	2800	2000
		4.7		$9.0\times17.5\times18.0$	B32522C1475+***	2560	2800	2000
		4.7	$\nabla$	$11.0\times18.5\times18.0$	B32522Q1475+***	—	2200	1200
		6.8		$11.0\times18.5\times18.0$	B32522C1685+***	—	—	1200
250	160	0.10		$5.0\times10.5\times18.0$	B32522C3104+***	4680	5200	4000
		0.15		$5.0\times10.5\times18.0$	B32522C3154+***	4680	5200	4000
		0.22		$5.0\times10.5\times18.0$	B32522C3224+***	4680	5200	4000
		0.33		$5.0\times10.5\times18.0$	B32522C3334+***	4680	5200	4000
		0.39		$5.0\times10.5\times18.0$	B32522C3394+***	4680	5200	4000
		0.47		$6.0\times11.0\times18.0$	B32522C3474+***	3840	4400	4000
		0.56		$7.0\times12.5\times18.0$	B32522C3564+***	3320	3600	4000

 $\nabla$  Wound capacitor technology

MOQ = Minimum Order Quantity, consisting of 4 packing units. Further E series and intermediate capacitance values on request.

#### Composition of ordering code

+ = Capacitance tolerance code:

- $M = \pm 20\%$
- K = ±10%
- $J = \pm 5\%$

\*\*\* = Packaging code:
289 = Ammo pack
189 = Reel
000 = Untaped (standard lead length 6 -1 mm)



General purpose (stacked/wound)

B32522



#### Ordering codes and packing units (lead spacing 15 mm)

V <sub>R</sub>	V <sub>RMS</sub>	C <sub>R</sub>		Max. dimensions	Ordering code	Ammo	Reel	Untaped
	f ≤60 Hz			$w \times h \times I$	(composition see	pack	pcs./	pcs./
V DC	V AC	μF		mm	below)	pcs./MOQ	MOQ	MOQ
250	160	0.68		$7.0\times12.5\times18.0$	B32522C3684+***	3320	3600	4000
		1.0		$8.5 \times 14.5 \times 18.0$	B32522C3105+***	2720	2800	2000
		1.0 5	$\nabla$	$8.5 \times 14.5 \times 18.0$	B32522N3105+***	2720	2800	2000
		1.5		$9.0 \times 17.5 \times 18.0$	B32522C3155+***	2560	2800	2000
		1.5 \	$\nabla$	$9.0 \times 17.5 \times 18.0$	B32522N3155+***	2560	2800	2000
		2.2		$11.0\times18.5\times18.0$	B32522C3225+***	_	_	1200
400	200	0.047		$5.0\times10.5\times18.0$	B32522E6473+***	4680	5200	4000
		0.068		$5.0\times10.5\times18.0$	B32522E6683+***	4680	5200	4000
		0.10		$5.0\times10.5\times18.0$	B32522E6104+***	4680	5200	4000
		0.15		$5.0\times10.5\times18.0$	B32522E6154+***	4680	5200	4000
		0.22		$6.0\times11.0\times18.0$	B32522E6224+***	3840	4400	4000
		0.33		$7.0 \times 12.5 \times 18.0$	B32522E6334+***	3320	3600	4000
		0.39		$9.0 \times 17.5 \times 18.0$	B32522E6394+***	2560	2800	2000
		0.47		$9.0 \times 17.5 \times 18.0$	B32522E6474+***	2560	2800	2000
		0.56		$9.0 \times 17.5 \times 18.0$	B32522E6564+***	2560	2800	2000
		0.68		$9.0 \times 17.5 \times 18.0$	B32522E6684+***	2560	2800	2000
		1.0		$11.0\times18.5\times18.0$	B32522E6105+***	—	—	1200
450	200	0.10	$\nabla$	$5.0\times10.5\times18.0$	B32522N6104+***	4680	5200	4000
		0.15	$\nabla$	$5.0\times10.5\times18.0$	B32522N6154+***	4680	5200	4000
		0.22	$\nabla$	$6.0\times11.0\times18.0$	B32522N6224+***	3840	4400	4000
		0.33	$\nabla$	$7.0 \times 12.5 \times 18.0$	B32522N6334+***	3320	3600	4000
		0.47	$\nabla$	$8.5 \times 14.5 \times 18.0$	B32522N6474+***	2720	2800	2000
		0.68	$\nabla$	$9.0 \times 17.5 \times 18.0$	B32522N6684+***	2560	2800	2000
		1.0	$\nabla$	$11.0\times18.5\times18.0$	B32522N6105+***	_	2200	1200
630	350	0.047		$5.0\times10.5\times18.0$	B32522D8473+***	-	5200	4000
		0.068		$6.0\times11.0\times18.0$	B32522D8683+***	—	4400	4000
		0.10		$7.0\times12.5\times18.0$	B32522D8104+***	_	3600	4000
		0.15		$8.5 \times 14.5 \times 18.0$	B32522D8154+***	_	2800	2000
		0.22		$9.0\times17.5\times18.0$	B32522D8224+***	-	2800	2000

 $\nabla$  Wound capacitor technology

MOQ = Minimum Order Quantity, consisting of 4 packing units. Further E series and intermediate capacitance values on request.

#### Composition of ordering code

- + = Capacitance tolerance code:
  - M = ±20%
  - K = ±10%
  - $J = \pm 5\%$

\*\*\* = Packaging code:
289 = Ammo pack
189 = Reel
000 = Untaped (standard lead length 6 -1 mm)





B32523

General purpose (wound)

#### Ordering codes and packing units (lead spacing 22.5 mm)

V <sub>R</sub>	V <sub>RMS</sub>	C <sub>R</sub>	Max. dimensions	Ordering code	Ammo	Reel	Untaped
	f ≤60 Hz		$w \times h \times I$	(composition see	pack		
V DC	V AC	μF	mm	below)	pcs./MOQ	pcs./MOQ	pcs./MOQ
63	40	3.3	6.0  imes 15.0  imes 26.5	B32523R0335+***	2720	2800	2880
		4.7	6.0  imes 15.0  imes 26.5	B32523R0475+***	2720	2800	2880
		6.8	$6.0\times15.0\times26.5$	B32523R0685+***	2720	2800	2880
		10	$7.0\times16.0\times26.5$	B32523R0106+***	2320	2400	2520
		15	$10.5\times16.5\times26.5$	B32523R0156+***	1560	1600	2160
		22	$12.0\times22.0\times26.5$	B32523R0226+***	_	_	1800
100	63	1.5	$6.0\times15.0\times26.5$	B32523Q1155+***	2720	2800	2880
		2.2	$6.0\times15.0\times26.5$	B32523Q1225+***	2720	2800	2880
		3.3	$6.0\times15.0\times26.5$	B32523Q1335+***	2720	2800	2880
		4.7	$7.0\times16.0\times26.5$	B32523Q1475+***	2320	2400	2520
		6.8	$8.5\times16.5\times26.5$	B32523Q1685+***	1960	2000	2040
		10	$10.5\times18.5\times26.5$	B32523Q1106+***	1560	1600	2160
		15	$12.0\times22.0\times26.5$	B32523Q1156+***	_	_	1800
250	160	0.47	$6.0\times15.0\times26.5$	B32523Q3474+***	2720	2800	2880
		0.68	$6.0\times15.0\times26.5$	B32523Q3684+***	2720	2800	2880
		1.0	$6.0\times15.0\times26.5$	B32523Q3105+***	2720	2800	2880
		1.5	$7.0\times16.0\times26.5$	B32523Q3155+***	2320	2400	2520
		2.2	$10.5\times16.5\times26.5$	B32523Q3225+***	1560	1600	2160
		3.3	$11.0\times20.5\times26.5$	B32523Q3335+***	1480	1400	2040
400	200	0.22	$6.0\times15.0\times26.5$	B32523Q6224+***	2720	2800	2880
		0.33	$6.0\times15.0\times26.5$	B32523Q6334+***	2720	2800	2880
		0.47	$7.0\times16.0\times26.5$	B32523Q6474+***	2320	2400	2520
		0.68	$8.5 \times 16.5 \times 26.5$	B32523Q6684+***	1920	2000	2040
		1.0	$10.5\times16.5\times26.5$	B32523Q6105+***	1560	1600	2160
		1.5	$11.0\times20.5\times26.5$	B32523Q6155+***	1480	1400	2040
630	200	0.10	$6.0\times15.0\times26.5$	B32523Q8104+***	2720	2800	2880
		0.15	$6.0\times15.0\times26.5$	B32523Q8154+***	2720	2800	2880
		0.22	$7.0\times16.0\times26.5$	B32523Q8224+***	2320	2400	2520
		0.33	$10.5\times16.5\times26.5$	B32523Q8334+***	1560	1600	2160
		0.47	$10.5\times20.5\times26.5$	B32523Q8474+***	1560	1600	2160
		0.68	$12.0\times22.0\times26.5$	B32523Q8684+***	-	-	1800

MOQ = Minimum Order Quantity, consisting of 4 packing units.

Further E series and intermediate capacitance values on request.

#### Composition of ordering code

+ = Capacitance	tolerance code	:
-----------------	----------------	---

 $K = \pm 10\%$ 

 $J = \pm 5\%$ 

\*\*\* = Packaging code:

289 = Ammo pack

000 = Untaped (standard lead length 6 -1 mm)



B32524 General purpose (wound)



#### Ordering codes and packing units (lead spacing 27.5 mm)

V <sub>R</sub>	V <sub>RMS</sub>	C <sub>R</sub>	Max. dimensions	Ordering code	Ammo	Reel	Untaped
	f ≤60 Hz		$w \times h \times I$	(composition see	pack		
V DC	V AC	μF	mm	below)	pcs./MOQ	pcs./MOQ	pcs./MOQ
63	40	4.7	$11.0 \times 21.0 \times 31.5$	B32524R0475+***	—	1400	1280
		6.8	11.0 × 21.0 × 31.5	B32524Q0685+***	_	1400	1280
		10	$11.0 \times 21.0 \times 31.5$	B32524R0106+***	_	1400	1280
		15	$11.0 \times 21.0 \times 31.5$	B32524R0156+***	_	1400	1280
		22	$11.0 \times 21.0 \times 31.5$	B32524R0226+***	_	1400	1280
		33	$12.5\times21.5\times31.5$	B32524R0336+***	_	1200	1120
		47	$18.0\times27.5\times31.5$	B32524R0476+***	_	_	800
		68	$18.0\times27.5\times31.5$	B32524R0686+***	_	_	800
		100	$22.0\times36.5\times31.5$	B32524R0107+***	_	_	640
100	63	4.7	$11.0\times21.0\times31.5$	B32524Q1475+***	_	1400	1280
		6.8	$11.0\times21.0\times31.5$	B32524Q1685+***	—	1400	1280
		10	$11.0\times21.0\times31.5$	B32524Q1106+***	—	1400	1280
		15	$11.0\times21.0\times31.5$	B32524Q1156+***	—	1400	1280
		22	$14.0\times24.5\times31.5$	B32524Q1226+***	—	1000	1040
		33	$18.0\times27.5\times31.5$	B32524Q1336+***	—	-	800
		47	$21.0\times31.0\times31.5$	B32524Q1476+***	-	-	720
_		68	$22.0\times36.5\times31.5$	B32524Q1686+***	—	—	640
250	160	1.5	$11.0\times21.0\times31.5$		—	1400	1280
		2.2	$11.0\times21.0\times31.5$	B32524Q3225+***	_	1400	1280
		3.3	$11.0\times21.0\times31.5$	B32524Q3335+***	_	1400	1280
		4.7	$11.0\times21.0\times31.5$	B32524Q3475+***	-	1400	1280
		6.8	$11.0\times21.0\times31.5$	B32524R3685+***	_	1400	1280
		10	$12.5\times21.5\times31.5$	B32524R3106+***	-	1200	1120
		15	$15.0\times24.5\times31.5$	B32524R3156M***	—	—	960
		15	$18.0\times27.5\times31.5$	B32524R3156J***	_	_	960
		15	$18.0\times27.5\times31.5$	B32524R3156K***	—	—	960
		22	$19.0\times30.0\times31.5$	B32524R3226+***	_		720
		33	$22.0\times36.5\times31.5$	B32524R3336+***	_	_	640

MOQ = Minimum Order Quantity, consisting of 4 packing units. Further E series and intermediate capacitance values on request.

#### Composition of ordering code

- + = Capacitance tolerance code:
  - $M = \pm 20\%$
  - K = ±10%
  - $J = \pm 5\%$

\*\*\* = Packaging code:

289 = Ammo pack

- 189 = Reel
- 000 = Untaped (standard lead length 6 -1 mm)





B32524

General purpose (wound)

#### Ordering codes and packing units (lead spacing 27.5 mm)

V <sub>R</sub>	V <sub>RMS</sub>	C <sub>R</sub>	Max. dimensions	Ordering code	Ammo	Reel	Untaped
	f ≤60 Hz		$w \times h \times I$	(composition see	pack		
V DC	V AC	μF	mm	below)	pcs./MOQ	pcs./MOQ	pcs./MOQ
400	200	0.68	$11.0\times19.0\times31.5$	B32524Q6684+***	_	1400	1280
		1.0	$11.0\times19.0\times31.5$	B32524Q6105+***	_	1400	1280
		1.5	$11.0\times19.0\times31.5$	B32524Q6155+***	_	1400	1280
		2.2	$11.0 \times 21.0 \times 31.5$	B32524R6225+***	_	1400	1280
		3.3	$14.0\times24.5\times31.5$	B32524R6335+***	_	1000	1040
		4.7	$14.0\times24.5\times31.5$	B32524R6475+***	_	1000	1040
		6.8	$18.0\times27.5\times31.5$	B32524R6685+***	_	_	800
		10	$22.0\times36.5\times31.5$	B32524R6106+***	—	_	640
630	220	0.33	$11.0\times21.0\times31.5$	B32524Q8334+***	_	1400	1280
		0.47	$11.0\times21.0\times31.5$	B32524Q8474+***	—	1400	1280
		0.68	$11.0\times21.0\times31.5$	B32524Q8684+***	—	1400	1280
		1.0	$14.0\times24.5\times31.5$	B32524Q8105+***	—	1000	1040
		1.5	$18.0\times27.5\times31.5$	B32524Q8155+***	—	—	800
		2.2	$21.0\times31.0\times31.5$	B32524Q8225+***	_	_	720

MOQ = Minimum Order Quantity, consisting of 4 packing units.

Further E series and intermediate capacitance values on request.

#### Composition of ordering code

+ = Capacitance tolerance code:

- $M = \pm 20\%$
- K = ±10%
- $J = \pm 5\%$

\*\*\* = Packaging code:

289 = Ammo pack

- 189 = Reel
- 000 = Untaped (standard lead length 6 -1 mm)



B32526 General purpose (wound)



#### Ordering codes and packing units (lead spacing 37.5 mm)

V <sub>R</sub>	V <sub>RMS</sub>	C <sub>R</sub>	Max. dimensions	Ordering code	Ammo	Reel	Untaped
	f ≤60 Hz		$w \times h \times l$	(composition see	pack		
V DC	V AC	μF	mm	below)	pcs./MOQ	pcs./MOQ	pcs./MOQ
63	40	22	$12.0 \times 22.0 \times 41.5$	B32526R0226+***	_	_	1620
		33	$12.0\times22.0\times41.5$	B32526R0336+***	_	_	1620
		47	$12.0\times22.0\times41.5$	B32526R0476+***	_	_	1620
		56	$24.0\times15.0\times41.5$	B32526T0566+***	_	_	1040
		68	$16.0\times28.5\times41.5$	B32526R0686+***	_	_	800
		82	$24.0\times19.0\times41.5$	B32526T0826+***	_	_	780
		100	$18.0\times32.5\times41.5$	B32526R0107+***	_	_	720
		150	$20.0\times39.5\times42.0$	B32526R0157+***	_	_	640
_		220	$28.0\times42.5\times42.0$	B32526R0227A***	_	_	440
100	63	15	$12.0\times22.0\times41.5$	B32526R1156+***	_	_	1620
		22	$12.0\times22.0\times41.5$	B32526R1226+***	—	_	1620
		33	$14.0\times25.0\times41.5$	B32526R1336+***	—	_	1380
		33	$24.0\times15.0\times41.5$	B32526T1336+***	—	_	1040
		47	$16.0\times28.5\times41.5$	B32526R1476+***	_	_	800
		47	$24.0\times19.0\times41.5$	B32526T1476+***	_	_	780
		68	$18.0\times32.5\times41.5$	B32526R1686+***	_	_	720
		100	$20.0\times39.5\times42.0$	B32526R1107+***	_	_	640
		150	$28.0\times42.5\times42.0$	B32526R1157+***	_	_	440
250	160	4.7	$12.0\times22.0\times41.5$	B32526R3475+***	-	-	1620
		6.8	$12.0\times22.0\times41.5$	B32526R3685+***	—	_	1620
		10	$12.0\times22.0\times41.5$	B32526R3106+***	_	_	1620
		15	$14.0\times25.0\times41.5$	B32526R3156+***	_	_	1380
		15	$24.0\times15.0\times41.5$	B32526T3156+***	_	_	1040
		22	$16.0\times28.5\times41.5$	B32526R3226+***	_	_	800
		22	$24.0\times19.0\times41.5$	B32526T3226+***	_	_	780
		33	$20.0\times39.5\times42.0$	B32526R3336+***	_	_	640
		47	$20.0\times39.5\times42.0$	B32526R3476+***	_	-	640
		68	$28.0\times42.5\times42.0$	B32526R3686+***	—	—	440

MOQ = Minimum Order Quantity, consisting of 4 packing units. Further E series and intermediate capacitance values on request.

#### Composition of ordering code

+ = Capacitance tolerance code:

 $M = \pm 20\%$ 

 $K = \pm 10\%$ 

$$J = \pm 5\%$$

 $A = -15 \dots +5\%$  (220 µF type only)

\*\*\* = Packaging code:

000 = Untaped (standard lead length 6 -1 mm)





## B32526 General purpose (wound)

#### Ordering codes and packing units (lead spacing 37.5 mm)

V <sub>R</sub>	V <sub>RMS</sub>	C <sub>R</sub>	Max. dimensions	Ordering code	Ammo	Reel	Untaped
	f ≤60 Hz		$w \times h \times I$	(composition see	pack		
V DC	V AC	μF	mm	below)	pcs./MOQ	pcs./MOQ	pcs./MOQ
400	200	3.3	$12.0\times22.0\times41.5$	B32526R6335+***	_	-	1620
		4.7	$12.0\times22.0\times41.5$	B32526R6475+***	_	-	1620
		5.6	$24.0\times15.0\times41.5$	B32526T6565+***	_	-	1040
		6.8	$14.0\times25.0\times41.5$	B32526R6685+***	_	-	1380
		8.2	$24.0\times19.0\times41.5$	B32526T6825+***	_	-	780
		10	$18.0\times32.5\times41.5$	B32526R6106+***	_	-	720
		15	$20.0\times39.5\times42.0$	B32526R6156+***	_	-	640
		22	$28.0\times42.5\times42.0$	B32526R6226+***	—	-	440

MOQ = Minimum Order Quantity, consisting of 4 packing units. Further E series and intermediate capacitance values on request.

#### Composition of ordering code

+ = Capacitance tolerance code:

\*\*\* = Packaging code:

000 = Untaped (standard lead length 6 -1 mm)

- $\begin{array}{l} M=\pm20\%\\ K=\pm10\% \end{array}$
- $J = \pm 5\%$
- A = -15 ... +5% (220  $\mu\text{F}$  type only)



B32520 ... B32529

MKT

General purpose (stacked/wound)

## **Technical data**

Reference standard: IEC 60384-2:2005. AEC-Q200D compliance on request. All data given at T = 20  $^\circ\text{C},$  unless otherwise specified.

Rated temperature $T_{\rm B}$	+85 °C				
Operating temperature range		ng temperature	T <sub>op max</sub>	+125 °C	
	-	ory temperature		+125 °C	
		ory temperature		−55 °C	
	Rated tempe			+85 °C	
Dissipation factor tan $\delta$ (in 10 <sup>-3</sup> )	· · · ·	C <sub>B</sub> ≤ 0.1 μF	0.1 μF < C	C <sub>B</sub> ≤1μF	C <sub>R</sub> > 1 μF
at 20 °C (upper limit values)	1 kHz	8	8		10
	10 kHz	15	15		_
	100 kHz	30	_		_
Insulation resistance R <sub>ins</sub>	V <sub>B</sub>	C <sub>B</sub> ≤ 0.33 μF		C <sub>R</sub> > 0.33	μF
or time constant $\tau = C_R \cdot R_{ins}$	≤ 100 V DC	3750 MΩ		1250 s	•
at 20 °C, rel. humidity $\leq$ 65%	≥ 250 V DC	7500 MΩ		2500 s	
(minimum as-delivered values)					
DC test voltage	$1.4 \cdot V_R$ , 2 s	1		1	
Category voltage V <sub>c</sub>	T <sub>op</sub> (°C)	DC voltage de	erating	AC voltage	e derating
(continuous operation with	$T_{op} \le 85$			$V_{C,RMS} = V_{RMS}$	
$V_{DC}$ or $V_{AC}$ at f $\leq$ 60 Hz)	85 <t<sub>op≤125</t<sub>	$V_{\rm C} = V_{\rm R} \cdot (165)$	5-T <sub>op</sub> )/80	V <sub>C,RMS</sub> =V <sub>RI</sub>	$_{\rm MS} \cdot (165 - T_{\rm op})/80$
Operating voltage $V_{op}$ for	T <sub>op</sub> (°C)	DC voltage (max. hours)		-	
short operating periods	$T_{op} \le 100$			$V_{op} = 1.0 \cdot V_{C,RMS} (2000 \text{ h})$	
( $V_{DC}$ or $V_{AC}$ at f $\leq$ 60 Hz)	100 <t<sub>op≤125</t<sub>	$V_{op} = 1.25 \cdot V_{op}$	<sub>c</sub> (1000 h)	$V_{op} = 1.0$ ·	V <sub>C,RMS</sub> (1000 h)
Biased humidity	1000 h / 40 °	C / 93% relativ	e humidity	with $V_{R,DC}$	
Limit value after biased humidity test	Capacitance	change  ∆C/C		≤ 5%	
	Dissipation fa	actor change $\Delta$	tan δ	$\leq 5 \cdot 10^{-3}$	(at 1 kHz)
	Insulation res	sistance R <sub>ins</sub>		≥ 50% of	minimum
	or time const	ant $\tau = C_R \cdot R_{ir}$	าร	as-deliver	ed values
Reliability:					
Failure rate $\lambda$	1 fit (≤ 1 · 10	<sup>-9</sup> /h) at 0.5 · V <sub>F</sub>	₁, 40 °C		
Service life t <sub>SL</sub>	200 000 h at	$1.0 \cdot V_R$ , 85 °C	;		
	For conversion	on to other ope	rating cond	ditions and	temperatures,
Failure criteria:	refer to chap	ter "Quality, 2 F	Reliability".		
Total failure	Short circuit	or open circuit			
Failure due to variation	Capacitance	change $ \Delta C/C$		> 10%	
of parameters	Dissipation fa	actor tan $\delta$		> 2 · uppe	er limit value
	Insulation res	sistance R <sub>ins</sub>		< 150 MΩ	$2 (C_R \le 0.33 \ \mu F)$
	or time const	$ant \tau = C_R \cdot R_{ir}$	าร	< 50 s	$(C_R > 0.33 \ \mu F)$





B32520 ... B32529

General purpose (stacked/wound)

## Pulse handling capability

"dV/dt" represents the maximum permissible voltage change per unit of time for non-sinusoidal voltages, expressed in  $V/\mu s$ .

" $k_0$ " represents the maximum permissible pulse characteristic of the waveform applied to the capacitor, expressed in V<sup>2</sup>/µs.

Note:

The values of dV/dt and  $k_0$  provided below must not be exceeded in order to avoid damaging the capacitor.

## dV/dt values

Lead s	pacing	5 mm	7.5 mm	10 mm		15 mm		22.5 mm	27.5 mm	37.5 mm
Techno	ology	S	S	S	S W		W	W	W	W
V <sub>R</sub>	$V_{\text{RMS}}$									
V DC	V AC	dV/dt in V	<b>/</b> /μs							
50	32	200	_	_	_	_	_	_	_	_
63	40	250	120	50	_	30	_	3	1	0.8
100	63	300	150	75	_	50	5	4	3	1
250	160	400	200	150	_	100	10	8	5	4
400	200	600	275	175	_	125	_	10	8.5	6
450	200	_	_	_	_	_	20	_	_	_
630	400	800	—	320	—	150	_	15	12	_
S = Sta	S = Stacked, W = Wound									

#### k<sub>0</sub> values

Lead s	pacing	5 mm	7.5 mm	10 mm	10 mm		15 mm		27.5 mm	37.5 mm
Techno	ology	S	S	S	S W		W	W	W	W
V <sub>R</sub>	$V_{\text{RMS}}$									
V DC	V AC	$k_0$ in V²/µ	S							
50	32	20000	_	_	_	_	_	_	_	_
63	40	30000	15000	6300	_	3800	_	375	130	100
100	63	60000	30000	15000	_	10000	850	800	600	200
250	160	200000	100000	75000	_	50000	5000	4000	2500	2000
400	200	500000	220000	140000	_	100000	_	10000	8500	6000
450	200	_	_	_	_	—	15000	—	_	_
630	400	1000000	_	400000	_	190000	_	18000	15000	
S = Sta	S = Stacked, W = Wound									




MKT

## B32520 ... B32529

## General purpose (stacked/wound)

## Impedance Z versus frequency f

(typical values)









## Permissible AC voltage V<sub>RMS</sub> versus frequency f (for sinusoidal waveforms, T<sub>A</sub> ≤55 °C)

For  $T_A > 55 \,^{\circ}C$ , please refer to "General technical information", section 3.2.3.


## Lead spacing 5 mm





100 V DC/63 V AC



63 V DC/40 V AC







Please read Cautions and warnings and Important notes at the end of this document. Downloaded from



MKT

5

General purpose (stacked)


B32529

## Permissible AC voltage V<sub>RMS</sub> versus frequency f (for sinusoidal waveforms, T<sub>A</sub> $\leq$ 55 °C)


For  $T_A > 55 \,^{\circ}C$ , please refer to "General technical information", section 3.2.3.

## Lead spacing 5 mm

400 V DC/200 V AC



#### 630 V DC/400 V AC









## Permissible AC voltage V\_{RMS} versus frequency f (for sinusoidal waveforms, T\_A $\leq$ 55 °C)


For  $T_A > 55 \,^{\circ}C$ , please refer to "General technical information", section 3.2.3.

## Lead spacing 7.5 mm







250 V DC/160 V AC



100 V DC/63 V AC







Please read *Cautions and warnings* and *Important notes* at the end of this document. Downloaded from Arrow.com.



B32521

MKT

10


General purpose (stacked/wound)

## Permissible AC voltage V\_{RMS} versus frequency f (for sinusoidal waveforms, T\_A $\leq$ 55 °C)


For  $T_A > 55 \,^{\circ}C$ , please refer to "General technical information", section 3.2.3.

## Lead spacing 10 mm


63 V DC/40 V AC




250 V DC/160 V AC



100 V DC/63 V AC










## Permissible AC voltage V\_{RMS} versus frequency f (for sinusoidal waveforms, T\_A $\leq$ 55 °C)

For  $T_A > 55 \,^{\circ}C$ , please refer to "General technical information", section 3.2.3.

## Lead spacing 10 mm

630 V DC/200 V AC





B32522

MKT


15


General purpose (stacked/wound)


## Permissible AC voltage V\_{RMS} versus frequency f (for sinusoidal waveforms, T\_A $\leq$ 55 °C)

For  $T_A > 55 \,^{\circ}C$ , please refer to "General technical information", section 3.2.3.


## Lead spacing 15 mm









#### 100 V DC/63 V AC







Please read *Cautions and warnings* and *Important notes* at the end of this document. Downloaded from Arrow.com.







## Permissible AC voltage V<sub>RMS</sub> versus frequency f (for sinusoidal waveforms, T<sub>A</sub> $\leq$ 55 °C)


For  $T_A > 55 \,^{\circ}C$ , please refer to "General technical information", section 3.2.3.

## Lead spacing 15 mm





#### 630 V DC/200 V AC









## Permissible AC voltage V<sub>RMS</sub> versus frequency f (for sinusoidal waveforms, T<sub>A</sub> ≤55 °C)


For  $T_A > 55 \,^{\circ}C$ , please refer to "General technical information", section 3.2.3.

## Lead spacing 22.5 mm





## 100 V DC/63 V AC



0.22 µF

0.68 µF

1.0 µF 1.5 µF

 $5 \ 10^4$ 

 $5 \ 10^{5}$ 

Hz 10<sup>6</sup>

- f

5 10<sup>3</sup>

10

6

4

2

1 └── 10<sup>2</sup>






## Permissible AC voltage V<sub>RMS</sub> versus frequency f (for sinusoidal waveforms, T<sub>A</sub> $\leq$ 55 °C)

For  $T_A > 55 \,^{\circ}C$ , please refer to "General technical information", section 3.2.3.

## Lead spacing 22.5 mm

630 V DC/200 V AC





MKT


27.5



## Permissible AC voltage V\_{RMS} versus frequency f (for sinusoidal waveforms, T\_A $\leq$ 55 °C)

For  $T_A > 55 \,^{\circ}C$ , please refer to "General technical information", section 3.2.3.

## Lead spacing 27.5 mm



Please read *Cautions and warnings* and *Important notes* at the end of this document. Downloaded from Arrow.com.






## Permissible AC voltage V<sub>RMS</sub> versus frequency f (for sinusoidal waveforms, T<sub>A</sub> $\leq$ 55 °C)

For  $T_A > 55 \,^{\circ}C$ , please refer to "General technical information", section 3.2.3.


## Lead spacing 27.5 mm

630 V DC/220 V AC






KMK1226-T




## Permissible AC voltage $V_{RMS}$ versus frequency f (for sinusoidal waveforms, $T_A \leq 55 \ ^{\circ}C$ )

For  $T_A > 55 \,^{\circ}C$ , please refer to "General technical information", section 3.2.3.

## Lead spacing 37.5 mm



#### 100 V DC/63 V AC



6

4

2

1 └─ 10<sup>1</sup>

10 µF

15 µF

47 μF

5 10<sup>3</sup>

5 10<sup>4</sup>

Hz 10<sup>5</sup>

5 10<sup>2</sup>

1 └ 10<sup>1</sup>

5 10<sup>2</sup>

5 10<sup>3</sup>

5 10<sup>4</sup>

Hz 10<sup>5</sup>

f





## **Mounting guidelines**

#### 1 Soldering

#### 1.1 Solderability of leads

The solderability of terminal leads is tested to IEC 60068-2-20:2008, test Ta, method 1.

Before a solderability test is carried out, terminals are subjected to accelerated ageing (to IEC 60068-2-2:2007, test Ba: 4 h exposure to dry heat at 155 °C). Since the ageing temperature is far higher than the upper category temperature of the capacitors, the terminal wires should be cut off from the capacitor before the ageing procedure to prevent the solderability being impaired by the products of any capacitor decomposition that might occur.

Solder bath temperature	235 ±5 °C
Soldering time	2.0 ±0.5 s
Immersion depth	2.0 +0/ $-0.5$ mm from capacitor body or seating plane
Evaluation criteria:	
Visual inspection	Wetting of wire surface by new solder ≥90%, free-flowing solder

#### 1.2 Resistance to soldering heat

Resistance to soldering heat is tested to IEC 60068-2-20:2008, test Tb, method 1. Conditions:


Serie	S	Solder bath temperature	Soldering time
MKT	boxed (except $2.5 \times 6.5 \times 7.2$ mm) coated uncoated (lead spacing >10 mm)	260 ±5 °C	10 ±1 s
MFP MKP	(lead spacing >7.5 mm)		
MKT	boxed (case $2.5 \times 6.5 \times 7.2$ mm)		5±1 s
MKP MKT	(lead spacing ≤7.5 mm) uncoated (lead spacing ≤10 mm) insulated (B32559)		<4 s recommended soldering profile for MKT uncoated (lead spacing $\leq$ 10 mm) and insulated (B32559)

# **公TDK**



## B32520 ... B32529

## General purpose (stacked/wound)



Immersion depth	2.0 + 0/-0.5 mm from capacitor body or seating plane
Shield	Heat-absorbing board, (1.5 $\pm$ 0.5) mm thick, between
	capacitor body and liquid solder
Evaluation criteria:	
Visual inspection	No visible damage
	2% for MKT/MKP/MFP
$\Delta C/C_0$	5% for EMI suppression capacitors
tan δ	As specified in sectional specification

## 1.3 General notes on soldering

Permissible heat exposure loads on film capacitors are primarily characterized by the upper category temperature  $T_{max}$ . Long exposure to temperatures above this type-related temperature limit can lead to changes in the plastic dielectric and thus change irreversibly a capacitor's electrical characteristics. For short exposures (as in practical soldering processes) the heat load (and thus the possible effects on a capacitor) will also depend on other factors like:

- Pre-heating temperature and time
- Forced cooling immediately after soldering
- Terminal characteristics: diameter, length, thermal resistance, special configurations (e.g. crimping)
- Height of capacitor above solder bath
- Shadowing by neighboring components
- Additional heating due to heat dissipation by neighboring components
- Use of solder-resist coatings






The overheating associated with some of these factors can usually be reduced by suitable countermeasures. For example, if a pre-heating step cannot be avoided, an additional or reinforced cooling process may possibly have to be included.

#### Recommendations

As a reference, the recommended wave soldering profile for our film capacitors is as follows:



KMK1744-9-E



B32520 ... B32529

MKT

General purpose (stacked/wound)

Body temperature should follow the description below:

- MKP capacitor During pre-heating: T<sub>p</sub> ≤110 °C During soldering: T<sub>s</sub> ≤120 °C, t<sub>s</sub> ≤45 s
- MKT capacitor During pre-heating: T<sub>p</sub> ≤125 °C During soldering: T<sub>s</sub> ≤160 °C, t<sub>s</sub> ≤45 s

When SMD components are used together with leaded ones, the film capacitors should not pass into the SMD adhesive curing oven. The leaded components should be assembled after the SMD curing step.

Leaded film capacitors are not suitable for reflow soldering.

In order to ensure proper conditions for manual or selective soldering, the body temperature of the capacitor (T<sub>s</sub>) must be  $\leq$ 120 °C.

One recommended condition for manual soldering is that the tip of the soldering iron should be <360 °C and the soldering contact time should be no longer than 3 seconds.

For uncoated MKT capacitors with lead spacings  $\leq$ 10 mm (B32560/B32561) the following measures are recommended:

- pre-heating to not more than 110 °C in the preheater phase
- rapid cooling after soldering

Please refer to our Film Capacitors Data Book in case more details are needed.



мкт

B32520 ... B32529

General purpose (stacked/wound)

## **Cautions and warnings**

- Do not exceed the upper category temperature (UCT).
- Do not apply any mechanical stress to the capacitor terminals.
- Avoid any compressive, tensile or flexural stress.
- Do not move the capacitor after it has been soldered to the PC board.
- Do not pick up the PC board by the soldered capacitor.
- Do not place the capacitor on a PC board whose PTH hole spacing differs from the specified lead spacing.
- Do not exceed the specified time or temperature limits during soldering.
- Avoid external energy inputs, such as fire or electricity.
- Avoid overload of the capacitors.
- Consult us if application is with severe temperature and humidity condition.
- There are no serviceable or repairable parts inside the capacitor. Opening the capacitor or any attempts to open or repair the capacitor will void the warranty and liability of TDK Electronics.
- Please note that the standards referred to in this publication may have been revised in the meantime.

The table below summarizes the safety instructions that must always be observed. A detailed description can be found in the relevant sections of the chapters "General technical information" and "Mounting guidelines".

Торіс	Safety information	Reference chapter "General technical information"
Storage conditions	Make sure that capacitors are stored within the specified range of time, temperature and humidity conditions.	4.5 "Storage conditions"
Flammability	Avoid external energy, such as fire or electricity (passive flammability), avoid overload of the capacitors (active flammability) and consider the flammability of materials.	5.3 "Flammability"
Resistance to vibration	Do not exceed the tested ability to withstand vibration. The capacitors are tested to IEC 60068-2-6:2007. TDK Electronics offers film capacitors specially designed for operation under more severe vibration regimes such as those found in automotive applications. Consult our catalog "Film Capacitors for Automotive Electronics".	5.2 "Resistance to vibration"



B32520 ... B32529

MKT

General purpose (stacked/wound)

Topic	Safety information	Reference chapter "Mounting guidelines"
Soldering	Do not exceed the specified time or temperature limits during soldering.	1 "Soldering"
Cleaning	Use only suitable solvents for cleaning capacitors.	2 "Cleaning"
Embedding of capacitors in finished assemblies	When embedding finished circuit assemblies in plastic resins, chemical and thermal influences must be taken into account. Caution: Consult us first, if you also wish to embed other uncoated component types!	3 "Embedding of capacitors in finished assemblies"

#### Display of ordering codes for TDK Electronics products

The ordering code for one and the same product can be represented differently in data sheets, data books, other publications, on the company website, or in order-related documents such as shipping notes, order confirmations and product labels. The varying representations of the ordering codes are due to different processes employed and do not affect the specifications of the respective products.

Detailed information can be found on the Internet under

www.tdk-electronics.tdk.com/orderingcodes.

## Correlation of data sheet values and modelling tool outputs

Data sheet values and results of design tools may deviate as they have not been derived in the same context.

While data sheets show individual parameter statements without considering a possible dependency to other parameters. Tools model a complete given scenario as input and processed inside the tool.

Furthermore as we constantly strive to improve our models, the results of tools can change over time and be a non-binding indication only.



мкт **Т**-----

## B32520 ... B32529

General purpose (stacked/wound)

## Symbols and terms

Symbol	English	German
α	Heat transfer coefficient	Wärmeübergangszahl
$\alpha_{c}$	Temperature coefficient of capacitance	Temperaturkoeffizient der Kapazität
Α	Capacitor surface area	Kondensatoroberfläche
βc	Humidity coefficient of capacitance	Feuchtekoeffizient der Kapazität
С	Capacitance	Kapazität
C <sub>R</sub>	Rated capacitance	Nennkapazität
$\Delta C$	Absolute capacitance change	Absolute Kapazitätsänderung
$\Delta C/C$	Relative capacitance change (relative	Relative Kapazitätsänderung (relative
	deviation of actual value)	Abweichung vom Ist-Wert)
$\Delta C/C_R$	Capacitance tolerance (relative deviation	
	from rated capacitance)	vom Nennwert)
dt	Time differential	Differentielle Zeit
$\Delta t$	Time interval	Zeitintervall
$\Delta T$	Absolute temperature change	Absolute Temperaturänderung
	(self-heating)	(Selbsterwärmung)
∆tan δ	Absolute change of dissipation factor	Absolute Änderung des Verlustfaktors
$\Delta V$	Absolute voltage change	Absolute Spannungsänderung
dV/dt	Time differential of voltage function (rate	Differentielle Spannungsänderung
	of voltage rise)	(Spannungsflankensteilheit)
$\Delta V / \Delta t$	Voltage change per time interval	Spannungsänderung pro Zeitintervall
E	Activation energy for diffusion	Aktivierungsenergie zur Diffusion
ESL	Self-inductance	Eigeninduktivität
ESR	Equivalent series resistance	Ersatz-Serienwiderstand
f	Frequency	Frequenz
f <sub>1</sub>	Frequency limit for reducing permissible	Grenzfrequenz für thermisch bedingte
	AC voltage due to thermal limits	Reduzierung der zulässigen
		Wechselspannung
f <sub>2</sub>	Frequency limit for reducing permissible	Grenzfrequenz für strombedingte
	AC voltage due to current limit	Reduzierung der zulässigen
٤	Decement frequency	Wechselspannung
f <sub>r</sub>	Resonant frequency	Resonanzfrequenz
F <sub>D</sub>	Thermal acceleration factor for diffusion	Therm. Beschleunigungsfaktor zur Diffusion
F <sub>T</sub>	Derating factor	Deratingfaktor
i	Current (peak)	Stromspitze
I <sub>C</sub>	Category current (max. continuous	Kategoriestrom (max. Dauerstrom)
	current)	



B32520 ... B32529

MKT

General purpose (stacked/wound)

Symbol	English	German
I <sub>RMS</sub>	(Sinusoidal) alternating current, root-mean-square value	(Sinusförmiger) Wechselstrom
l <sub>z</sub>	Capacitance drift	Inkonstanz der Kapazität
k <sub>o</sub>	Pulse characteristic	Impulskennwert
Ls	Series inductance	Serieninduktivität
λ	Failure rate	Ausfallrate
λο	Constant failure rate during useful	Konstante Ausfallrate in der
	service life	Nutzungsphase
$\lambda_{\text{test}}$	Failure rate, determined by tests	Experimentell ermittelte Ausfallrate
$P_{diss}$	Dissipated power	Abgegebene Verlustleistung
$P_{gen}$	Generated power	Erzeugte Verlustleistung
Q	Heat energy	Wärmeenergie
ρ	Density of water vapor in air	Dichte von Wasserdampf in Luft
R	Universal molar constant for gases	Allg. Molarkonstante für Gas
R	Ohmic resistance of discharge circuit	Ohmscher Widerstand des
		Entladekreises
R <sub>i</sub>	Internal resistance	Innenwiderstand
<b>R</b> <sub>ins</sub>	Insulation resistance	Isolationswiderstand
R <sub>P</sub>	Parallel resistance	Parallelwiderstand
Rs	Series resistance	Serienwiderstand
S	severity (humidity test)	Schärfegrad (Feuchtetest)
t	Time	Zeit
Т	Temperature	Temperatur
τ	Time constant	Zeitkonstante
tan δ	Dissipation factor	Verlustfaktor
$tan \; \delta_{\scriptscriptstyle D}$	Dielectric component of dissipation factor	Dielektrischer Anteil des Verlustfaktors
tan $\delta_P$	Parallel component of dissipation factor	Parallelanteil des Verlfustfaktors
tan $\delta_s$	Series component of dissipation factor	Serienanteil des Verlustfaktors
T <sub>A</sub>	Temperature of the air surrounding the component	Temperatur der Luft, die das Bauteil umgibt
T <sub>max</sub>	Upper category temperature	Obere Kategorietemperatur
T <sub>min</sub>	Lower category temperature	Untere Kategorietemperatur
t <sub>OL</sub>	Operating life at operating temperature and voltage	Betriebszeit bei Betriebstemperatur und -spannung
T <sub>op</sub>	Operating temperature, $T_A + \Delta T$	Beriebstemperatur, $T_A + \Delta T$
T <sub>R</sub>	Rated temperature	Nenntemperatur
T <sub>ref</sub>	Reference temperature	Referenztemperatur
t <sub>SL</sub>	Reference service life	Referenz-Lebensdauer



мкт **Т**----

## B32520 ... B32529

## General purpose (stacked/wound)

Symbol	English	German
V <sub>AC</sub>	AC voltage	Wechselspannung
V <sub>c</sub>	Category voltage	Kategoriespannung
$V_{C,RMS}$	Category AC voltage	(Sinusförmige)
		Kategorie-Wechselspannung
$V_{CD}$	Corona-discharge onset voltage	Teilentlade-Einsatzspannung
$V_{ch}$	Charging voltage	Ladespannung
$V_{\text{DC}}$	DC voltage	Gleichspannung
$V_{FB}$	Fly-back capacitor voltage	Spannung (Flyback)
Vi	Input voltage	Eingangsspannung
Vo	Output voltage	Ausgangssspannung
$V_{op}$	Operating voltage	Betriebsspannung
$V_p$	Peak pulse voltage	Impuls-Spitzenspannung
$V_{pp}$	Peak-to-peak voltage Impedance	Spannungshub
V <sub>R</sub>	Rated voltage	Nennspannung
ν <sub>R</sub>	Amplitude of rated AC voltage	Amplitude der Nenn-Wechselspannung
$V_{\text{RMS}}$	(Sinusoidal) alternating voltage,	(Sinusförmige) Wechselspannung
	root-mean-square value	
$V_{\text{SC}}$	S-correction voltage	Spannung bei Anwendung "S-correction"
$V_{sn}$	Snubber capacitor voltage	Spannung bei Anwendung
		"Beschaltung"
Z	Impedance	Scheinwiderstand
е	Lead spacing	Rastermaß



The following applies to all products named in this publication:

- 1. Some parts of this publication contain statements about the suitability of our products for certain areas of application. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out that such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application. As a rule, we are either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether a product with the properties described in the product specification is suitable for use in a particular customer application.
- 2. We also point out that in individual cases, a malfunction of electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health (e.g. in accident prevention or lifesaving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of an electronic component.
- 3. The warnings, cautions and product-specific notes must be observed.
- 4. In order to satisfy certain technical requirements, some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as hazardous). Useful information on this will be found in our Material Data Sheets on the Internet (www.tdk-electronics.tdk.com/material). Should you have any more detailed questions, please contact our sales offices.
- 5. We constantly strive to improve our products. Consequently, the products described in this publication may change from time to time. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order. We also reserve the right to discontinue production and delivery of products. Consequently, we cannot guarantee that all products named in this publication will always be available. The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.
- 6. Unless otherwise agreed in individual contracts, all orders are subject to our General Terms and Conditions of Supply.



#### Important notes

- 7. Our manufacturing sites serving the automotive business apply the IATF 16949 standard. The IATF certifications confirm our compliance with requirements regarding the quality management system in the automotive industry. Referring to customer requirements and customer specific requirements ("CSR") TDK always has and will continue to have the policy of respecting individual agreements. Even if IATF 16949 may appear to support the acceptance of unilateral requirements, we hereby like to emphasize that only requirements mutually agreed upon can and will be implemented in our Quality Management System. For clarification purposes we like to point out that obligations from IATF 16949 shall only become legally binding if individually agreed upon.
- 8. The trade names EPCOS, CarXield, CeraCharge, CeraDiode, CeraLink, CeraPad, CeraPlas, CSMP, CTVS, DeltaCap, DigiSiMic, ExoCore, FilterCap, FormFit, LeaXield, MiniBlue, MiniCell, MKD, MKK, ModCap, MotorCap, PCC, PhaseCap, PhaseCube, PhaseMod, PhiCap, PowerHap, PQSine, PQvar, SIFERRIT, SIFI, SIKOREL, SilverCap, SIMDAD, SiMic, SIMID, SineFormer, SIOV, ThermoFuse, WindCap, XieldCap are trademarks registered or pending in Europe and in other countries. Further information will be found on the Internet at www.tdk-electronics.tdk.com/trademarks.

Release 2020-06