


GLASS PASSIVATED BRIDGE RECTIFIERS

REVERSE VOLTAGE - 50 to 1000Volts
FORWARD CURRENT - 10 Amperes

FEATURES

- Rating to 1000V PRV
- Ideal for printed circuit board
- Low forward voltage drop, high current capability
- Reliable low cost construction utilizing molded plastic technique results in inexpensive product
- The plastic material has UL flammability classification 94V-0



Dimensions in inches and (millimeters)

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Rating at 25°C ambient temperature unless otherwise specified.

Single phase, half wave, 60Hz, resistive or inductive load.

For capacitive load, derate current by 20%

CHARACTERISTICS	SYMBOL	GBJ 10005	GBJ 1001	GBJ 1002	GBJ 1004	GBJ 1006	GBJ 1008	GBJ 1010	UNIT
Maximum Recurrent Peak Reverse Voltage	V_{RRM}	50	100	200	400	600	800	1000	V
Maximum RMS Voltage	V_{RMS}	35	70	140	280	420	560	700	V
Maximum DC Blocking Voltage	V_{DC}	50	100	200	400	600	800	1000	V
Maximum Average Forward Rectified Current @ $T_c=110^\circ\text{C}$ (with heatsink Note 2) @ $T_c=110^\circ\text{C}$ (without heatsink)	$I_{(AV)}$	10.0 3.5						A	
Peak Forward Surge Current 8.3ms Single Half Sine-Wave Super Imposed on Rated Load (JEDEC Method)	I_{FSM}	220						A	
Maximum Forward Voltage at 5.0A DC	V_F	1.0						V	
Maximum DC Reverse Current @ $T_J=25^\circ\text{C}$ at Rated DC Blocking Voltage @ $T_J=125^\circ\text{C}$	I_R	10.0 500						μA	
I^2t Rating for Fusing ($t < 8.3\text{ms}$)	I^2t	200.86						A^2s	
Typical Junction Capacitance Per Element (Note1)	C_J	55						pF	
Typical Thermal Resistance	$R_{\theta JC}$	1.4						$^\circ\text{C}/\text{W}$	
Operating Temperature Range	T_J	-55 to +150						$^\circ\text{C}$	
Storage Temperature Range	T_{STG}	-55 to +150						$^\circ\text{C}$	

NOTES: 1. Measured at 1.0MHz and applied reverse voltage of 4.0V DC.

2. Device mounted on 150mm*150mm*1.6mm Cu plate heatsink.

3. The typical data above is for reference only (典型值仅供参考).

FIG.1-FORWARD CURRENT DERATING CURVE




FIG.2-MAXMUN NON-REPETITIVE SURGE CURRENT




FIG.3-TYPICAL JUNCTION CAPACITANCE




FIG.4-TYPICAL FORWARD CHARACTERISTICS





FIG.5-TYPICAL REVERSE CHARACTERISTICS



The cruve graph is for reference only, can't be the basis for judgment(曲线图仅供参考)!