

A50.20.100 0...120°C L1=60x9mm copper alloy CL.2

Bimetallic thermometer TYP48-50

Item number: 12013811

Quantity: 1 pcs.

Order code: A50.20.100-H-C1F-060DMFRGD-1ZZZZZZZBK-ZZZ

2BZTM5003

Overview: A50.20.100 0...120°C L1=60x9mm copper alloy CL.2
Case material: steel, zinc plated
Pointer: plastic, black Window: acrylic, (SAN)
detachable, with retainer screw; Mat.=Cu-alloy G1/2B
Dial background: white
WIKA
Data sheet: TM50.03

Details: Bimetallic thermometer TYP48-50
Model: A50 Standard version
Design: standard, steel case
Nominal size [NG, d1]: 100 mm
Case material: steel, zinc plated
Unit: °C
Scale range: 0 °C ... 120 °C
Insertion length L1: 60 mm
Stem diameter: 9 mm
Stem material: copper alloy
Thermowell: detachable, with retainer screw;
Thermowell material: Cu-alloy
Process connection: G 1/2 B
Manufacturer logo: *WIKA*
Pointer: plastic, black
Window: acrylic, (SAN)
Accuracy class: class 2 per EN 13190
Dial background: White
Data sheet: TM50.03