


1. Wiring Diagram.



2. Cable test condition :  
 Open / Short : 100%  
 Insulation resistance : 5M ohms  
 Contact resistance : 2 ohm  
 Hipot : DC 300V / 1 sec

3. Each pcs with PE polybag.

9	PVC	45P PVC BLUE OVERMOLD	18g	P2
8	SCREW	#4-40UNC T41.2 BLUE	2	
7	CONN	HD15 BLU MALE G/F	1	P2
6	SCREW	#4-40UNC RE34 WHITE	2	
5	PE	LLDPE 500026 6201	16g	
4	PVC	45P PVC WHITE OVERMOLD	22g	
3	CORE	OD17.5*L28.5*ID9.5	2	
2	CONN	DVI24+5 MALE G/F BLK	1	P1
1	CABLE	UL2919 «1C*28AWG (7/0.12TC) +AL+S24/0.12TCCA» *3C+6C*28AWG (7/0.12TC) +A+B (96/0.12AM) +D OD8.0 BLACK	1	5000mm
NO.	PART NO.	DESCRIPTION	QTY	UNIT/REF

BILL OF MATERIAL

B	ADD COPPER	2021/8/24
A	INITIAL RELEASE	2014/11/12
REV/ECN	DESCRIPTION	DATE
	P/N:	751-20010-00500
	TITLE	OBL DVI+TO VGA 24+5-15PIN
DRAWN	WENC	DATE 08/24/21
CHECKED	EDWIN	DATE 08/24/21
APPROVAL		
CUSTOMER P/N:		
CUSTOMER:		
SHEET	1 OF 1	

Cnc Tech,LLC

