C4AF, Radial, 2 or 4 Leads, 250 – 400 VAC, for Harsh Environment AC Filtering (Automotive Grade)



Overview

The C4AF capacitor is a polypropylene metallized film capacitor with a rectangular, plastic box-type design (white or grey in color) filled with resin, and uses 2 or 4 tinned copper wires. These capacitors are intended to withstand harsh environmental conditions.


Automotive grade devices meet the demanding Automotive Electronics Council's AEC-Q200 qualification requirements.

Applications

Typical applications include clamping, AC and harmonic filtering in UPS systems, motor drives, renewable energy, and automotive systems.

Benefits

- · Self-healing
- Low loss
- High ripple current
- High contact reliability
- · Optimized AC voltage performance
- · Suitable for high frequency applications
- · Able to withstand harsh environmental conditions
- Automotive grades (AEC-Q200)




Part Number System

C4	A	F	1	В	W	5330	Α	3	N	J
Series	Туре	Application	Rated Voltage (VAC)	Case	Terminals Code	Capacitance Code (pF)	C-Spec	Lead Diameter (mm)	Size Code: B x H x L (mm)	Tolerance
C4 = MKP Power Capacitors	A = Box, wire terminals	F = AC filtering	1 = 250 9 = 310 7 = 350 3 = 400	B = Box plastic case E = Box plastic case, extended (> 35 x 50 x 57.5)	U = 2 pins W = 4 pins	Digits 2 - 4 indicate the first three digits of the capacitance value. First digit indicates the number of zeros to be added.	A = Standard Grade	1 = 0.8 3 = 1.2	Digit 6 = B W = 11 x 20 x 31.5 X = 13 x 25 x 31.5 Y = 14 x 28 x 31.5 1 = 19 x 29 x 31.5 2 = 22 x 37 x 31.5 F = 20 x 40 x 42 J = 28 x 37 x 42 L = 30 x 45 x 42 M = 3 0 x 45 x 57.5 N = 35 x 50 x 57.5 Digit 6 = E A = 45 x 56 x 57.5 B = 45 x 65 x 57.5	J = 5% K = 10%



Dimensions - Millimeters



Size	Code		p	р	1		В		1		L	LL		d	
Digit 6	Digit 14	Nominal	Tolerance	Nominal	Tolerance	Nominal	Tolerance	Nominal	Tolerance	Nominal	Tolerance	Nominal	Tolerance	Nominal	Tolerance
В	W	27.5	±0.4	-	-	11.0	+0.3	20.0	+0.2	31.5	+0.5	6	+0/-2	0.8	±0.05
В	Х	27.5	±0.4	-	-	13.0	+0.3	25.0	+0.2	31.5	+0.5	6	+0/-2	0.8	±0.05
В	Υ	27.5	±0.4	-	-	14.0	+0.3	28.0	+0.2	31.5	+0.5	6	+0/-2	0.8	±0.05
В	1	27.5	±0.4	-	-	19.0	+0.3	29.0	+0.2	31.5	+0.5	6	+0/-2	0.8	±0.05
В	2	27.5	±0.4	-	-	22.0	+0.3	37.0	+0.2	31.5	+0.5	6	+0/-2	0.8	±0.05
В	F	37.5	±0.4	5.1/10.2	±0.4	20.0	+0.4	40.0	+0.2	42.0	+0.6	6	+0/-2	1.2	±0.05
В	J	37.5	±0.4	10.2	±0.4	28.0	+0.4	37.0	+0.2	42.0	+0.6	6	+0/-2	1.2	±0.05
В	L	37.5	±0.4	20.3	±0.4	30.0	+0.4	45.0	+0.2	42.0	+0.6	6	+0/-2	1.2	±0.05
В	0	37.5	±0.4	20.3	±0.4	35.0	+0.4	50.0	+0.2	42.0	+0.6	6	+0/-2	1.2	±0.05
В	М	52.5	±0.4	20.3	±0.4	30.0	+0.5	45.0	+0.3	57.5	+0.8	6	+0/-2	1.2	±0.05
В	N	52.5	±0.4	20.3	±0.4	35.0	+0.5	50.0	+0.3	57.5	+0.8	6	+0/-2	1.2	±0.05
Е	Α	52.5	±0.4	20.3	±0.4	45.0	+0.5	56.0	+0.3	57.5	+0.8	6	+0/-2	1.2	±0.05
Е	В	52.5	±0.4	20.3	±0.4	45.0	+0.5	65.0	+0.3	57.5	+0.8	6	+0/-2	1.2	±0.05

Qualification

Reference Standards	IEC 61071, EN 61071, VDE0560
Climatic Category	55/105/56 according to IEC 60068-1

Automotive grade products meet or exceed the requirements outlined by the Automotive Electronics Council. Details regarding test methods and conditions are referenced in document AEC-Q200, Stress Test Qualification for Passive Components. For additional information regarding the Automotive Electronics Council and AEC-Q200, please visit their website at www.aecouncil.com.



General Technical Data

Dielectric	Polypropylene metallized film, non-inductive type, self-healing property
Application	AC Filtering (250 VAC, 310 VAC, 350 VAC, 400 VAC) 250 VAC rating reccomended ONLY for controlled output filtering
Special Features	AEC-Q200 qualified
Climatic Category	55/105/56 IEC 60068-1
Maximum Operating Temperature	105 °C
Lower Operating Temperature	-55°C
Standard	IEC 61071, EN 61071, VDE0560, AEC-Q200
Protection	Solvent resistant plastic case UL 94 V-0 compliant Thermosetting resin sealing UL 94 V-0 compliant
Installation	Any position
Leads	Tinned copper wires - standard lead wire length 6 (+0/-2) mm
Packaging	Packed in cardboard trays with protection for the terminals
RoHS Compliance	Compliant with Directive 2002/95/EC and Directive 2011/65/EU of the European Parliament and of the Council on 8 June 2011, including Commission Delegated Directive (EU) 2015/863 amending Annex II to Directive 2011/65/EU.

Electrical Characteristics

Rated Capacitance Range	1 to 62 μF					
Rated Voltage (VNAC) Range	250 to 400 VAC (50/60 Hz)					
Capacitance Tolerance	$\pm 5\%$ (J) or $\pm 10\%$ (K) measured at T = $\pm 25^{\circ}$ C $\pm 5^{\circ}$ C					
Dissipation Factor PP Maximum (tgδ0)	≤ 0.0007 with T = 25°C ±5°C					
Surge Voltage	$1.5 * V_{NDC}$ for maximum 10 times in lifetime at T = $25 ° C \pm 5 ° C$					
Overveltage (IEC 61071)	1.15 * V_{NDC} for maxijmum 30 minutes, once per day					
Overvoltage (IEC 61071)	1.3 * V _{NDC} for maximum 1 minute, once per day					
Peak Non-Repetitive Current	$1.5 * I_{PKR}$, for maximum 1,000 times in lifetime					
Insulation Resistance	IR x C \geq 30,000 seconds at 100 VDC 1 minute at T = +25°C, \pm 5°C					
Capacitance Deviation in the operating temperature range -55 to 105°C	±2.5% maximum on capacitance value measured at T = +25°C, ±5°C					
Temperature Storage	-40 to +80°C					
Storage time	≤ 36 months from the date marked on the label glued to the package					
Permissible Relative Humidity - Storage	Annual average ≤ 70%, 85% on 30 days/year randomly distributed throughout year. Dewing not admissible.					



Life Expectancy

Life Expectancy	\geq 60,000 hours at V _{NAC} and T _{HS} = +85°C
Capacitance Drop at End of Life	-5% (typical)
Failure Rate	See Life Expectancy/Failure Quota Graphs

Test Method


Peak Non-Repetitive Maximum Current	I _{PKR} x 1.5
Test Voltage Terminal to Terminal $V_{\scriptscriptstyle TT}$	1.5 * V _{NDC} for 10 seconds
Test Voltage Terminal to Case $V_{\tau c}$	2 k VAC - 50/60 Hz for 60 seconds
Endurance Test	500 hours + 500 hours at 1.25 x rated voltage at 85°C
Endurance rest	500 hours + 500 hours at 1.25 x operative voltage t 105°C
Damp Heat	IEC 60068-2-78
	250 and 310 V _{NAC} version:
TUD Took OF (OF with Voltage	240 VAC, 85°C/85% R.H. 500 hours: Δ C/C < 10% and Δ Tg < 3*10 ⁻³ at 1 kHz IR ≥ 50% initial limit
THB Test 85/85 with Voltage	350 and 400 V _{NAC} version:
	310 VAC, 85°C/85% R.H. 500 hours: ΔC/C < 10% and ΔTg < 3*10 ⁻³ at 1 kHz IR ≥ 50% initial limit
Change of Temperature	IEC 60068-2-14

Operative Voltage Derating

	Voltage (VAC)						
Operating Voltage	250	310	350	400			
Rated Voltage at 85°C (T _{HS})	250	310	350	400			
Operating Voltage at 105°C (T _{HS})	175	217	245	280			




Life Expectancy/Failure Quota* Graphs



^{*} Evaluated considering an environmental conditions as dry condition.

Environmental condition reference






Life Expectancy/Failure Quota Graphs cont.

KEMET defines maximum ripple current, based on hot spot/ambient self-heating temperature. For C4AF, maximum allowed self-heating is 30°C, with ambient temperature up to 55°C. DT is reduced linearly with increasing ambient temperature, down to 0°C at 100°C (no self-heating allowed at maximum operating temperature):

$\Delta T_{HS Lim}$ vs. Ambient Temperature





Power Losses & Hot Spot Temperature Calculation

At each frequency, the power lossess are the sum of:

1. Dielectric power losses

$$P_D(f_i) = 2 * \pi * f_i * C * V(f_i)^2 * tg\delta_0$$

which can be alternatively calculated as

$$P_D(f_i) = \frac{l(f_i)^2}{2 * \pi * f_i * C} * tg\delta_0$$

where:

$$tgd_0 = 7 * 10^{-4}$$
 (maximum value)

2. Joule power losses

$$P_J(f_i) = Rs * I(f_i)^2$$

The total power losses are the sum of the components at each frequency:

$$P_{T} = \sum_{i} [P_{D}(f_{i}) + P_{J}(f_{i})]$$

The thermal jump in the hot spot is:

$$\Delta T_{HS} = P_T * R_{th}$$

The hot spot temperature is:

$$T_{HS} = T_a + \Delta T_{HS}$$



Power Losses & Hot Spot Temperature Calculation cont.

Limits for the formulas

The limits listed below should not be exceeded:

$$1. \quad \sqrt{\sum_{i} V(f_{i})^{2}} \leq VAC_{MAX}$$

2.
$$\sqrt{\sum_{i} I(f_{i})^{2}} \leq I_{RMS_{MAX}}$$

$$T_{HS} = T_a + \Delta T_{HS} \le (T_{HS})_{MAX}$$

where Ta is the ambient temperature (steady state temperature of the cooling air flowing around the capacitor, measured at 100 mm of distance from the capacitor and at a height of 2/3 height of the capacitor).

Example of calculation

P/N: C4AF9BW5100A3JK	$P_D(50) = 2 * \pi * 50 * 10 * 10^{-6} * 310^2 * 7 * 10^{-4} = 0.211$ [W]
Rated V _{RMS} = 310 [V _{RMS}]	$P_D(15,000) = [7.9^2/(2 * \pi * 15,000 * 10 * 10^{-6})] * 7 * 10^{-4} = 0.0463 [W]$
Rated I _{RMS MAX} = 16.6 [A]	$P_J(50) = 4.2 * 10^{-3} * [(2 * \pi * 50 * 10 * 10^{-6} * 310)^2] = 0.0398 [W]$
$R_s = 4.2[m\Omega]$	$P_J(15000) = 4.2 * 10^{-3} * 7.9^2 = 0.262 [W]$
R _{th} = 18 [°C/W]	P _T = 0.211+0.0463+0.0398+0.262 =0.5591 [W]
Fundamental Frequency F ₁ = 50 [Hz]	ΔT _{HS} = 18 * 0.559 = 10 [°C]
Ripple Frequency F ₂ = 15,000 [Hz]	T_{HS} = $Ta + \Delta T_{HS}$
Fundamental Voltage V ₁ = 310 [V~]	T_{HS} = 75 + 10 = 85 [°C] » OK since hot spot temperature is less than maximum admitted
Ripple Current I ₂ = 7.9 [A]	Expected Life at T _{HS} = 85°C » 60,000 hours (see lifetime curve)
T _a = 75°C	
$I_1 = I(50) = 2 * \pi * 50 * 10 * 10^{-6} * 310 = 0.973 [A]$	
$V_2 = V(15,000) = [7.9/(2 * \pi * 15,000 * 10 * 10^{-6})] = 8.4 [V]$	



Environmental Compliance

As a leading global supplier of electronic components and an environmentally conscious company, KEMET continually aspires to improve the environmental effects of our manufacturing processes and our finished electronic components.

In Europe (RoHS Directive) and in some other geographical areas such as China (China RoHS), legislation has been enacted to prevent or otherwise limit the use of certain hazardous materials, including lead (Pb), in electronic equipment. KEMET monitors legislation globally to ensure compliance and endeavors to adjust our manufacturing processes and/or electronic components as may be required by applicable law.

For military, medical, automotive, and some commercial applications, the use of lead (Pb) in the termination is necessary and/or required by design. KEMET is committed to communicating RoHS compliance to our customers. Information related to RoHS compliance will be provided in data sheets and using specific identifiers on the packaging labels.

All KEMET power film capacitors are RoHS compliant.

Materials & Environment

The selection of raw materials that KEMET uses for the production of its electronic components is the result of extensive experience. KEMET directs specific attention toward environmental protection. KEMET selects its suppliers according to ISO 9001 standards and performs statistical analyses on raw materials before acceptance for use in manufacturing our electronic components. All materials are, to the best of KEMET's knowledge, non-toxic and free from cadmium; mercury; chrome and compounds; polychlorine triphenyl (PCB); bromide and chlorinedioxins bromurate clorurate; CFC and HCFC; and asbestos.

Dissipation Factor

Dissipation factor is a complex function involved with capacitor inefficiency. The $tg\delta$ may vary up and down with increased temperature. For more information, refer to Performance Characteristics.

Sealing

Hermetically Sealed Capacitors

As the temperature increases, the pressure inside the capacitor increases. If the internal pressure is high enough, it can cause a breach in the capacitor. Such a breach can result in leakage, impregnation, filling fluid, or moisture susceptibility.

Barometric Pressure

The altitude at which hermetically sealed capacitors are operated controls the capacitor's voltage rating. As the barometric pressure decreases, the susceptibility to terminal arc-over increases. Non-hermetic capacitors can be affected by internal stresses due to pressure changes. These effects can be in the form of capacitance changes, dielectric arc-over, and/or low insulation resistance. Altitude can also affect heat transfer. Heat that is generated in an operation cannot be dissipated properly, and high RI2 losses and eventual failure can result.



Table 1 - Ratings & Part Number Reference

Cap Value	V _{NAC}	V _{NDC}		Dim	nensi (mm)	ons		dV/dt	lpkr	ESL	R _s	I _{rms} maximum (*)	Rth (HS/Amb)	Packaging Quantity	PART NUMBER
(µF)			В	Н	L	р	p1	V/µs	Apk	nH	mΩ	A _{rms}	(°C/W)	quantity	NOMBER
								V _{NAC} at 8	5°C = 250 \	AC; V _{OPAC}	at 105°C =	175 VAC			
1	250	500	11	20	31.5	27.5	١	38	38	24	22	4.5	44	256	C4AF1BU4100A1WK
1.5	250	500	11	20	31.5	27.5	١	38	56	24	15.6	5.4	44	256	C4AF1BU4150A1WK
2.2	250	500	13	25	31.5	27.5	١	38	83	25	11.8	6.9	36	234	C4AF1BU4220A1XK
3.3	250	500	19	29	31.5	27.5	\	38	125	26	9	8.9	29	72	C4AF1BU4330A11K
4.7	250	500	19	29	31.5	27.5	\	38	179	26	7.4	10	29	72	C4AF1BU4470A11K
6.8	250	500	22	37	31.5	27.5	١	38	259	28	6.6	12.1	23	64	C4AF1BU4680A12K
7.5	250	500	22	37	31.5	27.5	١	38	285	28	6.4	12.3	23	64	C4AF1BU4750A12K
10	250	500	20	40	42	37.5	10.2	27	272	29	4.8	15.2	20	58	C4AF1BW5100A3FK
15	250	500	30	45	42	37.5	20.3	27	400	33	3.4	20.8	15	36	C4AF1BW5150A3LK
22	250	500	35	50	42	37.5	20.3	27	587	35	2.6	25.4	13	30	C4AF1BW5220A30K
24.5	250	500	35	50	42	37.5	20.3	27	654	35	2.4	26.3	13	30	C4AF1BW5245A30K
33	250	500	35	50	57.5	52.5	20.3	18	587	38	3.4	26.1	10	23	C4AF1BW5330A3NK
47	250	500	45	56	57.5	52.5	20.3	18	837	41	2.8	32	8	18	C4AF1EW5470A3AK
55	250	500	45	56	57.5	52.5	20.3	18	960	41	2.4	33.9	8	18	C4AF1EW5550A3AK
62	250	500	45	65	57.5	52.5	20.3	18	1116	45	2.4	36.5	7	18	C4AF1EW5620A3BK
						0_0		V _{usc} at 8	5°C = 310 \	AC; V _{OPAC}	at 105°C =				
1	310	630	11	20	31.5	27.5	\	45	45	24	20.8	4.5	44	256	C4AF9BU4100A1WK
1.5	310	630	13	25	31.5	27.5	ì	45	68	25	15	6	36	234	C4AF9BU4150A1XK
2.2	310	630	14	28	31.5	27.5	Ì	45	99	26	11.4	7.2	33	96	C4AF9BU4220A1YK
3.3	310	630	19	29	31.5	27.5	ì	45	149	26	8.6	9	29	72	C4AF9BU4330A11K
4.7	310	630	22	37	31.5	27.5	Ì	45	212	28	7.6	11	23	64	C4AF9BU4470A12K
6.8	310	630	20	40	42	37.5	10.2	32	218	30	5.8	13.5	20	58	C4AF9BW4680A3FK
10	310	630	28	37	42	37.5	10.2	32	320	29	4.2	16.6	15	36	C4AF9BW5100A3JK
15	310	630	35	50	42	37.5	20.3	32	480	35	3	23.1	13	30	C4AF9BW5150A30K
17	310	630	35	50	42	37.5	20.3	32	560	35	2.8	23.8	13	30	C4AF9BW5170A30K
22	310	630	35	50	57.5	52.5	20.3	21	462	38	4.2	23.2	10	23	C4AF9BW5220A3NK
33	310	630	45	56	57.5	52.5	20.3	21	693	41	3	30.3	8	18	C4AF9EW5330A3AK
37.5	310	630	45	56	57.5	52.5	20.3	21	788	41	2.8	30.9	8	18	C4AF9EW5375A3AK
42	310	630	45	65	57.5	52.5	20.3	21	882	45	2.6	34.5	7	18	C4AF9EW5420A3BK
	J.,		B	Н	L	P	P1	V/µs	Apk	nH	mΩ	A _{rms}	(°C/W)	.,	2 7 2 7 . 20. 10 DK
Cap Value (μF)	V _{NAC}	V _{NDC}		<u> </u>	nsions	-		dV/dt	lpkr	ESL	R _s	I _{rms} maximum (*)	Rth (HS/Amb)	Packaging Quantity	PART NUMBER

For Packaging quantites not listed, please contact KEMET.

Items in bold font are only for sampling.

^(*) Current corresponding to 30°C of self-heating in dry conditions and composed by nominal 50 Hz current at rated VAC plus 10 kHz overlapped harmonics. For Expected Life and FIT performances, please refer always to the Curves reported inside the datasheet based on working voltage and hot spot temperatures.



Table 1 - Ratings & Part Number Reference cont.

Cap Value	V _{NAC}	V _{NDC}		Dim	nensi (mm)			dV/dt	lpkr	ESL	R _s	I _{rms} maximum (*)	Rth (HS/Amb)	Packaging Quantity	PART NUMBER
(µF)			В	Н	L	р	р1	V/µs	Apk	nH	mΩ	A _{rms}	(°C/W)	Qualitity	HOMBER
	V_{NAC} at 85°C = 350 VAC; V_{OPAC} at 105°C = 245 VAC														
1	350	700	13	25	31.5	27.5	١	115	115	25	10.6	6.1	36	234	C4AF7BU4100A1XK
1.5	350	700	14	28	31.5	27.5	١	115	173	26	8.2	7.5	33	96	C4AF7BU4150A1YK
2.2	350	700	19	29	31.5	27.5	١	115	253	26	6.6	9.1	29	72	C4AF7BU4220A11K
3.3	350	700	22	37	31.5	27.5	١	115	380	28	6	11.4	23	64	C4AF7BU4330A12K
3.7	350	700	22	37	31.5	27.5	١.	115	426	28	5.8	11.7	23	64	C4AF7BU4370A12K
4.7	350	700	20	40	42	37.5	10.2	75	353	30	4	14.7	20	58	C4AF7BW4470A3FK
6.8	350	700	28	37	42	37.5	10.2	75	510	29	2.8	18.3	18	36	C4AF7BW4680A3JK
10	350	700	35	50	42	37.5	20.3	75	750	35	2.2	24.8	13	30	C4AF7BW5100A30K
12.5	350	700	35	50	42	37.5	20.3	75	938	35	2	26.1	13	30	C4AF7BW5125A30K
15	350	700	35	50	57.5	52.5	20.3	50	750	38	2.8	27.1	10	23	C4AF7BW5150A3NK
22	350	700	45	56	57.5	52.5	20.3	50	1100	41	2.2	34.2	8	18	C4AF7EW5220A3AK
27	350	700	45	56	57.5	52.5	20.3	50	1350	41	2.0	35.4	8	18	C4AF7EW5270A3AK
32	350	700	45	65	57.5	52.5	20.3	50	1600	41	1.8	39.9	7	18	C4AF7EW5320A3BK
								V _{NAC} at 85	°C = 400 V	AC; V _{OPAC}	at 105°C =	280 VAC			
1	400	800	14	28	31.5	27.5	\	141	141	26	9.8	6.5	33	96	C4AF3BU4100A1YK
1.5	400	800	19	29	31.5	27.5	١	141	212	26	7.6	8.1	29	72	C4AF3BU4150A11K
2.2	400	800	22	37	31.5	27.5	\	141	310	28	6.8	10.2	23	64	C4AF3BU4220A12K
2.5	400	800	22	37	31.5	27.5	\	141	353	28	6.4	10.6	23	64	C4AF3BU4250A12K
3.3	400	800	20	40	42	37.5	10.2	90	297	30	4.8	13	20	58	C4AF3BW4330A3FK
4.7	400	800	28	37	42	37.5	10.2	90	423	29	3.4	16.1	18	36	C4AF3BW4470A3JK
6.8	400	800	30	45	42	37.5	20.3	90	612	33	2.6	20.4	15	36	C4AF3BW4680A3LK
9	400	800	35	50	42	37.5	20.3	90	810	35	2.2	24.1	13	30	C4AF3BW4900A30K
10	400	800	30	45	57.5	52.5	20.3	61	610	35	3.4	21.8	12	27	C4AF3BW5100A3MK
15	400	800	45	56	57.5	52.5	20.3	61	915	41	2.6	31.1	8	18	C4AF3EW5150A3AK
20	400	800	45	56	57.5	52.5	20.3	61	1220	41	2.2	33.3	8	18	C4AF3EW5200A3AK
22.5	400	800	45	65	57.5	52.5	20.3	61	1373	45	2	37.4	7	18	C4AF3EW5225A3BK
			В	Н	L	P	P1	V/µs	Apk	nΗ	mΩ	A _{rms}	(°C/W)		
Cap Value (µF)	V _{NAC}	V _{NDC}		Dime	nsions	(mm)		dV/dt	lpkr	ESL	R _s	I _{rms} maximum (*)	Rth (HS/Amb)	Packaging Quantity	PART NUMBER

For Packaging quantites not listed, please contact KEMET.

Items in bold font are only for sampling.

^(*) Current corresponding to 30°C of self-heating in dry conditions and composed by nominal 50 Hz current at rated VAC plus 10 kHz overlapped harmonics. For Expected Life and FIT performances, please refer always to the Curves reported inside the data-sheet based on working voltage and hot spot temperatures



Soldering Process

The implementation of the RoHS directive has resulted in the selection of SnAuCu (SAC) alloys, or SnCu alloys, as the primary solder material. This has increased the liquidus temperature from 183° C for a SnPb eutectic alloy to $217 - 221^{\circ}$ C for new alloys. As a result, the heat stress to the components, even in wave soldering, has increased considerably due to higher pre-heat and wave temperatures. Polypropylene capacitors are especially sensitive to heat (the melting point of polypropylene is $160 - 170^{\circ}$ C). Wave soldering can be destructive, especially for mechanically small polypropylene capacitors (with lead spacing of 5 - 15 mm), and great care must be taken during soldering. The recommended solder profiles from KEMET should be used. Contact KEMET with any questions. In general, the wave soldering curve from IEC Publication 61760-1 Edition 2 serves as a solid guideline for successful soldering. See Figure 1.


Reflow soldering is not recommended for through-hole film capacitors. Exposing capacitors to a soldering profile in excess of the recommended limits may result in degradation or permanent damage to the capacitors.

Do not place the polypropylene capacitor through an adhesive curing oven to cure resin for surface mount components. Insert through-hole parts after curing the surface mount parts. Contact KEMET to discuss the actual temperature profile in the oven, if through-hole components must pass through the adhesive curing process. A maximum two soldering cycles is recommended. Allow time for the capacitor surface temperature to return to normal before the second soldering cycle.

Manual Soldering Recommendations


Following is the recommendation for manual soldering with a soldering iron.

Recommended Soldering Temperature



The soldering iron tip temperature should be set at 350°C (+10°C) maximum with the soldering duration not to exceed more than 3 seconds.

Wave Soldering Recommendations





Soldering Process cont.


Wave Soldering Recommendations cont.

1. The tables indicates the maximum set-up temperature of the soldering process

Dielectric		imum Pre emperatu	Maximum Peak Soldering Temperature			
Film Material	Capacitor Pitch ≤ 10 mm	Capacitor Pitch = 15 mm	Capacitor Pitch > 15 mm	Capacitor Pitch ≤ 15 mm	Capacitor Pitch > 15 mm	
Polyester	130°C	130°C	130°C	270°C	270°C	
Polypropylene	100°C	110°C	130°C	260°C	270°C	
Paper	130°C	130°C	140°C	270°C	270°C	
Polyphenylene Sulphide	150°C	150°C	160°C	270°C	270°C	

2. The maximum temperature measured inside the capacitor: set the temperature so that inside the element the maximum temperature is below the limit.

Dielectric Film Material	Maximum Temperature Measured Inside the Element	
Polyester	160°C	
Polypropylene	110°C	
Paper	160°C	
Polyphenylene Sulphide	Sulphide 160°C	



Temperature monitored inside the capacitor.


Selective Soldering Recommendations

Selective dip soldering is a variation of reflow soldering. In this method, the printed circuit board with through-hole components to be soldered is pre-heated and transported over the solder bath, as in normal flow soldering, without touching the solder. When the board is over the bath, it is stopped. Pre-designed solder pots are lifted from the bath with molten solder, only at the places of the selected components, and pressed against the lower surface of the board to solder the components.


The temperature profile for selective soldering is similar to the double wave flow soldering outlined in this document. However, instead of two baths, there is only one with a time from 3 – 10 seconds. In selective soldering, the risk of overheating is greater than in double wave flow soldering, and great care must be taken so that the parts do not overheat.



Construction




Winding Scheme





Marking



Manufacturing Date Code (IEC-60062) Y = Year, Z = Month			
2010	Α	January	1
2011	В	February	2
2012	С	March	3
2013	D	April	4
2014	E	May	5
2015	F	June	6
2016	Н	July	7
2017	J	August	8
2018	K	September	9
2019	L	October	0
2020	M	November	N
2021	N	December	D
2022	Р		
2023	R		
2024	S		
2025	T		
2026	U		
2027	V		
2028	W		
2029	Х		
2030	Α		



KEMET Electronics Corporation Sales Offices

For a complete list of our global sales offices, please visit www.kemet.com/sales.

Disclaimer

All product specifications, statements, information and data (collectively, the "Information") in this datasheet are subject to change. The customer is responsible for checking and verifying the extent to which the Information contained in this publication is applicable to an order at the time the order is placed. All Information given herein is believed to be accurate and reliable, but it is presented without guarantee, warranty, or responsibility of any kind, expressed or implied.

Statements of suitability for certain applications are based on KEMET Electronics Corporation's ("KEMET") knowledge of typical operating conditions for such applications, but are not intended to constitute – and KEMET specifically disclaims – any warranty concerning suitability for a specific customer application or use. The Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by KEMET with reference to the use of KEMET's products is given gratis, and KEMET assumes no obligation or liability for the advice given or results obtained.

Although KEMET designs and manufactures its products to the most stringent quality and safety standards, given the current state of the art, isolated component failures may still occur. Accordingly, customer applications which require a high degree of reliability or safety should employ suitable designs or other safeguards (such as installation of protective circuitry or redundancies) in order to ensure that the failure of an electrical component does not result in a risk of personal injury or property damage.

Although all product-related warnings, cautions and notes must be observed, the customer should not assume that all safety measures are indicted or that other measures may not be required.