

**A-series, W-Series  
ZQV 1.5N/5 BL**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Product image****Spring connection with PUSH IN Technology**

The innovative PUSH IN technology reduces the amount of time you spend on wiring to a minimum. Direct insertion guarantees high conductor pull-out forces and simple handling for all conductor types.

**General ordering data**

|            |                            |
|------------|----------------------------|
| Type       | ZQV 1.5N/5 BL              |
| Order No.  | <a href="#">1985590000</a> |
| GTIN (EAN) | 4050118370430              |
| Qty.       | 20 pc(s).                  |

**Data sheet**

**A-series, W-Series  
ZQV 1.5N/5 BL**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**

**Dimensions and weights**

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Width      | 16 mm   | Width (inches)  | 0.63 inch  |
| Height     | 21.9 mm | Height (inches) | 0.862 inch |
| Depth      | 2.8 mm  | Depth (inches)  | 0.11 inch  |
| Net weight | 1.537 g |                 |            |

**Temperatures**

|                           |               |                           |       |
|---------------------------|---------------|---------------------------|-------|
| Storage temperature, max. | 40 °C         | Storage temperature, min. | 10 °C |
| Storage temperature       | 10 °C...40 °C |                           |       |

**Material data**

|                           |       |        |      |
|---------------------------|-------|--------|------|
| Material                  | Wemid | Colour | blue |
| UL 94 flammability rating | V-0   |        |      |

**Additional technical data**

|                          |     |                |         |
|--------------------------|-----|----------------|---------|
| Explosion-tested version | Yes | Type of fixing | Plugged |
|--------------------------|-----|----------------|---------|

**Dimensions**

|                 |        |
|-----------------|--------|
| Pitch in mm (P) | 3.5 mm |
|-----------------|--------|

**Rating data**

|               |        |
|---------------|--------|
| Rated current | 17.5 A |
|---------------|--------|

**Classifications**

|             |             |            |             |
|-------------|-------------|------------|-------------|
| ETIM 6.0    | EC000489    | ETIM 7.0   | EC000489    |
| eClass 9.0  | 27-14-11-40 | eClass 9.1 | 27-14-11-40 |
| eClass 10.0 | 27-14-11-40 |            |             |

**Product information**

Product information Due to stability and temperature reasons It is only possible to break out 60% of contact elements The usage of cross connectors reduces the rated voltage to 400V The voltage reduced to 25V if cut cross connection with blank cut edges are used

**Approvals**

Approvals



ROHS Conform

**Downloads**

|                    |   |
|--------------------|---|
| Engineering Data   | <a href="#">EPLAN, WSCAD, Zuken E3.S</a>  |
| Engineering Data   | <a href="#">STEP</a>  |
| User Documentation | <a href="#">2434520000_BED-ANL_ZQV_A_REIHE.pdf</a><br><a href="#">StorageConditionsTerminalBlocks</a> |