7-SEGMEN

12



Data sheet acquired from Harris Semiconductor SCHS072B – Revised July 2003

CMOS BCD-to-7-Segment Latch Decoder Drivers

High-Voltage Types (20-Volt Rating)






200 - 25097

CD4511B types are BCD-to-7-segment latch decoder drivers constructed with CMOS logic and n-p-n bipolar transistor output devices on a single monolithic structure. These devices combine the low quiescent power dissipation and high noise immunity features of RCA CMOS with n-p-n bipolar output transistors capable of sourcing up to 25 mA. This capability allows the CD4511B types to drive LED's and other displays directly.

Lamp Test (LT), Blanking (BL), and Latch Enable or Strobe inputs are provided to test the display, shut off or intensity-modulate it, and store or strobe a BCD code, respectively. Several different signals may be multiplexed and displayed when external multiplexing circuitry is used.

The CD4511B types are supplied in 16-lead hermetic dual-in-line ceramic packages (F3A suffix), 16-lead dual-in-line plastic packages (E suffix), 16-lead small-outline packages (NSR suffix), and 16-lead thin shrink small-outline packages (PW and PWR suffixes).

These devices are similar to the type MC14511.



CD4511B TERMINAL ASSIGNMENT

Features:

- High-output-sourcing capability up to 25 mA
- Input latches for BCD Code storage
- Lamp Test and Blanking capability
- 7-segment outputs blanked for BCD input codes > 1001
- 100% tested for quiescent current at 20 V
- Max. input current of 1 μA at 18 V, over full package-temperature range, 100 nA at 18 V and 25°C
- 5-V, 10-V, and 15-V parametric ratings

Applications:

Driving common-cathode LED displays

V_{SS}=8 V_{DD}=16

FUNCTIONAL DIAGRAM

- Multiplexing with common-cathode LED displays
- Driving incandescent displays

CD4511B Types

■ Driving low-voltage fluorescent displays

MAXIMUM RATINGS, Absolute-Maximum Values: DC SUPPLY-VOLTAGE RANGE, (VDD) Voltages referenced to VSS Terminal) -0.5V to +20V INPUT VOLTAGE RANGE, ALL INPUTS -0.5V to VDD +0.5V DC INPUT CURRENT, ANY ONE INPUT ±10mA POWER DISSIPATION PER PACKAGE (PD): For TA = -55°C to +100°C For TA = +100°C to +125°C Derate Linearity at 12mW/°C to 200mW DEVICE DISSIPATION PER OUTPUT TRANSISTOR FOR TA = FULL PACKAGE-TEMPERATURE RANGE (All Package Types) 100mW OPERATING-TEMPERATURE RANGE (Tatg) STORAGE TEMPERATURE (Tatg) At distance 1/16 ± 1/32 inch (1.59 ± 0.79mm) from case for 10s max +265°C

OPERATING CONDITIONS AT TA = 25°C Unless Otherwise Specified

For maximum reliability, nominal operating conditions should be selected so that operation is always within the following ranges

Characteristic	V _{DD}	Min.	Max.	Units	
Supply Voltage Range (T _A): (Full Package-Temperature Range)	-	3	18	٧	
	5	150	-	ns	
Set-Up Time (t _S)	10	70	_	ns	
	15	40		ns	
	5	0	_	ns	
Hold Time (tH)	10	0	_	ns	
	15	0	-	ns	
	5	400	_	ns	
Strobe Pulse Width (t _W)	10	160		ns	
	15	100	_	ns	

CD4511B Types

STATIC ELECTRICAL CHARACTERISTICS

	TEST CONDITIONS			LIMITS AT INDICATED TEMPERATURES (°C)								
					LI	IMITS AT	r indiça	ATED TE	EMPER#	TURES	(oc)	
CHARACTERISTIC	ІОН	v _o	VIN	V _{DD}		ſ	Γ		Ι	+25	•	Units
	(mA)	(V)	(V)	(V)	-55	-40	+85	+125	Min.	Тур.	Max.	
Quiescent Device	<u> </u>	_	_	5	5	5	150	150	_	0.04	5	
Current: IDD			_	10	10	10	300	300	_	0.04	10	μА
Max,			_	15	20	20	600	600		0.04	20	۳.
			_	20	100	100	3000	3000	-	0.08	100	
Output Voltage:				_			0.05					
Law Lavel Ma	-		0,5	5 10			0.05 0.05		· -	0	0.05	١,,
Low-Level VOL Max.		<u> </u>	0,10	15			0.05		-	0	0.05	: V
IVIGA.	<u> </u>	<u> </u>							<u> </u>		0.05.	<u> </u>
112-6-1	<u> </u>	-	0,5	5	4	4	4.2	4.2	4.1	4.55	<u> </u>	l
High-Level V _{OH}	_	-	0,10	10 15	9	9	9.2	9.2	9.1	9.55		٧
Min.			0.15	15	14	14	14.2.	14.2	14.1	14.55	-	ļ
Input Low	_	0.5,3.8		5	1.5					_	1.5	
Voltage, VIL	_	1,8.8	-	10			3		-		3	v
Max.		1.5,13.8		15			4		-	_	4	
Input High	-	0.5,3.8		5			3.5		3.5	-	_	
Voltage, V _{IH}	V _{IH} _ 1,8.8 10 7					7	_	_	٧			
Min.		1.5,13.8		15			11		11		-	
	0			4	4.0	4.0	4.20	4.20	4.10	4.55		
	5	-							_	4.25		
	10			5	3.80	3.80	3.90	3.90	3.90	4.10	_	v
	15	-			-	3.50	3.50		3.95	_	-	
	20	-			3.55	3.55	3.30	-	3.40	3.75		
	25				3.40	3.40	-		3.10	3.55	~	1
	0			•	9.0	9.0	9.20	9.20	9.10	9.55		
Output Drive	5					-	-		_	9.25	-	
Voltage:	10	-	-		8.85	8.85	9.00	9.00	9.00	9.15		v
High Level VOH	15	_	-	10			-		-	9.05		
Min.	20	-	-		8.70	8.70	8.40	8.40	8.60	8.90		
	25	-	_		8.60	8.60	_		8.30	8.75	_	
	0			🕈	14.0	14.0	14.20	14.20	14.10	14.55		
ļ	5				-	-	-	-		14.30		
	10			15	13.90	13.90	14.0	14.0	14.0	14.20		V
	15 20				13.75	12.75	13.50	1250	12.70	14.10		
j	25		-]	13.75	13.75 13.65	13.50	13.50	13.70 13.50	13.95 13.80	-	
	25				13.05	13.05		_	13.50	13.60		
Output Low								,				
(Sink) Current,	_	0.4	0,5	5	0.64	0.61	0.42	0.36	0.51	1	_	
OL.		0.5	0,10	10	1.6	1.5	1.1	0.9	1.3	2.6		mΑ
Min.	_	1.5	0,15	15	4.2	4	2.8	2.4	3.4	6.8		
Input Current, I _{IN} Max.	-	0,18	0,18	18	±0.1	±0.1	±1	±1	-	±10-5	±0.1	μΑ




Fig. 1 — Typical output low (sink) current characteristics.




Fig. 2 — Typical data-to-output, low-to-high-level propagation dalay time as a function of load capacitance.




Fig. 3 — Typical data-to-output, high-to-low-level propagation delay time as a function of load capacitance.




Fig. 4 — Typical low-to-high-level transition time as a function of load capacitance.

CD4511B Types

DYNAMIC ELECTRICAL CHARACTERISTICS at $T_A = 25^{\circ}C$, Input t_r , $t_f = 20$ ns, C_L = 50 pF, R_L = 200 k Ω

CHARACTERISTIC	Test Conditions	A	LIMITS All Package		UNITS	
X	Y _{DD} Volts	Min.	Тур.	Max.		
Propagation Delay Time:	5	_	520	1040		
(Data)	10	_	210	420	ns	
High-to-Low Level, tpHL	15	-	150	300		
	5	_	660	1320		
Low-to-High Level, tPLH	10	l –	260	520	ns	
	15	_	180	360	<u> </u>	
Propagation Delay Time:	5	_	350	700		
(BL)	10	-	175	350	ns	
High-to-Low Level, tpHL	15	_	125	250		
	5		400	800		
> Low-to-High Level, tpLH	10	_	175	350	ns	
	15	- ,	150	300		
Propagation Delay Time:	5	-	250	500		
(LT)	10	-	125	250	ns	
High-to-Low Level, tpHL	15		85	170		
	5	_	150	300		
Low-to-High Level, tPLH	10	_	75	150	ns	
	15	_	50	100		
Transition Time:	. 5	_	40	80		
	10	-	30	60	пs	
Low-to-High Level, tTLH	15		25	50	٠	
	5	-	125	310		
	10	_	75	185	ns	
High-to-Low Level, tTHL	15	_	65	160		
Minimum Co. Ha Ti	5	150	75	_		
Minimum Set-Up Time, t _S	10	70	35	-	ns	
	15	40	20	_		
	5	0	-75	_		
Minimum Hold Time, tH	10	0	-35	_	ns	
	15	0	-20	_		
6. I B. W	5	400	200	_		
Strobe Pulse Width, t _W	10	160	80	. —	ns	
	15	100	50			
Input Capacitance, CIN			5	7.5	pF	




Fig. 5 - Typical high-to-low transition time as a function of load capacitance.




Fig. 6 - Typical voltage drop (V_{DD} to output) vs. output source current as a function of supply.






Fig. 7 - Typical dynamic power dissipation characteristics.

CD4511B Types




APPLICATIONS Interfacing with Various Displays



Duty Cycle = 100%

ISEG = IDIODEAVG. = 20 mA at Luminous Intensity/Segment = 250 microcandles

Fig. 15 - Driving common-cathode 7-segment LED displays (example Hewlet-Packard 5082-7740).



Multiplexing Scheme Showing 2 of 7 Segments Connected


Transistors T₁-T₄ (RCA-2N3053 or 2N2102) have I_C Max.rating >7xI_{SEG}

Duty Cycle = 25% I SEG = $^{[I]}$ DIODE_{AVG} I × 4 $_{R}$ = $^{(V}$ OH - V DF - V CE I

ISEG

All unused inputs on CD4555 are connected to V_{DD} or V_{SS}


Fig. 18 — Multiplexing with common-cathode 7-segment LED displays (example Hewlet-Packard 5082-7404 4 character display or 4 discrete Monosanto Man 3 displays).



A medium-brightness intensity display can be obtained with low-voltage fluorescent displays such as the Tung-Sol Digivac S/G** Series.

**Trademark Tung-Sol Division Wagner Electric Co.


Fig. 16 — Driving low-voltage fluorescent displays.



2 of 7 Segments Shown Connected

Resistors R from V_{DD} to each 7-segment driver output are chosen to keep all Numitron segments slightly on and warm.

Fig. 17 — Driving incandescent displays (RCA Numitron DR2000 series displays).



Dimensions and pad layout for CD45118 chip.

Dimensions in parentheses are in millimeters and are derived from the basic inch dimensions as indicated. Grid graduations are in mils (10^{-3}) inch).





22-Jul-2020

PACKAGING INFORMATION

Orderable Device	Status	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead finish/ Ball material	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
CD4511BE	ACTIVE	PDIP	N	16	25	Green (RoHS & no Sb/Br)	NIPDAU	N / A for Pkg Type	-55 to 125	CD4511BE	Samples
CD4511BEE4	ACTIVE	PDIP	N	16	25	Green (RoHS & no Sb/Br)	NIPDAU	N / A for Pkg Type	-55 to 125	CD4511BE	Samples
CD4511BF	ACTIVE	CDIP	J	16	1	TBD	SNPB	N / A for Pkg Type	-55 to 125	CD4511BF	Samples
CD4511BF3A	ACTIVE	CDIP	J	16	1	TBD	SNPB	N / A for Pkg Type	-55 to 125	CD4511BF3A	Samples
CD4511BNSR	ACTIVE	SO	NS	16	2000	Green (RoHS & no Sb/Br)	NIPDAU	Level-1-260C-UNLIM	-55 to 125	CD4511B	Samples
CD4511BNSRG4	ACTIVE	SO	NS	16	2000	Green (RoHS & no Sb/Br)	NIPDAU	Level-1-260C-UNLIM	-55 to 125	CD4511B	Samples
CD4511BPW	ACTIVE	TSSOP	PW	16	90	Green (RoHS & no Sb/Br)	NIPDAU	Level-1-260C-UNLIM	-55 to 125	CM511B	Samples
CD4511BPWG4	ACTIVE	TSSOP	PW	16	90	Green (RoHS & no Sb/Br)	NIPDAU	Level-1-260C-UNLIM	-55 to 125	CM511B	Samples
CD4511BPWR	ACTIVE	TSSOP	PW	16	2000	Green (RoHS & no Sb/Br)	NIPDAU	Level-1-260C-UNLIM	-55 to 125	CM511B	Samples

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

⁽²⁾ **RoHS:** TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

⁽³⁾ MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.



PACKAGE OPTION ADDENDUM

22-Jul-2020

- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead finish/Ball material Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

OTHER QUALIFIED VERSIONS OF CD4511B, CD4511B-MIL:

Catalog: CD4511B

• Military: CD4511B-MIL

NOTE: Qualified Version Definitions:

- Catalog TI's standard catalog product
- Military QML certified for Military and Defense Applications

PACKAGE MATERIALS INFORMATION

www.ti.com 16-Oct-2020

TAPE AND REEL INFORMATION





Α0	
В0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

Device	Package Type	Package Drawing			Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
CD4511BPWR	TSSOP	PW	16	2000	330.0	12.4	6.9	5.6	1.6	8.0	12.0	Q1

www.ti.com 16-Oct-2020



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)	
CD4511BPWR	TSSOP	PW	16	2000	853.0	449.0	35.0	

N (R-PDIP-T**)

PLASTIC DUAL-IN-LINE PACKAGE

16 PINS SHOWN



- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- Falls within JEDEC MS-001, except 18 and 20 pin minimum body length (Dim A).
- The 20 pin end lead shoulder width is a vendor option, either half or full width.





SMALL OUTLINE PACKAGE



- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

 2. This drawing is subject to change without notice.

 3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not
- exceed 0.15 mm per side.
- 4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
- 5. Reference JEDEC registration MO-153.



SMALL OUTLINE PACKAGE



NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



SMALL OUTLINE PACKAGE



NOTES: (continued)

- 8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 9. Board assembly site may have different recommendations for stencil design.



MECHANICAL DATA

NS (R-PDSO-G**)

14-PINS SHOWN

PLASTIC SMALL-OUTLINE PACKAGE



- A. All linear dimensions are in millimeters.
- B. This drawing is subject to change without notice.
- C. Body dimensions do not include mold flash or protrusion, not to exceed 0,15.



14 LEADS SHOWN



- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- C. This package is hermetically sealed with a ceramic lid using glass frit.
- D. Index point is provided on cap for terminal identification only on press ceramic glass frit seal only.
- E. Falls within MIL STD 1835 GDIP1-T14, GDIP1-T16, GDIP1-T18 and GDIP1-T20.

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

Tl's products are provided subject to Tl's Terms of Sale (www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such Tl products. Tl's provision of these resources does not expand or otherwise alter Tl's applicable warranties or warranty disclaimers for Tl products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2020, Texas Instruments Incorporated