



PRODUCT NUMBER: 1028640
SP1000 Safety Eyewear, Black
Frame, ClearLens

Provides protection against impact, wind, dust and airborne debris. Ideal for dirty, high-particulate work environments such as grinding, chipping, shaving and sanding.

Honeywell

Overview

Reference Number

1028640

Product Type

Eye and Face Protection

Range

Spectacles

Line

Dual lenses

Brand

Honeywell

Industry

- Building and Construction
- Metal steel
- Mining and Quarrying
- Petro-chemical
- Transportation

Product Use

General use and protection against impact and dust

Features & Benefits

Feature

Soft and flexible nose piece

Benefit

Conforms to a variety of facial profiles and minimises slippage

Feature

Soft, high-quality face cushioning and padded temple tips

Benefit

Offers all-day comfort

Feature

Highly adjustable flame-resistant headband

Benefit

Provides excellent fit

Feature

Wrap-around 8-base dual-lens style

Benefit

Exceptional peripheral vision and coverage

Feature

Top and bottom indirect ventilation and Dura-streme dual anti-fog/anti-scratch coating

Benefit

Durable performance with minimised fogging

Technical Description

Shade Lens Color

Clear

Lens Coating

Dura-streme Dual Technology Anti-fog and Anti-Scratch

Shade Lens Material

Polycarbonate

Replacement Lens

No

Frame Color

Black Painted

Frame Material

Polycarbonate

Dielectric

Yes

Temple Type

Padded Temple Tips

Certifications

 E.C. Declaration of Conformity

EC Category PPE

2

Quality Assurance

ISO 9001 / 2000

EC Certificate Number

C9119.3B-D

EC Attestation

 EC Attestation

EC Attestation Number

C9119.3B-D

Certifications

- EN 166

Literature & Documents

SP1000 leaflet GB_original

http://www.honeywellsafety.com/supplementary/documents_and_downloads/eye_and_face_protection/eyewear/39047/1033.aspx

EC-type examination certificate


C9119.3B-D

Applicant / manufacturer	SPERIAN Eye & Face Protection, Inc. 10, Thurber Blvd. SMITHFIELD, RI 02917 USA
Identification of the manufacturer	B-D
Product type	Eye-protector, safety spectacles with filtering action, UV and sunglare filters
Model name	Spectacles / 1028640, 1028643, 1028644 see schedule identifying the different models
Standard(s) / technical rules	DIN EN 166, 170, 172 : 2002 Annex II of the PPE-Directive 89/686/EEC
Test reports	1083-ECS-09, INSPEC 09.12.66 + 09.12.67 1034-ECS-10
Material	Lenses: polycarbonate Temples and headbands: plastics
Marking	UV: 2C-X B-D 1 FT K N – 166 FT 3 CE Sunglare: 5-Y B-D 1 FT K N – 166 FT 3 CE for details see schedule for the different models

Herewith, ECS certifies that the named models comply with the basic requirements for health and safety as they are provided by the European Directive for Personal Protective Equipment 89/686/EEC. This certificate is based both / either on the test results as they are summarized in the named test reports, and/or on the technical documentation as it is delivered by the manufacturer. The applicant / manufacturer agrees to the General Business Rules of the ECS GmbH and to additional agreements as they are named in the application for conformity assessment.

The eye-protection device is to be marked as assigned. Either / both the frame and / or the ocular, spectacle, goggle or shield must be signed, as appropriate. If different marking has been assessed, the lowest marking must be applied, respectively. The validity of this EC-type examination will expire, if the manufacturer modifies the safety-relevant properties of this product with comparison to the tested one or if the requirements in the standards or technical rules will be revised and/or tightened. Name, address and identification number 1883 of the notified body ECS must be indicated in the information brochure of this product.

ECS GmbH
Notified Body 1883
23/04/10


Dr. Bernhard Schmitz
ECS-Certification



ECS GmbH – European Certification Service
Augenschutz und Persönliche Schutzausrüstung
Laserschutz und Optische Messtechnik
Hüttfeldstraße 50
73430 Aalen, Germany

CERTIFICATION SCHEDULE

Company: SPERIAN Eye & Face Protection, SMITHFIELD, RI USA

Annex to the EC-type examination certificate registration number C9119.3B-D, dated from 23/04/10:

The following products are included in this EC-type examination certificate:

Spectacle name	Measurement report	Additional specs	Scale and marking for the unit of ocular and frame
1028640	10831-ECS-09 10834-ECS-09 10835-ECS-09 INSPEC 09.12.66 INSPEC 09.12.67 10341-ECS-10	Valid for all types: Optical class: 1 Protection against high-speed particles, low energy impact at extremes of temperatures (FT)	UV-filtering action: 2C-1.2 B-D 1 FT K N – 166 FT 3 CE
1028643	10832-ECS-09 10834-ECS-09 10835-ECS-09 INSPEC 09.12.66 INSPEC 09.12.67 10342-ECS-10	C: recognition of signal lights Resistance to surface damage by fine particles (K) Resistance to fogging of oculars (N)	UV- / sunglare filtering action: 2C-2.5 / 5-2.5 B-D 1 FT K N – 166 FT 3 CE
1028644	10833-ECS-09 10834-ECS-09 10835-ECS-09 INSPEC 09.12.66 INSPEC 09.12.67 10343-ECS-10	Only when equipped with headband: protection against droplets and splashes of liquids (3)	UV-filtering action: 2C-1.2 B-D 1 FT K N – 166 FT 3 CE

Additional remark:

If the lenses and frames are marked separately, the following markings shall be applied:

- for the lenses: X / Y B-D 1 FT K N CE (for X, Y see table above)
- for the frame: B-D 166 FT 3 CE

CERTIFICATION/TEST REPORT RECEIPT FORM

DATE RECEIVED: 7/16/10

PRODUCT: SP1000

CERTIFICATION TEST REPORT

SIGNATURES

Q.A. MANAGER: *John Perich*

DIRECTOR QUALITY SYSTEMS: *[Signature]*

DIRECTOR R & D: *[Signature]*



E.C. Declaration of Conformity

The manufacturer or its legal representative supplier in the European Community:

Honeywell Safety Products Europe

Declares that the Personal Protective Equipment described here after conforms to the provisions of the European Council Directive 89/686/CEE:

Designation: SP1000 Safety Eyewear, Black Frame, ClearLens

Reference: 1028640

Standard(s): EN166, EN170

This PPE is the object of the below EC examination certificate n°:

C9119.3B-D

Delivered by:

ECS

Obere Bahnstrasse, 25

73431

Aalen

Germany

+49 (0)7361 9757396

+49 (0)7361 5562434

www.ecs-eyesafe.de

Drawn up in Aalen, Germany, on the 10/06/2015

By: Bernhard Schmit

Division: Eye and Face Protection

HONEYWELL SAFETY PRODUCTS EUROPE
Immeuble Edison - ZI Paris Nord II - 33 rue des Vanesses
BP 55288 Villepinte - 95958 ROISSY CDG CEDEX
SAS au capital 17 750 000 € - Siret 348 882 307 00137
Tel. +331 4990 7979 - Fax +331 4990 7980

ZI Paris Nord II 33, rue des Vanesses BP 50288 95958 Roissy CDG France

Tel: +33 (0) 49 90 79 79 Fax: +33 (0)1 49 90 79 80

www.honeywellsafety.com

SP1000™

Honeywell



**SP1000™,
Powerful eyewear for today's
demanding work environments.**

Premium Eyewear for today's demanding work environments



Premier Performance

- Provides protection against impact, sun, wind, dust and airborne debris. Ideal for dirty, high-particulate work environments such as grinding, chipping, shaving and sanding.
- Available with Dura-streme™ dual coating technology which combines our two best lens coatings
 - anti-fog on the interior and anti-scratch on the exterior
 - for 3x longer lens life*.

* Comparative lens life test performed using a Bayer Abrasion Test method and may vary between environment and application.

Premier Comfort & Fit

- Soft and flexible nose piece conforms to a variety of facial profiles and minimises slippage.
- Soft, high-quality face cushioning and padded temple tips offer all-day comfort.
- Highly adjustable flame-resistant headband provides excellent fit.



Clear - ideal for most indoor work applications



HDL Yellow - ideal for low-light applications where enhanced contrast is needed



Grey - minimises strong outdoor sunlight and glare






Flexible design can be used with temple or headband (both included).



- Premier comfort and seal with high-quality face cushioning, flexible nose piece and adjustable headband.
- Exceptional peripheral vision and coverage with wrap-around 8-base dual-lens style.
- Durable performance with minimised fogging thanks to top and bottom indirect ventilation and Dura-streme dual anti-fog/anti-scratch coating.

REFERENCES - ORDERING INFORMATION

Article No	Description	Lens	Lens coating	Lens Marking	Temple Marking	Headband clip marking
 10 286 40	SP1000	Clear	Dura-streme™	2C - 1.2 B-D 1FT KN	B-D 166 FT CE	B-D 166 3 FT CE
 10 286 44	SP1000	HDL Yellow	Dura-streme™	2C - 1.2 B-D 1FT KN	B-D 166 FT CE	B-D 166 3 FT CE
 10 286 43	SP1000	Grey	Dura-streme™	2C-2.5 / 5-2.5 B-D 1FT KN	B-D 166 FT CE	B-D 166 3 FT CE

Lead them to safety – Build an enduring culture of safety through comprehensive education, innovative technologies, and comfortable, high-performance products. Honeywell Safety Products is the ideal partner for a cultural transformation that inspires workers to make safer choices on their own.

HONEYWELL SAFETY PRODUCTS

UNITED KINGDOM

Honeywell Safety Products UK LTD

Unit 3 Elmwood

Chineham Park

Basingstoke RG24 8WG

United Kingdom

Phone: +44 (0) 1256 693 200

Fax: +44 (0) 1256 693 300

Email: info-uk.hsp@honeywell.com

INTERNATIONAL

Honeywell Safety Products Europe SAS

Immeuble Edison Paris Nord 2

33, rue des Vanesses – CS 55288 Villepinte

95958 Roissy CDG Cedex – France

Phone: +33 (0)1 49 90 79 79

Fax: +33 (0)1 49 90 71 04

Email: info-export.hsp@honeywell.com

