

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

Tyco Electronics AMP GmbH

ALL RIGHTS RESERVED.

LOC	DIST
FT	0

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	C2	REVISED PER ECO-12-007964	03MAY2012	KH	MS

INTERLOCKING FEATURE

282811-3 AS SHOWN

1 MATERIALS AND FINISH  
HOUSING: PA 6-6, UL 94-V0, COLOR GREEN.  
TERMINAL: COPPER ALLOY, TIN PLATED.

2 SUITABLE FOR 1,6-2,4mm PC BOARD THICKNESS.

3 END-TO-END STACKABLE W/INTERLOCK WITHOUT LOSS OF CENTERLINE SPACING.

4 RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC. FILE N° E60677.

5 IMQ CERTIFICATE WITH SURVEILLANCE IN CONFORMITY WITH IEC 998-1/998-2-1.

6 NOT CUMULATIVE TOLERANCE.

20	4	282811-4
15	3	282811-3
10	2	282811-2
<b>DIM. A</b>	<b>N° OF POS.</b>	<b>PART NUMBER</b>

RECOMMENDED PC BOARD LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	24JUL2001	TE Connectivity <b>STE</b>	
DIMENSIONS:		CHK	24JUL2001		
mm		APVD	24JUL2001		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	108-20166		
0 PLC ±-		APPLICATION SPEC	114-20079	NAME	
1 PLC ±.2		WEIGHT	-	TERMINAL BLOCK HEADER ASSEMBLY	
2 PLC ±.25		CUSTOMER DRAWING		90 DEGREE STACKING W/INTERLOCK	
3 PLC ±-		SCALE	3:1	5mm PITCH	
4 PLC ±-		SHEET	1	RESTRICTED TO	
ANGLES ±2		OF	1	-	
FINISH		REV	C2		
MATERIAL					

1470-19 (3/11)

Pro/ENGINEER DRAWING

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[282811-4](#)