




pui
audio™ inc
a projects unlimited company

POM-2246P-C33-R Omni-Directional Microphone





3541 Stop Eight Road • Dayton, Ohio 45414

Product Overview

- 6mm overall diameter and 2.2mm height with pin terminals
- -46 dB sensitivity for use in most environments
- Wide 2 to 10 VDC operating voltage and 50-16,000 Hz frequency response
- >60 dB signal-to-noise ratio and 2.2 kOhm impedance
- Omni-directional polar pattern for great off-axis response
- Internal 33 pF capacitor filters out GSM TDMA noise

Typical Frequency Response and Sensitivity







pui
audio™
INC
a projects unlimited company

POM-2246P-C33-R

Omni-Directional Microphone

| Mechanical and Environment Testing | |
|------------------------------------|--|
| Test Description | Test Condition |
| High Temperature | 70°C with random humidity for 200 hours |
| Low Temperature | -40°C with random humidity for 200 hours |
| Humidity | 40°C with 90% relative humidity for 200 hours |
| Vibration | 3 mm movement for 3 minutes in each of 3 axis |
| Drop Test | 70 cm free fall onto 20 mm thick board, two directions |
| Temperature Cycle Test | -10°C to 50°C, 5 cycles |





SPECIFICATIONS

| PARAMETERS | VALUES | UNIT |
|------------------------------|---------|------|
| DIRECTIVITY | OMINI | - |
| SENSITIVITY | -46 ± 3 | dB |
| STANDARD OPERATING VOLTAGE | 2 | Vdc |
| MAX OPERATING VOLTAGE | 10 | Vdc |
| CURRENT CONSUMPTION (MAX) | 0.5 | mA |
| IMPEDANCE | 2.2 | KOhm |
| SIGNAL TO NOISE RATIO (MIN.) | 60 | dB |
| TERMINAL | PIN | - |
| INTERNAL CAPACITOR | 33 | pF |

THIS DOCUMENT CONTAINS DATA PROPRIETARY TO PROJECTS UNLIMITED, INC. ANY USE OR REPRODUCTION, IN ANY FORM, WITHOUT PRIOR WRITTEN PERMISSION OF PROJECTS UNLIMITED, INC. IS PROHIBITED.
©2003, Projects Unlimited Inc.


REVISION HISTORY

| LTR | DESCRIPTION | DATE | APPROVED |
|-----|--|-----------|----------|
| - | RELEASED FROM ENGINEERING | 5/24/2006 | |
| A | ADDED TERMINAL POLARITY | 2/2/2007 | B.R. |
| B | REVISED TO INVENTOR 3-D DRAWING TEMPLATE | 9/27/2010 | B.R. |



NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. SPECIFICATIONS SUBJECT TO CHANGE OR WITHDRAWAL WITHOUT NOTICE.
3. THIS PART IS RoHS 2002/95/EC COMPLIANT.
4. MICROPHONE CLOTH OVER FACE IS IP51 RATED.

| | | | | | | | | | |
|--|--|-------------|------------------------|------------|-----------|-------------------|-----------|--------------|----------------|
| UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN MILLIMETERS, TOLERANCES ARE ±0.5 AND ANGLES ARE ±3°. | SIZE | Designed by | Date | Checked by | Date | Approved by | Date | Drawn Date | |
| | A3 | J.D. | 5/24/2006 | E.P. | 5/24/2006 | B.R. | 5/24/2006 | 9/27/2010 | |
| POM-2246P-C33-R.idw |  pui audio a projects unlimited company | | POM-2246P-C33-R | | | Microphone | | Edition - | Sheet 1 / 1 |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[PUI Audio:](#)

[POM-2246P-C33-R](#)