


PRODUCT NUMBER  
SEE TABLE


mat'l. code		surface / tolerance		projection		product family	
ISO 1302		ISO 1101		ISO 1101		QUICKIE	
date		tolerances unless otherwise specified		title		sheet of 10 size	
AD V42013	LSS 1/25/95	XXXL/XXXL3		HEADER QUICKIE SLIM LINE		66506 A3	
AE V50332	MRC 5/25/95	XXXL/XXXL3		VERTICAL 4 WALL		type Product Customer Drawing	
AF N05-0060	ERE 8/08/05	±2°		scale 1:1		dwg no	
AG M06-0282	AGS 7/22/06	L. SANDERS 1/25/95		FCG		66506	
AH M07-0363	MHT 8/17/07	M. SMYK 1/25/95		AK AK AK AK AK AK		9 10	
AJ N08-0138	R.B 07/08/08	CHR J. ROMBERGER 1/25/95					
AK	J.Z. 2012-07-04	M. SMYK 1/25/95					
sheet	revisior	AK	AK	AK	AK	AK	AK
index	sheet	1	2	3	4	5	6

PRODUCT NUMBER  
SEE TABLE



NOTES:

1. SAME POSITION TOLERANCE APPLIES TO BOTH ENDS OF PINS.
2. MOLDING MATERIAL: GLASS-FILLED POLYESTER, FLAME RETARDANT PER UL 94 V-0, COLOR: BLACK.
3. 1" MAX. DRAFT PERMISSIBLE ON ALL SURFACES.
4. 3 LBS./1.36 KG MIN. TERMINAL PULL-OUT FORCE.
5. TERMINAL MATERIAL: PHOSPHORUS BRONZE.
6. TO DETERMINE DIMENSIONS:  
N = NUMBER OF POSITIONS PER ROW
7. UNDER PLATING: 50µ"/1.27µm Ni.
8. PART NUMBERS WITH "R" FOLLOWING THE PART NUMBER (EXAMPLE 66506-326 R.) HAS RETENTION. (ONLY PARTS WITH .105", .120, AND .150 ROUND OR SQUARE TAILS CAN HAVE RETENTION.) LOCATION IS MANUFACTURER'S OPTION.
9. PART NUMBERS WITH "T" FOLLOWING PART NUMBER (EXAMPLE 66506-068 T IS PACKED IN TUBES.) (CALL PRODUCT MANAGER FOR AVAILABILITY.)
10. SEE 68751 FOR LATCHES.
11. MAY BE ORDERED WITH "G" PACK PACKAGING BY ADDING "G" TO DASH NUMBER.
12. ADD "LF" SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION & PART NUMBERS WITH "LF" SUFFIX ADDED IN THE TABLE ARE LEAD FREE.
13. IF "LF" P/N THE PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
14. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 15 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.57mm MINIMUM THICK CIRCUIT BOARD. SEE APPLICATION NOTES/PROCEDURES IF THEY ARE AVAILABLE.
15. THIS PRODUCT HAS 100% TIN PLATING IN THE INTERFACE AND HAS NOT BEEN TESTED FOR WHISKER GROWTH IN ALL INTERCONNECT ENVIRONMENTS.
16. PLATING OPTIONS:  
PERFORMANCE PLATING WILL BE EITHER GOLD OR GXT ON CONTACT OR TAIL, OPTIONALLY TIN ON TAIL.



mat'l. code	surface / tolerance	projection	product family
AK	ISO 1302 / ISO 406 / ISO 101	QUICKIE	QUICKIE
date	tolerances unless otherwise specified	title	HEADER QUICKIE SLIM LINE VERTICAL 4 WALL
angles	XX±01/XX±03	dwg no	66506
linear	XXX±.003/XXX±.013	sheet of	2
±2"	XXX±.003/XXX±.013	size	A3
dr	L. SANDERS 1/25/95	type	Product Customer Drawing
engr	M. SMYK 1/25/95		
chr	J. ROMBERGER 1/25/95		
appd	M. SMYK 1/25/95		
sheet index	revision		
	sheet		

PRODUCT NUMBER NOTE 8, 9 & 12	SIZE	STYLE	DIM C	DIM J	PIN PLATING	PLASTIC MATERIAL
66506-001	2 X 5	B	.400/10.16	.105/2.67	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 2
-002				.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-003				.675/17.15	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-004				.105/2.67	120/200u" TIN LEAD	
-004LF				.105/2.67	100/160u" TIN	
-005				.150/3.81	120/200u" TIN LEAD	
-005LF				.150/3.81	100/160u" TIN	
-006				.675/17.15	120/200u" TIN LEAD	
-006LF	2 X 5	B	.400/10.16	.675/17.15	100/160u" TIN	
-007	2 X 10	D	.900/22.86	.105/2.67	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-008				.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-009				.675/17.15	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-010				.105/2.67	120/200u" TIN LEAD	
-010LF				.105/2.67	100/160u" TIN	
-011				.150/3.81	120/200u" TIN LEAD	
-011LF				.150/3.81	100/160u" TIN	
-012				.675/17.15	120/200u" TIN LEAD	
-012LF	2 X 10		.900/22.86	.675/17.15	100/160u" TIN	
-013	2 X 13		1.200/30.48	.105/2.67	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-014				.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-015				.675/17.15	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-016				.105/2.67	120/200u" TIN LEAD	
-016LF				.105/2.67	100/160u" TIN	
-017				.150/3.81	120/200u" TIN LEAD	
-017LF				.150/3.81	100/160u" TIN	
-018				.675/17.15	120/200u" TIN LEAD	
-018LF	2 X 13		1.200/30.48	.675/17.15	100/160u" TIN	
-019	2 X 17		1.600/40.64	.105/2.67	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-020				.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-021				.675/17.15	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-022				.105/2.67	120/200u" TIN LEAD	
-022LF				.105/2.67	100/160u" TIN	
-023				.150/3.81	120/200u" TIN LEAD	
-023LF				.150/3.81	100/160u" TIN	
-024				.675/17.15	120/200u" TIN LEAD	
66506-024LF	2 X 17	D	1.600/40.64	.675/17.15	100/160u" TIN	NOTE 2


mat'l. code	AK	surface	ISO 1302	tolerance	ISO 406 ISO 101	projection	first angle	product family	QUICKIE
tech nodr		date		angles	unless otherwise specified	INCH/MM		title	HEADER QUICKIE SLIM LINE VERTICAL 4 WALL
sheet index		revision		±2"		scale 1:1		dwg no	66506
sheet				dr	L. SANDERS	1/25/95		sheet of	5
index				engr	M. SMYK	1/25/95		size	A3
				chr	J. ROMBERGER	1/25/95		type	Product Customer Drawing
				appd	M. SMYK	1/25/95			

PRODUCT NUMBER NOTE 8, 9 & 12	SIZE	STYLE	DIM C	DIM J	PIN PLATING	PLASTIC MATERIAL
66506 -025	2 X 20	D	1.900/48.26	.105/2.67	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 2
-026				.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-027				.675/17.15	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-028				.105/2.67	120/200u" TIN LEAD	
-028LF				.105/2.67	100/160u" TIN	
-029				.150/3.81	120/200u" TIN LEAD	
-029LF				.150/3.81	100/160u" TIN	
-030				.675/17.15	120/200u" TIN LEAD	
-030LF	2 X 20		1.900/48.26	.675/17.15	100/160u" TIN	
-031	2 X 25		2.400/60.96	.105/2.67	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-032				.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-033				.675/17.15	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-034				.105/2.67	120/200u" TIN LEAD	
-034LF				.105/2.67	100/160u" TIN	
-035				.150/3.81	120/200u" TIN LEAD	
-035LF				.150/3.81	100/160u" TIN	
-036				.675/17.15	120/200u" TIN LEAD	
-036LF	2 X 25	D	2.400/60.96	.675/17.15	100/160u" TIN	
-037	2 X 7	C	.600/15.24	.105/2.67	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-038				.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-039				.675/17.15	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-040				.105/2.67	120/200u" TIN LEAD	
-040LF				.105/2.67	100/160u" TIN	
-041				.150/3.81	120/200u" TIN LEAD	
-041LF				.150/3.81	100/160u" TIN	
-042				.675/17.15	120/200u" TIN LEAD	
-042LF	2 X 7	C	.600/15.24	.675/17.15	100/160u" TIN	
-043	2 X 8	D	.700/17.78	.105/2.67	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-044				.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-045				.675/17.15	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-046				.105/2.67	120/200u" TIN LEAD	
-046LF				.105/2.67	100/160u" TIN	
-047				.150/3.81	120/200u" TIN LEAD	
-047LF				.150/3.81	100/160u" TIN	
-048				.675/17.15	120/200u" TIN LEAD	
66506 -048LF	2 X 8	D	.700/17.78	.675/17.15	100/160u" TIN	NOTE 2

mat'l. code	AK	surface	ISO 1302	tolerance	ISO 1101	projection	product family	QUICKIE
tech ngr date		angles		unless otherwise specified		title	HEADER QUICKIE SLIM LINE	
sheet index		line	XX:XX/XX:XX	XX:XX/XX:XX	XX:XX/XX:XX	INCH/MM	VERTICAL 4 WALL	
revision		±2"				scale 1:1		
sheet		dr	L. SANDERS	1/25/95			dwg no	66506
index		engt	M. SMYK	1/25/95			sheet # of	10
		chr	J. ROMBERGER	1/25/95			size	A3
		appd	M. SMYK	1/25/95			type	Product Customer Drawing

PRODUCT NUMBER NOTE 8, 9 & 12	SIZE	STYLE	DIM C	DIM J	PIN PLATING	PLASTIC MATERIAL
66506 -049	2 X 5	B	.400/10.16	.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	NOTE 2
-050	2 X 10	D	.900/22.86			
-051	2 X 13		1.200/30.48			
-052	2 X 17		1.600/40.64			
-053	2 X 20		1.900/48.26			
-054	2 X 25	D	2.400/60.96			
-055	2 X 7	C	.600/15.24			
-056	2 X 8	D	.700/17.78	.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-057	2 X 30		2.900/73.66	.105/2.67	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-058				.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-059				.675/17.15	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-060				.105/2.67	120/200u" TIN LEAD	
-060LF				.105/2.67	100/160u" TIN	
-061				.150/3.81	120/200u" TIN LEAD	
-061LF				.150/3.81	100/160u" TIN	
-062				.675/17.15	120/200u" TIN LEAD	
-062LF				.675/17.15	100/160u" TIN	
-063				.105/2.67	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-064				.150/3.81		
-065	2 X 30	D	2.900/73.66	.675/17.15		
-066	2 X 5	B	.400/10.16	.105/2.67		
-067	2 X 5	B	.400/10.16	.675/17.15		
-068	2 X 7	C	.600/15.24	.105/2.67		
-069	2 X 7	C	.600/15.24	.675/17.15		
-070	2 X 8	D	.700/17.78	.105/2.67	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-071	2 X 8	D	.700/17.78	.675/17.15	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-072	2 X 10		.900/22.86	.105/2.67		
-073	2 X 10		.900/22.86	.675/17.15		
-074	2 X 13		1.200/30.48	.105/2.67		
-075	2 X 13		1.200/30.48	.675/17.15		
-076	2 X 17		1.600/40.64	.105/2.67		
-077	2 X 17		1.600/40.64	.675/17.15		
-078	2 X 20		1.900/48.26	.105/2.67		
-079	2 X 20		1.900/48.26	.675/17.15		
-080	2 X 25		2.400/60.96	.105/2.67		
66506 -081	2 X 25	D	2.400/60.96	.675/17.15	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	NOTE 2


mat'l. code	AK	surface	ISO 1302	tolerance	ISO 406 ISO 101	projection	1st angle	product family	QUICKIE
tech ngr		date		angles	tolerances unless otherwise specified			title	HEADER QUICKIE SLIM LINE VERTICAL 4 WALL
sheet index		revision		line	XXL/01/XXL03 XXX/001/XXX013 XXX/002/XXX061	INCH/MM		dwg no	66506
sheet				±2"		scale 1:1		type	Product Customer Drawing
				dr	L. SANDERS	1/25/95		size	A3
				engr	M. SMYK	1/25/95			
				chr	J. ROMBERGER	1/25/95			
				appd	M. SMYK	1/25/95			



FCI  
Copyright FCI

PRODUCT NUMBER NOTE 8.9 & 12	SIZE	STYLE	DIM C	DIM J	PIN PLATING	PLASTIC MATERIAL
66506-082	2 X 5	B	.400/10.16	.105/2.67	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u NI	NOTE 2
-083	2 X 5	B	.400/10.16	.150/3.81		
-084	2 X 5	B	.400/10.16	.675/17.15		
-085	2 X 7	C	.600/15.24	.105/2.67		
-086	2 X 7	C	.600/15.24	.150/3.81		
-087	2 X 7	C	.600/15.24	.675/17.15		
-088	2 X 8	D	.700/17.78	.105/2.67		
-089	2 X 8	D	.700/17.78	.150/3.81		
-090	2 X 8	D	.700/17.78	.675/17.15		
-091	2 X 10	D	.900/22.86	.105/2.67		
-092	2 X 10	D	.900/22.86	.150/3.81		
-093	2 X 10	D	.900/22.86	.675/17.15		
-094	2 X 13	D	1.200/30.48	.105/2.67		
-095	2 X 13	D	1.200/30.48	.150/3.81		
-096	2 X 13	D	1.200/30.48	.675/17.15		
-097	2 X 17	D	1.600/40.64	.105/2.67		
-098	2 X 17	D	1.600/40.64	.150/3.81		
-099	2 X 17	D	1.600/40.64	.675/17.15		
-100	2 X 20	D	1.900/48.26	.105/2.67		
-101	2 X 20	D	1.900/48.26	.150/3.81		
-102	2 X 20	D	1.900/48.26	.675/17.15		
-103	2 X 25	D	2.400/60.96	.105/2.67		
-104	2 X 25	D	2.400/60.96	.150/3.81		
-105	2 X 25	D	2.400/60.96	.675/17.15	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u NI	
-106	2 X 30	D	2.900/73.66	.105/2.67	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u NI	
-107	2 X 30	D	2.900/73.66	.150/3.81	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u NI	
-108	2 X 30	D	2.900/73.66	.675/17.15	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u NI	
-109	2 X 5	B	.400/10.16	.105/2.67	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-110				.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-111				.675/17.15	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-112				.105/2.67	120/200u" TIN LEAD	
-112LF				.105/2.67	100/160u" TIN	
-113				.150/3.81	120/200u" TIN LEAD	
-113LF				.150/3.81	100/160u" TIN	
-114				.675/17.15	120/200u" TIN LEAD	
-114LF				.675/17.15	100/160u" TIN	
66506-114LF	2 X 5	B	.400/10.16	.675/17.15		NOTE 2

mat'l. code	AK	surface	ISO 1302	tolerance	ISO 101	projection	product family
tech ngr date		angles		tolerances unless otherwise specified		title	QUICKIE
sheet index		line	XXL/01/XXL03		INCH/MM	HEADER QUICKIE SLIM LINE	
revision		±2"	XXXL/002/XXXL061		scale 1:1	VERTICAL 4 WALL	
sheet		dr	L. SANDERS	1/25/95		dwg no	66506
		engr	M. SMYK	1/25/95		sheet of	6 of 10
		chr	J. ROMBERGER	1/25/95		size	A3
		appd	M. SMYK	1/25/95		type	Product Customer Drawing



PRODUCT NUMBER NOTE 8,9 & 12	SIZE	STYLE	DIM C	DIM J	PIN PLATING	PLASTIC MATERIAL
66506-115	2 X 5	B	.400/10.16	.105/2.67	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u NI	NOTE 2
-116				.150/3.81	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u NI	
-117				.675/17.15	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u NI	
-118				.105/2.67	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-119				.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-120	2 X 5	B	.400/10.16	.675/17.15	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	NOTE 2
-121						
THRU						
-216						
DISCONTINUED						
-217	2 X 12	D	1.100/27.94	.105/2.67	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u NI	NOTE 2
-218					30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-219					30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-220				.105/2.67	120/200u* TIN LEAD	
-220LF				.105/2.67	100/160u* TIN	
-221				.150/3.81	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u NI	
-222					30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-223					30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-224				.150/3.81	120/200u* TIN LEAD	
-224LF				.150/3.81	100/160u* TIN	
-225				.675/17.15	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u NI	
-226					30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-227					30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-228					120/200u* TIN LEAD	
-228	2 X 12		1.100/27.94	.675/17.15	100/160u* TIN	
-229	2 X 15		1.400/35.56	.105/2.67	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u NI	
-230					30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-231					30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-232				.105/2.67	120/200u* TIN LEAD	
-232LF				.105/2.67	100/160u* TIN	
-233	2 X 15	D	1.400/35.56	.150/3.81	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u NI	
-234	2 X 15	D	1.400/35.56	.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-235				.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-236				.150/3.81	120/200u* TIN LEAD	
-236LF				.150/3.81	100/160u* TIN	
66506-237	2 X 15	D	1.400/35.56	.675/17.15	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u NI	NOTE 2

mat'l. code	surface	tolerance	projection	product family
trtecn n0dr	ISO 1302	ISO 1101	1st angle	QUICKIE
date	tolerances unless otherwise specified			
	angles	LINEAR	INCH/MM	title
	±2°	XXX:XXX/XXX:XXX	scale 1:1	HEADER QUICKIE SLIM LINE
	dr	L. SANDERS	1/25/95	VERTICAL 4 WALL
	engr	M. SMYK	1/25/95	dwg no
	chr	J. ROMBERGER	1/25/95	66506
	appd	M. SMYK	1/25/95	sheet no
sheet index	revision			type
	sheet			Product Customer Drawing

PRODUCT NUMBER NOTE 8,9 & 12	SIZE	STYLE	DIM C	DIM J	PIN PLATING	PLASTIC MATERIAL
66506-238	2 X 5	B	.400/10.16	.675/17.15	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	NOTE 2
-239					30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-240					120/200u" TIN LEAD	
-240LF	2 X 15		1.400/35.56	.675/17.15	100/160u" TIN	
-241	2 X 22		2.100/53.34	.105/2.67	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u NI	
-242					30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-243					30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-244				.105/2.67	120/200u" TIN LEAD	
-244LF				.105/2.67	100/160u" TIN	
-245				.150/3.81	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u NI	
-246					30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-247					30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-248				.150/3.81	120/200u" TIN LEAD	
-248LF				.150/3.81	100/160u" TIN	
-249				.675/17.15	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u NI	
-250					30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-251					30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	
-252	2 X 22		2.100/53.34	.675/17.15	120/200u" TIN LEAD	
66506-252LF	2 X 22		2.100/53.34	.675/17.15	100/160u" TIN	
66506-253	2 X 17	D	1.600/40.64	.105/2.67	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u NI	NOTE 2
66506-254						
THRU					UNAVAILABLE	
66506-279						
66506-280	2 X 10	D	.900/22.86	.105/2.67	120/200u" TIN LEAD	NOTE 2
66506-280LF	2 X 10	D	.900/22.86	.105/2.67	100/160u" TIN	NOTE 2
66506-281						
THRU					UNAVAILABLE	
66506-306						
66506-307	2 X 5	B	.400/10.16	.097/2.46	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	NOTE 2
-308	2 X 5	B	.400/10.16			
-309	2 X 7	C	.600/15.24			
-310	2 X 8	D	.700/17.78			
-311	2 X 10		.900/22.86			
-312	2 X 12		1.100/27.94			
-66506-313	2 X 13	D	1.200/30.48	.097/2.46	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u NI	NOTE 2

mat'l. code	surface	tolerance	projection	product family
AK	ISO 1302	ISO 1101	1st angle	QUICKIE
	angles	line ar	INCH/MM	title
	±2"	XXX:XXX/XXX:XXX	scale 1:1	HEADER QUICKIE SLIM LINE
	dr L. SANDERS	1/25/95		VERTICAL 4 WALL
	engt M. SMYK	1/25/95		dwg no 66506
	chr J. ROMBERGER	1/25/95		sheet 8 of 10 size A3
	appd M. SMYK	1/25/95		type Product Customer Drawing
sheet index	revision			
	sheet			



PRODUCT NUMBER NOTE 8.9 & 12	SIZE	STYLE	DIM C	DIM J	PIN PLATING (NOTE 16)	PLASTIC MATERIAL NOTE 2
66506-314	2 X 15	D	1.400/35.56	.097/2.46	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-315	2 X 17		1.600/40.64			
-316	2 X 20		1.900/48.26			
-317	2 X 22		2.100/53.34			
-318	2 X 25		2.400/60.96			
-319	2 X 30		2.900/73.66	.097/2.46	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-320	2 X 8		.700/17.78	.105/2.67	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-321	2 X 25		2.400/60.96		30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-322	2 X 8		.700/17.78		50u"/1.27u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-323	2 X 17		1.600/40.64	.105/2.67	50u"/1.27u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-324	2 X 25		2.400/60.96	.120/3.05	15u"/.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-325	2 X 25		2.400/60.96	.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-326	2 X 10		.900/22.86	.120/3.05	15u"/.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-327	2 X 17		1.600/40.64	.120/3.05	15u"/.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-328	2 X 25		2.400/60.96	.120/3.05	15u"/.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-329	2 X 13		1.200/30.48	.150/3.81	15u"/.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-330	2 X 25		2.400/60.96		15u"/.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-331	2 X 30		2.900/73.66		15u"/.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-332	2 X 17		1.600/40.64		15u"/.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-333	2 X 20		1.900/48.26	.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-334	2 X 10		.900/22.86	.105/2.67	15u"/.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-335	2 X 20		1.900/48.26	.105/2.67	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-336	2 X 22		2.100/53.34	.105/2.67	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-337	2 X 12	D	1.100/27.94	.150/3.81	15u"/.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-338	2 X 5	B	.400/10.16	.150/3.81	15u"/.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-339	2 X 4	B	.300/7.62	.105/2.67	15u"/.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	
66506-340	2 X 10	D	.900/22.86	.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 2

mat'l. code	surface	tolerance	projection	product family
AK	ISO 1302	ISO 1101	1st angle	QUICKIE
	angles	line	INCH/MM	title
	±2°	XXX:XXX/XXX:XXX	scale 1:1	HEADER QUICKIE SLIM LINE
	dr	L. SANDERS	1/25/95	VERTICAL 4 WALL
	engr	M. SMYK	1/25/95	dwg no
	chr	J. ROMBERGER	1/25/95	66506
	appd	M. SMYK	1/25/95	sheet of 10 size
sheet index	revision			Product Customer Drawing
	sheet			

PRODUCT NUMBER NOTE 8, 9 & 12	SIZE	STYLE	DIM C	DIM J	PIN PLATING (NOTE 16)	PLASTIC MATERIAL
66506-341	2 X 17	D	1.600/40.64	.150/3.81	30u"/.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 2
-342	2 X 10	D	.900/22.86	.150/3.81	15u"/.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 2
-343	2 X 17	D	1.600/40.64	.150/3.81	15u"/.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 2
-344	UNASSIGNED					
-345	2 X 20	D	1.900/48.26	.120/3.05	15u"/.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 2
-346	UNASSIGNED					
-347	UNASSIGNED					
-348	2 X 5	B	.400/10.16	.105/2.67	15u"/.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 2
-349	2 X 7	C	.600/15.24			
-350	2 X 8	D	.700/17.78			
-351	2 X 10		.900/22.86			
-352	2 X 13		1.200/30.48			
-353	2 X 17		1.600/40.64			
-354	2 X 20		1.900/48.26			
-355	2 X 22		2.100/53.34			
-356	2 X 25		2.400/60.96			
-357	2 X 30		2.900/73.66	.105/2.67	15u"/.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-358	2 X 10		.900/22.86	.150/3.81	30u"/.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 11
-359	2 X 17		1.600/40.64	.150/3.81	30u"/.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 11
-360	2 X 12	D	1.100/27.94	.295/7.49	15u"/.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-361	2 X 5	B	.400/10.16	.105/2.67	15u"/.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-362	2 X 5	B	.400/10.16	.105/2.67	30u"/.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-363	2 X 8	D	.700/17.78	.105/2.67		
-364	2 X 10	D	.900/22.86	.105/2.67		
-365	2 X 15	D	1.400/35.56	.105/2.67		
-366	2 X 17	D	1.600/40.64	.105/2.67		
-367	2 X 5	B	.400/10.16	.150/3.81		
-368	2 X 17	D	1.600/40.64	.150/3.81		
66506-369	2 X 25	D	2.400/60.96	.150/3.81	30u"/.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 2

NOTE 11  
NOTE 11

mat'l. code	AK	surface	ISO 1302	tolerance	ISO 1101	projection	QUICKIE	product family	QUICKIE
tech nodr		angles		tolerances unless otherwise specified		title			
date		line	XXE/000/XXE/061			INCH/MM			
		±2"				scale 1:1			
		dr	L. SANDERS	1/25/95				dwg no	sheet 10 of 10 size
		engt	M. SMYK	1/25/95					A3
		chr	J. ROMBERGER	1/25/95					
		appd	M. SMYK	1/25/95					
sheet index		revision						type	Product Customer Drawing
sheet									