
PCB Power Relay

The Best Seller G2R









- Safety-oriented design with dielectric strength of 5,000 V between coil and contacts, and surge resistance of 10,000 V.
- AC and DC types are both available for operational coils.

RoHS Compliant





■Model Number Legend

G2R----1 2 3 4 5 6 7

1. Relay Function

None: Single-side stable K : Double-winding latching

2. Number of poles

1: 1-pole 2: 2-pole

3. Contact Form

None: NO/NC A : NO

4. Contact Type

None: Single

Z : Bifurcated contact

5. Enclosure rating

None: Flux protection

(T-type is an enclosed

relay)

4 : Fully sealed

6. Terminal Shape

None: PCB terminals T : Quick-connect (upper bracket mounting #187) 7. Classification

None: Standard E: High-capacity H: High-sensitivity U : For ultrasonically cleanable

Z : Full-wave rectifier

■Model Configuration

		Number	of poles	1-р	oole	2-р	ole	Minimum
Terminal Shape	Classification	Enclosure rating	Contact form	SPST-NO (1a)	SPDT (1c)	DPST-NO (2a)	DPDT (2c)	packing unit
		Flux protection	AC	G2R-1A	000.1	G2R-2A	G2R-2	
Standard Bifurcated	04	Flux protection	DC	GZR-TA	G2R-1	GZR-ZA	GZR-Z	100
	Standard	Fully sealed	AC	COD 144	G2R-14	000.044	G2R-24	pcs/tray
			DC G2R-1A4	G2H-14	G2R-2A4	G2H-24		
	Bifurcated	Flux protection	DC	G2R-1AZ	G2R-1Z	-	-	50
PCB terminals	contact	Fully sealed		G2R-1AZ4	G2R-1Z4	-	-	pcs/tray
	High-capacity	Flux protection	AC	G2R-1A-E	G2R-1-E		-	
	підп-сарасіту		DC	G2R-TA-E	G2n-1-E	_		100 pcs/tray
	High-sensitivity	Flux protection	DC	G2R-1A-H	G2R-1-H	G2R-2A-H	G2R-2-H	
İ	Double-winding latching	Flux protection	DC	G2RK-1A	G2RK-1	G2RK-2A	G2RK-2	50 pcs/tray
Quick-connect	Standard	Unsealed	AC	G2P-1A-T	G2R-1-T			100
Quick-connect S	Statiuatu	Ulisealeu	DC G2R-1A-T		GZH-1-1	_	_	pcs/tray

Note 1. Full-wave rectifier and supersonic cleaner compatible models are also available. Refer to page 3.

2. Sockets for PCB terminal models are not provided.

■Ordering Information

● PCB Terminal Models

		Number of poles		1-pole	2-pole		
Classification	Enclosure rating	Contact form	Model	Rated coil voltage	Model	Rated coil voltage	
				12, 24, 100/(110) VAC		12, 24, 100/(110) VAC	
		NO	G2R-1A	200/(220) VAC	G2R-2A	200/(220) VAC	
		INO	GZN-TA	5, 6, 12, 24, 48 VDC	GZN-ZA	5, 6, 12, 24, 48 VDC	
	Flux protection			100 VDC		100 VDC	
	Flux protection			12, 24, 100/(110) VAC		12, 24, 100/(110) VAC	
		NO/NC	G2R-1	200/(220) VAC	G2R-2	200/(220) VAC	
		NO/NO	GZN-1	5, 6, 12, 24, 48 VDC	GZN-Z	5, 6, 12, 24, 48 VDC	
Standard				100 VDC		100 VDC	
Standard				12, 24, 100/(110) VAC		12, 24, 100/(110) VAC	
		NO	G2R-1A4	200/(220) VAC	G2R-2A4	200/(220) VAC	
		INO	GZN-TA4	5, 6, 12, 24, 48 VDC	G2N-2A4	5, 6, 12, 24, 48 VDC	
	Fully sealed			100 VDC		100 VDC	
	I ully sealed			12, 24, 100/(110) VAC		12, 24, 100/(110) VAC	
		NO/NC	G2R-14	200/(220) VAC	G2R-24	200/(220) VAC	
			G2R-14	5, 6, 12, 24, 48 VDC		5, 6, 12, 24, 48 VDC	
				100 VDC		100 VDC	
High-sensitivity		NO	G2R-1A-H	5, 6, 12, 24, 48 VDC	G2R-2A-H	5, 6, 12, 24, 48 VDC	
r light-sensitivity	Flux protection	NO/NC	G2R-1-H	5, 6, 12, 24, 48 VDC	G2R-2-H	5, 6, 12, 24, 48 VDC	
Double-winding	Tida protection	NO	G2RK-1A	5, 6, 12, 24 VDC	G2RK-2A	5, 12, 24 VDC	
latching		NO/NC	G2RK-1	5, 6, 12, 24 VDC	G2RK-2	5, 6, 12, 24 VDC	
		NO	G2P-1A7	12, 24, 48 VDC			
	Flux protection	NO	G2R-1AZ	100 VDC			
	I lux protection	NO/NC	G2R-1Z	5, 6, 12, 24, 48 VDC		_	
Bifurcated		NO/NO	GZN-1Z	100 VDC			
contact		NO	G2R-1AZ4	5, 12, 24, 48 VDC			
	Fully sealed	110	GZN-TAZ4	100 VDC			
	I ully sealed	NO/NC	G2R-1Z4	5, 12, 24, 48 VDC		_	
		NO/NC	G2h-124	100 VDC			
				12, 24, 100/(110) VAC			
		NO	G2R-1A-E	200/(220) VAC			
		INO	GZN-TA-E	5, 6, 12, 24, 48 VDC		_	
High-capacity	Flux protection			100 VDC			
т пун-сараску	I lux protection			12, 24, 100/(110) VAC			
		NO/NC	G2R-1-E	200/(220) VAC		_	
		140/140	GZII-I-E	5, 6, 12, 24, 48 VDC		•	
				100 VDC			

Note: When ordering, add the rated coil voltage to the model number.

Example: G2R-1A AC12

Rated coil voltage

However, the notation of the coil voltage on the product case as well as on the packing will be marked as $\square\square$ VAC.

Quick-connect Terminal (#187)

		Number of poles	1-pole		
Classification	Enclosure rating	Contact form	Model	Rated coil voltage	
				12, 24, 100/(110) VAC	
		NO	G2R-1A-T	200/(220) VAC	
		INO	GZN-TA-T	5, 6, 12, 24, 48 VDC	
Standard	Unsealed			100 VDC	
Staridard	Unsealed			12, 24, 100/(110) VAC	
		NO/NC	G2R-1-T	200/(220) VAC	
		NO/NC	G2R-1-1	5, 6, 12, 24, 48 VDC	
				100 VDC	

● Full-wave Rectifier

		Number of poles	1	-pole	2-pole		
Classification	Enclosure rating	Contact form	Model	Rated coil voltage	Model	Rated coil voltage	
		NO	G2R-1A-Z	5, 12, 24 VDC	G2R-2A-Z	5, 6, 12, 24, 48 VDC	
El.	Flux protection	NO	G2N-1A-2	100 VDC	GZN-ZA-Z	100 VDC	
	Flux protection	NO/NC	G2R-1-Z	5, 12, 24, 48 VDC	G2R-2-Z	12, 24, 48 VDC	
Standard		NO/NO	G2N-1-2	100 VDC	G2N-2-2	100 VDC	
Standard		NO	G2R-1A4-Z	5, 12, 48 VDC	G2R-2A4-Z	24, 48 VDC	
	Fully sealed	NO		100 VDC	G2N-2A4-2	100 VDC	
	I ully sealed	NO/NC	G2R-14-Z	5, 12, 24, 48 VDC	G2R-24-Z	5, 12, 24 VDC	
		NO/NC	G2N-14-Z	100 VDC	G2N-24-2	100 VDC	
		NO	G2R-1A-EZ	5, 12, 24 VDC			
High-capacity	Flux protection	INO	GZN-TA-EZ	100 VDC		-	
		NO/NC	G2R-1-EZ	12, 24, 48 VDC			

● For Ultrasonically Cleanable

	Number of poles			1-pole	2-pole		
Classification	Enclosure rating	Contact form	Model	Rated coil voltage	Model	Rated coil voltage	
				12, 24, 100/(110) VAC		100/(110) VAC	
	NO	G2R-1A4-U	200/(220) VAC	G2R-2A4-U	-		
				5, 6, 12, 24, 48 VDC		5, 12, 24 VDC	
Standard Fully sealed	Fully sealed			100/(110) VAC 200/(220) VAC		24, 100/(110) VAC 200/(220) VAC	
		NO/NC	G2R-14-U	5, 12, 24, 48 VDC	G2R-24-U	5, 12, 24, 48 VDC	
				100 VDC		100 VDC	

Note: When ordering, add the rated coil voltage to the model number.

Example: G2R-1A-T AC12

Rated coil voltage

However, the notation of the coil voltage on the product case as well as on the packing will be marked as $\square\square$ VAC.

■Ratings

● Coil

	Item	Rated current (mA)		Coil resistance	Must operate voltage (V)	Must release voltage (V)	Max. voltage (V)	Power consumption
Classification	Rated voltage	50 Hz 60 Hz		(Ω)	% of rated voltage			(VA, W)
Standard	12 VAC	93	75	65				
Quick-connect	24 VAC	46.5	37.5	260	80% max.	30% min.	140% (at 23°C)	Approx. 0.9
Fully sealed	100/(110) VAC	11	9/(10.6)	4,600	60% max.	30% 11111.		(60 Hz)
High-capacity	200/(220) VAC	5.5	4.5/(5.3)	20,200				
	5 VDC	106		47		15% min.	170% (at 23°C)	Approx. 0.53
Standard	6 VDC	88.2		68				
High-capacity Bifurcated contact	12 VDC	43.6		275	- 70% max.			
Quick-connect	24 VDC	21.8		1,100				
Fully sealed	48 VDC	1	1.5	4,170]			
	100 VDC		5.3	18,870				
	5 VDC	7	1.4	70				
	6 VDC	6	0	100		15% min.	4=00/	
High-sensitivity	12 VDC	3	0	400	70% max.		170% (at 23°C)	Approx. 0.36
	24 VDC	1	5	1,600				
	48 VDC		7.5	6,400				

- Note 1. The rated current and coil resistance are measured at a coil temperature of 23°C with a tolerance of+15%/-20% (AC rated current) or ±10% (DC coil resistance).
 - 2. AC coil resistances shown above are only reference values.
 - 3. The operating characteristics are measured at a coil temperature of 23°C.
 - 4. The "Max. voltage" is the maximum voltage that can be applied to the relay coil.

● Coil: Double-winding Latching Relays

Item	Set Coil		Reset coil		Must set voltage (V)	Must reset voltage (V)	Max. voltage (V)	Power cor	nsumption
Rated voltage	Rated current (mA)	Coil resistance (Ω)	Rated current (mA)	Coil resistance (Ω)	% of rated voltage		Set Coil (mW)	Reset coil (mW)	
5 VDC	167	30	119	42					
6 VDC	138	43.5	100	60	70% max.	70% max.	140% (at 23°C)	Approx. 850	Approx. 600
12 VDC	70.6	170	50	240	70% max.				
24 VDC	34.6	694	25	960					

- Note 1. The rated current and coil resistance are measured at a coil temperature of 23°C with a tolerance of ±10%.
 - 2. The operating characteristics are measured at a coil temperature of 23°C.
 - 3. The "Max. voltage" is the maximum voltage that can be applied to the relay coil.



◆ Contacts: Flux Protection Type

Classification		Standard type Quick-connect Terminal (1single-pole type)			High-cap	acity type	Bifurcated contact type		High-sensitivity type			
Number of poles	1-pole		2-pole		1-pole		2-pole		1-pole		2-pole	
Load	Resistive load	Inductive load (cos\phi = 0.4; L/R = 7 ms)		Inductive load (cos\psi = 0.4; L/R = 7 ms)		Inductive load (cos ϕ = 0.4; L/R = 7 ms)		Inductive load (cos\psi = 0.4; L/R = 7 ms)		Inductive load (cos \$\phi = 0.4; L/R = 7 ms)		Inductive load (cosφ = 0.4; L/R = 7 ms)
Contact type	Single			Sir	igle	Bifurcated		Single				
Contact material						Ag-alloy	(Cd free)					
Rated load	10 A at 250 VAC 10 A at 30 VDC	7.5 A at 250 VAC 5 A at 30 VDC	5 A at 250 VAC 5 A at 30 VDC	2 A at 250 VAC 3 A at 30 VDC	16 A at 250 VAC 16 A at 30 VDC	8 A at 250 VAC 8 A at 30 VDC	5 A at 250 VAC 5 A at 30 VDC	2 A at 250 VAC 3 A at 30 VDC	5 A at 250 VAC 5 A at 30 VDC	2 A at 250 VAC 3 A at 30 VDC	3 A at 250 VAC 3 A at 30 VDC	1 A at 250 VAC 1.5 A at 30 VDC
Rated carry current	10	Α	5	A	16	6 A	5	Α	5	A	3	Α
Max. switching voltage		380 VAC,	125 VDC			380 VAC,	125 VDC			380 VAC,	125 VDC	
Max. switching current	10 A 5 A		Α	16	6 A	5	Α	5	Α	3	Α	
Failure rate (P level) (reference value) *	evel) 100 mA at 5 VDC		10 mA a	at 5 VDC	100 mA	at 5 VDC	1 mA at 5 VDC		100 mA at 5 VDC		10 mA at 5 VDC	

^{*} This value was measured at a switching frequency of 120 operations/min.

● Contacts: Fully Sealed Type

С	Classification		Standard type (Si		Bifurcated	contact type		
Num	ber of poles	1- _F	oole	2-p	oole	1-pole		
Item	Load	Resistive load (cosφ = 1)	Inductive load (cosφ = 0.4; L/R = 7 ms)	Resistive load (cos ϕ = 1)	Inductive load (cosφ = 0.4; L/R = 7 ms)	Resistive load (cos ϕ = 1)	Inductive load (cosφ = 0.4; L/R = 7 ms)	
Contact type		Sir	ngle	Sir	ngle	Bifu	rcated	
Contact materi	ial	Ag-alloy (Cd free)						
Rated load		8 A at 250 VAC 8 A at 30 VDC	6 A at 250 VAC 4 A at 30 VDC	4 A at 250 VAC 4 A at 30 VDC	1.5 A at 250 VAC 2.5 A at 30 VDC	5 A at 250 VAC 5 A at 30 VDC	2 A at 250 VAC 3 A at 30 VDC	
Rated carry cu	ırrent	8	A	4	4 A		5 A	
Max. switching	yoltage	380 VAC	, 125 VDC	380 VAC	, 125 VDC	380 VAC, 125 VDC		
Max. switching	current	8	A	4	A	5 A		
Failure rate (P (reference valu	,	100 mA	at 5 VDC	10 mA at 5 VDC		1 mA at 5 VDC		

^{*} This value was measured at a switching frequency of 120 operations/min.

● Contacts: Latching Type

Number of poles	1-p	oole	2-pole			
Item Load	Resistive load (cos (cos = 1)	Inductive load (cosφ = 0.4; L/R = 7 ms)	Resistive load (cosφ = 1)	Inductive load (cos\phi = 0.4; L/R = 7 ms)		
Contact type	Sir	ngle	Single			
Contact material		Ag-alloy (Cd free)				
Rated load	5 A at 250 VAC 5 A at 30 VDC	3.5 A at 250 VAC 2.5 A at 30 VDC	3 A at 250 VAC 3 A at 30 VDC	1.5 A at 250 VAC 2 A at 30 VDC		
Rated carry current	5	A	3 A			
Max. switching voltage	380 VAC	, 125 VDC	380 VAC, 125 VDC			
Max. switching current	5	A	3 A			
Failure rate (P level) (reference value) *	100 mA	at 5 VDC	10 mA at 5 VDC			

^{*} This value was measured at a switching frequency of 120 operations/min.

■Characteristics

Standard Relays

Item	Number of poles	1-pole	2-pole			
Contact res		30 m $Ω$ max.	50 m $Ω$ max.			
Operate tim		15 ms max.				
Release tim		AC: 10 ms max.; DC: 5 ms max.				
Max.	Mechanical	18,000 operations/hr				
operating frequency	Electrical	1,800 ope	erations/hr			
Insulation re	esistance *3	1,000 l	MΩ min.			
	Between coil and contacts	5,000 VAC, 50/60 Hz				
Dielectric strength	Between contacts of different polarity	-	3,000 VAC, 50/60 Hz for 1 min			
Strongth	Between contacts of the same polarity	1,000 VAC, 50/60 Hz for 1 min				
Insulation distance	Between coil and contacts	Clearance: 8 mm, Creepage: 8 mm				
Vibration	Destruction	10 to 55 to 10 Hz, 0.75 mm single amplitude (1.5 mm double amplitude)				
resistance	Malfunction	amplitude (1.5 mm	z, 0.75 mm single n double amplitude)			
Shock	Destruction	,	0 m/s ²			
resistance	Malfunction		en energized; n no energized			
Durability	Mechanical	AC coil: 10,000,000 operations min.; DC coil: 20,000,000 operations min. (at 18,000 operations/hr)				
	Electrical	100,000 operations min. (at 1,800 operations/hr under rated load)				
	erating temperature	-40°C to 70°C (with no icing)				
	erating humidity	5% to 85%				
Weight		Approx. 17 g (/	Approx. 20 g *4)			

- Note: The values here are initial values.

 *1. Measurement conditions: 5 VDC, 1 A, voltage-drop method.

 *2. Measurement conditions: Rated operating voltage applied, not including contact bounce.
- Measurement conditions: The insulation resistance was measured with a 500 VDC megohmmeter at the same locations as the dielectric strength was measured.

 Value for quick-connect terminals.

Double-winding Latching Relays

Item	Number of poles	1-pole	2-pole		
Contact resista		30 m Ω max.	50 mΩ max.		
Set	Time *2		max.		
OCI	Min. set pulse width *3		ms		
	Time *2	20 ms max.			
Reset	Min. reset pulse width *3		ms		
Max.operating	Mechanical		erations/hr		
frequency	Electrical		erations/hr		
Insulation resis		1,000 N	lΩ min.		
	Between coil and contacts	5,000 VAC, 50/	60 Hz for 1 min		
Dielectric	Between contacts of different polarity	- 3,000 VAC, 50/60 Hz for			
strength	Between contacts of the same polarity	1,000 VAC, 50/60 Hz for 1 min			
	Between set and reset coils	1,000 VAC, 50/60 Hz for 1 min			
Insulation distance	Between coil and contacts	Clearance: 8 mm,	Creepage: 8 mm		
Vibration	Destruction	10 to 55 to 10 Hz, 0.75 mm single amplitude (1.5 mm double amplitude)			
resistance	Malfunction		, 0.75 mm single double amplitude)		
Shock	Destruction	1,000) m/s ²		
resistance	Malfunction	Set: 500m/s ² Arma Reset: 200m/s ² Co			
Durability	Mechanical	(at 18,000 o	perations min perations/hr)		
Durability	Electrical	100,000 operations min. (at 1,800 operations/hr under rated load)			
Ambient operat	ting temperature	-40°C to 70°C (with no icing or condensation)			
Ambient operat	ting humidity	5% to 85%			
Weight		Approx	x. 17 g		

- Note: The values here are initial values.


 *1. Measurement conditions: 5 VDC, 1 A, voltage-drop method.

 *2. Measurement conditions: Rated operating voltage applied, not including contact bounce.
- *3. *4. Measurement couditions: Rated operating voltage applied.
 Measurement conditions: The insulation resistance was measured with a 500 VDC megohmmeter at the same locations as the dielectric strength was measured.


■Engineering Data

Maximum Switching Capacity Flux Protection/Plug-in Relays


G2R-1, G2R-1A, G2R-1-T, G2R-1A-T




G2R-1-H, G2R-1A-H, G2R-2, G2R-2A




G2R-1-E, G2R-1A-E



G2R-2-H, G2R-2A-H




G2R-1Z, G2R-1AZ




Switching voltage (V)


G2RK-1A, G2RK-1




G2RK-2A, G2RK-2




Fully Sealed Relays G2R-14, G2R-1A4



G2R-24, G2R-2A4




G2R-1Z4, G2R-1AZ4




Durability


Flux Protection/Plug-in Relays G2R-1, G2R-1A, G2R-1-T, G2R-1A-T




G2R-1-E, G2R-1A-E




G2R-1Z, G2R-1AZ




G2R-1-H, G2R-1A-H, G2R-2, G2R-2A




G2R-2-H, G2R-2A-H




G2RK-1A, G2RK-1




G2RK-2A, G2RK-2




Fully Sealed Relays G2R-14, G2R-1A4




G2R-24, G2R-2A4




G2R-1Z4, G2R-1AZ4




Ambient Temperature vs. Maximum **Coil Voltage**



Ambient Temperature vs. Must Operate and Must Release Voltage G2R-1




G2R-2




Note: The maximum coil voltage refers to the maximum value in a varying range of operating power voltage, not a continuous voltage.

Shock Malfunction


G2R-1 Number of Relays: 5 pcs



G2R-2 Number of Relays: 5 pcs



• Keep-power decrement with time G2RK-1



■Dimensions

Relays with PCB Terminals (SPDT (1c) Relays) G2R-1(-Z)

G2R-1Z G2R-1-H




This illustration is the G2R-1 model.

13 max (12.7)* 29 max 25.5 max. (25.3)* (0.3)0.3


0.16

* Average value ** With AC coil or "-H" models: 0.3.

PCB Mounting Holes (BOTTOM VIEW) Tolerance: ±0.1 mm



Terminal Arrangement/ Internal Connections (BOTTOM VIEW)




Relays with PCB Terminals (SPST-NO (1a) Relays)

G2R-1A(-Z) G2R-1AZ G2R-1A-H




G2R-1A model.




0.16 * Average value ** With AC coil or "-H" models: 0.3. This illustration is the

PCB Mounting Holes (BOTTOM VIEW)

Tolerance: ±0.1 mm




Terminal Arrangement/ Internal Connections (BOTTOM VIEW)




Relays with PCB Terminals (SPDT (1c) /High-capacity Relays) G2R-1-E(Z)






PCB Mounting Holes (BOTTOM VIEW)




Terminal Arrangement/ Internal Connections

(BOTTOM VIEW)




Relays with PCB Terminals (SPST-NO (1a)/High-capacity Relays) G2R-1A-E(Z)




PCB Mounting Holes


(BOTTOM VIEW) Tolerance: ±0.1 mm




Terminal Arrangement/ Internal Connections (BOTTOM VIEW)



Note: Orientation marks are indicated as follows: 🗒 🛛









(BOTTOM VIEW) Tolerance: ±0.1 mm 3.5 3.5 (2.7) 7.5 Five, 1.3-dia holes


PCB Mounting Holes















PCB Mounting Holes (BOTTOM VIEW) Tolerance: ±0.1 mm




Terminal Arrangement/ Internal Connections (BOTTOM VIEW)













PCB Mounting Holes (BOTTOM VIEW)



Terminal Arrangement/ Internal Connections (BOTTOM VIEW)




(After confirming coil polarity, wire correctly.)


Double-winding Latching Relays with

PCB Terminals (SPST-NO (1a) Relays) G2RK-1A






PCB Mounting Holes (BOTTOM VIEW) Tolerance: ±0.1 mm



Terminal Arrangement/ Internal Connections (BOTTOM VIEW)




(After confirming coil polarity, wire correctly.)


Double-winding Latching Relays with PCB Terminals (DPDT (2c) Relays)








PCB Mounting Holes (BOTTOM VIEW)




Terminal Arrangement/ Internal Connections (BOTTOM VIEW)




(After confirming coil polarity, wire correctly.)

Double-winding Latching Relays with PCB Terminals (DPST-NO (2a) Relays)






PCB Mounting Holes (BOTTOM VIEW)




Terminal Arrangement/ Internal Connections (BOTTOM VIEW)




(After confirming coil polarity, wire correctly.)

G2R-2(-Z)


G2R-2-H





PCB Mounting Holes

(BOTTOM VIEW)




Relays with PCB Terminals (DPST-NO (2a) Relays) G2R-2A


Relays with PCB Terminals

G2R-2A-H G2R-2A-Z






PCB Mounting Holes (BOTTOM VIEW) Tolerance: ±0.1 mm




Terminal Arrangement/ Internal Connections (BOTTOM VIEW)



Relays with PCB Terminals (DPDT (2c) Relays) G2R-24(-Z)(-U)






PCB Mounting Holes (BOTTOM VIEW) Tolerance: ±0.1 mm


Eight, 1.3-dia. holes (2.7)

Terminal Arrangement/ Internal Connections (BOTTOM VIEW)




Relays with PCB Terminals (DPST-NO (2a) Relays) G2R-2A4(-Z)(-U)






PCB Mounting Holes


(BOTTOM VIEW) Tolerance: ±0.1 mm





Terminal Arrangement/ Internal Connections (BOTTOM VIEW)




Relays with Quick-connect Terminals (SPDT (1c) Relays) G2R-1-T








Mounting Holes (BOTTOM VIEW) Tolerance: ±0.1 mm





Note: Model number of quick-connect terminal is 187.

Terminal Arrangement/ Internal Connections (BOTTOM VIEW)




Relays with Quick-connect Terminals (SPST-NO (1a) Relays) G2R-1A-T






* Average value

(13.1)*




Mounting Holes (BOTTOM VIEW) Tolerance: ±0.1 mm



Note: Model number of quick-connect terminal is 187.

Terminal Arrangement/ Internal Connections (BOTTOM VIEW)



Note: Orientation marks are indicated as follows: []

■Approved Standards

• The approval rating values for overseas standards are different from the performance values determined individually. Confirm the values before use.

UL Recognized: File No. E41643 1-pole

Model	Contact	Coil ratings	Contact ratings	Number of test
	IOIIII			operations
G2R-1A		5 to 110 VDC 12 to 220 VAC	10 A, 250 VAC (General Use) at 40°C	100,000
G2R-1A4	SPST-NO		000) at 10 0	
G2R-1A-H	(1a)		5 A, 277 VAC (General Use) at 40°C	6,000
G2R-1A-T			10 A, 30 VDC (Resistive) at 40°C	100,000
G2R-1	SPDT (1c)			
G2R-14				
G2R-1-H			TV-3 (N. O. only) at 40°C	25,000
G2R-1-T				25,000
G2R-1AZ	SPST-NO		5 A, 250 VAC (General Use) at 40°C	6,000
G2R-1AZ4	(1a)	5 to 110 VDC		
G2R-1Z	SPDT	12 to 220 VAC	5 A, 30 VDC (Resistive) at 40°C	
G2R-1Z4	(1c)			
G2R-1A-E	SPST-NO (1a)		16 A, 250 VAC (General Use) at 40°C	30,000
G2R-1-E	_		16 A, 30 VDC (Resistive) at 40°C	6,000
GZN-1-E	(1c)		TV-3 (N. O. only) at 40°C	25,000

2-pole

Model	Contact form	Coil ratings	Contact ratings	Number of test operations
G2R-2A	DDOT NO	5 to 110 VDC 12 to 220 VAC	5 A, 250 VAC (General Use) at 40°C	6,000
G2R-2A4	DPST-NO (2a)			
G2R-2A-H			5 A, 30 VDC (Resistive) at 40°C	100,000
G2R-2	DPDT (2c)			100,000
G2R-24			TV-3 (N. O. only) at 40°C	25,000
G2R-24-H	, -,			20,000

CSA Certified: File No. LR31928 1-pole

Model	Contact form	Coil ratings	Contact ratings	Number of test operations
G2R-1A		5 to 110 VDC 12 to 220 VAC	10 A, 250 VAC (General Use) at 40°C	100,000
G2R-1A4	SPST-NO			
G2R-1A-H	(1a)			
G2R-1A-T			40.4.00.1/0.0	100,000
G2R-1			10 A, 30 VDC (Resistive) at 40°C	
G2R-14	SPDT (1c)			
G2R-1-H			TV-3 (N. O. only) at 40°C	25,000
G2R-1-T				
G2R-1AZ	SPST-NO (1a) SPDT	5 to 110 VDC 12 to 220 VAC	5 A, 250 VAC (General Use) at 40°C	6,000
G2R-1AZ4				
G2R-1Z			5 A, 30 VDC (Resistive) at 40°C	
G2R-1Z4	(1c)			
G2R-1A-E	SPST-NO (1a)	5 to 110 VDC 12 to 220 VAC	16 A, 250 VAC (General Use) at 40°C 16 A, 30 VDC	6,000
G2R-1-E	SPDT (1c)		(Resistive) at 40°C TV-3 (N. O. only) at 40°C	25,000

2-pole

Model	Contact form	Coil ratings	Contact ratings	Number of test operations
G2R-2A	DDOT NO	5 to 110 VDC 12 to 220 VAC	5 A, 250 VAC (General Use) at 40°C	6,000
G2R-2A4	DPST-NO (2a)			
G2R-2A-H			5 A, 30 VDC (Resistive)	100,000
G2R-2	DPDT (2c)		at 40°C	100,000
G2R-24			TV-3 (N. O. only) at 40°C	25,000
G2R-24-H	(==)			25,000

EN/IEC, VDE Certified: (p/E) Certificate No. 40015012

Model	Contact form	Coil ratings	Contact ratings	Number of test operations
G2R-1(A)-E	1	5, 6, 12, 24, 48, 100 VDC 12, 24, 100/110, 200/220 VAC	16 A, 250 VAC (cosφ = 1.0) at 70°C	
G2R-()	1	5, 6, 12, 24, 48, 100 VDC 12, 24, 100/110, 200/220 VAC	10 A, 250 VAC (cosφ = 1.0) at 40°C	100,000
			10 A, 30 VDC (0 ms) at 40°C	
	5, 6, 12, 24, 48, 100 VDC 2 12, 24, 100/110, 200/220 VAC	48, 100 VDC	5 A, 250 VAC (cosφ = 1.0) at 40°C	
		5 A, 30 VDC (0 ms) at 40°C		

EN, TÜV Certified: Registration No. R50030327

Model	Contact form	Coil ratings	Contact ratings	Number of test operations
G2R-1(A)-E	1	5 to 110 VDC 12 to 220 VAC	16 A, 250 VAC (cosφ = 1.0) at 70°C	
	1 1	5 to 110 VDC 12 to 220 VAC	10 A, 250 VAC (cos = 1.0) at 70°C	100,000
G2R-()			10 A, 30 VDC (0 ms) at 70°C	
dzn-()	2 1.1	5 to 110 VDC	5 A, 250 VAC (cos = 1.0) at 40°C	
		12 to 220 VAC	5 A, 30 VDC (0 ms) at 40°C	


■Precautions

• Please refer to "PCB Relays Common Precautions" for correct use.

Correct Use

Mounting

 When mounting a number of relays on a PCB, be sure to provide a minimum mounting space of 5 mm between the two juxtaposed relays as shown below.



Handling

 The terminals are compatible with Faston receptacle #187 and are suitable for positive-lock mounting. Use only Faston terminals with the specified numbers.

Select leads for connecting Faston receptacles with wire diameters that are within the allowable range for the load current.

Do not apply excessive force to the terminals when mounting or dismounting the Faston receptacle. Also, do not insert terminals at an angle, or insert/remove multiple terminals at the same time. Be sure to insert and remove terminals carefully one at a time.

Refer to the following table for examples of positive-lock connectors made by AMP. Contact the manufacturer directly for details on connectors including availability.

Туре	Receptacle terminals	Positive housing
#187 (Width 4.75)	AMP170330-1 (170324-1) AMP170331-1 (170325-1) AMP170332-1 (170326-1)	AMP172074-1 (natural color) AMP172074-4 (yellow) AMP172074-5 (green) AMP172074-6 (blue)

Note: The numbers shown in parentheses are for air-feeding.

Minimum Pulse Width of Doublewinding Latching Relays

- The minimum pulse width shown in the table of characteristics are values measured under conditions of ambient temperature at 23°C with rated operating voltage imposed on coil. The Relay may not provide a satisfactory performance as its holding ability decreases depending on the operating circuit conditions and ambient temperature, or decreases due to degradation over time. In actual operation, impose to the coil a rated operating voltage with a pulse width that is suitable to the actual load, and reset the setting at least once a year, to correspond to the degradation over time.
- When using the Relay in a strong magnetic field environment, the magnetic body may be demagnetized due to the influence of environment, causing the Relay to malfunction.

Therefore, do not use the Relay in a strong magnetic field environment.

Degradation over Time of Doublewinding Latching Relays Holding Ability

• If a double-winding latching Relay is used left set for an extended period, changes over time will degrade the magnetic force, and the reduction in holding ability may cause the set status to be released. This is also because of the properties of semi-hard magnetic material, and the rate of degradation over time depends on the ambient environment (e.g., temperature, humidity, vibration, and presence or absence of external magnetic fields). Perform maintenance at least once a year by resetting, applying the rated voltage again, and then setting.

■Wiring High Capacity (-E) Models

 High-capacity models (-E) have a structure that connects two terminals from one contact.

When designing the circuit, use both terminals.

If you use only one terminal, the relay may be unable to satisfy specified performance.

Please check each region's Terms & Conditions by region website.

OMRON Corporation

Electronic and Mechanical Components Company

Regional Contact

Americas

https://www.components.omron.com/

Asia-Pacific

https://ecb.omron.com.sg/

Korea

https://www.omron-ecb.co.kr/

Europe

http://components.omron.eu/

China

https://www.ecb.omron.com.cn/

Japan

https://www.omron.co.jp/ecb/

Cat. No. K013-E1-20 0818(0207)(O)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Omron:

G2R-1E-AC120 G2R-2-DC12 G2R-1A-E-T130-DC24 G2R-1-E-DC5 G2R-14-DC5 G2R-1A-DC24 G2R-2A-DC12 G2R-24-DC12 G2R-14-DC12 G2R-24-AC220 G2R-14-AC24 G2R-1A-E-DC12 G2R-1A-E-DC24 G2R-24-AC24 G2R-2-AC120 G2R-24-AC120 G2R-14-AC120 G2R-1A-T-AC24 G2R-2-DC24 G2R-1-E-DC24 G2R-1-DC24 G2R-1-DC24 G2R-1-DC12 G2R-1A-AC120 G2R-24-DC24 G2R-14-DC24 G2R-1-E-DC12 G2R-1A4-DC24 G2R-2-DC5 G2R-1-DC110 G2R-1-AC220 G2R-1-ASI-DC24 G2R-1-ASI-DC12 G2R-1-DC48 G2R-1-DC5 G2R-1-DC6 G2R-1-E-AC24 G2R-1-E-AC240 G2R-1-E-ASI-DC12 G2R-1-E-ASI-DC24 G2R-1-E-ASI-DC24 G2R-1-E-ASI-DC24 G2R-1-E-DC48 G2R-1-E-DC48 G2R-1-E-T130 DC24 G2R-1-H-DC12 G2R-1-H-DC12 G2R-1-H-DC24 G2R-1-H-DC48 G2R-1-H-DC5 G2R-1-H-DC6 G2R-1-H-T130 DC12 G2R-1-T-AC240 G2R-1-T-AC240 G2R-1-H-DC48 G2R-1-H-DC5 G2R-1-H-DC6 G2R-1A-AC240 G2R-1A-ASI-DC12 G2R-1A-DC12 G2R-1A-H-DC5 G2R-1A-H-DC5 G2R-1A-H-DC5 G2R-1A-H-DC5 G2R-1A-H-DC5 G2R-1A-H-DC5 G2R-1A-H-DC5 G2R-1A-H-DC5 G2R-1A-H-DC6