



SC-DB

Surface Conditioning Disc Backed Scotch Brite™ Discs for Cleaning Operations

Scotch-Brite™ Technical Data Sheet

Construction

Grades:

Type A (brown): coarse

Dimensions:

Diameter 115-200 mm

Bore 22 mm

Power Tools



Features	Advantages	Benefits
Surface conditioning web	Open construction	Anti-loading
Fiber backing	Effective on edges and corners	Long product life; for use on angle grinders
Integrated grinding aid coating	Even suitable for dry applications	Wet and/or dry operations
Controlled cutting action	Less stock removal	Will not alter critical tolerances

SC-DB

Materials

Steel, stainless steel, non-ferrous metals, plastics, lacquers.

Application

Removing rust and cleaning flat metal parts; removing discoloration and residual sealants; surface preparation after weldseam removal, prior to coating or painting; reducing roughness after sanding.

Accessories

Back-up pad 09583 (Ø 115 mm)

Back-up pad 09921 (Ø 178 mm)

Recommended use

Diameter mm	Maximum Operating Speed rpm	Recommended Speed rpm
115	8000	6500
125	8000	6500
150	6000	4800
178	6000	4800
200	4500	3500

Safety Notice



Certification

3M Production plants are ISO 9002 certified.

3M Service

Do you have technical questions?

Your contact

Telephone:

Telefax:

For environmental or product safety questions, contact your local 3M subsidiary or call

Telephone: +49 21 31 / 14 20 42

Telefax: +49 21 31 / 14 35 87

Important Notice:

All represented statements depict 3M's personal experience. Please determine the applicability of this particular product to your specific requirements prior to use. All questions regarding liability and warranty for this product are regulated in accordance with 3M's General Terms & Conditions, unless superseded by local statute.



3M Laboratories (Europe)
Zweigniederlassung der 3M Deutschland GmbH
Hansastr. 9
D-41453 Neuss

Telephone 0 21 31 / 14 3234
Telefax 0 21 31 / 14 3223

SC-DB-english.doc
Version 10/00