





LOC		DIST		REVISIONS			
P	LTN	DESCRIPTION	DATE	DWN	APVD		
B		REV PER ECO 16-000458	8-16-16	CT	DH		



SCALE 15:1



1. MATERIAL:
 HOUSING: LCP, COLOR: BLACK
 CONTACT: COPPER ALLOY

2. FINISH:
 COMPLIANT PIN: 1.27µm MIN TIN LEAD OVER
 1.27µm MIN NICKEL

3. DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.

4. REFERENCE APPLICATION SPEC 114-32055 FOR RECOMMENDED
 PLATED THRU HOLE DIAMETER AND PLATING THICKNESS
 (TIER 2 RIGHT ANGLE PLUG).

5. FINISH:
 COMPLIANT PIN: 0.5µm MIN TIN OVER
 1.27 µm MIN NICKEL

5	MATTE TIN	2102785-2
2	93/7 TIN LEAD	2102785-1
PLATING	DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: D. BELACK 11OCT2011	TE Connectivity
DIMENSIONS: mm		CHK: A. TSANG 10-11-2011	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD: A. TSANG 10-11-2011	NAME: RT2 SFF, FLEX-TO-BOARD, CONNECTOR PRODUCT SPEC: 108-32042 APPLICATION SPEC: 114-32055 WEIGHT: 1.27 CUSTOMER DRAWING
0 PLC ±0.13		RESTRICTED TO	
1 PLC ±0.05		SIZE: A100779C=2102785	
2 PLC ±0.05		SCALE: 10:1 SHEET 1 OF 1 REV B	
3 PLC ±0.05			
4 PLC ±0.05			
ANGLES ±2°			
FINISH			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2102785-1](#)