



# 28105

Products > Controls and Monitors > Operator Controls > Hour Meters > ac Hour Meters > 28100 Series > 28105

## Overview

**Honeywell Multi-Range ac Hour Meter, round opening, three-screw flange, 0.25 in bent blade termination, 100K hours, 90 Vac to 264 Vac operating voltage, 100/120/240 V, 50/60 Hz**  
[View More](#)



## Technical Specifications

Product Type	Multi-Range ac	Function	Hour Meter
Appearance	Round	Mounting	3 Screw
Voltage	90 Vac to 264 Vac	Volts ac	100/120/240 Vac
Frequency	50 Hz/60 Hz	Hours	100K
Logo Top	Quartz	Logo Bottom	Hours 1/10

[View More](#)

View documents in: English ▾

## Documents

TITLE	DOCUMENT TYPE	LANGUAGE	SIZE
<b>True Time Stamp - Hour Meters</b>	Case Study	English	345KB
<b>Hour Meters Line Guide</b>	Product Line Guide	English	571KB
<b>Industrial Product Line Card</b>	Line Card/Selection Chart	English	571KB
<b>Sensors and Switches for Potential Medical Applications</b>	Application Note	English	883KB

[View More](#)

## Product Features

- Records time 0 to 99,999.9 hours
- Accuracy to ±0.02 %
- CSA, UL, CE approvals
- Totally sealed from dirt and moisture
- Termination - 1/4 in blade
- Options include custom lens and terminal orientation (up, down, straight)

## Applications

- Infotech
- Surtran
- Industrial
- Medical
- Marine

- [view distributor inventory](#)
- [sample request](#)
- [email technical support](#)
- [start a chat we're offline](#)
- [get support](#)
- [email sales](#)
- [find a distributor](#)
- [email this page](#)

**NAVIGATION LINKS**

[HOME PAGE](#)

[PRODUCTS](#)

[DISTRIBUTOR INVENTORY](#)

[INDUSTRIES](#)

[SUPPORT](#)

[NEWS & EVENTS](#)

[ABOUT US](#)

**DISTRIBUTOR LINKS**

[ECOM LOGIN](#)

[LEARN CENTER](#)

[REQUEST ACCESS TO ECOM](#)


[SALES/AD PORTAL LOGIN](#)

[SALES/AD PORTAL ACCESS REQUEST](#)

[SAMPLE REQUEST](#)

[SUPPLIER MICROSITE](#)

**LANGUAGE**

English 

**SOCIAL MEDIA**



**SITE INFORMATION**

[PRIVACY STATEMENT](#)

[SITE MAP](#)

[TERMS & CONDITIONS](#)

This site uses cookies to simplify and improve your usage and experience of this website. Cookies are small text files stored on the device you are using to access this website. If you ignore this message and continue without changing your browser settings, we will assume that you are consenting to our use of cookies. For further information on our use of cookies, please see [Privacy Statement](#)

**Don't show this message again**