

ix Industrial 10A-1 plug SL-S



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 181 2560 XL
Specification	ix Industrial 10A-1 plug SL-S
HARTING eCatalogue	https://b2b.harting.com/09451812560XL

Identification

Category	Connectors
Series	HARTING ix Industrial®
Identification	Data
Element	Cable connector

Version

Termination method	Solder termination
Shielding	Fully shielded, 360° shielding contact
Number of contacts	8
Additional contacts	+ 2x GND
Coding	Type A
Pack contents	Packaging with 100 pieces

Technical characteristics

Conductor cross-section	AWG 28/7 ... AWG 22/7
Wire outer diameter	≤1.55 mm
Rated current	1.5 A
Rated voltage	50 V AC 60 V DC
Contact resistance	≤30 mΩ
Shielding resistance	≤100 mΩ
Limiting temperature	-40 ... +85 °C
Storage temperature	-30 ... +60 °C

Page 1 / 3 | Creation date 2020-02-13 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application.

HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany
Phone +49 5772 47-97200 | electronics@HARTING.com | www.HARTING.com



Pushing Performance

Technical characteristics

Insertion force	≤25 N
Withdrawal force	≤25 N
Mating cycles	≥5,000
Degree of protection acc. to IEC 60529	IP20
Cable diameter	5.5 ... 7.2 mm
Test voltage $U_{r.m.s.}$	0.5 kV
Transmission characteristics	Cat. 6 _A Class E _A up to 500 MHz
Data rate	10 Mbit/s
	100 Mbit/s
	1 Gbit/s
	2.5 Gbit/s
	5 Gbit/s
Retention force	≥80 N locking

Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	Black
Material (contacts)	Copper alloy
Surface (contacts)	Au over Ni
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Specifications	IEC 61076-3-124
UL / CSA	UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079

Commercial data

Packaging size	100
Net weight	8.6 g



Pushing Performance

Commercial data

Country of origin	Japan
European customs tariff number	85389099
eCl@ss	27440101 Rectangular connectors (set)