


- Quick Links**
- [RoHS/LF P/N Search](#)
- Documentation**
- [Customer drawing search](#)
- [Free search](#)
- Services**
- [Distributor list](#)

Start > Search=30331706\* > 30331706


**30331706**

**30331706 : 17 way 14X1.2+2X2.8+1X4.8 Male coupling**



Customer drawing

ACTIVE



[Add to Favorites](#)

[Print Datasheet](#)

FCI Brings You More

- [Contact our sales/technical support](#)
- [Sample request](#)

[Specifications](#) [Download document](#) [Mating Half](#)

**General** Mechanical Physical Terminal 1 Type Terminal 2 Type Environmental Other Features

General	
<b>Application</b>	Wire to Wire Harness in-line
<b>Ways</b>	17
<b>Coding version</b>	1
<b>Product Type</b>	Housing
<b>Coding</b>	Yes
<b>Features</b>	17 way Female Housing with TPA Mechanical Polarization Plastic Locking Feature
<b>Hybrid</b>	Yes
<b>Main Terminal family</b>	Other
<b>Main Terminal size</b>	1.2 mm
<b>Sealed</b>	No
<b>Terminal Size</b>	14x1.2+2x2.8+1x4.8
Mechanical	
<b>Connector mating force</b>	< 75N
Physical	
<b>Color</b>	White
<b>Material</b>	PBT-GF10
<b>Temperature (Range)</b>	-40°C to +105°C
Terminal 1 Type	
<b>Terminal type 1</b>	Male 1.2 mm Terminal
<b>Ways for Terminal Type 1</b>	14
<b>Contact insertion force for Terminal Type 1</b>	< 5N
<b>Contact Pitch for Terminal Type 1</b>	3.2 mm
<b>Retention force (Contact) for Terminal Type 1</b>	> 50N
Terminal 2 Type	
<b>Terminal type 2</b>	DCK Female 2.8 mm Terminal
<b>Ways for Terminal Type 2</b>	2
<b>Contact insertion force for Terminal Type 2</b>	< 10N
<b>Contact Pitch for Terminal Type 2</b>	7.5 mm
<b>Retention force (Contact) for Terminal Type 2</b>	> 100N
Environmental	
<b>IMDS</b>	Yes
Other Features	
<b>Market</b>	Passenger Vehicles
<b>Type</b>	Male
<b>Part Situation</b>	Active
<b>Disclaimer</b>	For more information, please contact your local sales office. Displayed data is for information purposes only The supply of some products might be limited to some customers