
Sealed Ultra Subminiature Basic Switch

Smallest sealed snap-action switch in the industry with a very long stroke for reliable ON/OFF action

- The case dimensions are 78% of conventional models, contributing to down-sizing of mechanical modules.
- Extra-long stroke even without levers. (OT reference value: 1.4 mm).
- Made of environmentally-friendly materials. All models are lead-free, including molded lead wire models.



Model Number Legend

1. Mounting Structure -

A: Without posts (base-mounting)

BR: Long post on right BL: Long post on left

C: M3-screw mounting models

ER: Short post on right EL: Short post on left

2. Raitings

2:5 VDC 1mA to 12 VDC 2A

3. Actuator

- 0: Pin plunger
- 1: Hinge lever
- 2: Long hinge lever
- 3: Simulated roller lever
- 4: Hinge roller lever
- 5 : Straight leaf lever
- 6: Leaf lever
- 7 : Simulated roller leaf lever
- 8: Long leaf lever

4. Contact form

1: SPDT

D2HW-12345-6-7

2: SPST-NC (Molded lead wire models only)

3: SPST-NO (Molded lead wire models only)

5. Terminals

D, DS: PCB terminals (Straight) DR, DRS: PCB Terminals (Right-angled) DL, DLS: PCB Terminals (Left-angled)

H, HS : Solder terminals

M, MS : Molded lead wires downwards MR, MRS: Molded lead wires on right-side ML, MLS: Molded lead wires on left-side

Note. UL/cUL approved versions are available. In this case, a "S" will be added to the end of the model number.

The Lead wire is a UL approved wire (AWG24, UL1007).

6. Special Specification

7. Special Industry Specification

List of Models

●PCB-mounted Models

List o				Long post on right	Short post
Actuator	Termi	nals	Contact form		on right
Din plunger		Straight		-	-
Pin plunger	For PCB	Angled	SPDT	D2HW-BR201DR	D2HW-ER201DR
Ulinga layer		Straight		•	-
Hinge lever		Angled		D2HW-BR211DR	D2HW-ER211DR
Long hinge	FOI FCB	Straight	SPDT	•	-
lever		Angled		D2HW-BR221DR	D2HW-ER221DR
Simulated roller		Straight		-	-
hinge lever		Angled		D2HW-BR231DR	D2HW-ER231DR

			List of Models	Long post on left	Short post	Without posts	
Actuator	Term	inals	Contact form	Long post on left	on left Q		
Din plunger		Straight		-	-	D2HW-A201D	
Pin plunger	-	Angled		D2HW-BL201DL	D2HW-EL201DL	-	
His wallana	Straight		-	-	D2HW-A211D		
Hinge lever		Angled	For PCB Angled	SPDT	D2HW-BL211DL	D2HW-EL211DL	-
Long hinge	- FOI PCB	Straight	יו מאס	-	-	D2HW-A221D	
lever	-	Angled	-	D2HW-BL221DL	D2HW-EL221DL	-	
Simulated roller	\sim	Straight		-	-	D2HW-A231D	
hinge lever	-	Angled		D2HW-BL231DL	D2HW-EL231DL	-	

Note1. Angled terminals and posts are the same direction.

Note2. "S" is added to the end of the model number for the UL/cUL-approved version Consult your OMRON sales representative for details.

D2HW

•Models with Solder Terminals or Molded Lead Wires

			List of Models	Long post on right	Short post on right
Actuator	Terr	minals	Contact form		•
	Solder		SPDT	D2HW-BR201H	D2HW-ER201H
			SPDT	D2HW-BR201M	D2HW-ER201M
		Downwards	SPST-NC	D2HW-BR202M	D2HW-ER202M
Pin plunger	Molded		SPST-NO	D2HW-BR203M	D2HW-ER203M
p.ago	lead wires	Right-side	SPST-NC	D2HW-BR202MR	D2HW-ER202MR
		J	SPST-NO	D2HW-BR203MR	D2HW-ER203MR
		Left-side	SPST-NC	D2HW-BR202ML	D2HW-ER202ML
	0.11		SPST-NO	D2HW-BR203ML	D2HW-ER203ML
	Solder		SPDT SPDT	D2HW-BR211H D2HW-BR211M	D2HW-ER211H D2HW-ER211M
		Downwards	SPST-NC	D2HW-BR211M D2HW-BR212M	D2HW-ER211M
		Downwards	SPST-NO	D2HW-BR213M	D2HW-ER213M
Hinge lever	Molded		SPST-NC	D2HW-BR213M D2HW-BR212MR	D2HW-ER212MR
	lead wires	Right-side	SPST-NO	D2HW-BR213MR	D2HW-ER213MR
			SPST-NC	D2HW-BR212ML	D2HW-ER212ML
		Left-side	SPST-NO	D2HW-BR213ML	D2HW-ER213ML
	Solder		SPDT	D2HW-BR221H	D2HW-ER221H
			SPDT	D2HW-BR221M	D2HW-ER221M
		Downwards	SPST-NC	D2HW-BR222M	D2HW-ER222M
Lang bing a layer	Malded		SPST-NO	D2HW-BR223M	D2HW-ER223M
Long hinge lever	Molded	Dight side	SPST-NC	D2HW-BR222MR	D2HW-ER222MR
	lead wires	Right-side	SPST-NO	D2HW-BR223MR	D2HW-ER223MR
		Left-side	SPST-NC	D2HW-BR222ML	D2HW-ER222ML
		Leit-Side	SPST-NO	D2HW-BR223ML	D2HW-ER223ML
	Solder		SPDT	D2HW-BR231H	D2HW-ER231H
Simulated roller hinge lever	Molded lead wires		SPDT	D2HW-BR231M	D2HW-ER231M
		Downwards	SPST-NC	D2HW-BR232M	D2HW-ER232M
			SPST-NO	D2HW-BR233M	D2HW-ER233M
		Right-side	SPST-NC	D2HW-BR232MR	D2HW-ER232MR
		Tilgiti Side	SPST-NO	D2HW-BR233MR	D2HW-ER233MR
		Left-side	SPST-NC	D2HW-BR232ML	D2HW-ER232ML
			SPST-NO	D2HW-BR233ML	D2HW-ER233ML
	Solder	1	SPDT	D2HW-BR241H	D2HW-ER241H
	Molded	Downwards Right-side	SPDT	D2HW-BR241M	D2HW-ER241M
Llings valley			SPST-NC	D2HW-BR242M	D2HW-ER242M
Hinge roller			SPST-NO	D2HW-BR243M D2HW-BR242MR	D2HW-ER243M D2HW-ER242MR
lever	lead wires		SPST-NC SPST-NO	D2HW-BR243MR	D2HW-ER243MR
			SPST-NC	D2HW-BR243ML	D2HW-ER243ML
		Left-side	SPST-NO	D2HW-BR243ML	D2HW-ER243ML
	Solder		SPDT	D2HW-BR251H	D2HW-ER251H
	Coldo		SPDT	D2HW-BR251M	D2HW-ER251M
		Downwards	SPST-NC	D2HW-BR252M	D2HW-ER252M
Straight leaf			SPST-NO	D2HW-BR253M	D2HW-ER253M
lever	Molded	5	SPST-NC	D2HW-BR252MR	D2HW-ER252MR
	lead wires	Right-side	SPST-NO	D2HW-BR253MR	D2HW-ER253MR
		Loft oi-l-	SPST-NC	D2HW-BR252ML	D2HW-ER252ML
		Left-side	SPST-NO	D2HW-BR253ML	D2HW-ER253ML
	Solder		SPDT	D2HW-BR261H	D2HW-ER261H
			SPDT	D2HW-BR261M	D2HW-ER261M
		Downwards	SPST-NC	D2HW-BR262M	D2HW-ER262M
Leaf lever	Molded		SPST-NO	D2HW-BR263M	D2HW-ER263M
Loui lovoi	lead wires	Right-side	SPST-NC	D2HW-BR262MR	D2HW-ER262MR
	iodd Wiles	riigiit side	SPST-NO	D2HW-BR263MR	D2HW-ER263MR
		Left-side	SPST-NC	D2HW-BR262ML	D2HW-ER262ML
		20.1 0.00	SPST-NO	D2HW-BR263ML	D2HW-ER263ML
	Solder		SPDT	D2HW-BR271H	D2HW-ER271H
			SPDT	D2HW-BR271M	D2HW-ER271M
0: 1 . 1 . 1		Downwards	SPST-NC	D2HW-BR272M	D2HW-ER272M
Simulated roller	Molded		SPST-NO	D2HW-BR273M	D2HW-ER273M
leaf lever	lead wires	Right-side	SPST-NC	D2HW-BR272MR	D2HW-ER272MR
			SPST-NO	D2HW-BR273MR	D2HW-ER273MR
		Left-side	SPST-NC	D2HW-BR272ML	D2HW-ER272ML
			SPST-NO	D2HW-BR273ML	D2HW-ER273ML
		Downwords	SPDT	D2HW-BR281M	D2HW-ER281M
		Downwards	SPST-NC SPST-NO	D2HW-BR282M	D2HW-ER282M
^	Molded			D2HW-BR283M D2HW-BR282MR	D2HW-ER283M D2HW-ER282MR
Long leaf lever					
Long leaf lever	lead wires	Right-side	SPST-NC		
Long leaf lever		Right-side Left-side	SPST-NO SPST-NC	D2HW-BR283MR D2HW-BR282ML	D2HW-ER283MR D2HW-ER282ML

Note1. The length of standard lead wires (AVSS 0.5) for molded lead wire models shown above is 30 cm.

Note2. "S" is added to the end of the model number for the UL/cUL-approved version The lead wire models are UL approved wires (AWG24, UL1007). Consult your OMRON sales representative for details.



●Models with Solder Terminals or Molded Lead Wires

			List of Models		Short post	M3-screw
	_			Long post on left	on left	mounting
Actuator		minals	Contact form SPDT	DOHW BLOOTH	D2HW-EL201H	D2HW-C201H
	Solder		SPDT	D2HW-BL201H D2HW-BL201M	D2HW-EL201H D2HW-EL201M	D2HW-C201H D2HW-C201M
		Downwards	SPST-NC	D2HW-BL201M D2HW-BL202M	D2HW-EL201M D2HW-EL202M	D2HW-C201M D2HW-C202M
		Downwards	SPST-NC	D2HW-BL202M	D2HW-EL202M	D2HW-C202M D2HW-C203M
Pin plunger	Molded		SPST-NC	D2HW-BL202MR	D2HW-EL203M	D2HW-C203M
	lead wires	Right-side	SPST-NO	D2HW-BL203MR	D2HW-EL203MR	D2HW-C203MR
			SPST-NC	D2HW-BL203ML	D2HW-EL203MH	DZITW-CZUSWIA
		Left-side	SPST-NO	D2HW-BL203ML	D2HW-EL203ML	
	Solder		SPDT	D2HW-BL211H	D2HW-EL211H	D2HW-C211H
	Coldor		SPDT	D2HW-BL211M	D2HW-EL211M	D2HW-C211M
		Downwards	SPST-NC	D2HW-BL212M	D2HW-EL212M	D2HW-C212M
		20111114140	SPST-NO	D2HW-BL213M	D2HW-EL213M	D2HW-C213M
Hinge lever	Molded		SPST-NC	D2HW-BL212MR	D2HW-EL212MR	D2HW-C212MR
	lead wires	Right-side	SPST-NO	D2HW-BL213MR	D2HW-EL213MR	D2HW-C213MR
			SPST-NC	D2HW-BL212ML	D2HW-EL212ML	-
		Left-side	SPST-NO	D2HW-BL213ML	D2HW-EL213ML	-
	Solder		SPDT	D2HW-BL221H	D2HW-EL221H	D2HW-C221H
			SPDT	D2HW-BL221M	D2HW-EL221M	D2HW-C221M
		Downwards	SPST-NC	D2HW-BL222M	D2HW-EL222M	D2HW-C222M
	- Madalada		SPST-NO	D2HW-BL223M	D2HW-EL223M	D2HW-C223M
Long hinge lever	Molded	Disday side	SPST-NC	D2HW-BL222MR	D2HW-EL222MR	D2HW-C222MR
	lead wires	Right-side	SPST-NO	D2HW-BL223MR	D2HW-EL223MR	D2HW-C223MR
		Left-side	SPST-NC	D2HW-BL222ML	D2HW-EL222ML	-
		Leit-side	SPST-NO	D2HW-BL223ML	D2HW-EL223ML	-
	Solder	1	SPDT	D2HW-BL231H	D2HW-EL231H	D2HW-C231H
			SPDT	D2HW-BL231M	D2HW-EL231M	D2HW-C231M
		Downwards	SPST-NC	D2HW-BL232M	D2HW-EL232M	D2HW-C232M
Simulated roller	Molded		SPST-NO	D2HW-BL233M	D2HW-EL233M	D2HW-C233M
hinge lever	lead wires	Right-side	SPST-NC	D2HW-BL232MR	D2HW-EL232MR	D2HW-C232MR
	lead wires	night-side	SPST-NO	D2HW-BL233MR	D2HW-EL233MR	D2HW-C233MR
		Left-side	SPST-NC	D2HW-BL232ML	D2HW-EL232ML	-
		Leit-side	SPST-NO	D2HW-BL233ML	D2HW-EL233ML	-
	Solder		SPDT	D2HW-BL241H	D2HW-EL241H	D2HW-C241H
	Molded lead wires	Downwards Right-side	SPDT	D2HW-BL241M	D2HW-EL241M	D2HW-C241M
			SPST-NC	D2HW-BL242M	D2HW-EL242M	D2HW-C242M
Hinge roller			SPST-NO	D2HW-BL243M	D2HW-EL243M	D2HW-C243M
lever			SPST-NC	D2HW-BL242MR	D2HW-EL242MR	D2HW-C242MR
	load Wildo		SPST-NO	D2HW-BL243MR	D2HW-EL243MR	D2HW-C243MR
		Left-side	SPST-NC	D2HW-BL242ML	D2HW-EL242ML	-
			SPST-NO	D2HW-BL243ML	D2HW-EL243ML	-
	Solder		SPDT	D2HW-BL251H	D2HW-EL251H	D2HW-C251H
			SPDT	D2HW-BL251M	D2HW-EL251M	D2HW-C251M
0		Downwards	SPST-NC	D2HW-BL252M	D2HW-EL252M	D2HW-C252M
Straight leaf	Molded		SPST-NO	D2HW-BL253M	D2HW-EL253M	D2HW-C253M
lever	lead wires	Right-side	SPST-NC	D2HW-BL252MR	D2HW-EL252MR	D2HW-C252MR
			SPST-NO SPST-NC	D2HW-BL253MR	D2HW-EL253MR	D2HW-C253MR
		Left-side	SPST-NO	D2HW-BL252ML D2HW-BL253ML	D2HW-EL252ML D2HW-EL253ML	-
	Solder		SPST-NO SPDT	D2HW-BL253ML D2HW-BL261H	D2HW-EL253ML D2HW-EL261H	D2HW-C261H
	Joidei		SPDT	D2HW-BL261M	D2HW-EL261M	D2HW-C261H D2HW-C261M
		Downwards	SPST-NC	D2HW-BL262M	D2HW-EL261M	D2HW-C262M
		Downwarus	SPST-NO	D2HW-BL263M	D2HW-EL263M	D2HW-C263M
Leaf lever	Molded		SPST-NC	D2HW-BL262MR	D2HW-EL262MR	D2HW-C262MR
	lead wires	Right-side	SPST-NO	D2HW-BL263MR	D2HW-EL263MR	D2HW-C263MR
			SPST-NC	D2HW-BL262ML	D2HW-EL262ML	
		Left-side	SPST-NO	D2HW-BL263ML	D2HW-EL263ML	-
	Solder		SPDT	D2HW-BL271H	D2HW-EL271H	D2HW-C271H
			SPDT	D2HW-BL271M	D2HW-EL271M	D2HW-C271M
		Downwards	SPST-NC	D2HW-BL272M	D2HW-EL272M	D2HW-C272M
Simulated roller	Meldel		SPST-NO	D2HW-BL273M	D2HW-EL273M	D2HW-C273M
leaf lever	Molded	Disclot - ! -! -	SPST-NC	D2HW-BL272MR	D2HW-EL272MR	D2HW-C272MR
	lead wires	Right-side	SPST-NO	D2HW-BL273MR	D2HW-EL273MR	D2HW-C273MR
		Loft side	SPST-NC	D2HW-BL272ML	D2HW-EL272ML	-
		Left-side	SPST-NO	D2HW-BL273ML	D2HW-EL273ML	-
			SPDT	D2HW-BL281M	D2HW-EL281M	D2HW-C281M
		Downwards	SPST-NC	D2HW-BL282M	D2HW-EL282M	D2HW-C282M
	Molded		SPST-NO	D2HW-BL283M	D2HW-EL283M	D2HW-C283M
Long leaf lever		Dight side	SPST-NC	D2HW-BL282MR	D2HW-EL282MR	D2HW-C282MR
<u> </u>	lead wires	Right-side	SPST-NO	D2HW-BL283MR	D2HW-EL283MR	D2HW-C283MR
		Loft oids	SPST-NC	D2HW-BL282ML	D2HW-EL282ML	-
		Left-side	SPST-NO	D2HW-BL283ML	D2HW-EL283ML	-
lote1 The length of stands	rd load wires (/	1//SS () 5) for m	olded lead wire r	nodels shown above is 30 cm	•	•

Note1. The length of standard lead wires (AVSS 0.5) for molded lead wire models shown above is 30 cm.

Note2. "S" is added to the end of the model number for the UL/cUL-approved version The lead wire models are UL approved wires (AWG24, UL1007). Consult your OMRON sales representative for details.

Contact form


●SPDT



SPST-NC, (Molded Lead Wire Models Only)



SPST-NO, (Molded Lead Wire Models Only)



Contact Specifications

	Specification	Crossbar		
Contact	Material	Gold alloy		
	Gap (standard value)	0.5 mm		
Minimum app	plicable load (see note)	5 VDC 1mA		

Ratings

Rated voltage	Resistive load
125 VAC	0.1A
12 VDC 24 VDC	2A 1A
42 VDC	0.5A

Note. The above rating values apply under the following test conditions.

- (1) Ambient temperature: 20±2°C
- (2) Ambient humidity: 65±5 %
- (3) Operating frequency: 30 operations/min

Approved Safety Standard

Consult your OMRON sales representative for specific models with standard approvals.

UL (UL61058-1/cUL C22.2 No.61058-1)

Mo	odel	D2HW
Rated voltage I	tem	Resistive load
100 VAC		0.1A
12 VDC		2A
24 VDC		1A
42 VDC		0.5A

Characteristics

Permissible operating speed		1 mm to 500 mm/s (for pin plunger models)		
Permissible op	erating frequency	30 operations/min		
Insulation resis	stance	100 M Ω min. (at 500 VDC with insulation tester)		
Contact Terminals		100 mΩ max.		
resistance (initial value)	Molded lead wire models	150 m Ω max.		
	Between terminals of the same polarity	600 VAC 50/60 Hz 1min		
Dielectric strength	Between current-carrying metal parts and ground	1,500 VAC 50/60 Hz 1 min		
Between terminals and non-current-carrying metal parts		1,500 VAC 50/60 Hz 1 min		
Vibration resistance * 1	Malfunction	10 to 55 Hz, 1.5 mm double amplitude		
Shock	Durability	1,000 m/s ² {approx. 100G} max.		
resistance	Malfunction * 1	300 m/s ² {approx. 30G} max.		
Durability * 2	Mechanical	1,000,000 operations min. (30 operations/min)		
Durability 2	Electrical	100,000 operations min. (20 operations/min)		
Degree of	Terminals	IEC IP67 (excluding the terminals on terminal models)		
protection	molded lead wire models	IEC IP67		
Ambient operating temperature		-40 to +85°C (at ambient humidity of 60% max.) (with no icing or condensation)		
Ambient opera	ting humidity	95% max. (for +5 to +35°C)		
Weight		Approx. 0.7 g (for pin plunger models with terminals)		


Note. The data given above are initial values.

- *1. For the pin plunger models, the above values apply for use at the free position, operating position, and total travel position. For the lever models, they apply at the total travel position. Close or open circuit of the contact is time may
- *2. For testing conditions, consult your OMRON sales representative.


Mounting Structure and Reference Positions for Operating Characteristics (Unit: mm)

●Without posts D2HW-A□ FP OP TTP 7 Standard Position 133 3 + 53+


●Long post D2HW-B□




●M3-screw Mounting Models D2HW-C□




Mounting Hole Dimensions (Reference)



Mounting Hole Dimensions (Reference)




●Short post D2HW-E□




Note. The reference positions used for Free Position (FP), Operating Position (OP), and Total Travel Position (TTP) values are as shown above for each type of mounting.


Terminals/Appearances (Unit: mm)


●PCB terminals (Straight)






<PCB Cutout Dimensions (Reference)>






●PCB terminals (Right-angled)






Solder terminals

5.08±0.1 5.08±0.




●Molded Lead Wires on Left-side




* UL approved wires (AWG24, UL1007) are used for UL/cUL standard approved items.

●Molded Lead Wires on Right-side



* UL approved wires (AWG24, UL1007) are used for UL/cUL standard approved items.

Molded Lead Wires Downwards



UL approved wires (AWG24, UL1007) are used for UL/cUL standard approved items.

Dimensions (Unit: mm) / Operating Characteristics


The following illustrations and drawings are representative models. When ordering, replace \Box with the code for the mounting structure, contact form and terminal that you need.

See the "**EList of Models**" for available combinations of appearances.

Refer to page 3 to 4 for the mounting structures and terminal forms.

●Pin plunger D2HW-□20□□






2	
H	H
- -5	3-

Operating characteristics		Туре	Without posts	Models with Posts	M3-screw Mounting Models	
Operating Force	OF	Max.	0.75N {76 gf}			
Releasing Force	RF	Min.	0.10N {10 gf}			
Overtravel	OT		1.4 mm (reference value)			
Movement Differential	MD	Max.	0.25 mm			
Free Position	FP	Max.	11.2 mm 7.2 mm			
Operating Position	OP		10.4±0.2 mm 6.4±0.2 mm			
Total Travel Position	TTP	Max.	9.1 mm	5.1	mm	

●Hinge Lever D2HW-□21□□






Operating characteristics Type		Without posts	posts with Posts Mounting Models			
Operating Force	OF	Мах.	0.75N {76 gf}			
Releasing Force	RF	Min.	0.07N {7 gf}			
Overtravel	OT		1.6 mm (reference value)			
Movement Differential	MD	Max.	0.5 mm			
Free Position	FP	Max.	12.8 mm 8.8 mm			
Operating Position	OP		11.5±0.5 mm 7.5±0.5 mm			
Total Travel Position	TTP	Max.	10 mm	6 ו	mm	

●Long Hinge Lever D2HW-□22□□






Operating characteristics		Туре	Without posts	Models with Posts	M3-screw Mounting Models	
Operating Force	OF	Max.	0.5N {50 gf}			
Releasing Force	RF	Min.	0.03N {3 gf}			
Overtravel	OT		2.5 mm (reference value)			
Movement Differential	MD	Max.	0.8 mm			
Free Position	FP	Max.	15.5 mm 11.5 mm			
Operating Position	OP		13.3±0.8 mm 9.3±0.8 mm			
Total Travel Position	TTP	Max.	11 mm	7 r	mm	

Simulated Roller Lever

D2HW-□23□□






Operating characteristics		Туре	Without posts	Models with Posts	M3-screw Mounting Models	
Operating Force	OF	Мах.	0.65N {66 gf}			
Releasing Force	RF	Min.	0.05N {5 gf}			
Overtravel	OT		1.9 mm (reference value)			
Movement Differential	MD	Max.	0.5 mm			
Free Position	FP	Max.	16.5 mm 12.5 mm			
Operating Position	OP		15.2±0.5 mm 11.2±0.5 mm			
Total Travel Position	TTP	Max.	13.5 mm 9.5 mm			

●Hinge Roller Lever D2HW-□24□□






Operating characteristics		Туре	Models with Posts	M3-screw Mounting Models
Operating Force	OF	Max.	0.65N {66 gf}	
Releasing Force	RF	Min.	0.03N {3 gf}	
Overtravel	OT		1.9 mm (reference value	
Movement Differential	MD	Max.	0.6 mm	
Free Position	FP	Max.	15.3 mm	
Operating Position	OP		14±0.	6 mm
Total Travel Position	TTP	Max.	12.3 mm	

Note1. Unless otherwise specified, a tolerance of $\pm 0.2 \text{mm}$ applies to all dimensions.

Note2. The operating characteristics are for operation in the A direction (\P).

●Leaf straight lever D2HW-□25□□






Operating characteristics		Туре	Models with Posts	M3-screw Mounting Models
Operating Force	OF	Max.	1.2N {122 gf}	
Releasing Force	RF	Min.	0.05N {5 gf}	
Overtravel	OT		2.5 mm (reference value)	
Movement Differential	MD	Max.	0.7 mm	
Free Position	FP	Max.	11.9 mm	
Operating Position	OP		8.1±0.8 mm	
Total Travel Position	TTP	Max.	6.0	mm

●Leaf Lever D2HW-□26□□






Operating characteristics		Туре	Models with Posts	M3-screw Mounting Models
Operating Force Releasing Force	OF RF	Max. Min.	1.8N {183 gf} 0.20N {20 gf}	
Overtravel	OT	.,	1.8 mm (reference value)	
Movement Differential	MD	Max.	0.5 mm	
Free Position	FP	Max.	9.3 mm	
Operating Position	OP		7.4±0	.5 mm
Total Travel Position	TTP	Max.	5.8	mm

●Simulated Roller Lever

D2HW-□**27**□□






Operating characteristics		Туре	Models with Posts	M3-screw Mounting Models
Operating Force	OF	Max.	1.8N {183 gf}	
Releasing Force	RF	Min.	0.20N {20 gf}	
Overtravel	OT		2.0 mm (reference value)	
Movement Differential	MD	Max.	0.5 mm	
Free Position	FP	Max.	13.0 mm	
Operating Position	OP		10.8±0).5 mm
Total Travel Position	TTP	Max.	8.9	mm

●Long Leaf Lever D2HW-□28□□





Operating characteristics		Туре	Models with Posts	M3-screw Mounting Models
Operating Force	OF	Мах.	0.9N {92 gf}	
Releasing Force	RF	Min.	0.05N {5 gf}	
Overtravel	OT		2.8 mm (reference value)	
M 1000 011	MD		0.7 mm	
Movement Differential	MD	Max.	0.7	mm
Free Position	FP	Мах.	19	
				mm

Note1. Unless otherwise specified, a tolerance of ± 0.2 mm applies to all dimensions. Note2. The operating characteristics are for operation in the A direction (\P).

Precautions

★Please refer to "General Information" for correct use.

Cautions

●Degree of Protection

• Do not use this product underwater.

Although molded lead wire models satisfy the test conditions for the standard given below, this test is to check the ingress of water into the switch enclosure after submerging the Switch in water for a given time. Satisfying this test condition does not mean that the Switch can be used underwater.

JIS C0920:

Degrees of protection provided by enclosures of electrical apparatus (IP Code)

IEC 60529:

Degrees of protection provided by enclosures (IP Code) Degree of protection: IP67

(check water intrusion after immersion for 30 min. submerged 1m underwater)

- Do not operate the Switch when it is exposed to water spray, or when water drops adhere to the Switch surface, or during sudden temperature changes, otherwise water may intrude into the interior of the Switch due to a suction effect.
- Prevent the Switch from coming into contact with oil and chemicals.

Otherwise, damage to or deterioration of Switch materials may result.

 Do not use the Switch in areas where it is exposed to silicon adhesives, oil, or grease. Otherwise faulty contact may result due to the generation of silicon oxide.

Soldering

When soldering the lead wire to the terminal, first insert the lead wire conductor through the terminal hole and then conduct soldering.

Make sure that the temperature of the soldering iron tip does not exceed 300°C, and complete the soldering within 3 seconds. Do not apply any external force for 1 minute after soldering.

Soldering at an excessively high temperature or soldering for more than 3 seconds may deteriorate the characteristics of the Switch.

In case of automatic soldering, please do not apply the heat beyond 260°C within 5 seconds. Pay careful attention so that flux or solder liquid does not flow over the edge of the PCB panel.

●Side-actuated (Cam/Dog) Operation

 When using a cam or dog to operate the Switch, factors such as the operating speed, operating frequency, push-button indentation, and material and shape of the cam or dog will affect the durability of the Switch. Confirm performance specifications under actual operating conditions before using the Switch in applications.

Correct Use

Mounting

- Turn OFF the power supply before mounting or removing the Switch, wiring, or performing maintenance or inspection.
 Failure to do so may result in electric shock or burning.
- For M3-screw mounting models, use M3 mounting screws with plane washers or spring washers to securely mount the Switch.

Tighten the screws to a torque of 0.27 to 0.29 N·m {27.5 to 29.5 gf}. Exceeding the specified torque may result in deterioration of the sealing or damage.


 For models with posts, secure the posts by thermal caulking or by pressing into an attached device. When pressed into an attached device, provide guides on the opposite ends of the posts to ensure that they do not fall out or rattle.
 Thermal caulking conditions varies according to the equipment, jig and base used for switch mounting. Consult your OMRON sales representative for details.

Operating Body

 Use an operating body with low frictional resistance and of a shape that will not interfere with the sealing rubber, otherwise the plunger may be damaged or the sealing may deteriorate.

Handling

- Do not handle the Switch in a way that may cause damage to the sealing rubber.
- When handling the Switch, ensure that pressure is not applied to the posts in the directions shown in the following diagram.
 Also, ensure that uneven pressure or pressure in a direction other than the operating direction is not applied to the Actuator as shown in the following diagram. Otherwise, the post, Actuator, or Switch may be damaged, or the service life may be reduced.



Wiring Molded Lead Wire Models

 When wiring molded lead wire models, ensure that there is no weight applied on the wire or that there are no sharp bends near the parts where the wire is drawn out.
 Otherwise, damage to the Switch or deterioration in the sealing may result.

●Using Micro Loads

 Even when using micro load models within the operating range, if inrush/surge current occurs, it may increase the contact wear and so decrease durability. Therefore, insert a contact protection circuit where necessary.

Please check each region's Terms & Conditions by region website.

OMRON Corporation Device & Module Solutions Company

Regional Contact

Americas

https://components.omron.com/us

Asia-Pacific

https://components.omron.com/ap

Korea

https://components.omron.com/kr

https://components.omron.com/eu

China

https://components.omron.com.cn

Japan

https://components.omron.com/jp