



För icke direkt toleranssatta mått gäller toleransklass
General tolerances if not otherwise stated

NOM DIM MM		TOL CLASS		
From	To	A	B	C
(1)	6	±0.05	±0.1	±0.2
(6)	30	±0.1	±0.2	±0.5
(30)	100	±0.15	±0.3	±0.8
(100)	300	±0.2	±0.5	±1.2
(300)	1000	±0.3	±0.8	±2

Hål / Holes H13

Skarpa kanter brutna där ej annat anges.
No sharp edges unless otherwise specified.

Övriga generella toleranser enligt ritning 4100-4644.
Additional general tolerances in accordance with drawing 4100-4644.



11 4300-3692

Rev	Change order	Change: A = Added W = Was D = Deleted	Date	Sign
11	1067110	C 4300-3692	14.0519	SE

FÖRSPÄNNING / PRELOAD: 120 ± 20 N

Tolkmått / Gauge dimensions (mm)		
URTAG	Gåtolk	Stopptolk
NEST	GO	NO GO
5.41	∅5.36	∅5.46
10.90	∅10.85	∅10.95
2.54	∅2.49	∅2.59
1.69	∅1.66	∅1.72

Material			Behandling/Treatment			Status Fristläppt		
Konstr./Design OS	Ritad/Drawn TGW	Datum/Date 2009-11-03	Skala/Scale 1:2	Kontr./Checked IP	Godk./Approved NE	Ämne/Blank		
pressmaster ®						Vikt/Weight, gram		Art grp 012
Benämning/Denomination KRIMPTÅNG 241-8380 CRIMPING TOOL KCC 2511						Ritn nr/Drawing no 43002204		REV 011