Metallic Systems - Stainless Steel KSU - Uncovered Conduit



Technical Characteristics

Conforms to

BSI Kitemark KM-90009 Low voltage directive

Approvals and Standards	• • • • • • • • • • •	$\mathbf{\hat{v}}$					
Degree of mechanical protection	Very high flexibility & fatigue life						
Degree of protection	IP40 - As star	ndard with C	GFMS fittings				
UV protection	Very High						
Finish	Self Coloured						
Application	Indoors - light	industrial,	buildings ma	rine, corrosive enviror	nments		
Normal operating temperature range	Static	Min Temp - 65°C - 45°C	Max Temp +350°C +250 °C				
For use with - Fitting range	KF-E - <u>GFMS</u>						
Fire performance	Test S	Standard	Pe	rformance Rating			
	Not	Rated		Not Rated	Inherent Low Fire Hazard Resistance to Flame Propagation		
Testing data	Click or See p	bage <u>3</u>					
Type of material	Stainless Stee	el AISI 316L	-				
Image							



Cable Management Products Ltd. CMG House - Station Road - Coleshill - B46 1HT - United Kingdom Tel: +44(0)1675 468 222 - Fax: +44(0)1675 464 930 Technical Support e-mail: <u>cmg.conduitsystems@tnb.com</u> - <u>www.kopex.co.uk</u>




The Company's policy is one of continuous improvement and reserves the right to change specifications at any time without prior notice.

Metallic Systems - Stainless Steel KSU - Uncovered Conduit



Technical & Dimensional Data

Conduit size metric (mm)	10	12	16	20	25	32	40	-
Conduit size US trade (inches)	1/4"	5/16"	3/8"	1/2"	3/4"	1"	1 1/4"	-
Part code	KSU01*	KSU02*	KSU03*	KSU04*	KSU05*	KSU06*	KSU07*	-
Coil length (m)	10/30	10/30	10/30	10/30	10/30	10/20	10/20	-
A - Outside diameter (mm)	9.6	12.8	16.1	20.2	24.7	32.0	40.0	-
B - Inside diameter (mm)	7.0	10.0	12.9	17.0	21.1	28.4	36.4	-
C - Static bend radius (mm)	20.0	20.0	24.0	32.0	45.0	55.0	65.0	-
Average weight (KG/100m)	9.5	12.9	15.6	21.7	27.0	36.0	45.5	-
*For ordering code add coil length to part code - e.g KSU0410								





Metallic Systems - Stainless Steel

KSU - Uncovered Conduit



BS EN 61386 Classification

	Fitting	Compression	Impact	Min temp	Max temp	bending	electrical	IP solids	IP water	Corrosion	Tensile	Non-flame Propogating	Suspended load
KSU04	GFMS	4	4	5	6	4	0	4	0	4	4	1	5

Mechanical Properties

Test Type	Methods / Standards	Requirements	Value
Crush Strength @ 23°C	IEC61386-1	<25% crush >90% recovery	>1250N
Impact Strength @ 23 °C	IEC61386-1	No Cracks <20% deformation	>20J
Impact Strength @-45 °C	IEC61386-1	No Cracks. <20% deformation	>20J
Tensile Strength	IEC61386-1	With GFMS Type Fitting	>1000N
Tensile Strength		Ultimate pull-out of GFMS Fitting	1450N
Dynamic Bend radius @ -45 °C	IEC61386-23	5000 cycles minimum	4xOD

Thermal Properties

Test Type	Methods / Standards	Requirements	Value
Minimum Temperature	IEC61386-23	Dynamic 5000 cycles	-45°C
Maximum Temperature	IEC61386-23	Dynamic 5000 cycles	250°C
Minimum Static		Permanent Use	-65°C
Maximum Static		Permanent Use	350°C

Chemical Resistance Chart

	Astm No.1	Diesel oil	Methyl Bromide	Sulphur Dioxide (Gas)
	Astm No.2	Diethylamine	MEK	Sulphuric Acid (10%)
Key:	Astm No.3	Ethanol	Nitric Acid (10%)	Sulphuric Acid (70%)
	Acetic Acid (10%)	Ether	Nitric Acid (70%)	Toluene
Suitable :		Ethylamine	Oxalic Acid	Transformer Oil
	Aluminium Chloride	Ethylene Glycol	Ozone (Gas)	1,1,1-Trichloroethane
Limited Suitability :	Aniline	Ethyl Ethanoate	Paraffin oil	Trichloroethylene
	Benzaldehyde	Freon 32	Petrol	Turpentine
Unsuitable :	Benzene	Hydrochloric Acid (10%)	Phenol	Vegetable Oil
	Carbon tetrachloride	Hydrochloric Acid (36%)	Sea Water	Vinyl Acetate
Not Tested :	Chlorine water	Hydrogen Peroxide (35%)	Silver Nitrate	Water
	Chloroform	Hydrogen Peroxide (87%)	Skydrol	White Spirit
	Citric Acid	Lactic Acid	Sodium Chloride	Zinc Chloride
	Copper Sulphate	Lubricating oil	Sodium Hydroxide (10%)	
	Cresol	Methanol	Sodium Hydroxide (60%)	

The information above is given as a guide only and is based on published technical data and experience. The chemical resistance of the above products is dependant on factors such as chemical exposure, concentration of the chemical and temperature. The above chemicals are valid for a temperature of 23°C. Use of the above table is at the users own discretion and risk. Those using it must satisfy themselves that their application presents no health and safety risks. The end user should assess compatibility with their application and contact Thomas & Betts for further information.

ADHERENCE TO THE CURRENT WIRING REGULATIONS BS7671 OR NEC WIRING REGULATIONS (FOR USA) IS STRONGLY ADVISED.

MINIMUM BEND RADIUS FOR FLEXING IS DEPENDANT UPON MINIMUM TEMPERATURE, BENDING FREQUENCY AND CHEMICAL ENVIRONMENT.



Cable Management Products Ltd. CMG House - Station Road - Coleshill - B46 1HT - United Kingdom Tel: +44(0)1675 468 222 - Fax: +44(0)1675 464 930 Technical Support e-mail: <u>cmg.conduitsystems@tnb.com</u> - <u>www.kopex.co.uk</u>

The Company's policy is one of continuous improvement and reserves the right to change specifications at any time without prior notice.

A Member of the ABB Group