

Multilayer Ceramic Chip Capacitors

CGA5L1X8L1E106K160AC New Product



TDK item description ? CGA5L1X8L1E106KT****

Applications Automotive Grade

Feature 150°C High Temperature Application
AEC-Q200 AEC-Q200

Series CGA5(3216) [EIA 1206]

Status Production



Images are for reference only and show exemplary products.

[PDF file of this page](#)

[Contact](#)


- Documents**
- [Catalog](#)
 - [Specification](#)
 - [RoHS Certificate](#)
 - [SVHC/REACH Certificate](#) Update
 - [Selection Guide for Automotive MLCC](#) New
 - [Sample Kits](#)
 - [Characterization Sheet](#)

Size	
Length(L)	3.20mm +0.30,-0.10mm
Width(W)	1.60mm +0.30,-0.10mm
Thickness(T)	1.60mm +0.30,-0.10mm
Terminal Width(B)	0.20mm Min.
Terminal Spacing(G)	1.00mm Min.
Recommended Land Pattern (PA)	2.10mm to 2.50mm(Flow Soldering) 2.00mm to 2.40mm(Reflow Soldering)
Recommended Land Pattern (PB)	1.10mm to 1.30mm(Flow Soldering) 1.00mm to 1.20mm(Reflow Soldering)
Recommended Land Pattern (PC)	1.00mm to 1.30mm(Flow Soldering) 1.10mm to 1.60mm(Reflow Soldering)

Electrical Characteristics	
Capacitance	10μF ±10%
Rated Voltage	25VDC
Temperature Characteristic ?	X8L(+15,-40%)
Dissipation Factor (Max.)	5%
Insulation Resistance (Min.)	50MΩ

Other	
Soldering Method	Wave (Flow) Reflow
AEC-Q200	Yes
Packing	Blister (Plastic)Taping [180mm Reel]
Package Quantity	2000pcs

Characteristic Graph (This is reference data, and does not guarantee the products characteristics.)



CGA5L1X8L1E106K160AC

Change settings

CGA5L1X8L1E106K160AC

Change settings

Capacitance

CGA5L1X8L1E106K160AC

Change settings

DC Bias Characteristic

CGA5L1X8L1E106K160AC

Change settings

Temperature Characteristic

CGA5L1X8L1E106K160AC(No Bias) CGA5L1X8L1E106K160AC(DC Bias = 12.5)

Change settings

Ripple Temperature Rising

CGA5L1X8L1E106K160AC(100 kHz) CGA5L1X8L1E106K160AC(500 kHz) CGA5L1X8L1E106K160AC(1 MHz)

Change settings



[Selection Guides](#) [Search by Part No.](#) [Search by Characteristics](#) [Distributor Inventory Check](#) [Cross Reference](#)

Products

[Capacitors](#) >

[Inductors \(Coils\)](#) >

[EMC Components](#) >

[RF Components and Modules](#) >

[Voltage / Current / Temperature Protection Devices](#) >

[Sensors and Sensor Systems](#) >

- [Ceramic Switching / Heating, Piezo Components, Buzzers and Microphones](#) >
- [Transformers](#) >
- [Ferrites and Accessories](#) >
- [Noise Suppressing / Magnetic Sheet](#) >
- [Anechoic Chambers and Radio Wave Absorbers](#) >
- [Power Supplies](#) >
- [Magnets](#) >
- [Flash Storages](#) >
- [Wireless Power Transfer](#) >
- [FA Systems](#) >
- [Transparent Conductive Film](#) >
- [Micro Modules \(Substrates with Built-in ICs, Products Utilizing with SESUB\)](#) >
- [Solar Cells](#) >
- [Biosensor](#) >
- [Application Specific IC \(ASIC\) Development and Supply](#) >

Application Guides

Technical Support

Tech Library

Environment

Contact

News

Home

About TDK

TDK Worldwide

[Terms of Use](#) [Privacy Policy](#) [Cookie Policy](#) [Counterfeit Products](#)

Copyright(c) 2019 TDK Corporation. All rights reserved.
TDK logo is a trademark or registered trademark of TDK Corporation.

