

The ZH connector is very small with a mounting height of 5.6mm and a thickness of only 3.5mm. Contact retention lances on the housing make insertion easier, while the dimple at the center of the contact ensures reliable contact with the post.


- · Compact, low profile design
- Housing lances
- Reliable contact construction
- Distortion resistant construction
- Compatible with the ZR insulation displacement connectors

PC board layout and Assembly layout

(Through-hole type (viewed from soldering side) >


Top entry type

JST



Note: 1. Tolerances are non-cumulative: ±0.05 mm for all centers.
2. Hole dimension differ according to the type of PC board and piercing method. If PC boards made of hard material are used, the hole dimensions should be larger. The dimensions above should serve as a guideline. Contact JST for details.

SMT type (viewed from component side) >



2. Tolerances are non-cumulative: ±0.05 mm for all centers.

3. The dimensions above should serve as a guideline. Contact JST for details.




- Current rating: 1.0 A AC, DC (AWG #26)
- Voltage rating: 50 V AC, DC
- Temperature range: -25°C to +85°C (including temperature rise in applying electrical current)
- Contact resistance: Initial value/ 20 m Ω max.
- After environmental tests/ 30 mΩ max. • Insulation resistance: 500 MΩ min.
- Withstanding voltage: 500 VAC/minute
- Applicable wire: AWG #32 to #26
- Applicable PC board thickness: 0.6 to 1.2 mm, 1.6 mm
- * Refer to "General Instruction and Notice when using
- Terminals and Connectors" at the end of this catalog.
- * Contact JST for details.
- * Compliant with RoHS.

Standards -

Recognized E60389


0.7 min

Certified LR20812



ZH CONNECTOR

Contact



machine Crimp applicat

MKS-L

Model No.		Q'ty/		
	mm ²	AWG#	Insulation O.D. (mm)	reel
SZH-002T-P0.5	0.08 ~0.13	28~26	0.8~1.1	13,000
SZH-003T-P0.5	0.032~0.08	32~28	0.5~0.9	16,000
	Materia	l and Finish		

Phosphor bronze, tin-plated (reflow treatment)


RoHS compliance

Applicator				Crimping	Applicator			
tor	Dies	Crimp applicator with dies	Contact	machine	Crimp applicator	Dies	Crimp applicator with dies	
	MK/SZH-002-05	APLMK SZH002-05	0711 000T D0 5		MKS-L	MK/SZH-003-05	APLMK SZH003-05	
			SZH-003T-P0.5	AP-K2N	*MKS-SC	SC/SZH-003-05	APLSC SZH003-05	

SZH-002T-P0.5 AP-K2N Note: *Strip-crimp applicator.

Housing

Contact



<For reference> As the color identification, the following alphabet shall be put in the underlined part. For availability, delivery and minimum order quantity, contact JST.


ZHR-2-00 ex.

Circuit No.1

(blank)...natural (white)

K...black R...red E...blue M...green L...lemon yellow LE...light blue DO...dark orange H...gray





Circuits	Model No.	Dimensio	Q'ty/				
Circuits	Woder No.	А	В	bag			
2	ZHR-2	1.5	4.5	1,000			
3	ZHR-3	3.0	6.0	1,000			
4	ZHR-4	4.5	7.5	1,000			
5	ZHR-5	6.0	9.0	1,000			
6	ZHR-6	7.5	10.5	1,000			
6	ZHR-6(3.0)	15.0	18.0	1,000			
7	ZHR-7	9.0	12.0	1,000			
8	ZHR-8	10.5	13.5	1,000			
9	ZHR-9	12.0	15.0	1,000			
10	ZHR-10	13.5	16.5	1,000			
11	ZHR-11	15.0	18.0	1,000			
12	ZHR-12	16.5	19.5	1,000			
13	ZHR-13	18.0	21.0	1,000			
Material							

PA 66, UL94V-0, natural (white)

RoHS compliance

Note: 1. ZHR-6(3.0) is 6 circuits 3.0mm pitch plugged up. As for this housing, only circuit No.1 is marked.

2. ZHR-6(3.0) is not UL/CSA approved.

	Model No.			Dimensions (mm)		Q'ty/box			
Circuits	Top entry type	Side entry type	Note) Top entry type	Note) Side entry type	A	В	Top entry type	Side entry type	Side entry type-3.4
2	B2B-ZR	S2B-ZR	B2B-ZR-3.4	S2B-ZR-3.4	1.5	4.5	2,000	2,000	2,000
3	B3B-ZR	S3B-ZR	B3B-ZR-3.4	S3B-ZR-3.4	3.0	6.0	2,000	2,000	1,000
4	B4B-ZR	S4B-ZR	B4B-ZR-3.4	S4B-ZR-3.4	4.5	7.5	2,000	2,000	2,000
5	B5B-ZR	S5B-ZR	B5B-ZR-3.4	S5B-ZR-3.4	6.0	9.0	2,000	1,000	1,000
6	B6B-ZR	S6B-ZR	B6B-ZR-3.4	S6B-ZR-3.4	7.5	10.5	2,000	1,000	1,000
7	B7B-ZR	S7B-ZR	B7B-ZR-3.4	S7B-ZR-3.4	9.0	12.0	1,000	1,000	1,000
8	B8B-ZR	S8B-ZR	B8B-ZR-3.4	S8B-ZR-3.4	10.5	13.5	1,000	1,000	1,000
9	B9B-ZR	S9B-ZR	B9B-ZR-3.4	S9B-ZR-3.4	12.0	15.0	1,000	1,000	1,000
10	B10B-ZR	S10B-ZR	B10B-ZR-3.4	S10B-ZR-3.4	13.5	16.5	1,000	1,000	1,000
11	B11B-ZR	S11B-ZR	B11B-ZR-3.4	S11B-ZR-3.4	15.0	18.0	1,000	500	500
12	B12B-ZR	S12B-ZR	B12B-ZR-3.4	S12B-ZR-3.4	16.5	19.5	1,000	500	500
13	B13B-ZR	S13B-ZR	B13B-ZR-3.4	S13B-ZR-3.4	18.0	21.0	500	500	500

Material and Finish

Pin: Brass, copper-undercoated, tin-plated (reflow treatment) Wafer: Glass-filled PA 66, UL94V-0, natural (ivory)

RoHS compliance This product displays (LF)(SN) on a label.

Note: Headers with 3.4mm long solder tails, suited for the 1.6mm thick PC board.

<For reference> As the color identification,

the following alphabet shall be put in the underlined part. For availability, delivery and minimum order quantity, contact JST.

ex. B2B-ZR-3.4-oo


(blank)...natural (ivory)


K...black R...red E...blue M...green Y...Yellow



ZH CONNECTOR

SMT type shrouded header





Circuits	Model No.		Dimensions (mm)		
	Side entry type	A	В	Q't ree	
2	S2B-ZR-SM2-TF	1.5	4.5	1,0	
3	S3B-ZR-SM2-TF	3.0	6.0	1,0	
4	S4B-ZR-SM2-TF	4.5	7.5	1,0	
5	S5B-ZR-SM2-TF	6.0	9.0	1,0	
6	S6B-ZR-SM2-TF	7.5	10.5	1,0	
7	S7B-ZR-SM2-TF	9.0	12.0	1,0	
8	S8B-ZR-SM2-TF	10.5	13.5	1,0	
9	S9B-ZR-SM2-TF	12.0	15.0	1,0	
10	S10B-ZR-SM2-TF	13.5	16.5	1,0	
11	S11B-ZR-SM2-TF	15.0	18.0	1,0	
12	S12B-ZR-SM2-TF	16.5	19.5	1,0	
13	S13B-ZR-SM2-TF	18.0	21.0	1,0	

Material and Finish

Pin: Brass, copper-undercoated, tin-plated (reflow treatment) Wafer: Glass-filled PA 46, UL94V-0, natural (ivory)

RoHS compliance This product displays (LF)(SN) on a label.

SM4 type

0' ''	Model No.			ons (mm)	Q'ty/reel	
Circuits	Top entry type	Side entry type	A	В	Top entry type	Side entry type
2	B2B-ZR-SM4-TF	S2B-ZR-SM4A-TF	1.5	6.0	1,000	1,000
3	B3B-ZR-SM4-TF	S3B-ZR-SM4A-TF	3.0	7.5	1,000	1,000
4	B4B-ZR-SM4-TF	S4B-ZR-SM4A-TF	4.5	9.0	1,000	1,000
5	B5B-ZR-SM4-TF	S5B-ZR-SM4A-TF	6.0	10.5	1,000	1,000
6	B6B-ZR-SM4-TF	S6B-ZR-SM4A-TF	7.5	12.0	1,000	1,000
7	B7B-ZR-SM4-TF	S7B-ZR-SM4A-TF	9.0	13.5	1,000	1,000
8	B8B-ZR-SM4-TF	S8B-ZR-SM4A-TF	10.5	15.0	1,000	1,000
9	B9B-ZR-SM4-TF	S9B-ZR-SM4A-TF	12.0	16.5	1,000	1,000
10	B10B-ZR-SM4-TF	S10B-ZR-SM4A-TF	13.5	18.0	1,000	1,000
11	B11B-ZR-SM4-TF	S11B-ZR-SM4A-TF	15.0	19.5	1,000	1,000
12	B12B-ZR-SM4-TF	S12B-ZR-SM4A-TF	16.5	21.0	1,000	1,000
13	B13B-ZR-SM4-TF	S13B-ZR-SM4A-TF	18.0	22.5	1,000	1,000

Material and Finish

Pin: Brass, copper-undercoated, tin-plated (reflow treatment) Wafer: PA 6T, UL94V-0, natural (ivory)

Solder tab: Brass, copper-undercoated, tin-plated (reflow treatment)

RoHS compliance This product displays (LF)(SN) on a label. Note: 1. PA 9T is used for some colored products.

2. The products listed above are supplied on embossed-tape. 3. Contact JST for the top entry type headers with suction cap.

<For reference> As the color identification,

the following alphabet shall be put in the underlined part. For availability, delivery and minimum order quantity, contact JST.

S2B-ZR-SM4A-oo-TF ex.

(blank)...natural (ivory)

K...black R...red E...blue M...green L...lemon yellow LE...light blue DO...dark orange DH...dark gray