


# FLEX STACK

## LOW-PROFILE .025" SQ POST HEADERS

(2.54 mm) .100" PITCH • TLW/MTLW SERIES



### TLW/MTLW

**Board Mates:**  
BSW, CES, SLW, HLE

#### FEATURES

These headers provide the ultimate low-profile (0.64 mm) .025" square post board stacking system. The high quality Phosphor Bronze terminals are available with a standard short post height (TLW Series) for mating with low-profile sockets, or the post height can be Modified (MTLW Series) to accommodate IDC assemblies and other applications.

#### SPECIFICATIONS

**Insulator Material:**  
Black Liquid Crystal Polymer  
**Terminal Material:**  
Phosphor Bronze  
**Plating:**

Au or Sn over  
50 μ" (1.27 μm) Ni  
**Current Rating (TLW/SLW):**  
5.2 A per pin  
(2 pins powered)  
**Operating Temp Range:**  
-55 °C to +105 °C with Tin  
-55 °C to +125 °C with Gold

#### PROCESSING

**Lead-Free Solderable:**  
Yes

#### ALSO AVAILABLE

MOQ Required

Other platings  
Notch option

**Note:**  
Some lengths, styles and options are non-standard, non-returnable. MTLW Series is non-standard, non-returnable.

TLW	- 1	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	ROW OPTION	OTHER OPTION
-----	-----	------------------	------------	----------------	------------	--------------


**01 thru 40**  
= Single Row  
**01 thru 36**  
= Double Row

Specify **LEAD STYLE** from chart


**-F**  
= Gold flash on post, Matte Tin on tail  
**-G**  
= 10 μ" (0.25 μm) Gold on post, Gold flash on tail  
**-T**  
= Matte Tin

**-S**  
= Single Row  
**-D**  
= Double Row

**-RA**  
= Right-angle (-01 Lead Style only)  
**"-XX"**  
= Polarized Position Specify position for omitted pin.



-05 & -06



LEAD STYLE	A	B
-01	N/A	(5.84) .230
-05	(4.32) .170	(2.67) .105
-06	(3.43) .135	

MTLW	- 1	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	ROW OPTION	POST HEIGHT
------	-----	------------------	------------	----------------	------------	-------------





**01 thru 40**  
= Single Row  
**01 thru 36**  
= Double Row

Specify **LEAD STYLE** from chart

**-F**  
= Gold flash on post, Matte Tin on tail  
**-L**  
= 10 μ" (0.25 μm) Gold on post, Matte Tin on tail  
**-G**  
= 10 μ" (0.25 μm) Gold on post, Gold flash on tail  
**-T**  
= Matte Tin

**-S**  
= Single Row  
**-D**  
= Double Row

**"-XXX"**  
= Post Height Dimension (In inches)



LEAD STYLE	OAL
-05	(8.51) .335
-06	(7.62) .300
-07	(10.92) .430
-08	(13.46) .530
-09	(18.54) .730
-10	(21.08) .830
-22	(16.00) .630
-23	(11.30) .445
-24	(12.19) .480

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Samtec:

[TLW-105-06-G-S](#) [TLW-102-05-G-S](#) [TLW-114-06-G-S](#) [TLW-110-05-G-D](#) [TLW-116-06-G-S](#) [TLW-114-05-G-S](#) [TLW-120-05-T-S](#) [TLW-120-05-G-S](#) [TLW-103-06-G-S](#) [TLW-105-06-G-S-04](#) [TLW-110-06-G-S](#) [TLW-107-06-G-D](#) [TLW-102-06-G-S](#) [TLW-116-06-T-S](#) [TLW-108-06-T-D](#) [TLW-106-06-G-S](#) [TLW-112-06-G-S](#) [TLW-115-06-G-D](#) [TLW-108-05-G-S](#) [TLW-112-06-T-D](#) [TLW-110-06-T-S](#) [TLW-107-05-T-D](#) [TLW-103-05-G-S-02](#) [TLW-110-06-G-D](#) [TLW-112-06-G-D](#) [TLW-115-05-G-D](#) [TLW-120-06-G-D](#) [TLW-105-06-T-D](#) [TLW-117-06-TM-S](#) [TLW-140-06-G-S](#) [TLW-103-05-G-S](#) [TLW-120-06-T-S](#) [TLW-120-05-G-D](#) [TLW-103-01-G-S-RA](#) [TLW-106-05-T-D](#) [TLW-102-06-G-D](#) [TLW-103-06-G-D](#) [TLW-108-06-G-D](#) [TLW-102-05-T-S](#) [TLW-107-06-T-D](#) [TLW-103-05-TM-D](#) [TLW-105-05-G-S](#) [TLW-105-06-G-D](#) [TLW-101-05-T-S](#) [TLW-103-06-G-D-03](#) [TLW-108-06-T-S-05](#) [TLW-102-05-G-D](#) [TLW-140-05-G-S](#) [TLW-104-05-T-S](#) [TLW-105-05-G-D](#) [TLW-105-05-T-S](#) [TLW-113-06-G-D](#) [TLW-102-06-TM-D](#) [TLW-101-06-T-S](#) [TLW-107-05-G-D](#) [TLW-110-06-T-D](#) [TLW-110-05-T-D](#) [TLW-120-06-G-S](#) [TLW-104-05-G-D](#) [TLW-108-06-T-S](#) [TLW-104-06-G-D](#) [TLW-120-05-TM-S](#) [TLW-112-06-TM-S](#) [TLW-108-05-G-D](#) [TLW-107-05-T-S](#) [TLW-140-06-T-S](#) [TLW-107-05-G-S](#) [TLW-103-06-T-S](#) [TLW-104-06-T-D](#) [TLW-110-05-G-S](#) [TLW-116-05-T-S](#) [TLW-108-06-G-S](#) [TLW-120-06-TM-S](#) [TLW-106-06-T-D](#) [TLW-104-05-G-S](#) [TLW-102-06-F-S](#) [TLW-103-05-T-S](#) [TLW-102-06-T-S](#) [TLW-105-05-T-D](#) [TLW-122-06-G-S](#) [TLW-136-06-G-D](#) [TLW-104-05-T-D](#) [TLW-110-05-T-S](#) [TLW-106-06-T-S](#) [TLW-118-05-G-S](#) [TLW-108-05-T-S](#) [TLW-103-05-G-D](#) [TLW-106-05-G-D](#) [TLW-107-06-G-S-04](#) [TLW-104-06-G-S](#) [TLW-114-06-T-S](#) [TLW-108-05-T-D](#) [TLW-103-05-T-D](#) [TLW-106-06-G-D](#) [TLW-136-06-T-D](#) [TLW-103-06-T-D](#) [TLW-102-06-G-D-01](#) [TLW-116-05-G-S](#) [TLW-102-05-F-S](#) [TLW-104-06-T-S](#)