



Bestückungsplan / contact layout



bestückt / assemble

Leiterplatten-Lochbild / PCB drillhole pattern



Elastische Einpresszone 2,5 mm / compliant pressfit zone 2,5 mm

Isolierwerkstoff / housing material : LCP GF30

Bauart 2 / type 2

Anforderungsstufe 1 = 500 Steckzyklen / performance class 1 = 500 mating cycles

Fehlende Masse und Angaben gemäß IEC 60 603-2 / DIN EN 60 603-2

Missing information and dimensions according to IEC 60 603-2 / DIN EN 60 603-2

Schichtaufbau im metallisierten Loch siehe Zeichnung 164062/Nr.6

diameter of drilled hole see drawing 164062/Nr.6

- 1) $\phi 1,0 \pm 0,06$ Durchmesser des metallisierten Loches
- $\phi 1,0 \pm 0,06$ Diameter of finished plated-through hole

Consider protection memo from DIN 34

| | | | | | |
|--|------------|----------------------|--|---|-----|
| Information: | | Tolerances | | Scale | 2:1 |
| All rights reserved. Only for information. To insure that this is the latest version of this drawing, please contact one of the ERNI companies before using. | | All Dimensions in mm | | Designation | |
| Subject to modification without prior notice. Drawing will not be updated. | | www.ERNI.com | | Federleiste H 11 EE Fem. Connector H 11 EE | |
| c | 14.12.2010 | ERNI | | 424655 | |
| Index | Date | V:00070330.SZA | | STVH11 | |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[424655](#) [424655-E](#)