






CLF6045T-470M-D

Applications	 Automotive Grade
Feature	 Wire Wound
	 Magnetic Shield
	 Ferrite Core
	 AEC-Q200
Series	CLF-D Series / CLF6045-D Type
Status	Production (Recommended Alternate Part is available.)(Recommended Alternate Part Number:CLF6045NIT-470M-D)



Size	
Length(L)	6.20mm +/-0.20mm
Width(W)	5.90mm +/-0.20mm
Thickness(T)	4.50mm +/-0.30mm
Recommended Land Pattern (A)	1.70mm Nom.
Recommended Land Pattern (B)	3.60mm Nom.
Recommended Land Pattern (C)	2.20mm Nom.


Electrical Characteristics	
Inductance	47uH +/-20% at 100kHz
Rated Current (L Change) [Typ.]	900mA (10% Down)
Rated Current (Temperature Rise) [Typ.]	1.3A (30degC Rise)
DC Resistance [Nom.]	130mΩ
DC Resistance [Max.]	156mΩ

Other	
Operating Temp. Range (Including Self-Temp. Rise)	-40 to 150degC
Soldering Method	Reflow, Iron Soldering
AEC Q200	Yes
Packing	Blister (Plastic)Taping [330mm Reel]
Package Quantity	1000Pcs Min.
Weight	0.6g


•This PDF document was created based on the data listed on the TDK Corporation website.
 •All specifications are subject to change without notice.

CLF6045T-470M-D


Characteristic Graphs (This is reference data, and does not guarantee the product's characteristics.)




CLF6045T-470M-D



CLF6045T-470M-D



CLF6045T-470M-D




CLF6045T-470M-D


•This PDF document was created based on the data listed on the TDK Corporation website.
 •All specifications are subject to change without notice.

CLF6045T-470M-D

Characteristic Graphs (This is reference data, and does not guarantee the product's characteristics.)




CLF6045T-470M-D(Amb. Temp. = 20degc)



CLF6045T-470M-D(DC = 0A)

CLF6045T-470M-D(DC = 0.45A)



CLF6045T-470M-D(Amb. Temp. = 20degc)

•This PDF document was created based on the data listed on the TDK Corporation website.
 •All specifications are subject to change without notice.