

# GCM2195C1H153JA16#

“#” indicates a package specification code.



## < List of part numbers with package codes >

GCM2195C1H153JA16D      GCM2195C1H153JA16J

## Appearance & Shape



## References

Packaging	Specifications	Standard Packing Quantity
D	180mm Paper Tape	4000
J	330mm Paper Tape	10000

Mass (typ.)	
1 piece	9.5mg
φ180mm Reel	152g

### Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# GCM2195C1H153JA16#

“#” indicates a package specification code.



## Specifications

Length	2.0±0.15mm
Width	1.25±0.15mm
Thickness	0.85±0.1mm
Capacitance	15000pF ±5%
Distance between external terminals g	0.7mm min.
External terminal size e	0.2 to 0.7mm
Operating Temperature Range	-55°C to 125°C
Rated Voltage	50Vdc
Size code in inch(mm)	0805 (2012M)
TC	0±30ppm/°C
Temperature characteristics (complied standard)	C0G(EIA)
Temperature range of temperature characteristics	25°C to 125°C

### Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.


# GCM2195C1H153JA16#

"#" indicates a package specification code.




## Characteristic Data


The charts below may show another part number which shares its characteristics.




GCM2195C1H153JA16 |Z| DCOV, 25degC



GCM2195C1H153JA16 R DCOV, 25degC



GCM2195C1H153JA16 C-DC bias capchange, 25.0degC, AC1V



GCM2195C1H153JA16 C-AC Voltage capchange, DCOV, 25.0d


**Attention**

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# GCM2195C1H153JA16#


“#” indicates a package specification code.

Temperature Characteristics



■ GCM2195C1H153JA16 C-Temp. capchange, DCOV, AC1Vrms

S Parameter S21



■ GCM2195C1H153JA16 S21 DCOV, 25degC

**Attention**

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.