


## **QBAT INDUSTRIAL H-SC3000HP**


NiMH Cylindrical Battery

Size: SC

## **Typical Characteristics**



QBAT INDUSTRIAL H-SC3000HP				
Specifications				
Nominal Voltage (V)			1.2V	
Capacity	Discharge rate		C/5	1C
	Nominal (mAh)		3000	2700
	Typical (mAh)		3050	2750
Dimension	Diameter (mm)		22.5 <sup>+0.5</sup> <sub>-0.5</sub>	
	Height (mm)		<b>42.5</b> <sup>+0.5</sup> <sub>-0.5</sub>	
Charging	Standard		300mA x 15 hrs	
	Quick		3000mA x 1.2 hrs T <sub>max</sub> =55°C -∆V = 5~8mV	
Operating Temperature (°C)	Standard Charging		0 ~ 45°C	
	Quick Charging		10 ~ 40°C	
	Discharging		-20 ~ 60°C	
	Storage		-20 ~ 35°C	
Internal Resistance		≦8m C	8m Ohm (upon 50% discharge)	
Weight		Approx. 56g		
Cuff-off Voltage (V)		1.00		



The data shown is correct at a temperature of  $20\pm5^{\circ}$ C Shutdown at- $\Delta$ V= 15mV, after reaching 120% of the rated capacity or at a temperature above 55°C

Qbat-battery.com

info@qbat-battery.com