

ix Industrial 10B-1 jack AH (1pcs.)




Image is for illustration purposes only. Please refer to product description.

Part number	09 45 281 9001 333
Specification	ix Industrial 10B-1 jack AH (1pcs.)
HARTING eCatalogue	https://b2b.harting.com/09452819001333

Identification

Category	Connectors
Series	HARTING ix Industrial®
Identification	Signal
Element	PCB connector
Specification	Horizontal

Version

Termination method	Solder termination
Shielding	Fully shielded, 360° shielding contact
Number of contacts	10
Coding	Type B
Pack contents	Sample

Technical characteristics

Rated current	1.5 A
Rated voltage	50 V AC 60 V DC
Contact resistance	≤30 mΩ
Shielding resistance	≤100 mΩ
Limiting temperature	-40 ... +85 °C
Storage temperature	-30 ... +60 °C
Insertion force	≤25 N
Withdrawal force	≤25 N



Pushing Performance

Technical characteristics

Mating cycles	≥5,000
Degree of protection acc. to IEC 60529	IP20
Test voltage $U_{r.m.s.}$	0.5 kV
Transmission characteristics	Cat. 6 _A Class E _A up to 500 MHz

Material properties

Material (insert)	Liquid crystal polymer (LCP)
Colour (insert)	Black
Material (contacts)	Copper alloy
Surface (contacts)	Au over Ni
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Specifications	IEC 61076-3-124
UL / CSA	UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079

Commercial data

Packaging size	1
Net weight	2 g
Country of origin	Japan
European customs tariff number	85366990
eCl@ss	27440402 PCB connector