


Mod. 7635.B

COPOLYMER POLYPROPYLENE WATERPROOF CASE

Large cases IP67 certified. Two man lift side handles and retractable handle. Self-oiling free running wheels. Four colors available and two internal standard configurations.




METRIC MM-KG-C°



INTERNAL DIMENSIONS		EXTERNAL DIMENSIONS		OTHER DATA	
L LENGTH	763 mm	L LENGTH	832 mm	WEIGHT EMPTY	9.4 Kg
W WIDTH	399 mm	W WIDTH	466 mm	WEIGHT WITH FOAM	11.8 Kg
D DEPTH	350 mm	D DEPTH	369 mm	WEIGHT WITH CUSTOM FOAM	Kg
LID	50 mm			VOLUME	106.6 lt
BASE	300 mm			BUOYANCY	82.2 Kg/max
				OPERATING TEMPERATURE	°C min -33 / max 90

IMPERIAL IN-LBS-F°



INTERNAL DIMENSIONS		EXTERNAL DIMENSIONS		OTHER DATA	
L LENGTH	30 1/16 in	L LENGTH	32 3/4 in	WEIGHT EMPTY	20.72 lbs
W WIDTH	15 11/16 in	W WIDTH	18 3/8 in	WEIGHT WITH FOAM	26.01 lbs
D DEPTH	13 3/4 in	D DEPTH	14 1/2 in	WEIGHT WITH CUSTOM FOAM	lbs
LID	1 15/16 in			VOLUME	28.16 gal
BASE	11 13/16 in			BUOYANCY	181.22 lbs/max
				OPERATING TEMPERATURE	°F min -27.4 / max 194