RGWX5TS65EHR

650V 75A Field Stop Trench IGBT

Datasheet

V _{CES}	650V
I _{C (100°C)}	75A
V _{CE(sat) (Typ.)}	1.5V
P_{D}	348W

Outline TO-247N (1) (2)(3)

Features

- 1) AEC-Q101 Qualified
- 2) Low Collector Emitter Saturation Voltage
- 3) Low Switching Loss & Soft Switching
- 4) Built in Very Fast & Soft Recovery FRD
- 5) Pb free Lead Plating; RoHS Compliant

Application

Automotive


On & Off Board Chargers

DC-DC Converters

PFC

Industrial Inverter

●Inner Circuit



Packaging Specifications

or ackaging opecinications					
	Packaging	Tube			
	Reel Size (mm)	-			
Tuno	Tape Width (mm)	-			
Type	Basic Ordering Unit (pcs)	450			
	Packing Code	C11			
	Marking	RGWX5TS65E			

● **Absolute Maximum Ratings** (at T_C = 25°C unless otherwise specified)

Parameter		Symbol	Value	Unit
Collector - Emitter Voltage		V _{CES}	650	V
Gate - Emitter Voltage		V_{GES}	±30	V
Callastay Current	T _C = 25°C	I _C	132	Α
Collector Current	T _C = 100°C	I _C	81	Α
Pulsed Collector Current		I _{CP} *1	300	Α
Diode Forward Current	T _C = 25°C	I _F	127	Α
	T _C = 100°C	I _F	80	Α
Diode Pulsed Forward Current		I _{FP} *1	300	Α
Dawer Dissination	T _C = 25°C	P _D	348	W
Power Dissipation	T _C = 100°C	P _D	174	W
Operating Junction Temperature		T _j	-40 to +175	°C
Storage Temperature		T _{stg}	-55 to +175	°C

^{*1} Pulse width limited by T_{jmax.}

●Thermal Resistance

Parameter	Symbol	Values			Unit
Falametei		Min.	Тур.	Max.	Offic
Thermal Resistance IGBT Junction - Case	$R_{\theta(j-c)}$	-	-	0.43	°C/W
Thermal Resistance Diode Junction - Case	$R_{\theta(j-c)}$	-	ı	0.57	°C/W

●IGBT Electrical Characteristics (at T_j = 25°C unless otherwise specified)

Parameter	Symbol	Conditions	Values			Unit
- Farameter	Symbol	Conditions	Min.		Max.	Offic
Collector - Emitter Breakdown Voltage	BV _{CES}	$I_{C} = 10 \mu A, V_{GE} = 0 V$	650	ı	ı	V
Collector Cut - off Current	I _{CES}	$V_{CE} = 650V, V_{GE} = 0V$	ı	ı	10	μА
Gate - Emitter Leakage Current	I _{GES}	$V_{GE} = \pm 30V, V_{CE} = 0V$	-	-	±200	nA
Gate - Emitter Threshold Voltage	$V_{GE(th)}$	$V_{CE} = 5V, I_{C} = 50.4 \text{mA}$	5.0	6.0	7.0	V
Collector - Emitter Saturation Voltage	V _{CE(sat)}	$I_{C} = 75A, V_{GE} = 15V,$ $T_{j} = 25^{\circ}C$ $T_{j} = 175^{\circ}C$	-	1.5 1.85	1.9 -	V

2/12


●IGBT Electrical Characteristics (at T_j = 25°C unless otherwise specified)

Parameter	Symbol	Conditions	Values			Unit
			Min.	Тур.	Max.	Offic
Input Capacitance	C _{ies}	$V_{CE} = 30V$,	-	5980	-	
Output Capacitance	C _{oes}	$V_{GE} = 0V$,	-	156	-	рF
Reverse transfer Capacitance	C _{res}	f = 1MHz	-	118	-	
Total Gate Charge	Q_g	V _{CE} = 400V,	-	213	-	
Gate - Emitter Charge	Q_{ge}	I _C = 75A,	-	42	-	nC
Gate - Collector Charge	Q_{gc}	V _{GE} = 15V	-	82	-	
Turn - on Delay Time	t _{d(on)}		-	59	-	
Rise Time	t _r	$I_C = 37.5A, V_{CC} = 400V,$ $V_{GF} = 15V, R_G = 10\Omega,$	-	18	-	ns mJ
Turn - off Delay Time	t _{d(off)}	$T_i = 25^{\circ}C$	-	243	-	
Fall Time	t _f	Inductive Load *E _{on} include diode reverse recovery	-	35	-	
Turn - on Switching Loss	E _{on}		-	0.99	-	
Turn - off Switching Loss	E _{off}		-	0.73	-	
Turn - on Delay Time	t _{d(on)}		-	55	-	
Rise Time	t _r	$I_C = 37.5A$, $V_{CC} = 400V$, $V_{GE} = 15V$, $R_G = 10\Omega$, $T_j = 175^{\circ}C$ Inductive Load *E _{on} include diode reverse recovery	-	18	-	ns
Turn - off Delay Time	t _{d(off)}		-	278	-	
Fall Time	t _f		-	76	-	
Turn - on Switching Loss	E _{on}		-	0.95	-	mJ
Turn - off Switching Loss	E _{off}		-	0.99	-	1113
Reverse Bias Safe Operating Area	RBSOA	$I_C = 300A$, $V_{CC} = 520V$, $V_P = 650V$, $V_{GE} = 15V$, $R_G = 100\Omega$, $T_j = 175^{\circ}C$	FU	LL SQUA	.RE	-

•FRD Electrical Characteristics (at $T_j = 25$ °C unless otherwise specified)

Parameter	Symbol	Conditions	Values			Unit
			Min.	Тур.	Max.	Offic
Diode Forward Voltage	V _F	$I_F = 75A,$ $T_i = 25^{\circ}C$	_	1.45	1.9	V
	'	T _j = 175°C	-	1.55	-	
Diode Reverse Recovery Time	t _{rr}		-	100	-	ns
Diode Peak Reverse Recovery Current	I _{rr}	$I_F = 37.5A,$ $V_{CC} = 400V,$	-	11.5	-	А
Diode Reverse Recovery Charge	Q _{rr}	di _F /dt = 200A/μs, Τ _j = 25°C	-	0.64	ı	μC
Diode Reverse Recovery Energy	E _{rr}		-	26.0	ı	μJ
Diode Reverse Recovery Time	t _{rr}	$I_F = 37.5A,$ $V_{CC} = 400V,$ $di_F/dt = 200A/\mu s,$ $T_j = 175^{\circ}C$	-	194	ı	ns
Diode Peak Reverse Recovery Current	I _{rr}		-	16.7	-	А
Diode Reverse Recovery Charge	Q _{rr}		-	1.93	-	μC
Diode Reverse Recovery Energy	E _{rr}		-	113	-	μJ

• Electrical Characteristic Curves






Fig.3 Forward Bias Safe Operating Area 1000 1µs 100 10µs Collector Current : I_C [A] 100µs 10 1 0.1 $T_{\rm C} = 25^{\circ}{\rm C}$ Single Pulse 0.01 10 100 1000 Collector To Emitter Voltage: V_{CE} [V]

400 350 Collector Current : Ic [A] 300 250 200 150 100 50 $T_i \le 175^{\circ}C$ V_{GF} = 15V 0 200 400 600 800 Collector To Emitter Voltage: V_{CE} [V]

Fig.4 Reverse Bias Safe Operating Area

•Electrical Characteristic Curves

Fig.5 Typical Output Characteristics




Fig.6 Typical Output Characteristics




Fig.7 Typical Transfer Characteristics





Fig.8 Typical Collector to Emitter Saturation Voltage vs. Junction Temperature



Collector To Emitter Saturation

Voltage: V_{CE(sat)} [V]



5

● Electrical Characteristic Curves

10

15

Gate To Emitter Voltage: V_{GE} [V]

Fig.9 Typical Collector to Emitter Saturation

Fig.10 Typical Collector to Emitter Saturation Voltage vs. Gate to Emitter Voltage





Fig.11 Typical Capacitance vs. Collector to Emitter Voltage 100000 C_{ies} 10000 Capacitance [pF] 1000 Coes 100 C_{res} 10 f = 1MHz $V_{GE} = 0V$ = 25°C 0.01 0.1 1 10 100 Collector To Emitter Voltage: V_{CE} [V]

Fig.12 Typical Gate Charge



Collector To Emitter Saturation

20

• Electrical Characteristic Curves

Fig.13 Typical Switching Time vs. Collector Current




Fig.14 Typical Switching Time vs. Gate Resistance




Fig.15 Typical Switching Energy Losses vs. Collector Current





Fig.16 Typocal Switching Energy Losses vs. Gate Resistance



•Electrical Characteristic Curves

Fig.17 Typical Switching Time vs. Collector Current




Fig.18 Typical Switching Time vs. Gate Resistance




Fig.19 Typical Switching Energy Losses vs. Collector Current





Fig.20 Typocal Switching Energy Losses vs. Gate Resistance



● Electrical Characteristic Curves


Fig.21 Typical Diode Forward Current vs. Forward Voltage 300 250 Forward Current : I_F [A] 200 150 100 $T_i = 25^{\circ}C$ $T_i = 175^{\circ}C$ 50 0 0.5 1 1.5 2 2.5 3 0 Forward Voltage: V_F [V]

vs. Forward Current 400 Reverse Recovery Time: t_{rr} [ns] 300 $T_i = 175^{\circ}C$ 200 100 $V_{CC} = 400V$ di_F/dt = 200A/µs $T_i = 25^{\circ}C$ Inductive load 0 25 50 75 100 125 150 0

Forward Current : I_F [A]

Fig.22 Typical Diode Revese Recovery Time

Fig.23 Typical Diode Reverse Recovery Current vs. Forward Current 20 $T_i = 175^{\circ}C$ Reverse Recovery Current : In [A] 15 10 5 $T_i = 25^{\circ}C$ $V_{CC} = 400V$ di_F/dt = 200A/µs Inductive load 0 25 0 50 75 100 125 150 Forward Current : I_F [A]



ROHM

10/12

•Electrical Characteristic Curves

Fig.25 Typical IGBT Transient Thermal Impedance





Fig.26 Typical Diode Transient Thermal Impedance



11/12

●Inductive Load Switching Circuit and Waveform




Fig.29 Diode Reverse Recovery Waveform

Fig.28 Inductive Load Waveform

Notes

- 1) The information contained herein is subject to change without notice.
- Before you use our Products, please contact our sales representative and verify the latest specifications.
- 3) Although ROHM is continuously working to improve product reliability and quality, semiconductors can break down and malfunction due to various factors.

 Therefore, in order to prevent personal injury or fire arising from failure, please take safety measures such as complying with the derating characteristics, implementing redundant and fire prevention designs, and utilizing backups and fail-safe procedures. ROHM shall have no responsibility for any damages arising out of the use of our Poducts beyond the rating specified by ROHM.
- 4) Examples of application circuits, circuit constants and any other information contained herein are provided only to illustrate the standard usage and operations of the Products. The peripheral conditions must be taken into account when designing circuits for mass production.
- 5) The technical information specified herein is intended only to show the typical functions of and examples of application circuits for the Products. ROHM does not grant you, explicitly or implicitly, any license to use or exercise intellectual property or other rights held by ROHM or any other parties. ROHM shall have no responsibility whatsoever for any dispute arising out of the use of such technical information.
- 6) The Products specified in this document are not designed to be radiation tolerant.
- 7) For use of our Products in applications requiring a high degree of reliability (as exemplified below), please contact and consult with a ROHM representative: transportation equipment (i.e. cars, ships, trains), primary communication equipment, traffic lights, fire/crime prevention, safety equipment, medical systems, servers, solar cells, and power transmission systems.
- 8) Do not use our Products in applications requiring extremely high reliability, such as aerospace equipment, nuclear power control systems, and submarine repeaters.
- 9) ROHM shall have no responsibility for any damages or injury arising from non-compliance with the recommended usage conditions and specifications contained herein.
- 10) ROHM has used reasonable care to ensure the accuracy of the information contained in this document. However, ROHM does not warrants that such information is error-free, and ROHM shall have no responsibility for any damages arising from any inaccuracy or misprint of such information.
- 11) Please use the Products in accordance with any applicable environmental laws and regulations, such as the RoHS Directive. For more details, including RoHS compatibility, please contact a ROHM sales office. ROHM shall have no responsibility for any damages or losses resulting non-compliance with any applicable laws or regulations.
- 12) When providing our Products and technologies contained in this document to other countries, you must abide by the procedures and provisions stipulated in all applicable export laws and regulations, including without limitation the US Export Administration Regulations and the Foreign Exchange and Foreign Trade Act.
- This document, in part or in whole, may not be reprinted or reproduced without prior consent of ROHM.



Thank you for your accessing to ROHM product informations. More detail product informations and catalogs are available, please contact us.

ROHM Customer Support System

http://www.rohm.com/contact/

General Precaution

- 1. Before you use our Products, you are requested to care fully read this document and fully understand its contents. ROHM shall not be in an y way responsible or liable for failure, malfunction or accident arising from the use of a ny ROHM's Products against warning, caution or note contained in this document.
- 2. All information contained in this docume nt is current as of the issuing date and subject to change without any prior notice. Before purchasing or using ROHM's Products, please confirm the latest information with a ROHM sale s representative.
- 3. The information contained in this doc ument is provided on an "as is" basis and ROHM does not warrant that all information contained in this document is accurate an d/or error-free. ROHM shall not be in an y way responsible or liable for any damages, expenses or losses incurred by you or third parties resulting from inaccuracy or errors of or concerning such information.

Notice – WE © 2015 ROHM Co., Ltd. All rights reserved. Rev.001