

# MBRD320G, SBRD8320G, MBRD330G, SBRD8330G, MBRD340G, SBRD8340G, MBRD350G, SBRD8350G, MBRD360G, SBRD8360G

MBRD320, MBRD340 and MBRD360 are Preferred Devices

## SWITCHMODE Power Rectifiers

### DPAK Surface Mount Package

These state-of-the-art devices are designed for use as output rectifiers, free wheeling, protection and steering diodes in switching power supplies, inverters and other inductive switching circuits.

#### Features

- Extremely Fast Switching
- Extremely Low Forward Drop
- Platinum Barrier with Avalanche Guardrings
- AEC-Q101 Qualified and PPAP Capable
- SBRD8 Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements
- All Packages are Pb-Free\*

#### Mechanical Characteristics:


- Case: Epoxy, Molded
- Weight: 0.4 Gram (Approximately)
- Finish: All External Surfaces Corrosion Resistant and Terminal Leads are Readily Solderable
- Lead and Mounting Surface Temperature for Soldering Purposes; 260°C Max. for 10 Seconds
- ESD Ratings:
  - ◆ Machine Model = C
  - ◆ Human Body Model = 3B




ON Semiconductor®

<http://onsemi.com>


### SCHOTTKY BARRIER RECTIFIERS 3.0 AMPERES, 20 – 60 VOLTS



DPAK  
CASE 369C



#### MARKING DIAGRAM



Y	= Year
WW	= Work Week
B3x0	= Device Code
x	= 2, 3, 4, 5, or 6
G	= Pb-Free Package

#### ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 2 of this data sheet.

**Preferred** devices are recommended choices for future use and best overall value.

\*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

**MBRD320G, SBRD8320G, MBRD330G, SBRD8330G, MBRD340G, SBRD8340G,  
MBRD350G, SBRD8350G, MBRD360G, SBRD8360G**

**MAXIMUM RATINGS**

Rating	Symbol	MBRD/SBRD8					Unit
		320	330	340	350	360	
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage	$V_{RRM}$ $V_{RWM}$ $V_R$	20	30	40	50	60	V
Average Rectified Forward Current ( $T_C = +125^\circ\text{C}$ , Rated $V_R$ )	$I_{F(AV)}$	3					A
Peak Repetitive Forward Current, $T_C = +125^\circ\text{C}$ (Rated $V_R$ , Square Wave, 20 kHz)	$I_{FRM}$	6					A
Nonrepetitive Peak Surge Current (Surge applied at rated load conditions halfwave, single phase, 60 Hz)	$I_{FSM}$	75					A
Peak Repetitive Reverse Surge Current (2 $\mu\text{s}$ , 1 kHz)	$I_{RRM}$	1					A
Operating Junction Temperature Range (Note 1)	$T_J$	-65 to +175					$^\circ\text{C}$
Storage Temperature Range	$T_{stg}$	-65 to +175					$^\circ\text{C}$
Voltage Rate of Change (Rated $V_R$ )	$dv/dt$	10,000					V/ $\mu\text{s}$

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

1. The heat generated must be less than the thermal conductivity from Junction-to-Ambient:  $dP_D/dT_J < 1/R_{\theta JA}$ .

**THERMAL CHARACTERISTICS**

Characteristic	Symbol	Value	Unit
Maximum Thermal Resistance, Junction-to-Case	$R_{\theta JC}$	6	$^\circ\text{C}/\text{W}$
Maximum Thermal Resistance, Junction-to-Ambient (Note 2)	$R_{\theta JA}$	80	$^\circ\text{C}/\text{W}$

2. Rating applies when surface mounted on the minimum pad size recommended.

**ELECTRICAL CHARACTERISTICS**

Characteristic	Symbol	Value	Unit
Maximum Instantaneous Forward Voltage (Note 3) $i_F = 3$ Amps, $T_C = +25^\circ\text{C}$ $i_F = 3$ Amps, $T_C = +125^\circ\text{C}$ $i_F = 6$ Amps, $T_C = +25^\circ\text{C}$ $i_F = 6$ Amps, $T_C = +125^\circ\text{C}$	$V_F$	0.6 0.45 0.7 0.625	V
Maximum Instantaneous Reverse Current (Note 3) (Rated dc Voltage, $T_C = +25^\circ\text{C}$ ) (Rated dc Voltage, $T_C = +125^\circ\text{C}$ )	$i_R$	0.2 20	mA

3. Pulse Test: Pulse Width = 300  $\mu\text{s}$ , Duty Cycle  $\leq 2.0\%$ .

**ORDERING INFORMATION**

Device	Package	Shipping <sup>†</sup>
MBRD320G	DPAK (Pb-Free)	75 Units / Rail
SBRD8320G	DPAK (Pb-Free)	75 Units / Rail
MBRD320RLG	DPAK (Pb-Free)	1,800 Tape & Reel
MBRD320T4G	DPAK (Pb-Free)	2,500 Tape & Reel
SBRD8320T4G	DPAK (Pb-Free)	2,500 Tape & Reel
MBRD330G	DPAK (Pb-Free)	75 Units / Rail
SBRD8330G	DPAK (Pb-Free)	75 Units / Rail

**MBRD320G, SBRD8320G, MBRD330G, SBRD8330G, MBRD340G, SBRD8340G,  
MBRD350G, SBRD8350G, MBRD360G, SBRD8360G**


**ORDERING INFORMATION**

Device	Package	Shipping†
MBRD330RLG	DPAK (Pb-Free)	1,800 Tape & Reel
MBRD330T4G	DPAK (Pb-Free)	2,500 Tape & Reel
SBRD8330T4G	DPAK (Pb-Free)	2,500 Tape & Reel
MBRD340G	DPAK (Pb-Free)	75 Units / Rail
SBRD8340G	DPAK (Pb-Free)	75 Units / Rail
MBRD340RLG	DPAK (Pb-Free)	1,800 Tape & Reel
MBRD340T4G	DPAK (Pb-Free)	2,500 Tape & Reel
SBRD8340T4G	DPAK (Pb-Free)	2,500 Tape & Reel
MBRD350G	DPAK (Pb-Free)	75 Units / Rail
SBRD8350G	DPAK (Pb-Free)	75 Units / Rail
MBRD350RLG	DPAK (Pb-Free)	1,800 Tape & Reel
SBRD8350RLG	DPAK (Pb-Free)	1,800 Tape & Reel
MBRD350T4G	DPAK (Pb-Free)	2,500 Tape & Reel
SBRD8350T4G	DPAK (Pb-Free)	2,500 Tape & Reel
MBRD360G	DPAK (Pb-Free)	75 Units / Rail
SBRD8360G	DPAK (Pb-Free)	75 Units / Rail
MBRD360RLG	DPAK (Pb-Free)	1,800 Tape & Reel
SBRD8360RLG	DPAK (Pb-Free)	1,800 Tape & Reel
MBRD360T4G	DPAK (Pb-Free)	2,500 Tape & Reel
SBRD8360T4G	DPAK (Pb-Free)	2,500 Tape & Reel


†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

**MBRD320G, SBRD8320G, MBRD330G, SBRD8330G, MBRD340G, SBRD8340G,  
MBRD350G, SBRD8350G, MBRD360G, SBRD8360G**

**TYPICAL CHARACTERISTICS**




**Figure 1. Typical Forward Voltage**



\*The curves shown are typical for the highest voltage device in the voltage grouping. Typical reverse current for lower voltage selections can be estimated from these curves if  $V_R$  is sufficient below rated  $V_R$ .


**Figure 2. Typical Reverse Current**




**Figure 3. Average Power Dissipation**

**MBRD320G, SBRD8320G, MBRD330G, SBRD8330G, MBRD340G, SBRD8340G,  
MBRD350G, SBRD8350G, MBRD360G, SBRD8360G**


**TYPICAL CHARACTERISTICS**



**Figure 4. Current Derating, Case**



**Figure 5. Current Derating, Ambient**




**Figure 6. Typical Capacitance**

**MBRD320G, SBRD8320G, MBRD330G, SBRD8330G, MBRD340G, SBRD8340G,  
MBRD350G, SBRD8350G, MBRD360G, SBRD8360G**

**PACKAGE DIMENSIONS**


**DPAK (SINGLE GAUGE)**  
CASE 369C-01  
ISSUE D



- NOTES:
1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
  2. CONTROLLING DIMENSION: INCHES.
  3. THERMAL PAD CONTOUR OPTIONAL WITHIN DIMENSIONS b3, L3 and Z.
  4. DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR BURRS. MOLD FLASH, PROTRUSIONS, OR GATE BURRS SHALL NOT EXCEED 0.006 INCHES PER SIDE.
  5. DIMENSIONS D AND E ARE DETERMINED AT THE OUTERMOST EXTREMES OF THE PLASTIC BODY.
  6. DATUMS A AND B ARE DETERMINED AT DATUM PLANE H.

DIM	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	0.086	0.094	2.18	2.38
A1	0.000	0.005	0.00	0.13
b	0.025	0.035	0.63	0.89
b2	0.030	0.045	0.76	1.14
b3	0.180	0.215	4.57	5.46
c	0.018	0.024	0.46	0.61
c2	0.018	0.024	0.46	0.61
D	0.235	0.245	5.97	6.22
E	0.250	0.265	6.35	6.73
e	0.090 BSC		2.29 BSC	
H	0.370	0.410	9.40	10.41
L	0.055	0.070	1.40	1.78
L1	0.108 REF		2.74 REF	
L2	0.020 BSC		0.51 BSC	
L3	0.035	0.050	0.89	1.27
L4	---	0.040	---	1.01
Z	0.155	---	3.93	---

**SOLDERING FOOTPRINT\***



SCALE 3:1 (mm/inches)

\*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor and are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

**PUBLICATION ORDERING INFORMATION**

**LITERATURE FULFILLMENT:**  
Literature Distribution Center for ON Semiconductor  
P.O. Box 5163, Denver, Colorado 80217 USA  
**Phone:** 303-675-2175 or 800-344-3860 Toll Free USA/Canada  
**Fax:** 303-675-2176 or 800-344-3867 Toll Free USA/Canada  
**Email:** orderlit@onsemi.com

**N. American Technical Support:** 800-282-9855 Toll Free  
USA/Canada  
**Europe, Middle East and Africa Technical Support:**  
Phone: 421 33 790 2910  
**Japan Customer Focus Center**  
Phone: 81-3-5817-1050

**ON Semiconductor Website:** [www.onsemi.com](http://www.onsemi.com)  
**Order Literature:** <http://www.onsemi.com/orderlit>  
For additional information, please contact your local Sales Representative