


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART # ▲	TAB SIZE		WIRE RANGE		COLOR	DIMENSIONS in. [mm]					TOOL CHART	
	ENGLISH in.	METRIC mm	ENGLISH AWG	METRIC mm ²		MAX. WIRE INSUL. DIA.	L ± .03 [0,8]	W ± .01 [0,3]	H ± .01 [0,3]	D ± .01 [0,3]	PRESSES: CP-861, CP-862, CP-871	APPLICATOR DIES: CA9, CA-800EZ
DNFR18250FIB-KD	.250 X .032	6,3 X 0,8	22-18	0,5-1,0	RED	.178 [4,52]	.57 [14,5]	.37 [9,4]	.21 [5,3]	.60 [15,2]	CD-800-9 CD9-9C	
DNFR18205FIB-KD	.205/.187 X .032	5,2/4,8 X 0,8										
DNFR18206FIB-KD	.205/.187 X .020	5,2/4,8 X 0,5										
DNFR14250FIB-KD	.250 X .032	6,3 X 0,8	16-14	1,5-2,5	BLUE	▲						
DNFR14205FIB-KD	.205/.187 X .032	5,2/4,8 X 0,8										
DNFR14206FIB-KD	.205/.187 X .020	5,2/4,8 X 0,5										

NOTES:

- USED FOR:
 - A. STRANDED COPPER WIRE ONLY
 - B. 221°F [105°C] MAX. OPERATING TEMPERATURE
 - C. 600V. MAX. BLDG WIRE
 - D. 6-12 LBS INITIAL INSERTION/WITHDRAWAL FORCE
- WIRE STRIP LENGTH:
 - 11/32 +1/32 [8,7 +0,8]
- MATERIAL:
 - A. STAMPING: CDA 260 BRASS, TIN PLATED
 - B. HOUSING: TYPE 6/6 NYLON
- SEE www.panduit.com FOR PACKAGE QUANTITIES INDICATED BY PART NUMBER SUFFIX
- DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT
- CURL SLOTS: DNFR18205FIB, DNFR18206FIB, DNFR14205FIB, DNFR14206FIB ONLY.



REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
---	---	---	---	---	ADDED "REEL SMART" TO DRAWING TITLE.	----
11	2/22/18	BWG	SKB	JADE	▲ REVISED DIMENSION LOCATION OF HOUSING WIDTH. REMOVED TITLE BLOCK TOLERANCES.	019464/00
10	10.10.12	JBN	LCA	VMB	ADDED METRIC EQUIVALENT. CHANGE PACKAGING NOTE. ADDED TOOLS CHART. UPDATED DRAWING TO CURRENT STANDARDS.	A41124

<p>TITLE FEMALE DISCONNECTS, NYLON FULLY INSULATED - RIGHT ANGLE REEL SMART ▲ CUSTOMER DRAWING</p>			
<p>ITEM REVISION NAME N41124BA/11</p>		<p>DATASET FILE NAME N41124BA_DC/11 - A41124_REV11</p>	
<p>UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]</p> <p>.X ± --- .XXX ± --- .XX ± --- ANGLE ± ---</p> <p>THIRD ANGLE PROJECTION</p>		<p>MATERIAL: SEE NOTES</p> <p>DRAWING NUMBER: A41124</p>	
<p>DRAWN BY MG</p>	<p>DATE -</p>	<p>CHK -</p>	<p>SCALE N.T.S.</p>
<p>SHT 1 OF 1</p>		<p>SIZE A</p>	

D10100DA/15