AC-DC Power Supplies Medical Type






















GHA-series



Feature

Wattage 700Wmax

Conduction cooling (GHA500F, GHA700F)

3" × 5"standard footprint

Less than 1U high

ITE and Medical safety approvals

Low leakage current

Suitable for BF application

(Output-FG: 1MOPP, Input-Output: 2MOPP) (GHA700F)

With Remote (Option)

With AUX1 (12V) (Optional Excluding GHA700F-12)

With AUX2 (5V) (Optional)

With FAN (GHA300F-SNF, GHA500F-SNF)

Safety agency approvals

UL60950-1 (GHA300F, 500F), UL62368-1 (GHA700F)

ANSI/AAMI ES60601-1, C-UL EN62368-1, EN60601-1 3rd Complies with IEC60601-1-2 4th

DEN-AN (GHA300F, 500F)

EN61558-2-16 (GHA700F)

5-year warranty (Refer to Instruction Manual)

CE marking

Low Voltage Directive **RoHS** Directive

UKCA marking

Electrical Equipment Safety Regulations RoHS Regulations

EMI

Complies with FCC-B, CISPR11-B, CISPR32-B, EN55011-B EN55032-B, VCCI-B

EMS Compliance : EN61204-3,EN61000-6-2

IEC60601-1-2 (2014), EN60601-1-2 (2015)

EN61000-4-2

EN61000-4-3

EN61000-4-4

EN61000-4-5

EN61000-4-6

EN61000-4-8 EN61000-4-11

Ordering information

GHA300F

GH A 300 F - - -









High voltage pulse noise type : EAP series Low leakage current type : EAM series

*A higher current rating EMI/EMC filter may be recommended in view of the other devices that could be connected in parallel with the power supply. ①Series name ②Single output

②Single output ③Output wattage ④Universal input ⑤Output voltage

©Output voltage ®Optional *6 T3 : mounting hole M3

J3 : Horizontal input connector J.S.T.connector type R3 : with Subfeatures (5VAUX,12VAUX,Remote, Power good)(Molex connector type)

: J.S.T.connector type

Specification is changed at option, refer to Instruction manual.

*with friction locks,J2R3

This power supply is manufactured by SMD technology. The stress to P.C.B like twisting or bending causes the defect of the unit, please handle the unit with care *Make sure necessary tests will be carried out on your end equipment with the power supply installed in accordance with any required EMC/EMI regulations.

MODEL		GHA300F-12	GHA300F-24	GHA300F-48
MAX OUTPUT WATTA	GE[W]	300	300	302.4
	Forced air at 50°C	12V 25A	24V 12.5A	48V 6.3A
DC OUTPUT	Convection at 40℃	12V 8.4A	24V 4.2A	48V 2.1A
	at 50°C	12V 4.5A	24V 2.2A	48V 1.1A

	MODEL		GHA300F-12	GHA300F-24	GHA300F-48				
	VOLTAGE[V]		AC90 - 264 1 ϕ (output derating is r	required at AC90V -115V *3)					
	OUDDENTIAL	ACIN 120V	3.3typ						
	CURRENT[A]	ACIN 230V	1.8typ						
	FREQUENCY[Hz]		50 / 60 (47 - 63)						
INPUT EFFICIENCY[%] POWER FACTOR	EEEIOIENOVIO/1	ACIN 120V	89typ	90typ	90typ				
	EFFICIENCY[%]	ACIN 230V	91typ	92typ	92typ				
	POWER FACTOR	ACIN 120V	0.95typ						
	(lo=100%)	ACIN 230V	0.90typ						
•		ACIN 120V	typ (Io=100%) (At cold start) (Ta=25℃)						
	INRUSH CURRENT[A]		Otyp (Io=100%) (At cold start) (Ta=25°C)						
	LEAKAGE CURREN	T[mA]	0.125/0.250max (ACIN 120V/240V 60Hz,lo=100%, According to IEC60601-1)						
	VOLTAGE[V]		12	24	48				
	CURRENT[A]	Forced air	25.0	12.5	6.3				
	CORRENT[A]	Convection	4.5	2.2	1.1				
	LINE REGULATION[48max	96max	192max				
	LOAD REGULATION			150max	240max				
	RIPPLE[mVp-p] *1		240max	240max	300max				
RIPPLI	ule e e e e e e e e e e e e e e e e e e		320max	320max	400max				
OUTPUT	RIPPLE NOISE[mVp-p]*1	0 to +50°C	300max	300max	480max				
001101	TIII T EE NOISE[IIIVP-P]*	-20 to 0℃	360max	360max	500max				
т	TEMPERATURE REGULATION[mV]		120max	240max	480max				
		-20 to +50°C	150max	290max	600max				
	DRIFT[mV]		48max	96max	192max				
	START-UP TIME[ms]		500typ (ACIN 120V, Io=100%)						
	HOLD-UP TIME[ms] OUTPUT VOLTAGE ADJUSTMENT		16typ (ACIN 120V, Io=100%)						
			10.80 to 13.20	21.60 to 26.40	43.20 to 52.80				
	OUTPUT VOLTAGE SET		12.00 to 12.48	24.00 to 24.96	48.00 to 49.92				
	OVERCURRENT PROT		Works over 105% of rating and rec						
PROTECTION	OVERVOLTAGE PROTEC	CTION[V]	13.80 to 16.80	27.60 to 33.60	55.20 to 67.20				
CIRCUIT AND	AUX1 (12V1A)		Optional						
OTHERS	AUX2 (5V1A)	-	Optional						
	REMOTE ON/OFF		Optional						
	PowerGood		Optional $AC4,000V$ 1minute, Cutoff current = 10mA, DC500V 50M Ω min (At Room Temperature) 2MOPP						
	INPUT-OUTPUT · RC	· AUX *7							
ISOLATION	INPUT-FG	FO :-	AC2,000V 1minute, Cutoff current = 10mA, DC500V 50M Ω min (At Room Temperature) 1MOPP AC500V 1minute, Cutoff current = 25mA, DC500V 50M Ω min (At Room Temperature)						
	OUTPUT · RC · AUX- OUTPUT-RC · AUX	FG *7							
			7.00001 minuto, outon current Long Boodet com min (remount for polataro)						
	OPERATING TEMP., HUMID. AND STORAGE TEMP., HUMID. AND								
ENVIRONMENT	VIBRATION	ALIIIUDE							
	IMPACT		10 - 55Hz, 19.6m/s² (2G), 3minutes period, 60minutes each along X, Y and Z axis 196.1m/s² (20G), 11ms, once each X, Y and Z axis						
	IIVIFACI				01-1). EN62368-1. EN60601-1 3rd.				
SAFETY AND	AGENCY APPROVAL	LS	Complies with DEN-AN, IEC60601-		01-1), EN02300-1, EN00001-1 31u,				
NOISE	CONDUCTED NOISE			PR11-B, CISPR22-B, EN55011-B, E	N55022-R				
REGULATIONS	HARMONIC ATTENU		Complies with IEC61000-3-2 (class		וווטטטבב ט				
	CASE SIZE/WEIGHT		76.2×35×127mm [3.0×1.4×5.0 i		.				
OTHERS	COOLING METHOD								
	COOLING WE I HOD		Convection, Forced air (Require external fan)						

- *1 This is the value that measured on measuring board with capacitor of 22 µF at 150mm from outout terminal.
- Measured by 20MHz oscilloscope or Ripple-Noise meter (Equivalent to KEISOKU-GIKEN: RM103).


 *2 Drift is the change in DC output for an eight hour period after a half-hour warm-up at 25°C, with the input voltage held constant at the rated input/output.
- *3 Derating is required.
- *4 Please contact us about dynamic load and input response.
- *5 Please contact us about another class.

- *6 Specification is changed at option, refer to Instruction Manual.
- *7 Applicable when AUX and remote control (optional) is added.
- To meet the specifications. Do not operate over-loaded condition.
 Sound noise may be generated by power supply in case of pulse load.
- * Parallel operation is not possible.
- * Forced air cooling is required to output up to MAX OUTPUT WATTAGE.
- Bottom layer P.C.B has electric potential which is required isolation from FG by clearance or creepage as the safety design issue.




- · High Power density:14.3W/inch3
- · 3"× 5"standard footprint
- · Industrial and Medical safety approvals
- · With Remote On/Off (Optional)
- · No minimum load is required
- · High efficiency 92% typ (Input Voltage 230V, Output Voltage 24V)
- · Fits 1U applications
- · Low leakage current
- · With AUX1 (12V), AUX2 (5V) (Optional)

Block diagram



External view

*External size of option J3 is different from standard model and refer to 6 Option and Others of instruction manual for details.



	Name plate	
35	COŞEL	16.5 [0.65] 24.5 [0.96]

- ** Tolerance ±1 [±0.04]
- Weight: 400g max
- * There is a total of four attachment holes
- * This power supply requires mounting on metal standoffs 5mm in height. (Insulating sheet is required if you do not use a spacer).
- Dimensions in mm, []=inchesScrew tightening torque : (TB501, 502) : 1.5N · m max
- Mounting toque: 0.6N · m max
 Avoid contact between TB501 and 502 wiring with mounting parts.
- Option: -J1: (J.S.T) connector type. Refer to Instruction Manual 6.

	Con	nector	Mating connector	Terminal	Mfr	
Standard	CN101	A-41671-A03A197-2	09-50-8031	08-50-0105		
R3	CN101	A-41071-AUSA197-2	09-30-6031	08-65-0114	.	
no	CN501	087831-0820	51110-0851	50394-8051	Molex *	
J2R3	CN101	A-41671-A03A197-2	09-50-8031	08-50-0105 08-65-0114	I I I I I I I I I I I I I I I I I I I	
CN501		87831-0841 51110-0860 50394-805		50394-8051		
J3	CN101	S2P3-VH				
J1	CN101	B2P3-VH	VHR-3N	SVH-21T-P1.1	J.S.T.	
J1R3	CN101	DZF3-VII				
JINS	CN501	B8B-PHDSS	PHDR-08VS	SPHD-002T-P0.5		

*Please note the pin position No.1 is different from Molex.

ı	FG	Mating connector	Terminal	Mfr	
-	250 Series	-	170603-2	Tyco Electronics	

<Pin Assignments>

<CN101>

Pin No.	Input			
1	AC(L)			
2				
3	AC(N)			

<CN501(Optional)>

Pin No.	Function
1	AUX1 : AUX1 (12V1A)
2	AUX1G: AUX1 (GND)
3	RC : REMOTE ON/OFF
4	RCG : REMOTE ON/OFF (GND)
5	PG : Power good
6	PGG : Power good (GND)
7	AUX2 : AUX2 (5V1A)
8	AUX2G: AUX2 (GND)



CN501

GHA500F

500







High voltage pulse noise type : EAP series Low leakage current type : EAM series

*A higher current rating EMI/EMC filter may be recommended in view of the other devices that could be connected in parallel with the power supply. 1) Series name 2) Single output 3) Output wattage 4) Universal input

(5)Output voltage Optional *6

T3: mounting hole M3 : J.S.T.connector type J3 : Horizontal input connector J.S.T.connector type

R3: with Subfeatures (5VAUX,12VAUX,Remote, Power good)(Molex connector type) *with friction locks,J2R3

P : Parallel Operation

Specification is changed at option, refer to Instruction manual.

This power supply is manufactured by SMD technology. The stress to P.C.B like twisting or bending causes the defect of the unit, please handle the unit with care *Make sure necessary tests will be carried out on your end equipment with the power supply installed in accordance with any required EMC/EMI regulations.

MODEL			GHA500F-12	GHA500F-15	GHA500F-24	GHA500F-30	GHA500F-48	GHA500F-56
MAX OUTPUT WATTAGE[W]			500.4	501	504	501	504	504
	Forced air		12V 41.7A	15V 33.4A	24V 21.0A	30V 16.7A	48V 10.5A	56V 9.0A
DC OUTPUT	Convection	at 40°C	12V 12.5A	15V 10.0A	24V 6.3A	30V 5.0A	48V 3.2A	56V 2.7A
		at 50°C	12V 9.2A	15V 7.4A	24V 4.6A	30V 3.7A	48V 2.3A	56V 1.9A
	conduction	at 0°C	12V 30.0A	15V 24.0A	24V 15.0A	30V 12.0A	48V 7.5A	56V 6.4A
	cooling	at 50℃	12V 16.7A	15V 13.4A	24V 8.4A	30V 6.7A	48V 4.2A	56V 3.6A

	MODEL		GHA500F-12	GHA500F-15	GHA500F-24	GHA500F-30	GHA500F-48	GHA500F-56		
	VOLTAGE[V]		AC90 - 264 1 φ (output derating is r	equired at AC90V -	·115V *3)				
	CURRENT[A]	ACIN 120V	5.4typ							
	CURRENT[A]	ACIN 230V								
INPUT	FREQUENCY[Hz]	FREQUENCY[Hz]		50 / 60 (47 - 63)						
	EFFICIENCY[%]	ACIN 120V	88typ	90typ	90typ	90typ	90typ	90typ		
	EFFICIENCY[%]	ACIN 230V	90typ	92typ	92typ	92typ	92typ	92typ		
	POWER FACTOR	ACIN 120V	0.95typ							
	(lo=100%)	ACIN 230V	0.90typ							
	INRUSH CURRENT[A]	ACIN 120V	20typ (Io=100%) (At cold start) (Ta=25°C)							
	INHUSH CURRENT[A]	ACIN 230V	40typ (Io=100%) (At cold start) (Ta=25℃)							
	LEAKAGE CURREN	T[mA]	0.125/0.250max	(ACIN 120V/240V	60Hz,lo=100%, A	ccording to IEC60	0601-1)			
	VOLTAGE[V]		12	15	24	30	48	56		
		Forced air	41.7	33.4	21.0	16.7	10.5	9.0		
LINE I LOAD RIPPL OUTPUT RIPPLE	CURRENT[A]	Convection	9.2	7.4	4.6	3.7	2.3	1.9		
		conduction cooling	16.7	13.4	8.4	6.7	4.2	3.6		
	LINE REGULATION	mV1 *4	48max	60max	96max	120max	192max	192max		
	LOAD REGULATION		100max	120max	150max	180max	240max	240max		
		0 to +50°C	240max	240max	240max	300max	300max	400max		
	RIPPLE[mVp-p] *1	-20 - 0℃	320max	320max	320max	400max	400max	500max		
	DIDDLE MOIOEC M. T.	0 to +50°C	300max	300max	300max	480max	480max	500max		
	RIPPLE NOISE[mVp-p]*1	-20 - 0°C	360max	360max	360max	500max	500max	580max		
	TEMPERATURE REGULATION[mV]	0 to +50°C	120max	150max	240max	300max	480max	480max		
			150max	180max	290max	360max	600max	600max		
	DRIFT[mV] *2		48max	60max	96max	120max	192max	192max		
	START-UP TIME[ms]		500typ (ACIN 120V, Io=100%)							
	HOLD-UP TIME[ms]		16typ (ACIN 120V, Io=100%)							
	OUTPUT VOLTAGE ADJUSTMENT	RANGE[V]	10.80 to 13.20	13.50 to 16.50	21.60 to 26.40	27.00 to 31.50	43.20 to 52.80	52.00 to 56.00		
	OUTPUT VOLTAGE SETTING[V]		12.00 to 12.48	15.00 to 15.30	24.00 to 24.96	30.00 to 31.20	48.00 to 49.92	55.00 to 56.00		
	OVERCURRENT PROT	ECTION	Works over 105%	6 of rating and rec	overs automatical	lly				
PROTECTION	OVERVOLTAGE PROTEC	CTION[V]	13.80 to 16.80	17.25 to 21.00	27.60 to 33.60	34.50 to 42.00	55.20 to 67.20	60.00 to 69.00		
CIRCUIT AND	AUX1 (12V1A)		Optional							
OTHERS	AUX2 (5V1A)		Optional							
UITENS	REMOTE ON/OFF		Optional							
	PowerGood		Optional							
	INPUT-OUTPUT · RC	· AUX *7								
ISOLATION	INPUT-FG		AC2,000V 1minute, Cutoff current = 10mA, DC500V 50M Ω min (At Room Temperature) 1MOPP							
ISOLATION	OUTPUT · RC · AUX-		AC500V 1minute, Cutoff current = 25mA, DC500V 50M Ω min (At Room Temperature)							
	OUTPUT-RC · AUX	*7	product immate, catem carrent Lenni, becook contra imm (richtcom fomperature)							
	OPERATING TEMP., HUMID. AND									
ENVIRONMENT	STORAGE TEMP., HUMID. AND	ALTITUDE				n (30,000feet) ma				
E14411 (O141ME141	VIBRATION					es each along X, Y	and Z axis			
	IMPACT		196.1m/s ² (20G)	1m/s² (20G), 11ms, once each X, Y and Z axis						
SAFETY AND					950-1, CAN/CSA60601-1)	, EN62368-1, EN60601-1	3rd, Complies with DEN-	AN, IEC60601-1-2 4th Ed.		
NOISE	CONDUCTED NOISE					-B, EN55011-B, Ef	N55022-B			
REGULATIONS	HARMONIC ATTENU		Complies with IE	C61000-3-2 (class	S A) *5					
OTHERS	CASE SIZE/WEIGHT			m [3.0×1.4×5.0 i						
COOLING METHOD			Convection, Forc	ed air (Require ext	ternal fan), Condu	ction cooling				

- This is the value that measured on measuring board with capacitor of 22 $\mu\,F$ at 150mm from output terminal.
- Measured by 20MHz oscilloscope or Ripple-Noise meter (Equivalent to KEISOKU-GIKEN: RM103). *2 Drift is the change in DC output for an eight hour period after a half-hour warm-up at 25°C, with the input voltage held constant at the rated input/output.
- *3 Derating is required.
- *4 Please contact us about dynamic load and input response.

- Please contact us about another class.
- *6 Specification is changed at option, refer to Instruction Manual.
- Applicable when AUX and remote control (optional) is added.
- To meet the specifications. Do not operate over-loaded condition.
- Sound noise may be generated by power supply in case of pulse load Parallel operation is available with -P option. Refer to 5.1on the instruction manual.
- Forced air cooling is required to output up to MAX OUTPUT WATTAGE.



· Wattage 500W max · High Power density:24.1W/inch3


· High efficiency 92% typ (Input Voltage 230V,Output Voltage 24V)

· Conduction cooling 3"× 5 "standard footprint

· Fits 1U applications · Industrial and Medical safety approvals


With Remote On/Off (Optional) · Low leakage current · With AUX1 (12V), AUX2 (5V) (Optional) · No minimum load is required

Block diagram



External view

*External size of option J3 is different from standard model and refer to 6 Option and Others of instruction manual for details.



- ** Tolerance ±1 [±0.04]
- Weight: 420g maxThere is a total of four attachment holes

- Base Plate : Aluminum
 Dimensions in mm, []=inches
 Screw tightening torque : (TB501, 502) : 1.5N · m max
 Mounting toque : 0.6N · m max
 Avoid contact between TB501 and 502 wiring with mounting parts.
- Option : -J1 : (J.S.T) connector type. Refer to Instruction Manual 6.

	Con	nector	Mating connector	Terminal	Mfr	
Standard	CN101	A-41671-A03A197-2	00 50 9021	08-50-0105		
R3	CN101	A-410/1-AUSA19/-2	09-30-6031	08-65-0114		
no	CN501	087831-0820	51110-0851	50394-8051	Molex *	
J2R3	CN101	A-41671-A03A197-2	09-50-8031	08-50-0105 08-65-0114	moion -	
	CN501	087831-0841	51110-0860	50394-8051		
J3	CN101	S2P3-VH				
J1	CN101	B2P3-VH	VHR-3N	SVH-21T-P1.1	J.S.T.	
J1R3 CN101		DZF3-VII			J.S.1.	
JINJ	CN501	B8B-PHDSS	PHDR-08VS	SPHD-002T-P0.5		

*Please note the pin position No.1 is different from Molex.

FG		Mating connector	Terminal	Mfr
-	250 Series	-	170603-2	Tyco Electronics

<Pin Assignments>

<CN101>

Pin No.	Input
1	AC(L)
2	
3	AC(N)

<CN501(Optional)>

Pin No.	Function
1	AUX1 : AUX1 (12V1A)
2	AUX1G: AUX1 (GND)
3	RC : REMOTE ON/OFF
4	RCG : REMOTE ON/OFF (GND)
5	PG : Power good
6	PGG : Power good (GND)
7	AUX2 : AUX2 (5V1A)
8	AUX2G: AUX2 (GND)



CN501

Ordering information

GHA700F

GH A 700 F - - -





High voltage pulse noise type : EAP series Low leakage current type : EAM series

*A higher current rating EMI/EMC filter may be recommended in view of the other devices that could be connected in parallel with the power supply.

■ BF

This power supply is manufactured by SMD technology. The stress to P.C.B like twisting or bending causes the defect of the unit, please handle the unit with care *Make sure necessary tests will be carried out on your end equipment with the power supply installed in accordance with any required EMC/EMI regulations.

①Series name ②Single output ③Output wattage ④Universal input ⑤Output voltage ⑥Optional *1

C : with Coating E : IEC Class II R3: With Subfeatures (5VAUX, 12VAUX*, Remote, Power good) *Excluding GHA700F-12

T3 : mounting hole M3 U1 : can attach an external capacitor unit

Specification is changed at option, refer to Instruction manual.

MODEL		GHA700F-12-J1	GHA700F-24-J1	GHA700F-30-J1	GHA700F-48-J1	GHA700F-56-J1	
MAX OUTPUT WATTAGE[W]		650.4	700.8	699.0	700.8	700.0	
DC OUTPUT	Forced air	at 50°C	12V 54.2A	24V 29.2A	30V 23.3A	48V 14.6A	56V 12.5A
	Convection	at 30℃	12V 33.4A	24V 16.7A	30V 13.4A	48V 8.4A	56V 7.2A
	Convection	at 50℃	12V 22.2A	24V 11.1A	30V 8.9A	48V 5.6A	56V 4.8A
	conduction cooling	at 50°C	12V 33.4A	24V 16.7A	30V 13.4A	48V 8.4A	56V 7.2A

	MODEL		GHA700F-12-J1	GHA700F-24-J1	GHA700F-30-J1	GHA700F-48-J1	GHA700F-56-J1		
	VOLTAGE[VAC]					GIIA7001 -40-01	GIIA7001 -30-01		
	1 1	ACIN 115V	85 - 264 1 φ (Refer to "Derating" and Instruction Manual 1.1)						
	CURRENT[A]	ACIN 115V	7.0typ						
	FREQUENCY[Hz]	ACIN 230V	3.5typ						
	FREQUENCT[HZ]		94.0typ (Po=400W) 94.0typ (Po=400W) 94.0typ (Po=400W) 94.0typ (Po=400W) 94.0typ (Po=400W)						
		ACIN 115V					71 \		
	EFFICIENCY[%]			93.0typ (Po=700W)			93.0typ (Po=700W)		
INPUT		ACIN 230V			96.0typ (Po=400W)		96.0typ (Po=400W)		
				95.5typ (P0=700W)	95.5typ (Po=700W)	95.5typ (P0=700W)	95.5typ (Po=700W)		
	POWER FACTOR	ACIN 115V							
	(Po=700W)			· · · · · · · · · · · · · · · · · · ·	-0-1				
	INRUSH CURRENT[A]	ACIN 115V	20typ (At rated load)	(At cold start) (Ta=25	5°C)				
				(At cold start) (Ta=25					
					ed load, According to				
	TOUCH CURRENT[ι A]			According to IEC60601				
	VOLTAGE[VAC]		12	24	30	48	56		
-		Forced air		29.2	23.3	14.6	12.5		
	CURRENT[A]	Convection	33.4	16.7	13.4	8.4	7.2		
		conduction cooling	33.4	16.7	13.4	8.4	7.2		
	LINE REGULATION[mV] *3	48max	96max	120max	192max	192max		
	LOAD REGULATION	[mV] *3 *9	100max	150max	180max	240max	240max		
	RIPPLE[mVp-p]	0 to +50°C	240max	300max	350max	550max	600max		
	*4 *10	-20°C to +0°C	320max	400max	500max	700max	750max		
OUTPUT	RIPPLE NOISE[mVp-p]		300max	400max	450max	650max	700max		
	*4 *10		360max	500max	600max	800max	850max		
			120max	240max	300max	480max	600max		
	TEMPERATURE REGULATION[mV]		150max	290max	360max	600max	720max		
	DRIFT[mV]	*5		96max	120max	192max	192max		
	START-UP TIME[ms]		500typ (ACIN 115V,		TZOTTUX	TOZITION	ΤΟΣΠΙάλ		
	HOLD-UP TIME[ms]		12typ (ACIN 115V, A						
	OUTPUT VOLTAGE ADJUSTMEN	IT DANCEIVI		22.80 to 26.40	28.50 to 33.00	45.60 to 52.80	53.20 to 61.60		
	OUTPUT VOLTAGE SE			24.00 to 24.96	30.00 to 31.20	48.00 to 49.92	56.00 to 58.24		
	OVERCHIRDENT DROT	ECTION	Marks over 105% of	rating and recovers a		40.00 10 49.92	30.00 10 30.24		
	OVERVOLTAGE PROTEC			27.60 to 33.60	34.50 to 42.00	55.20 to 67.20	64.40 to 78.40		
PROTECTION		TION[V]					04.40 10 70.40		
CIRCUIT AND	AUX1 (12V1A)		Optional (Refer to Instruction Manual 6.1) (Excluding GHA700F-12)						
OTHERS	AUX2 (5V1A)		Optional (Refer to Instruction Manual 6.1)						
	REMOTE ON/OFF		Optional (Refer to Instruction Manual 6.1) Optional (Refer to Instruction Manual 6.1)						
	POWER GOOD				D05001/50110		\ 0110DD		
	INPUT-OUTPUT · RC	AUX *7							
SOLATION	INPUT-FG		AC2,000V 1minute, Cutoff current = 10mA, DC500V 50MΩ min (At Room Temperature) 1MOPP						
	OUTPUT · RC · AUX-								
	OUTPUT-RC · AUX	*7	Treesest trimitate, eaten carrent zernin, zeesest centra trimit (richteem temperature)						
	OPERATING TEMP., HUMID. AND								
ENVIRONMENT	STORAGE TEMP., HUMID. AND	ALTITUDE	-30 to +80°C, 20 - 90%RH (Non condensing), 9,000m (30,000feet) max 10 - 55Hz, 19.6m/s² (2G), 3minutes period, 60minutes each along X, Y and Z axis						
	VIBRATION					ng X, Y and Z axis			
	IMPACT			ms, once each X, Y ar					
					C III)	,	EN62368-1, EN60601-1 3rd		
	I		Complies with FCC-B, VCCI-B, CISPR32-B, EN55011-B, EN55032-B						
NOISE	CONDUCTED NOISE		Complies with FCC-E	Complies with IEC61000-3-2 (class A)					
SAFETY AND NOISE REGULATIONS	CONDUCTED NOISE				, EN55011-B, EN5503	Z-D			
NOISE		IATOR *8	Complies with IEC61			Z-D			




- The listed options may affect the published standard specifications. Please contact us for detailed product specification. The current of input surge to a built-in EMI/EMIS Filter (0.2 ms or less) is excluded. In the case of dynamic fluctuations, the specifications may not be met. This is the value measured on measuring board with capacitor of 22 μ F and 0.1 μ F within 150mm from output terminal. Measured by 20MHz Oscilloscope or Rippie-Noise meter (KEISOKU-GIKEN:RM-104). Drit is the change in DC output for an eight hours period after a half-hour warm-up at 25°C, with the input voltage held constant at the rated input/output. The output is shut down when the overcurrent protection continues.


- Applicable when AUX and remote control (optional) is added. Please contact us about another class. The value at Ta=-20°C to +50°C. The value at rated load. To meet the specifications. Do not operate over-loaded condition. Parallel operation is not possible. Sound noise may be generated by power supply in case of pulse load. Forced air cooling is required to output up to MAX OUTPUT WATTAGE.

- · Wattage 700W max
- · High efficiency 96% typ (Input Voltage 230V, Output Voltage 24V)
- · 3"×5"standard footprint
- · Industrial and Medical safety approvals (Suitable for BF application)
- · With Remote On/Off (Optional)
- · Isolated dual AUX (AUX1 12V 1A, AUX2 5V 1A) (Optional)
- · High Power density:31.1W/inch3
- · Conduction cooling
- · Fits 1U applications
- Low leakage current
- · Complies with EN61558-2-16 (OVC III)
- Conformal coating (Optional)

Block diagram



External view



- ** Tolerance ±1 [±0.04]
- * Weight : 570g max
- ※ PCB Material / thickness : FR-4 / 1.7mm [0.07]
- Chassis Material : Aluminum
- ※ Dimensions in mm, []=inches
- Screw tightening torque : (TB501, 502) : M4 1.5N · m max
 Mounting torque : M3 0.6N · m max
- ※ Avoid contact between TB501 and 502 wiring with mounting parts.
- % The locations of the output capacitor depend on the model.

Co	nnector	Mating connector	Terminal	Mfr
CN1 B3P5-VH		VHR-5N	SVH-21T-P1.1 SVH-41T-P1.1	J.S.T.
CN2 *	B8B-PHDSS	PHDR-08VS	SPHD-001T-P0.5 SPHD-002T-P0.5	J.S.I.

*Option: R3 or U1

<CN1>

Pin No.	Input
1	FG
2	
3	AC(N)
4	
3	AC(L)

*Pin No.2 and 4 is NC at CN1

<CN2 (Option: R3)>

10112 (U	CONZ (Option: 110)>				
Pin No.	Function				
1	AUX1 : AUX1 (12V1A) *1				
2	AUX1G: AUX1 (GND) *1				
3	RC : REMOTE ON/OFF				
4	RCG : REMOTE ON/OFF (GND)				
5	PG : Power good				
6	PGG : Power good (GND)				
7	AUX2 : AUX2 (5V1A)				
8	AUX2G: AUX2 (GND)				

*Please refer to instruction manual for the pin assignments of the option U1

*1 In case of GHA700F-12, N.C.



GHA300F-SNF

A 300



Example recommended EMI/EMC filter EAC-10-472



High voltage pulse noise type : EAP series Low leakage current type : EAM series

*A higher current rating EMI/EMC filter may be recommended in view of the other devices that could be connected in parallel with the power supply.

- ①Series name ②Single output ③Output wattage ④Universal input ⑤Output voltage ⑥Optional *6
- J1: CN501
- PHconnector type(J.S.T.)

: CN501 Friction locks connector type (Molex)

Refer to the instruction manual 6.1.

*Make sure necessary tests will be carried out on your end equipment with the power supply installed in accordance with any required EMC/EMI regulations.

MODEL		GHA300F-12-SNF GHA300F-24-SNF		GHA300F-48-SNF
MAX OUTPUT WATTAGE[W]		300	300	302.4
DC OUTPUT	Forced air +50°C	12V 25.0A	24V 12.5A	48V 6.3A

	MODEL		GHA300F-12-SNF	GHA300F-24-SNF	GHA300F-48-SNF		
	VOLTAGE[V]		AC90 - 264 1 ϕ (output derating is	required at AC90V -115V *3)			
	CURRENT[A]	ACIN 120V	31				
	ACIN 230V						
	FREQUENCY[Hz]		50 / 60 (47 - 63)				
	EFFICIENCY[%]	ACIN 120V		89typ	89typ		
NPUT		ACIN 230V	31	91typ	91typ		
			0.95typ				
	(lo=100%)						
	INRUSH CURRENT[A]		20typ (lo=100%) (At cold start) (Ta				
			40typ (lo=100%) (At cold start) (Table 100%)		2001 ()		
	LEAKAGE CURREN	Γ[mA]	0.125/0.250max (ACIN 120V/240V				
	VOLTAGE[V]		12	24	48		
		Forced air		12.5	6.3		
}	LINE REGULATION		48max	96max	192max		
-	LOAD REGULATION			150max	240max		
	RIPPLE[mVp-p] *1		240max 320max	240max 320max	300max 400max		
ŀ			300max	300max	480max		
ОИТРИТ	RIPPLE NOISE[mVp-p]*1		360max	360max	500max		
			120max	240max	480max		
	TEMPERATURE REGULATION[mV]		150max	290max	600max		
-	DRIFT[mV]	*2		96max	192max		
-	START-UP TIME[ms]		500typ (ACIN 120V, Io=100%)				
	HOLD-UP TIME[ms]		16typ (ACIN 120V, Io=100%)				
	OUTPUT VOLTAGE ADJUSTMENT RANGE[V]		10.80 to 13.20	21.60 to 26.40	43.20 to 52.80		
ŀ	OUTPUT VOLTAGE ADJOSTIMENT HANGE[V]		12.00 to 12.48	24.00 to 24.96	48.00 to 49.92		
	OVERCURRENT PROT		Works over 105% of rating and recovers automatically *7				
İ	OVERVOLTAGE PROTEC		13.80 to 16.80	27.60 to 33.60	55.20 to 67.20		
ROTECTION	AUX1		10V 0.5A	1 = 1 = 1 = 1 = 1 = 1 = 1	7 3 3 3 3 3 3 3 3 3 3 3 3 3 3 3 3 3 3 3		
RCUIT AND	AUX2		5V 1A				
	REMOTE ON/OFF		Possible, AUX2 is available				
İ	PowerGood		Open collector				
İ	INPUT-OUTPUT · RC	AUX	AC4,000V 1minute, Cutoff current = 10mA, DC500V 50M Ω min (At Room Temperature) 2MOPP				
COL ATION	INPUT-FG		AC2,000V 1minute, Cutoff current = 10mA, DC500V 50MΩ min (At Room Temperature) 1MOPP				
SOLATION	OUTPUT · RC · AUX-	FG	AC500V 1minute, Cutoff current = 25mA, DC500V 50M Ω min (At Room Temperature)				
	OUTPUT-RC · AUX		AC500V 1minute, Cutoff current = 25mA, DC500V 50MΩ min (At Room Temperature)				
	OPERATING TEMP., HUMID. AND	ALTITUDE					
	STORAGE TEMP., HUMID. AND	ALTITUDE	-30 to +75°C, 20 - 90%RH (Non condensing), 9,000m (30,000feet) max				
INVIRONMENT	VIBRATION		10 - 55Hz, 19.6m/s² (2G), 3minutes period, 60minutes each along X, Y and Z axis				
	IMPACT		196.1m/s² (20G), 11ms, once each X, Y and Z axis				
AFETY AND	AGENCY APPROVAL	S			601-1), EN62368-1, EN60601-1 3rd		
IOISE			Complies with DEN-AN, IEC60601-				
EGULATIONS	CONDUCTED NOISE			PR11-B, CISPR22-B, EN55011-B, E	N55022-B		
	HARMONIC ATTENU		Complies with IEC61000-3-2 (class				
OTHERS	CASE SIZE/WEIGHT		85.2×41×165.3mm [3.35×1.61×	6.5 inches] (W×H×D) / 620g max			
	COOLING METHOD		Forced air				


- *1 This is the value that measured on measuring board with capacitor of 22 µF at 150mm from output terminal.
- Measured by 20MHz oscilloscope or Ripple-Noise meter (Equivalent to KEISOKU-GIKEN: RM103).
- *2 Drift is the change in DC output for an eight hour period after a half-hour warm-up at 25°C, with the input voltage held constant at the rated input/output.
- *3 Refer to "Derating".
- *4 Please contact us about dynamic load and input response

- Please contact us about another class.
- *6 Specification is changed at option, refer to Instruction Manual.
- When output current more than rated, output will shut down after 5 seconds or more, Recycle input after 3 minutes to reset the protection.
- To meet the specifications. Do not operate over-loaded condition.
- Sound noise may be generated by power supply in case of pulse load.




- · Full packaged design united with GHA's features and additional robastness.
- · High efficiency 91% typ (Input voltage 230V,Output voltage 24V)
- · Optical for 1U applications
- · Medical and Industrial safety approvals
- · Low leakage current
- · Conformal coating
- · Single remote ON/OFF control for DC output, AUX1 and Fan.
- · Isolated dual AUX (AUX1 10V 0.5A, AUX2 5V 1A)

Block diagram



External view



- X Tolerance ±1 [±0.04]
- Weight: 620g max
- W Upper PCB Material/thickness: FR-4/1.6mm
- * Lower PCB Material/thickness : FR-4/1.6mm
- * Chassis Material/thickness : Aluminum/1.5mm
- Cover Material/thickness : Aluminum/1.2mm
- Fan cover Material : PBTMounting torque : 1.5N · m (14.7kgf · cm) max
- Screw tightening torque M4 : 1.6N ⋅ m (16.9kgf ⋅ cm) max
- ※ Dimensions in mm, []=inches



M4

CN501

<CN501 mating connector and terminal>

FG

AC(N)

AC(L)

101100	Cortoo mating commenter and terminals								
Co	nnector	Mating connector	Terminal	Mfr					
SNF	087833-6320	51110-0851	50394-8051	Molex *					
SNFJ1	SNFJ1 S8B-PHDSS PHDR-08VS S		SPHD-002T-P0.5	J.S.T.					
SNFJ2	087833-0831	51110-0860	50394-8051	Molex *					

*Please note the pin position No.1 is different from Molex.

<CN501>

Pin No.	Function
1	AUX1 : AUX1 (10V0.5A)
2	AUX1G: AUX1 (GND)
3	RC : REMOTE ON/OFF
4	RCG : REMOTE ON/OFF (GND)
5	PG : Power good
6	PGG : Power good (GND)
7	AUX2 : AUX2 (5V1A)
8	AUX2G: AUX2 (GND)

CHARGE 40 ONE CHARGOE 45 ONE CHARGOE 04 ONE CHARGOE 00 ONE CHARGOE 40 ONE CHARGOE 50 ONE

GHA500F-SNF

500





High voltage pulse noise type : EAP series Low leakage current type : EAM series

*A higher current rating EMI/EMC filter may be recommended in view of the other devices that could be connected in parallel with the power supply.

①Series name ②Single output ③Output wattage ④Universal input ⑤Output voltage ⑥Optional *6

J1: CN501 PHconnector type(J.S.T.)

J2 : CN501 Friction locks connector

type (Molex)
: Parallel Operation

Refer to the instruction manual

*Make sure necessary tests will be carried out on your end equipment with the power supply installed in accordance with any required EMC/EMI regulations.

MODEL		GHA500F-12-SNF	GHA500F-15-SNF	GHA500F-24-SNF	GHA500F-30-SNF	GHA500F-48-SNF	GHA500F-56-SNF
MAX OUTPUT WATTAGE[W]		450	501	504	501	504	504
DC OUTPUT	Forced air +50°C	12V 37.5A	15V 33.4A	24V 21.0A	30V 16.7A	48V 10.5A	56V 9.0A

	MODEL		GHA500F-12-SNF	GHA500F-15-SNF	GHA500F-24-SNF	GHA500F-30-SNF	GHA500F-48-SNF	GHA500F-56-SNF			
	VOLTAGE[V]		AC90 - 264 1 ϕ (output derating is required at AC90V -115V *3)								
INPUT	CURRENT[A]	ACIN 120V	4.8typ	5.4typ							
	CORRENT[A]	ACIN 230V	2.6typ	2.9typ							
	FREQUENCY[Hz]		50 / 60 (47 - 63)								
	EFFICIENCY[%]	ACIN 120V	87typ	89typ	89typ	89typ	89typ	89typ			
	EFFICIENCY[%]	ACIN 230V	89typ	91typ	91typ	91typ	91typ	91typ			
	POWER FACTOR		0.95typ								
	(lo=100%)	ACIN 230V									
	INRUSH CURRENT[A]	ACIN 120V									
		ACIN 230V	1 - 31 (/ (-))))))))))))))))								
	LEAKAGE CURRENT[mA]		0.125/0.250max (ACIN 120V/240V 60Hz,Io=100%, According to IEC60601-1)								
	VOLTAGE[V]	,	12	15	24	30	48	56			
	CURRENT[A]	Forced air		33.4	21.0	16.7	10.5	9.0			
			48max	60max	96max	120max	192max	192max			
	LOAD REGULATION			120max	150max	180max	240max	240max			
	RIPPLE[mVp-p] *1		240max	240max	240max	300max	300max	400max			
			320max	320max	320max	400max	400max	500max			
	RIPPLE NOISE[mVp-p]*1		300max	300max	300max	480max	480max	500max			
OUTPUT	[360max	360max	360max	500max	500max	580max			
	TEMPERATURE REGULATION[mV]		120max	150max	240max	300max	480max	480max			
	DDIET:\a		150max	180max	290max	360max	600max	600max			
	DRIFT[mV] *2		TOTAL TOTAL								
	START-UP TIME[ms] HOLD-UP TIME[ms]		500typ (ACIN 120V, Io=100%) 16typ (ACIN 120V, Io=100%)								
	OUTPUT VOLTAGE ADJUSTMENT RANGE[V]		10.80 to 13.20	13.50 to 16.50	21.60 to 26.40	27.00 to 31.50	43.20 to 52.80	52.00 to 56.00			
	OUTPUT VOLTAGE SETTING[V]		12.00 to 12.48	15.00 to 15.30	24.00 to 24.96	30.00 to 31.20	48.00 to 49.92	55.00 to 56.00			
	OVERCURRENT PROTECTION		Works over 105% of rating and recovers automatically \$7								
	OVERVOLTAGE PROTECTIONIVI		13.80 to 16.80	17.25 to 21.00	27.60 to 33.60	34.50 to 42.00	55.20 to 67.20	60.00 to 69.00			
PROTECTION	ALIY1		12V 0.5A	17.120 to 2.1100	27.00 10 00.00	0 1100 10 12100	100.20 10 07.20	100.00 10 00.00			
CIRCUIT AND	AUX2		5V 1A								
OTHERS	REMOTE ON/OFF		Possible, AUX2 is available								
	PowerGood		Open collector								
	INPUT-OUTPUT · RC · AUX		AC4,000V 1minute, Cutoff current = 10mA, DC500V 50M Ω min (At Room Temperature) 2MOPP								
ISOLATION	INPUT-FG		AC2,000V 1minute, Cutoff current = 10mA, DC500V 50MΩ min (At Room Temperature) 1MOPP								
ISOLATION	OUTPUT · RC · AUX-	FG	AC500V 1minute, Cutoff current = 25mA, DC500V 50M Ω min (At Room Temperature)								
	OUTPUT-RC · AUX		AC500V 1 minute, Cutoff current = 25 mA, DC500V 50 M Ω min (At Room Temperature)								
	OPERATING TEMP., HUMID. AND ALTITUDE										
ENVIRONMENT			-30 to +80°C, 20 - 90%RH (Non condensing), 9,000m (30,000feet) max								
LITTINONIENT	VIBRATION		10 - 55Hz, 19.6m/s² (2G), 3minutes period, 60minutes each along X, Y and Z axis								
	IMPACT		196.1m/s² (20G), 11ms, once each X, Y and Z axis								
SAFETY AND	AGENCY APPROVALS		UL60950-1, ANSI/AAMI ES60601-1, C-UL(CSA60950-1, CAN/CSA60601-1), EN62368-1, EN60601-1 3rd,								
NOISE			Complies with DEN-AN, IEC60601-1-2 4th Ed.								
REGULATIONS	CONDUCTED NOISE		Complies with FCC-B, VCCI-B, CISPR11-B, CISPR22-B, EN55011-B, EN55022-B								
	HARMONIC ATTENU		Complies with IEC61000-3-2 (class A) *5								
OTHERS	CASE SIZE/WEIGHT		85.2×41×165.3mm [3.35×1.61×6.5 inches] (W×H×D) / 660g max								
	COOLING METHOD		Forced air								


- This is the value that measured on measuring board with capacitor of 22 $\mu\,F$ at 150mm from output terminal.
- Measured by 20MHz oscilloscope or Ripple-Noise meter (Equivalent to KEISOKU-GIKEN: RM103). *2 Drift is the change in DC output for an eight hour period after a half-hour warm-up at 25°C, with the input voltage held constant at the rated input/output.
- *3 Refer to "Derating".
- *4 Please contact us about dynamic load and input response

- Please contact us about another class.
- Specification is changed at option, refer to Instruction Manual.
- When output current more than rated, output will shut down after 5 seconds or more, Recycle input after 3 minutes to reset the protection.
- To meet the specifications. Do not operate over-loaded condition.
- Sound noise may be generated by power supply in case of pulse load.
- Parallel operation is available with -P option. Refer to 5.1on the instruction manual.




- · Full packaged design united with GHA's features, and additional robustness..
- · High efficiency 91% typ (Input voltage 230V,Output voltage 24V)
- · 50% minimized size compares with previous products.
- · Optical for 1U applications
- · Medical and Industrial safety approvals
- · Low leakage current
- · Conformal coating
- · Single remote ON/OFF control for DC output, AUX1 and Fan.
- · Isolated dual AUX (AUX1 12V 0.5A, AUX2 5V 1A)


Block diagram



External view



- X Tolerance ±1 [±0.04]
- Weight: 660g max
 Word PCB Material/thickness: FR-4/1.6mm
- X Lower PCB Material/thickness : AL/1.5mm
- Chassis Material/thickness : Aluminum/1.5mm X Cover Material/thickness: Aluminum/1.2mm
- ※ Fan cover Material : PBT
- Mounting torque: 1.5N ⋅ m (14.7kgf ⋅ cm) max
- ※ Screw tightening torque M4: 1.6N ⋅ m (16.9kgf ⋅ cm) max
- ※ Dimensions in mm, []=inches



Pin No.	Function
1	AUX1 : AUX1 (12V0.5A)
2	AUX1G: AUX1 (GND)
3	RC : REMOTE ON/OFF
4	RCG : REMOTE ON/OFF (GND)
5	PG : Power good
6	PGG : Power good (GND)
7	AUX2 : AUX2 (5V1A)
8	AUX2G: AUX2 (GND)

<CN501 mating connector and terminal>

FG

AC(N)

AC(L)

	Cortoo Finating Commoder and torrinials								
	Co	nnector	Mating connector	Terminal	Mfr				
SI	NF	087833-6320	51110-0851	50394-8051	Molex *				
SI	NFJ1	S8B-PHDSS	PHDR-08VS	SPHD-002T-P0.5	J.S.T.				
SI	NFJ2	087833-0831	51110-0860	50394-8051	Molex *				

*Please note the pin position No.1 is different from Molex.


CN501



Assembling and Installation Method

GHA300/500F

■Mounting method




GHA700F


■Mounting method















(F)


CN101

- ■AC voltage exist on the primary side therefore. In order to prevent electric shock, or to meet the leakage current requirements of the safety standard, you need to ensure the proper insolation distance.
- ■During use, keep the distance between d1 & d2 for to insulate between lead of component and metal chassis, use the spacer of 5mm or more between d2. If it is less than d1 & d2, insert the insulation sheet between power supply and metal chassis.


GHA300F



GHA500F



GHA700F





Case

Assembling and Installation Method

Remarks:


There is a possibility that it is not possible to cool enough when the power supply is used by the sealing up space as showing in right figure.

GHA300/500F-SNF

■Mounting screw

Screw length into power supply should be shorter than 6mm due to keep safety isolation clearance from inside components in right figure. Please fix power supply surely by screws in consideration of the weight.


- ■A cooling FAN is built-in. Please keep 30mm or more clearance both input and output side to make enough air ventilation. Do not block off cooling FAN's air flow for stable operation.
- ■When power supply is used where dust exist, it may cause of FAN failure. It is recommended to install a air filter to the system air ventilation duct.



Mounting screw


- ■The mounting screw should be M3. The hatched area shows the allowance of metal parts for mounting.
- ■If metallic fittings are used on the component side of the board, ensure there is no contact with surface mounted components.
- ■This product uses SMD technology. Please avoid the PCB installation method which includes the twisting stress or the bending stress.

GHA300/500F



GHA700F

*****The center of ϕ 7mm is the same point as the center of the mounting hole.




Derating

■Cooling method


Conduction cooling, forced air and convection cooling are available for GHA500F and GHA700F. Both Forced air and convection cooling are available for GHA300F. Please see instruction manual 3 for details. Please make sure the maximum component temperature rise given in instruction manual 3 is not exceeded.

GHA300/500F



*For maximum power in each cooling method, please apply.


GHA700F



*For maximum power in each cooling method, please apply.


Derating

GHA500F Ambient temperature derating curve at forced air (Reference value)




For the derating curves of other heat dissipation methods, see instruction manual 3.

*1 The maximum output power by wind speed conditions (Reference value)




GHA300F Ambient temperature derating curve at forced air (Reference value)




*For the derating curves of other heat dissipation methods, see instruction manual 3.

GHA300/500F-SNF Ambient temperature derating curve (Reference value)




GHA700F Ambient temperature derating curve at forced air (Reference value)



*For the derating curves of other heat dissipation methods, see instruction manual 3.

*1 The maximum output power by wind speed conditions (Reference value)





Instruction Manual

◆ It is necessary to read the "Instruction Manual" and "Before using our product" before you use our product.

Instruction Manual https://www.cosel.co.jp/redirect/catalog/en/GHA/ Before using our product https://en.cosel.co.jp/technical/caution/index.html





Basic Characteristics Data

Model	Circuit method	Switching frequency [kHz]	Input current *1 [A]	Inrush current protection	PCB/Pattern			Series/Parallel operation availability	
iviodei	Circuit method				Material	Single sided	Double sided	Series operation	Parallel operation
GHA300F	boost chopper	60 - 220	3.3	Thermistor	FR-4	_	Yes	Yes	No
	LLC resonant converters	90 - 180	3.3						
GHA500F	boost chopper	60 - 220	5.4	Thermistor	Aluminum/FR-4	Yes	Yes	Yes	*2
	LLC resonant converters	90 - 180	3.4						
GHA700F	boost chopper	55 - 75	6.3	Thermistor	FR-4	_	Yes	Yes	No
	LLC resonant converters	45 - 370	0.5						
GHA300F-SNF	boost chopper	60 - 220	3.3	Thermistor	FR-4	Yes	Yes	Yes	No
	LLC resonant converters	90 - 180	3.3						
GHA500F-SNF	boost chopper	60 - 220	5.4	Thermistor	Aluminum/FR-4	Yes	Yes	Yes	*2
	LLC resonant converters	90 - 180	J.4						

^{*1} The value of input current is at ACIN 120V and rated load.

^{*2} Parallel operation is available with -P option. Refer to 6.1on the instruction manual.