

MANUFACTURER'S DECLARATION

This declaration is to certify that the enclosure products described below, manufactured by Fibox Oy Ab, Finland, conform to the following product characteristics and standards.

Fibox ARCA IEC

Materials used:

| | |
|-------------|-----------------------------|
| Base | Polycarbonate, PC, RAL 7035 |
| Grey door | Polycarbonate, PC, RAL 7035 |
| Glazed door | Polycarbonate, clear |
| Gasket | Polyurethane, PUR |

Product characteristics

Ingress Protection: IP 66 (EN/IEC 60529)
Impact strength:

Gray door: IK10 +35 °C / IK09 -25 °C (EN/IEC 62262)
Glazed door: IK08 +35 °C / IK09 -25 °C (EN/IEC 62262)

Mechanical strength: 6J (EN 61439-4)

Material Flammability Rating Base UL 94-5V

Glow Wire Test 960°C

Temperature range

In continuous use -40°C - +80°C
Short term use -40°C - +120°C

Static loads

Mounting plate 2 kg/dm²
Mounting rail 10 kg/rail, max 30 kg/cabinet
Door 10 kg

Totally insulated

Halogen free compliance (DIN/VDE 0472, Part 815)

The products fulfils the essential safety requirements for CE conformity marking according to the Low voltage Directive (2006/95/EC)

Nominal voltage up to 1000 V AC and 1500 V DC

The products conforms to the standards:

EN/IEC 62208, Empty enclosures for low-voltage switchgear and controlgear assemblies

EN/IEC 61439-1, EN/IEC 61439-4, Low-voltage switchgear and controlgear assemblies

UL 508A Industrial control panels



Pawel Wielinski
Director, Product Management