

Absolute encoders – multitrurn

Compact electronic multitrurn, magnetic	Sendix M3668 / M3688 (shaft / hollow shaft)	IO-Link
--	--	----------------



The Sendix M36 with Energy Harvesting Technology is an electronic multitrurn encoder in compact design, without gear and without battery. It is characterized by robustness, reliability and cost-efficiency.

With Smart Sensor Profile for easy and fast integration into the application.



Safety-Lock™	High rotational speed	Temperature range	High protection level	High shaft load capacity	Shock / vibration resistant	Reverse polarity protection	Surface protection salt spray-tested optional	Energy Harvesting

Reliable and insensitive

- Sturdy bearing construction in Safety-Lock™ design for resistance against vibration and installation errors.
- Reduced number of components ensures magnetic insensitivity.
- IP67 protection and wide temperature range -40°C ... +85°C.
- Without gear and without battery, thanks to the Energy Harvesting technology.

Up-to-the-minute performance


- Operation possible with any IO-Link master.
- Point-to-point communication in automation networks.
- Use of cost-effective unshielded cables possible.
- Automatic saving of device parameters.
- Firmware update via IO-Link.

Order code	8.M3668	. XX 4 X . 41 X 2	If for each parameter of an encoder the underlined preferred option is selected, then the delivery time will be 10 working days for a maximum of 10 pieces. Qts. up to 50 pcs. of these types generally have a delivery time of 15 working days.	10 by 10						
Shaft version	Type	<table border="1" style="width: 100%; text-align: center;"> <tr> <td style="width: 10%;">a</td> <td style="width: 10%;">b</td> <td style="width: 10%;">c</td> <td style="width: 10%;">d</td> <td style="width: 10%;">e</td> <td style="width: 10%;">f</td> </tr> </table>	a	b	c	d	e	f		
a	b	c	d	e	f					
a Flange	1 = clamping flange, IP67, ø 36 mm [1.42"] 3 = clamping flange, IP65, ø 36 mm [1.42"] 2 = synchro flange, IP67, ø 36 mm [1.42"] <u>4 = synchro flange, IP65, ø 36 mm [1.42"]</u>	c Interface / power supply	<u>4 = IO-Link / 18 ... 30 V DC</u>	f Profile	<u>2 = Standard Profile</u> ¹⁾ 3 = Smart Sensor Profile ²⁾					
b Shaft (ø x L), with flat	1 = ø 6 x 12.5 mm [0.24 x 0.49"] <u>3 = ø 8 x 15 mm [0.32 x 0.59"]</u> 5 = ø 10 x 20 mm [0.39 x 0.79"] 2 = ø 1/4" x 12.5 mm [0.49"]	d Type of connection	3 = axial M12 connector, 4-pin <u>4 = radial M12 connector, 4-pin</u>	Optional on request	- Ex 2/22 - surface protection salt spray tested					
		e Fieldbus profile	<u>41 = IO-Link</u>							

Order code	8.M3688	. XX 4 X . 41 X 2	If for each parameter of an encoder the underlined preferred option is selected, then the delivery time will be 10 working days for a maximum of 10 pieces. Qts. up to 50 pcs. of these types generally have a delivery time of 15 working days.	10 by 10						
Hollow shaft	Type	<table border="1" style="width: 100%; text-align: center;"> <tr> <td style="width: 10%;">a</td> <td style="width: 10%;">b</td> <td style="width: 10%;">c</td> <td style="width: 10%;">d</td> <td style="width: 10%;">e</td> <td style="width: 10%;">f</td> </tr> </table>	a	b	c	d	e	f		
a	b	c	d	e	f					
a Flange	<u>2 = with stator coupling, IP65, ø 46 mm [1.81"]</u> 3 = with spring element, long, IP65 5 = with stator coupling, IP67, ø 46 mm [1.81"] 6 = with spring element, long, IP67	c Interface / power supply	<u>4 = IO-Link / 18 ... 30 V DC</u>	f Profile	<u>2 = Standard Profile</u> ¹⁾ 3 = Smart Sensor Profile ²⁾					
b Blind hollow shaft (insertion depth max. 18.5 mm [0.73"])	1 = ø 6 mm [0.24"] 3 = ø 8 mm [0.32"] <u>4 = ø 10 mm [0.39"]</u> 2 = ø 1/4"	d Type of connection	3 = axial M12 connector, 4-pin <u>4 = radial M12 connector, 4-pin</u>	Optional on request	- Ex 2/22 - surface protection salt spray tested					
		e Fieldbus profile	<u>41 = IO-Link</u>							

1) Delivered with default setting for Standard Profile (switchable to Smart Sensor Profile).
2) Delivered with default setting for Smart Sensor Profile (switchable to Standard Profile).

Absolute encoders – multiturn

Compact electronic multiturn, magnetic	Sendix M3668 / M3688 (shaft / hollow shaft)	IO-Link
Mounting accessory for shaft encoders		Order no.
Coupling	Bellows coupling \varnothing 19 mm [0.75"] for shaft 8 mm [0.32"]	8.0000.1102.0808
Mounting accessory for hollow shaft encoders		Order no.
Cylindrical pin, long for flange with spring element (flange type 3 + 6)	with fixing thread 	8.0010.4700.0000
Connection technology		Order no.
Cordset, pre-assembled	M12 female connector with coupling nut, 4-pin, A coded, straight single-ended 2 m [6.56'] PUR cable	05.00.6061.6211.002M
Connector, self-assembly	M12 female connector with coupling nut, 4-pin, A coded, straight	05.B8141-0

Further accessories can be found in the accessories section or in the accessories area of our website at: kuebler.com/accessories.
Additional connectors can be found in the connection technology section or in the connection technology area of our website at: kuebler.com/connection_technology.

Technical data

Mechanical characteristics		
Maximum speed		
shaft or blind hollow shaft version without shaft seal (IP65)		6000 min ⁻¹ 3000 min ⁻¹ (continuous)
shaft or blind hollow shaft version with shaft seal (IP67)		4000 min ⁻¹ 2000 min ⁻¹ (continuous)
Starting torque at 20°C [68°F]		
without shaft seal		< 0.007 Nm
with shaft seal (IP67)		< 0.01 Nm
Shaft load capacity	radial axial	40 N 20 N
Weight		approx. 0.2 kg [7.06 oz]
Protection acc. to EN 60529		IP65 or IP67
Working temperature range		-40°C ... +85°C [-40°F ... +185°F]
Materials	shaft / hollow shaft flange housing	stainless steel aluminum zinc die-cast
Shock resistance acc. to EN 60068-2-27		2500 m/s ² , 6 ms
Vibration resistance acc. to EN 60068-2-6		300 m/s ² , 10 ... 2000 Hz

Interface characteristics IO-Link	
Resolution singleturn	1 ... 16.384 (14 bit), scalable default: 16.384 (14 bit)
Absolute accuracy ¹⁾	±1°
Repeat accuracy	±0,2°
Number of revolutions (multiturn)	1 ... 262.144 (18 bit), scalable only via the total resolution default: 262.144 (18 bit)
Total resolution	4 ... 4.294.967.296 (32 bit), scalable default: 4.294.967.296 (32 bit)
Interface	IO-Link version 1.1 acc. to IEC 61131-9
Profile (details see manual)	Kübler Standard Profile or Smart Sensor Profile
Port classe	Type A

Electrical characteristics	
Power supply	18 ... 30 V DC
Current consumption (no load)	max. 30 mA
Reverse polarity protection of the power supply	ja
UL approval	file no. E224618
CE compliant acc. to	EMC guideline 2014/30/EU RoHS guideline 2011/65/EU

1) Over the whole temperature range.


Absolute encoders – multiturn

Compact electronic multiturn, magnetic	Sendix M3668 / M3688 (shaft / hollow shaft)	IO-Link
---	--	----------------

Terminal assignment

Interface	Type of connection	M12 connector, 4-pin				
4	3, 4	Signal:	Power supply +V DC	Reserved (no function)	Power supply 0 V (GND)	IO-Link communication (Data line)
		Abbreviation:	L+	res.	L-	C/Q
		Pin:	1	2	3	4

Top view of mating side, male contact base




M12 connector, 4-pin

Dimensions shaft version

Dimensions in mm [inch]

Clamping flange, ø 36 [1.42] Flange type 1 and 3

1 3 x M3, 6 [0.24] deep




D	Fit	L
6 [0.24]	h7	12,5 [0.49]
8 [0.32]	h7	15 [0.59]
10 [0.39]	f7	20 [0.79]
1/4"	h7	12,5 [0.49]

Synchro flange, ø 36 [1.42]

Flange type 2 and 4

1 4 x M3, 6 [0.24] deep



D	Fit	L
6 [0.24]	h7	12,5 [0.49]
8 [0.32]	h7	15 [0.59]
10 [0.39]	f7	20 [0.79]
1/4"	h7	12,5 [0.49]

Absolute encoders – multiturn

Compact electronic multiturn, magnetic

Sendix M3668 / M3688 (shaft / hollow shaft)

IO-Link

Dimensions hollow shaft version



Dimensions in mm [inch]

Flange with spring element, long Flange type 3 and 6

- 1 Slot spring element, recommendation: cylindrical pin DIN 7, $\varnothing 4$ [0.16]
- 2 Recommended torque for the clamping ring 0.7 Nm

D	Fit	L	D1
6 [0.24]	H7	18,5 [0.73]	24 [0.94]
8 [0.32]	H7	18,5 [0.73]	25,5 [1.00]
10 [0.39]	H7	18,5 [0.73]	25,5 [1.00]
1/4"	H7	18,5 [0.73]	24 [0.94]

L = insertion depth max. blind hollow shaft



Flange with stator coupling, $\varnothing 46$ [1.81] Flange type 2 and 5

- 1 Recommended torque for the clamping ring 0.7 Nm

D	Passung	L	D1
6 [0.24]	H7	18,5 [0.73]	24 [0.94]
8 [0.32]	H7	18,5 [0.73]	25,5 [1.00]
10 [0.39]	H7	18,5 [0.73]	25,5 [1.00]
1/4"	H7	18,5 [0.73]	24 [0.94]

L = insertion depth max. blind hollow shaft

