RUIL&N

Gas Discharge Tubes(GDT)

2RA-5 Series

Description


GDT is placed in front of, and in parallel with, sensitive telecom equipment such as power lines, communication lines, signal lines and data transmission lines to help protect them from damage caused by transient surge voltages that may result from lightning strikes and equipment switching operations. These devices do not influence the signal in normal operation. However, in the event of an overvoltage surge, such as a lightning strike, the GDT switches to a low impedance state and diverts the energy away from the sensitive equipment.

Our GDT offer a high level of surge protection, a broad voltage range, low capacitance, and many form factors including new surface mount devices, which makes them suitable for applications such as Main Distribution Frame (MDF) modules, high data-rate telecom applications (e.g. ADSL, VDSL), and surge protection on power lines. Their low capacitance also results in less signal distortion. When used in a coordinated circuit protection solution with PolySwitch devices, they can help equipment manufacturers meet stringent safety regulatory standards.

Features

- I Excellent response to fast rising transients
- I Stable breakdown voltage
- I GHz working frequency
- I 8/20µs Impulse current capability: 5KA
- I Non-Radioactive
- I Ultra Low capacitance (<1pF)
- I Lead-free compliant
- I RoHS and REACH compliant
- I Size: Φ5.5mm*6mm
- I Storage and operational temperature: -40~+90°C

Part Number Code



Agency Approvals

Agency	Standards	Certificate No.
A J°	UL497B	E465335
TÜVRheinland	EN 61643-311 IEC 61643-311	50571931


Applications

- I CATV equipment
- Antennas
- I RS 485

I

- I Telecom Base Station
- I Power Supply AC Main
- I EV power Charging
- I Inverter/Variable
- I Frequency Drivers (VFDs)
- I IEEE 802.3 compliant Ethernet interfaces

- I Broad Band equipment
- I xDSL, ADSL, ADSL2, VDSL, and VDSL2
- I Medical Electronics
- I Test Equipment
- I General Telecom Equipment
- I Renewable Energy



Gas Discharge Tubes(GDT)

2RA-5 Series

Electrical Characteristics

			Impulse					_	Life Ratings			
Part N	umber	DC Spark-over	-	Spark-over Voltage	Insulation Resistance	Canacitance	Glow Voltage @10mA	•	Impu Discha	rge	Alternating Discharge	Impulse Life
i uit iii		Voltage ^{1) 2)} @100V/S	100V/µS	1KV/µS			0.0	0	Curre @8/20		Current @50Hz 1S	@10/1000µ S 100A
				Тур.	Тур.		Nominal Max Nominal	Min				
DIP	SMD	v	v	v	GΩ	pF	v	v	KA	KA	Α	Times
2R075TA-5	2R075SA-5	75±20%	500	600	1	1	60	10	5	10	5	300
2R090TA-5	2R090SA-5	90±20%	500	600	1	1	60	10	5	10	5	300
2R150TA-5	2R150SA-5	150±20%	500	600	1	1	60	10	5	10	5	300
2R230TA-5	2R230SA-5	230±20%	600	700	1	1	60	10	5	10	5	300
2R250TA-5	2R250SA-5	250±20%	600	700	1	1	60	10	5	10	5	300
2R300TA-5	2R300SA-5	300±20%	750	850	1	1	60	10	5	10	5	300
2R350TA-5	2R350SA-5	350±20%	800	900	1	1	60	10	5	10	5	300
2R400TA-5	2R400SA-5	400±20%	850	950	1	1	60	10	5	10	5	300
2R420TA-5	2R420SA-5	420±20%	850	950	1	1	60	10	5	10	5	300
2R470TA-5	2R470SA-5	470±20%	900	1000	1	1	60	10	5	10	5	300
2R600TA-5	2R600SA-5	600±20%	1000	1200	1	1	60	10	5	10	5	300
2R800TA-5	2R800SA-5	800±20%	1200	1400	1	1	135	15	5	10	5	300
Glow to Arc tra	ansition Current				<0.	.5A						
Weight					DIF SM	Ŭ						
Operation and storage temperature				40)~+90°C							
Climatic category (IEC 60068-1)				40/	/90/21							
Marking, blue negative				RU XX Y	JILON XXX X -Nominal -Year of p	voltage						
Surface treatment					P -Nickel Pla	ated						

¹⁾ At delivery AQL 0.65 level II, DIN ISO 2859.

²⁾ In ionized mode.

³⁾ Insulation Resistance Measuring Voltage:

75V~150V at DC 50V

Other at DC 100V

Terms in accordance with ITU-T Rec. K.12, IEC 61643-311, GB/T18802.311, GB/T 9043.

Gas Discharge Tubes(GDT)

2RA-5 Series

Certifications table

Part N	lumber	RL ®	TÜVRheinland
DIP	SMD	UL497B	EN 61643-311 IEC 61643-311
2R075TA-5	2R075SA-5		-
2R090TA-5	2R090SA-5	•	-
2R150TA-5	2R150SA-5	•	-
2R230TA-5	2R230SA-5	•	
2R250TA-5	2R250SA-5		
2R300TA-5	2R300SA-5	•	-
2R350TA-5	2R350SA-5	•	-
2R400TA-5	2R400SA-5	•	
2R420TA-5	2R420SA-5	•	
2R470TA-5	2R470SA-5	•	
2R600TA-5	2R600SA-5	•	•
2R800TA-5	2R800SA-5		•

Notes:


2.

1. • indicates that the product has passed the certification.


-- indicates that the product is not certified.

Dimensions (Unit: mm/inch)


DIP Series (2RxxxTA-5)



SMD Series (2RxxxSA-5)







Recommended Soldering Pad Layout


Gas Discharge Tubes(GDT)

2RA-5 Series

Terms and definitions

NO.	ltem	Definitions			
1	Gas discharge tube(GDT)	A gap, or several gaps, in an enclosed discharge medium, other than air at atmospheric pressure, designed to protect apparatus or personnel, or both, from high transient voltages. Also referred to as "gas tube surge arrester".			
2	DC Spark-over Voltage	The voltage at which the gas discharge tube sparks over with slowly increasing d.c. voltage.			
3	Impulse Spark-over Voltage	The highest voltage which appears across the terminals of a gas discharge tube in the period between the application of an impulse of given wave-shape and the time when current begins to flow.			
5	Arc voltage	Voltage drop across the GDT during arc current flow.			
6	Glow voltage	Peak value of voltage drop across the GDT when a glow current is flowing.			
7	Impulse discharge current 8/20µs	Current impulse with a nominal virtual front time of 8 μs and a nominal time to half-value of 20 $\mu s.$			
8	Alternating Discharge Current	The rms value of an approximately sinusoidal alternating current passing through the gas discharge tube.			
9	Insulation Resistance	Insulation resistance shall be measured from each terminal to every other terminal of the GDT. The test is performed with DC50V when normal spark-over Voltage 70~150V, others with DC100V.			
10	Capacitance	The capacitance shall be measured once at 1 MHz between all terminals unless otherwise specified.			

Soldering Parameters - Wave soldering (Thru-Hole Devices)




Wave Solder	ing Condition	Pb-Free assembly
	Temperature Min	100°C
Preheat	Temperature Max	150°C
	Time (Min to Max)	60-180 Seconds
Solder Pot T	emperature	280°C Max
Solder Dwell	Time	2-5 Seconds

Gas Discharge Tubes(GDT)

2RA-5 Series

Soldering Parameters - Reflow Soldering (Surface Mount Devices)



Reflow Cond	lition	Pb - Free assembly	
	-Temperature Min (T _{s(min)})	150°C	
Preheat	-Temperature Max (T _{s(max)})	200°C	
	- Time (min to max) (t_s)	60 -180 Seconds	
Average ram to peak	p up rate (Liquids Temp T∟)	3°C/second max	
T _{S(max)} to TL -	Ramp-up Rate	5°C/second max	
Reflow	- Temperature (T _L) (Liquids)	217°C	
Kellow	- Time (min to max) (t _s)	60 -150 Seconds	
Peak Temper	rature (T _P)	260 +0/-5°C	
Time within Temperature	5°C of actual peak e (t _p)	10 - 30 Seconds	
Ramp-down	Rate	6°C/second max	
Time 25°C to	peak Temperature (T _P)	8 minutes Max	
Do not excee	ed	260°C	

Surface mounted components (SMD) may exhibit a temporary increase in the DC spark-over voltage after the solder reflow process. The components will recover within 24 hours. There is no quality defect nor change in protection levels during the temporary change in DC spark-over voltage.

Packaging Information

Axial Packaging (Bulk)

	PVC tray	Inner Box	Carton
Size	265 imes 148 imes 10mm	275×150×50mm	315×290×272mm
Quantity	MPQ: 1 tray=100pcs	MOQ: 1 Inner Box=5 trays=500pcs	1 Carton=10 Inner boxes=5,000pcs
Photos			RULER MERRIE WARNON CON

RUILIN


Gas Discharge Tubes(GDT)


2RA-5 Series

Axial Packaging (Tape & Reel)

Таре

Reel






According to IEC 60286-1

	Reel	Carton
Size	340×78mm	350×350×407mm
Quantity	MPQ/MOQ: 1 reel=1,000pcs	1 Carton=5 reels =5,000pcs
Photos		

Gas Discharge Tubes(GDT)

2RA-5 Series

SMD Packaging (Tape & Reel)



	Reel	Inner Box	Carton
Size	330×20.5mm	340×333×70mm	375×353×380mm
Quantity	MPQ/MOQ: 1 reel=1,000pcs	1 Inner Box=3 reels=3,000pcs	1 Carton=5 Inner boxes=15,000pcs
Photos			RULEN MERCE BASING CON

Version: A3/2023-02-06 File Number: SP-GDT-014

Gas Discharge Tubes(GDT)

Cautions and warnings

- I Do not operate surge arresters in power supply networks, whose maximum operating voltage exceeds the minimum spark-over voltage of the surge arresters.
- I Surge arresters may become hot in the event of longer periods of current stress (burn risk). In the event of overload the connectors may fail or the component may be destroyed.
- I If the contacts of the surge arresters are defective, current load can cause sparks and loud noises.
- I Surge arresters must be handled with care and must not be dropped.
- I Do not continue to use damaged surge arresters.
- I The shown SMD pad dimensions represent a safe way to mount the arrester and are a recommendation of the manufacturer. During the reflow process it must be assured that no solder material reduces the insulation distance between the pads below the arrester.
- I SMD surge arresters should be soldered within 24 month after shipment.