GF1A - GF1M

General Purpose Rectifiers (Glass Passivated)

Features

- Low Forward Voltage Drop
- High Current Capability
- Easy Pick and Place
- High Surge Current Capability
- This Device is Pb-Free and is RoHS Compliant



ON Semiconductor®

www.onsemi.com



SMA
CASE 403AE
(COLOR BAND DENOTES CATHODE)

MARKING DIAGRAM



\$Y = ON Semiconductor Logo &Z = Assembly Plant Code &3 = Data Code (Year & Week) GF1x = Specific Device Code x = A/B/D/G/J/K/M

ORDERING INFORMATION

See detailed ordering and shipping information on page 2 of this data sheet.

GF1A - GF1M

ABSOLUTE MAXIMUM RATINGS $T_A = 25$ °C unless otherwise noted

		Value							
Symbol	Parameter	1A	1B	1D	1G	1J	1K	1M	Units
V _{RRM}	Maximum Repetitive Reverse Voltage		100	200	400	600	800	1000	V
I _{F(AV)}	Average Rectified Forward Current, @ T _L = 125°C	1.0			Α				
I _{FSM}	Non-repetitive Peak Forward Surge Current 8.3 ms Single Half-Sine-Wave	30			А				
T _{stg}	Storage Temperature Range	-65 to +175		°C					
TJ	Operating Junction Temperature Range	-65 to +175			°C				

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

THERMAL CHARACTERISTICS

Symbol	Parameter	Value	Units
P _D	Power Dissipation	1.8	W
$R_{\theta JA}$	Thermal Resistance, Junction-to-Ambient*	80	°C/W
$R_{ heta JL}$	Thermal Resistance, Junction-to-Lead*	26	°C/W

^{*}Device mounted on PCB with 0.2 x 0.2" (5.0 x 5.0 mm) copper pad areas.

ELECTRICAL CHARACTERISTICS $T_A = 25^{\circ}C$ unless otherwise noted

		Device							
Symbol	Parameter	1A	1B	1D	1G	1J	1K	1M	Units
V _F	Maximum Forward Voltage @ 1.0 A	1.0		1.0 1.2		.2	V		
t _{rr}	Maximum Reverse Recovery Time $I_F = 0.5 \text{ A}, I_R = 1.0 \text{ A}, I_{rr} = 0.25 \text{ A}$	2.0			2.0				μS
I _R	Maximum Reverse Current @ Rated V_R $T_A = 25$ °C $T_A = 125$ °C	5.0 50				μΑ			
C _T	Typical Capacitance $V_R = 4.0 \text{ V}, f = 1.0 \text{ MHz}$	15			pF				

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

PACKAGE MARKING AND ORDERING INFORMATION

Device	Device Marking	Package	Quantity [†]			
GF1A	GF1A					
GF1B	GF1B					
GF1D	GF1D					
GF1G	GF1G	SMA	7500 / Tape & Reel			
GF1J	GF1J					
GF1K	GF1K					
GF1M	GF1M					

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

TYPICAL CHARACTERISTICS




Figure 1. Forward Current Derating Curve




Figure 2. Non-Repetitive Surge Current




Figure 3. Forward Voltage Characteristics




Figure 4. Reverse Current vs. Reverse Voltage





Figure 5. Total Capacitance

PACKAGE DIMENSIONS

SMA CASE 403AE ISSUE O



0.30

0.05

2.50 MAX 2.20 1.90


B

С

2.05 1.95 0.13 M C B

0.203

0.050



NOTES:

Α

- A. EXCEPT WHERE NOTED, CONFORMS ^ TO JEDEC DO214 VARIATION AC.
- B DOES NOT COMPLY JEDEC STANDARD VALUE.
 - C. ALL DIMENSIONS ARE IN MILLIMETERS.
 - D. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH AND TIE BAR PROTRUSIONS.
 - E. DIMENSIONS AND TOLERANCE AS PER ASME Y14.5–2009.
 - E. LAND PATTERN STD. DIOM5025X231M

GF1A - GF1M

ON Semiconductor and in are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hol

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303–675–2175 or 800–344–3860 Toll Free USA/Canada Fax: 303–675–2176 or 800–344–3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada

Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative