Inductive Proximity Sensor -18mm Square Plastic Housing Multicomp PRO



RoHS **Compliant**



Features

- Inductive sensor, style: squared shape, 18mm × 18mm × 36mm
- Mounting distance: 5mm shielded
- With LED operation indicate lamp, easily identifiable
- Standard sensing object: ferrous metals
- Protection rate: IP67, water resistant
- Over-current and short circuit protection; against polarity reversal.
- Widely applied in measuring, Counting, Rpm measuring in mechanism, chemical, paper manufacture light industry, etc.

Specifications

Mounting Distance : 5mm shielded Sensing Distance : 4.5mm shielded Power Supply : 10V DC to 30V DC

Frequency : 500Hz / 250Hz (DC 3/2 wires)

Current Output (DC/AC) : 200mA Ambient Temperature : -20°C to 70°C


Against Polarity Reversal : Yes


Short Circuit Protected : 3 wires: Yes / 2 wires: No

IP Rating : IP67

Electrical Connection








Picture Of Product

Flush (shielded)

Unit: mm



Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro




Inductive Proximity Sensor -18mm Square Plastic Housing Multicomp PRO




Installation


If used in an area surrounded by metal, Install the proximity Sensor as follows . (Sn = Sensing distance)




Inductive Proximity Application Direction


- A. Set mounting distance equal to 80% of Sn.
- B. Set mounting distance roughly equal to 50% of Sn when sensor is used measuring mounting frequency or operating in high speed circumstances.
- C. Mounting distance will change depending on material (iron, stainless steel, brass, copper and aluminium).







D. Inductive Proximity series connection and parallel connection



17/02/20 V1.0

Inductive Proximity Sensor -18mm Square Plastic Housing Multicomp PRO



Part Number Table

| Part Number | Output Type | Mounting Distance | Current Output | Power Supply | Wire Connector |
|-------------|-------------|-------------------|----------------|------------------|----------------|
| MP002223 | NPN NO | 5mm Shielded | ≤ 200mA | 10V DC to 30V DC | 3 Wire |
| MP002224 | NPN NC | | | | |
| MP002225 | PNP NO | | | | |
| MP002226 | PNP NC | | | | |
| MP002227 | DC NO | | | | 2 Wire |
| MP002228 | DC NC | | | | |

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

