

Search

Home > Products > Fuses > Axial Radial Thru Hole Fuses > TE5 Fuses > 400 > 40012500440

Print

40012500440 - 400 Series



Series: 400

[Fuse 400 Datasheet](#)

The Littelfuse 400 Series is a TE5® Time Lag Fuse with High Breaking Capacity.

Features:

- Operating temperature: -40°C to 125°C
- Higher nominal melting I²T
- Higher interrupt rating
- Broad current rating 500mA to 6.3A
- Lead-Free, Halogen-Free, Compliance with RoHS
- Shock safe casing

Applications:

- SMPS for NB, printers, adaptors, consumer electronics, industrial controllers, battery chargers

Questions? [Contact Littelfuse Support](#)

Check Stock

Order Samples

NEW!
Product Selection Guide eCatalog
[Read Now](#)

Electronics
News and Information
SIGN UP NOW

Feedback

Electrical Characteristics | **Technical Resources** | **Environmental Info**

| Property (Mouseover for details) | Value |
|---|---------------------------------|
| Ampere Rating (A) | 2.5 |
| Nominal Melting I ² T (A ² sec) | 61.94 |
| Interrupting Rating | 130A@250VAC |
| Min Operating Temp °C | -40 |
| Max Operating Temp (°C) | 85 |
| Nominal Power Dissipation (W) | 683 |
| Nominal Voltage Drop (mV) | 61 |
| Opening | Slo-Blo/Time Lag (T)/Time Delay |
| Package Size | TE5 (8.5x8mm) |
| VAC (V) | 250 |

Connect with Littelfuse
Sign up to receive special offers and news

For more details about how we use your information, check our [Privacy Statement](#).



Mobile Site

- About Littelfuse**
- About Littelfuse
 - Conflict Free Statement
 - History
 - Investor Relations
 - Legal
 - Press Room
 - Privacy Statement
 - Supply Chain Transparency
 - Website Feedback

- Explore Littelfuse**
- Capabilities Brochures
 - Careers
 - Check Distributor Stock
 - Competitor Cross Reference
 - Industries
 - Order Samples
 - Products
 - Services

- Technical Resources**
- Application Designs
 - Education
 - FAQs
 - iDesign™
 - Littelfuse University
 - Product Catalogs
 - Quality Documents
 - Technical Documents