

# A-BLOCK C60.10BP





NiCd Battery pack

Size: 5xAA

## Typical Characteristics



A-BLOCK C60.10BP			
Specifications			
Nominal Voltage (V)		6.0 V	
Capacity	Discharge rate	C/5	1C
	Nominal (mAh)	950	780
	Typical (mAh)	1000	820
Dimension	Length (mm)	72.5 <sup>+0.5</sup> <sub>-0.5</sub>	
	Width (mm)	49.5 <sup>+0.5</sup> <sub>-0.5</sub>	
Charging	Standard	100mA x 15 hrs	
	Quick	1000mA x 1.2 hrs T <sub>max</sub> =45°C -ΔV = 5~8mV	
Operating Temperature (°C)	Standard Charging	0 ~ 45°C	
	Quick Charging	10 ~ 40°C	
	Discharging	-20 ~ 60°C	
	Storage	-20 ~ 35°C	
Internal Resistance	≤ 60m Ohm (upon 50% discharge)		
Weight	Approx. 105g		
Cuff-off Voltage (V)	5.00		



The data shown is correct at a temperature of 20±5°C Shutdown at ΔV= 15mV, after reaching 120% of the rated capacity or at a temperature above 55°C