

GRM033R61A105ME15#

“#” indicates a package specification code.



< List of part numbers with package codes >

GRM033R61A105ME15J

GRM033R61A105ME15D

GRM033R61A105ME15W

Appearance & Shape



References

Packaging	Specifications	Standard Packing Quantity
J	330mm Paper Tape	50000
D	180mm Paper Tape	15000
W	180mm Paper Tape (W8P1)	30000

Mass (typ.)	
1 piece	0.33mg
φ180mm Reel	118g

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

GRM033R61A105ME15#

“#” indicates a package specification code.



Specifications

Length	0.6±0.09mm
Width	0.3±0.09mm
Thickness	0.3±0.09mm
Capacitance	1.0μF ±20%
Distance between external terminals g	0.2mm min.
External terminal size e	0.1 to 0.25mm
Operating Temperature Range	-55°C to 85°C
Rated Voltage	10Vdc
Size code in inch(mm)	0201 (0603M)
Capacitance change rate	±15.0%
Temperature characteristics (complied standard)	X5R(EIA)
Temperature range of temperature characteristics	-55°C to 85°C

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.


GRM033R61A105ME15#

“#” indicates a package specification code.




Characteristic Data


The charts below may show another part number which shares its characteristics.




■ GRM033R61A105ME15 |Z| DCOV, 25degC



■ GRM033R61A105ME15 R DCOV, 25degC



■ GRM033R61A105ME15 C-DC bias capchange, 25.0degC, AC1V




■ GRM033R61A105ME15 C-AC Voltage capchange, DCOV, 25.0d

Attention


- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

GRM033R61A105ME15#

“#” indicates a package specification code.



■ GRM033R61A105ME15 Temp.rise 1MHz



■ GRM033R61A105ME15 S21 DCOV, 25degC

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.