




APPLICABLE STANDARD				
RATING	OPERATING TEMPERATURE RANGE	-40°C TO + 85°C (NOTE 1) 	STORAGE TEMPERATURE RANGE	-10°C TO + 60°C (NOTE 3)
	OPERATING HUMIDITY RANGE 	40% TO + 80% (NOTE 2)	STORAGE HUMIDITY RANGE 	40% TO + 70% (NOTE 3)
	VOLTAGE	250V AC	APPLICABLE CONNECTOR	DF11-*DS-2C
	CURRENT	AWG24 : 2A AWG26 : 2A AWG28 : 1A	APPLICABLE CABLE	AWG24~28

SPECIFICATIONS

ITEM	TEST METHOD	REQUIREMENTS	QT	AT
------	-------------	--------------	----	----

CONSTRUCTION

GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	X	X
MARKING	CONFIRMED VISUALLY.		X	X

ELECTRIC CHARACTERISTICS

CONTACT RESISTANCE	100mA (DC OR 1000 Hz).	30mΩ MAX.	X	-
--------------------	------------------------	-----------	---	---

MECHANICAL CHARACTERISTICS




MECHANICAL OPERATION	30 TIMES INSERTIONS AND EXTRACTIONS.	① CONTACT RESISTANCE: 30mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-
CONTACT INSERTION AND EXTRACTION FORCE	□0.5±0.002 BY STEEL GAUGE.	INSERTION FORCE 4.4N MAX EXTRACTION FORCE 0.3N MIN	X	-
VIBRATION	FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, AT 2 h, FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 1μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-
SHOCK	490 m/s ² DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 1μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-

ENVIRONMENTAL CHARACTERISTICS

RAPID CHANGE OF TEMPERATURE	TEMPERATURE -55→ 5 TO 35→ 85→ 5 TO 35 °C TIME 30→10 TO 15→30→10 TO 15 min UNDER 5 CYCLES.	① CONTACT RESISTANCE: 30mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-
-----------------------------	---	--	---	---

REMARKS

NOTE 1:INCLUDING THE TEMPERATURE RISE BY CURRENT
NOTE 2:NO CONDENSING.
NOTE 3:APPLY TO THE CONDITION OF LONG TERM STORAGE FOR UNUSED PRODUCTS BEFORE PCB ON BOARD, AFTER PCB BOARD, OPERATINGTEMPERATURE AND HUMIDITY RANGE IS APPLIED FOR INTERIM STORAGE DURING TRANSPORTATION.

COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
 3	DIS-H-008583	MI. SAKIMURA	HK. UMEHARA	14.03.25
Unless otherwise specifid , refer to IEC 60512.			APPROVED	KJ. KATAYOSE 05.01.05
			CHECKED	TY. OMA 05.01.05
			DESIGNED	IO. DENPOUYA 05.01.05
			DRAWN	IO. DENPOUYA 05.01.05
Note QT:Qualification Test AT:Assurance Test X:Applicable Test		DRAWING NO.	ELC4-020864-00	
	SPECIFICATION SHEET		PART NO.	DF11-2428SCF
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL543-0500-2-00  1/1