

# GRM1885C1H1R0CA01#


“#” indicates a package specification code.



< List of part numbers with package codes >

GRM1885C1H1R0CA01J      GRM1885C1H1R0CA01D

## Appearance & Shape



## References

| Packaging | Specifications   | Standard Packing Quantity |
|-----------|------------------|---------------------------|
| J         | 330mm Paper Tape | 10000                     |
| D         | 180mm Paper Tape | 4000                      |

| Mass (typ.) |       |
|-------------|-------|
| 1 piece     | 6.3mg |
| φ180mm Reel | 144g  |

### Attention

- This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, its specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# GRM1885C1H1R0CA01#

“#” indicates a package specification code.

## Specifications

|  |                |
|--|----------------|
| Length   | 1.6±0.1mm      |
| Width  | 0.8±0.1mm      |
| Thickness  | 0.8±0.1mm      |
| Capacitance                                      | 1.0pF ±0.25pF  |
| Distance between external terminals g            | 0.5mm min.     |
| External terminal size e                         | 0.2 to 0.5mm   |
| Operating Temperature Range                      | -55°C to 125°C |
| Rated Voltage                                    | 50Vdc          |
| Size code in inch(mm)                            | 0603 (1608M)   |
| TC   | 0±30ppm/°C     |
| Temperature characteristics (complied standard)  | C0G(EIA)       |
| Temperature range of temperature characteristics | 25°C to 125°C  |

### Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.


# GRM1885C1H1R0CA01#

"#" indicates a package specification code.




## Characteristic Data

The charts below may show another part number which shares its characteristics.



■ GRM1885C1H1R0CA01 |Z| DCOV, 25degC



■ GRM1885C1H1R0CA01 R DCOV, 25degC



■ GRM1885C1H1R0CA01 C-DC bias capchange, 25.0degC, AC1V




■ GRM1885C1H1R0CA01 C-AC Voltage capchange, DCOV, 25.0d

**Attention**


- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# GRM1885C1H1R0CA01#

“#” indicates a package specification code.



■ GRM1885C1H1R0CA01 C-Temp. capchange, DCOV, AC1Vrms



■ GRM1885C1H1R0CA01 S21 DCOV, 25degC

**Attention**

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.