

# ATP CompactFlash Card Industrial Grade

# Targeted Product Portfolio, Engineered Specifically for Your Mission Critical Applications



CompactFlash cards in the original IDE/PATA interface continue to enjoy wide usage in industrial and embedded environments due to their durability and rugged build.

ATP's industrial CompactFlash cards work best in high-throughput applications requiring speedy transfers of large blocks of data, such as high-definition videos and camera systems.

Industrial temperature-rated CompactFlash cards can operate in critical temperature ranges, from -40°C to 85°C. Superior flash management capabilities such as Advanced Wear Leveling, bad block management, and AutoRefresh technology ensure data integrity, reliability and longevity for a wide range of applications and workloads. ATP's own PowerProtector provides hardware-based protection that prevents data loss or corruption due to power losses or fluctuations.

## **Key Features**

- Global wear leveling and bad block management
- AutoRefresh technology
- PowerProtector
- Power saving mode
- S.M.A.R.T. support

### Applications

- Portable compution
- Automation
- Industrial PC
- Gaming
- On board data storage



# Specifications

Product Name		CompactFlash Card						
Product Line		Premium	Superior					
Naming		1800Pi	1700Sc	1600Sc				
Flash Type		SLC	SLC mode	MLC				
Density		512 MB to 32 GB	4 GB to 16 GB	8 GB to 32 GB				
Performance	Sequential Read up to (MB/s)	61	110	108				
	Sequential Write up to (MB/s)	55	80	46				
Interface		UDMA 0~4	UDMA 0~6					
Operating Temperature		-40°C to 85°C	0°C to 70°C					
Endurance	TBW* (max.)	1,280 TB	128 TB	38 TB				
	DWPD* (max.)	22.4	11.2	1.7				
Reliability	MTBF @ 25°C	>5,000,000 hours	>2,000,000 hours					
	Number of Insertions	10,000 minimum						
Dimensions: L x W x H (mm)		36.4 x 42.8 x 3.3						

 $^{\ast}$  Under highest Sequential write value. May vary by density, configuration and applications.

Technologies & Add-On Services*		S.M.A.R.T.	Sudden Power-Off Recovery	Advanced Wear Leveling	AutoRefresh	Dynamic Data Refresh	Industrial Temperature	S Anti-Sulfur Resistors	Conformal Coating
Product Line	Premium	•	•	•	•	•	•	Δ	Δ
	Superior	•		٠	•	•		Δ	Δ

Δ: Customization option available on a project basis.

To learn more about this product, contact your ATP Representative.

ATP Global Footprint

#### ATP TAIWAN(HQ)

TEL: +886-2-2659-6368 FAX: +886-2-2659-4982

sales-apac@atpinc.com

#### ATP USA

TEL: +1-408-732-5000 FAX: +1-408-732-5055 sales@atpinc.com

#### ATP EUROPE

TEL: +49-89-374-9999-0 FAX: +49-89-374-9999-29 sales-europe@atpinc.com

#### ATP JAPAN

TEL: +81-3-6260-0797 FAX: +81-3-6260-0798 sales-japan@atpinc.com

#### ATP CHINA

TEL: +86-21-5080-2220 FAX: +86-21-9687-0000-026 sales@cn.atpinc.com

#### www.atpinc.com