

VOLTAGE RANGE: 100V
CURRENT: 2.0 A


Features

- Low forward voltage drop
- Guard ring for enhanced ruggedness and long term reliability
- Small foot print, surface mountable
- High frequency operation



Mechanical Data

- Case: SMA/DO-214AC, Molded Plastic
- Terminals: Solder Plated, Solderable per MIL-STD-750, Method 2026
- Polarity: Cathode Band or Cathode Notch
- Marking: Type Number
- Weight: 0.064 grams (approx.)



SMA(DO-214AC)		
Dim	Min	Max
A	2.29	2.92
B	4.00	4.60
C	1.27	1.63
D	0.15	0.31
E	4.80	5.59
G	0.10	0.20
H	0.76	1.52
J	2.01	2.62
All Dimensions in mm		

Maximum Ratings and Electrical Characteristics T_A = 25°C unless otherwise specified

SYMBOL	CHARACTERISTICS	VALUES	UNITS
I _{F(AV)}	Rectangular waveform	2	A
V _{RRM}		100	V
I _{FSM}	t _p = 5 μs sine	120	A
V _F	2 A _{pk} , T _J = 125 °C	0.72	V
T _J	Range	- 55 to 150	°C

PARAMETER	SYMBOL	VS-20MQ100-M3	UNITS
Maximum DC reverse voltage	V _R	100	V
Maximum working peak reverse voltage	V _{RWM}		

PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS
Maximum average forward current See fig. 4	I _{F(AV)}	50 % duty cycle at T _L = 113 °C, rectangular waveform On PC board 9 mm ² island (0.013 mm thick copper pad area)	2.1	A
		50 % duty cycle at T _L = 116 °C, rectangular waveform On PC board 9 mm ² island (0.013 mm thick copper pad area)	2	
Maximum peak one cycle non-repetitive surge current See fig. 6	I _{FSM}	5 μs sine or 3 μs rect. pulse	120	A
		10 ms sine or 6 ms rect. pulse	30	
Non-repetitive avalanche energy	E _{AS}	T _J = 25 °C, I _{AS} = 0.5 A, L = 8 mH	1.0	mJ
Repetitive avalanche current	I _{AR}		0.5	A

ELECTRICAL SPECIFICATIONS

PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS	
Maximum forward voltage drop See fig. 1	$V_{FM}^{(1)}$	2 A	0.91	V	
		1.5 A			0.85
		1 A			
		2 A	0.72		
		1.5 A			0.68
		1 A			
Maximum reverse leakage current See fig. 2	I_{RM}	$T_J = 25\text{ }^\circ\text{C}$	0.1	mA	
		$T_J = 125\text{ }^\circ\text{C}$			1
Threshold voltage	$V_{F(TO)}$	$T_J = T_J \text{ maximum}$	0.52	V	
Forward slope resistance	r_t		78.4	m Ω	
Typical junction capacitance	C_T	$V_R = 10\text{ V}_{DC}$, $T_J = 25\text{ }^\circ\text{C}$, test signal = 1 MHz	38	pF	
Typical series inductance	L_S	Measured lead to lead 5 mm from package body	2.0	nH	
Maximum voltage rate of change	dV/dt	Rated V_R	10 000	V/ μ s	

Note

(1) Pulse width = 300 μ s, duty cycle = 2 %

THERMAL - MECHANICAL SPECIFICATIONS

PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS
Maximum junction and storage temperature range	$T_J^{(1)}$, T_{Stg}		- 55 to 150	$^\circ\text{C}$
Maximum thermal resistance, junction to ambient	R_{thJA}	DC operation	80	$^\circ\text{C}/\text{W}$
Approximate weight			0.07	g
			0.002	oz.

Note

(1) $\frac{dP_{tot}}{dT_J} < \frac{1}{R_{thJA}}$ thermal runaway condition for a diode on its own heatsink




Fig. 1 - Maximum Forward Voltage Drop Characteristics




Fig. 2 - Typical Peak Reverse Current vs. Reverse Voltage




Fig. 3 - Typical Junction Capacitance vs. Reverse Voltage




Fig. 4 - Maximum Average Forward Current vs. Allowable Lead Temperature




Fig. 5 - Maximum Average Forward Dissipation vs. Average Forward Current