

You can view this page in:

EN DE SV FI CS DA EL ES FR HU IT JA KO NL NO PL PT RU SK  
TR ZH

# Detailed information for: 260-1050

This page contains technical data sheet, documents library and links to offering related to this product. If you require any other information, please contact us using form located at the bottom of the page.

# 260-1050

## General Information

<b>Extended Product Type:</b>	260-1050
<b>Product ID:</b>	7TCA296230R0060
<b>EAN:</b>	5016947002354
<b>Catalog Description:</b>	M16 INDEX EMC CABLE GLAND
<b>Long Description:</b>	Cable Gland, Stripped Cable Sheath Allowing the Outer Sheath to Be Completely Stripped from the Cable, M16 Thread, 10mm Thread Length, 26.7mm Gland Diameter, 24mm Across Flats Diameter, 6-9mm Cable Diameter Range, Nickel Plated Brass, Stainless Steel Spring, Rubber Seal, IP68

## Categories

Products » [Low Voltage Products and Systems](#) » [Installation Products](#) » [Cable Protection, Explosion Proof and Lighting](#) » [Flexible Cable Protection Systems](#)

## Additional Information

<b>Application:</b>	Provide Strain Relief and Connection for Conduit Systems
<b>Product Type:</b>	Index EMC Type A Cable Gland

## Ordering

<b>EAN:</b>	5016947002354
<b>UPC:</b>	786210271507
<b>Customs Tariff Number:</b>	8547200000

## Technical

<b>Number of Batteries:</b>	0
<b>Color:</b>	Brass
<b>Material:</b>	Nickel Plated Brass, Stainless Steel Spring, Rubber Seal (TPE-V)
<b>Size:</b>	M16

## Environmental

<b>WEEE Category:</b>	Product Not in WEEE Scope
-----------------------	---------------------------

## Container Information

<b>Package Level 1 Units:</b>	250 piece
<b>Package Level 1 Height:</b>	6 in 152 mm
<b>Package Level 1 Depth / Length:</b>	14 in 356 mm
<b>Package Level 1 Width:</b>	14 in 356 mm

## Certificates and Declarations (Document Number)

**Data Sheet, Technical Information:** [260-1050](#)

---

**Instructions and Manuals:** [260-1050](#)

---

**Declaration of Conformity - CE:** [9AKK107492A9618](#)

---

**RoHS Information:** [9AKK107992A8994](#)

---

**REACH Declaration:** [9AKK107992A8994](#)

### Classifications

**UNSPSC:** 39121431



---

© Copyright 2022 ABB